



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

LOCTITE SF 770 known as Loctite 770 10x300ml M/L

SDS No. : 153555
V006.1

Revision: 13.12.2017
printing date: 16.08.2018

Replaces version from: 21.03.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SF 770 known as Loctite 770 10x300ml M/L

Contains:

n-Heptane

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Primer, containing solvents

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Adhesives

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Flammable liquids	Category 2
H225 Highly flammable liquid and vapor.	
Skin irritation	Category 2
H315 Causes skin irritation.	
Specific target organ toxicity - single exposure	Category 3
H336 May cause drowsiness or dizziness.	
Target organ: Central Nervous System	
Aspiration hazard	Category 1
H304 May be fatal if swallowed and enters airways.	
Acute hazards to the aquatic environment	Category 1
H400 Very toxic to aquatic life.	
Chronic hazards to the aquatic environment	Category 1
H410 Very toxic to aquatic life with long lasting effects.	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Danger

Hazard statement:

H225 Highly flammable liquid and vapor.
H304 May be fatal if swallowed and enters airways.
H315 Causes skin irritation.
H336 May cause drowsiness or dizziness.
H410 Very toxic to aquatic life with long lasting effects.

Precautionary statement:

***** ***For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements***

Precautionary statement: Prevention

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.
No smoking.
P261 Avoid breathing vapours.
P273 Avoid release to the environment.

Precautionary statement: Response

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor.
P331 Do NOT induce vomiting.
P302+P352 IF ON SKIN: Wash with plenty of soap and water.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Primer, containing solvents

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
n-Heptane 142-82-5	205-563-8 01-2119457603-38	75- < 100 %	Flam. Liq. 2 H225 Asp. Tox. 1 H304 Skin Irrit. 2 H315 STOT SE 3 H336 Aquatic Acute 1 H400 Aquatic Chronic 1 H410

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

ASPIRATION: Coughing, shortness of breath, nausea. Delayed effect: bronchopneumonia or pulmonary oedema

Vapors may cause drowsiness and dizziness.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Small amounts of liquid aspirated into the respiratory system during ingestion or from vomiting may cause bronchopneumonia or pulmonary oedema.

Do not induce vomiting.

Seek medical attention from a specialist.

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Foam, extinguishing powder, carbon dioxide.

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

Do not expose to direct heat.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

Wipe up using absorbent material.
Store in a partly filled, closed container until disposal.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Use only in well-ventilated areas.
Avoid skin and eye contact.
See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.
Do not eat, drink or smoke while working.
Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, dry place.
Do not store near sources of heat or ignition, or reactive materials.

7.3. Specific end use(s)

Primer, containing solvents

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Heptane 142-82-5 [N-HEPTANE]	500	2.085	Time Weighted Average (TWA):		EH40 WEL
Heptane 142-82-5 [N-HEPTANE]	500	2.085	Time Weighted Average (TWA):	Indicative	ECLTV

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Heptane 142-82-5 [N-HEPTANE]	500	2.085	Time Weighted Average (TWA):	Indicative OELV	IR_OEL
Heptane 142-82-5 [N-HEPTANE]	500	2.085	Time Weighted Average (TWA):	Indicative	ECLTV
Methylcyclohexane 108-87-2 [METHYLCYCLOHEXANE]	400	1.600	Time Weighted Average (TWA):		IR_OEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
n-Heptane 142-82-5	Air						

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
n-Heptane 142-82-5	Workers	dermal	Long term exposure - systemic effects		300 mg/kg	
n-Heptane 142-82-5	Workers	Inhalation	Long term exposure - systemic effects		2085 mg/m ³	
n-Heptane 142-82-5	General population	dermal	Long term exposure - systemic effects		149 mg/kg	
n-Heptane 142-82-5	General population	Inhalation	Long term exposure - systemic effects		447 mg/m ³	
n-Heptane 142-82-5	General population	oral	Long term exposure - systemic effects		149 mg/kg	

Biological Exposure Indices:

None

8.2. Exposure controls:**Engineering controls:**

Ventilate working rooms thoroughly. Avoid naked flames, sparking and sources of ignition. Switch off electrical devices. Do not smoke, do not weld. Do not empty waste into waste water drains.

Respiratory protection:

Use only in well-ventilated areas.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	liquid liquid transparent, colourless, Clear
Odor	Aliphatic
Odour threshold	No data available / Not applicable
pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	96 - 98 °C (204.8 - 208.4 °F)
Flash point	-4 °C (24.8 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	
lower	1,1 % (V)
upper	6,7 % (V)
Vapour pressure (20 °C (68 °F))	35 mm hg
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	0,715 g/cm ³
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Not miscible
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

Ignition temperature 215 °C (419 °F)

SECTION 10: Stability and reactivity

10.1. Reactivity

Strong oxidizing agents.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

STOT-single exposure:

May cause drowsiness or dizziness.

Aspiration hazard:

May be fatal if swallowed and enters airways.

Skin irritation:

Causes skin irritation.

Solvent may remove essential oils from the skin making it susceptible to attack from other chemicals.

Eye irritation:

Prolonged or repeated contact may cause eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
n-Heptane 142-82-5	LD50	> 5.000 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
n-Heptane 142-82-5	LC50	> 29,29 mg/l	vapour	4 h	rat	OECD Guideline 403 (Acute Inhalation Toxicity)

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
n-Heptane 142-82-5	LD50	> 2.000 mg/kg	dermal		rabbit	OECD Guideline 402 (Acute Dermal Toxicity)

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
n-Heptane 142-82-5	irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
n-Heptane 142-82-5	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
n-Heptane 142-82-5	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
n-Heptane 142-82-5	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
	negative	in vitro mammalian chromosome aberration test	not applicable		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)

Reproductive toxicity:

Hazardous substances CAS-No.	Result / Classification	Species	Exposure time	Species	Method
n-Heptane 142-82-5	NOAEL P = 3000 ppm NOAEL F1 = 3000 ppm	inhalation: vapour		rat	OECD Guideline 416 (Two- Generation Reproduction Toxicity Study)

Repeated dose toxicity

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
n-Heptane 142-82-5		inhalation: vapour	16 weeks 12 hours/day, 7 days/week	rat	

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Very toxic to aquatic life with long lasting effects.
Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
n-Heptane 142-82-5	LC50	> 220 - 270 mg/l	Fish	96 h	Leuciscus idus	OECD Guideline 203 (Fish, Acute Toxicity Test)
n-Heptane 142-82-5	EC50	1,5 mg/l	Daphnia	48 h	Daphnia magna	other guideline:
n-Heptane 142-82-5	NOELR	1 mg/l	chronic Daphnia	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)

12.2. Persistence and degradability**Persistence and Biodegradability:**

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
---------------------------------	--------	-------------------------	---------------	--------

n-Heptane 142-82-5	readily biodegradable	aerobic	70 %	other guideline:
-----------------------	-----------------------	---------	------	------------------

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

The product evaporates readily.

Bioaccumulative potential:

No data available.

Hazardous components CAS-No.	LogPow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
n-Heptane 142-82-5		552		calculation		QSAR (Quantitative Structure Activity Relationship)
n-Heptane 142-82-5	4,66					OECD Guideline 107 (Partition Coefficient (n- octanol / water), Shake Flask Method)

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
n-Heptane 142-82-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Product disposal:**

Dispose of according to regulations.

Disposal of uncleaned packages:

Dispose of in accordance with local and national regulations.

Waste code

14 06 03 Other solvents and solvent mixtures

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information**14.1. UN number**

ADR	1206
RID	1206
ADN	1206
IMDG	1206
IATA	1206

14.2. UN proper shipping name

ADR	HEPTANES (solution)
RID	HEPTANES (solution)
ADN	HEPTANES (solution)
IMDG	HEPTANES (solution)
IATA	Heptanes (solution)

14.3. Transport hazard class(es)

ADR	3
RID	3
ADN	3
IMDG	3
IATA	3

14.4. Packing group

ADR	II
RID	II
ADN	II
IMDG	II
IATA	II

14.5. Environmental hazards

ADR	Environmentally Hazardous
RID	Environmentally Hazardous
ADN	Environmentally Hazardous
IMDG	Marine pollutant
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode: (D/E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**VOC content 100 %
(2010/75/EC)**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H225 Highly flammable liquid and vapor.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H336 May cause drowsiness or dizziness.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.