

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Sika® Plumbers Gold

1.2 Relevant identified uses of the substance or mixture and uses advised against

Product use : Adhesive

1.3 Details of the supplier of the safety data sheet

Company name of supplier : Sika Limited
Watchmead Welwyn Garden City
Hertfordshire. AL7 1BQ
Telephone : +44 (0)1707 394444
Telefax : +44 (0)1707 329129
E-mail address of person : EHS@uk.sika.com
responsible for the SDS

1.4 Emergency telephone number

National Chemical Emergency Centre (NCEC)
24 Hour Emergency Telephone Number +44 870 190 6777

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification (REGULATION (EC) No 1272/2008)

Skin sensitisation, Category 1 H317: May cause an allergic skin reaction.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Warning

Hazard statements : H317 May cause an allergic skin reaction.

Precautionary statements : **Prevention:**

P261 Avoid breathing mist or vapours.
P272 Contaminated work clothing should not be allowed out of the workplace.
P280 Wear protective gloves.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

Response:

P333 + P313 If skin irritation or rash occurs: Get medical advice/ attention.
P362 + P364 Take off contaminated clothing and wash it before reuse.

Disposal:

P501 Dispose of contents/container in accordance with local regulation.

Hazardous components which must be listed on the label:

trimethoxyvinylsilane
N-(3-(trimethoxysilyl)propyl)ethylenediamine

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

Ecological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

Toxicological information: The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Components

Chemical name	CAS-No. EC-No. Index-No. Registration number	Classification	Concentration (% w/w)
trimethoxyvinylsilane Contains: tetramethyl orthosilicate <= 0,2 %	2768-02-7 220-449-8 014-049-00-0 01-2119513215-52-XXXX	Flam. Liq. 3; H226 Acute Tox. 4; H332 Skin Sens. 1B; H317 Acute toxicity estimate Acute inhalation toxicity (vapour): 16,8 mg/l	>= 2,5 - < 5

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

N-(3-(trimethoxysilyl)propyl)ethylenediamine Contains: N,N'-bis[3-(trimethoxysilyl)propyl]ethylenediamine <= 3 % 1-(2-Aminoethyl)-2,2-dimethoxy-1-aza-2-silacyclopentane <= 3 %	1760-24-3 217-164-6 01-2119970215-39-XXXX	Eye Dam. 1; H318 Skin Sens. 1B; H317 STOT SE 3; H335 (Respiratory system)	>= 0,5 - < 1
--	---	--	--------------

For explanation of abbreviations see section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

- General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.
- If inhaled : Move to fresh air.
Consult a physician after significant exposure.
- In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.
- In case of eye contact : Remove contact lenses.
Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.
- If swallowed : Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

- Symptoms : Allergic reactions
See Section 11 for more detailed information on health effects and symptoms.
- Risks : sensitising effects
- May cause an allergic skin reaction.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : In case of fire, use water/water spray/water jet/carbon dioxide/sand/foam/alcohol resistant foam/chemical powder for extinction.

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

Special protective equipment : In the event of fire, wear self-contained breathing apparatus for firefighters

Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Deny access to unprotected persons.

6.2 Environmental precautions

Environmental precautions : Do not flush into surface water or sanitary sewer system.

6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see section 8).
Do not get in eyes, on skin, or on clothing.
For personal protection see section 8.
Persons with a history of skin sensitisation problems or asthma, allergies, chronic or recurrent respiratory disease should

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

not be employed in any process in which this mixture is being used.
Smoking, eating and drinking should be prohibited in the application area.
Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place. Store in accordance with local regulations.

Further information on storage stability : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Occupational Exposure Limits

Contains no substances with occupational exposure limit values.

Occupational exposure limits of decomposition products

Components	CAS-No.	Value type (Form of exposure)	Control parameters *	Basis *
methanol	67-56-1	TWA	200 ppm 260 mg/m ³	2006/15/EC
	Further information: Indicative, Identifies the possibility of significant uptake through the skin			
		TWA	200 ppm 266 mg/m ³	GB EH40
	Further information: Can be absorbed through the skin. The assigned substances are those for which there are concerns that dermal absorption will lead to systemic toxicity.			
		STEL	250 ppm 333 mg/m ³	GB EH40

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

*The above mentioned values are in accordance with the legislation in effect at the date of the release of this safety data sheet.

8.2 Exposure controls

Engineering measures

Maintain air concentrations below occupational exposure standards.
Ensure adequate ventilation, especially in confined areas.

Personal protective equipment

- | | | |
|--------------------------|---|---|
| Eye/face protection | : | Safety glasses with side-shields conforming to EN166
Eye wash bottle with pure water |
| Hand protection | : | Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.
Suitable for short time use or protection against splashes:
Butyl rubber/nitrile rubber gloves (> 0,1 mm)
Contaminated gloves should be removed.
Suitable for permanent exposure:
Viton gloves (0.4 mm),
breakthrough time >30 min. |
| Skin and body protection | : | Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work. |
| Respiratory protection | : | In case of inadequate ventilation wear respiratory protection. Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
organic vapor filter (Type A)
A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm
Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficient to keep the concentrations under the occupational exposure limits then respiration protection measures must be used. |

Environmental exposure controls

- | | | |
|----------------|---|---|
| General advice | : | Do not flush into surface water or sanitary sewer system. |
|----------------|---|---|

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

- | | | |
|------------|---|--------------|
| Appearance | : | paste |
| Colour | : | various |
| Odour | : | alcohol-like |

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

Melting point/ range / Freezing point : No data available

Boiling point/boiling range : No data available

Flammability (solid, gas) : No data available

Upper/lower flammability or explosive limits

Upper explosion limit / Upper flammability limit : No data available

Lower explosion limit / Lower flammability limit : No data available

Flash point : > 61 °C
Method: closed cup

Auto-ignition temperature : No data available

Decomposition temperature : No data available

pH : substance/mixture is non-soluble (in water)

Viscosity

Viscosity, dynamic : 210.000 mPa.s

Viscosity, kinematic : > 20,5 mm²/s (40 °C)

Solubility(ies)

Water solubility : insoluble

Partition coefficient: n-octanol/water : No data available

Vapour pressure : 0,01 hPa

Density : ca. 1,45 g/cm³ (20 °C)

Relative vapour density : No data available

Particle characteristics : No data available

9.2 Other information

No data available

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : No hazards to be specially mentioned.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

Hazardous decomposition products : methanol

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity

Not classified due to lack of data.

Components:

trimethoxyvinylsilane:

Acute oral toxicity : LD50 Oral (Rat): ca. 7.120 mg/kg

Acute inhalation toxicity : LC50: ca. 16,8 mg/l
Exposure time: 4 h
Test atmosphere: vapour

Acute toxicity estimate: 16,8 mg/l
Test atmosphere: vapour
Method: Calculation method

Acute dermal toxicity : LD50: 3.540 mg/kg

N-(3-(trimethoxysilyl)propyl)ethylenediamine:

Acute oral toxicity : LD50 Oral (Rat): 2.995 mg/kg

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

Skin corrosion/irritation

Not classified due to lack of data.

Serious eye damage/eye irritation

Not classified due to lack of data.

Respiratory or skin sensitisation

Skin sensitisation

May cause an allergic skin reaction.

Respiratory sensitisation

Not classified due to lack of data.

Germ cell mutagenicity

Not classified due to lack of data.

Carcinogenicity

Not classified due to lack of data.

Reproductive toxicity

Not classified due to lack of data.

STOT - single exposure

Not classified due to lack of data.

STOT - repeated exposure

Not classified due to lack of data.

Aspiration toxicity

Not classified due to lack of data.

11.2 Information on other hazards

Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher..

12.6 Endocrine disrupting properties

Product:

Assessment : The substance/mixture does not contain components considered to have endocrine disrupting properties according to REACH Article 57(f) or Commission Delegated regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605 at levels of 0.1% or higher.

12.7 Other adverse effects

Product:

Additional ecological information : There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.
Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

SECTION 14: Transport information

14.1 UN number or ID number

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

14.2 UN proper shipping name

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

14.3 Transport hazard class(es)

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA : Not regulated as a dangerous good

14.4 Packing group

ADR : Not regulated as a dangerous good
IMDG : Not regulated as a dangerous good
IATA (Cargo) : Not regulated as a dangerous good
IATA (Passenger) : Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

Not applicable

14.7 Maritime transport in bulk according to IMO instruments

Not applicable for product as supplied.

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Relevant EU provisions transposed through retained EU law

UK REACH List of restrictions (Annex 17) : Conditions of restriction for the following entries should be considered:
Number on list 20: dioctyltin oxide
Number on list 52: 1,2-Benzenedicarboxylic acid, di-C9-11-

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

branched alkyl esters, C10-rich

UK REACH Candidate list of substances of very high concern (SVHC) for Authorisation : Not applicable

The Persistent Organic Pollutants Regulations (retained Regulation (EU) 2019/1021 as amended for Great Britain) : Not applicable

International Chemical Weapons Convention (CWC) Schedules of Toxic Chemicals and Precursors : Not applicable

Regulation (EU) No 2024/590 on substances that deplete the ozone layer : Not applicable

UK REACH List of substances subject to authorisation (Annex XIV) : Not applicable

GB Export and import of hazardous chemicals - Prior Informed Consent (PIC) Regulation : Not applicable

Control of Major Accident Hazards Regulations 2015 (COMAH) : Not applicable

Volatile organic compounds : Law on the incentive tax for volatile organic compounds (VOCV)
no VOC duties

Directive 2010/75/EU of 24 November 2010 on industrial and livestock rearing emissions (integrated pollution prevention and control)
Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations
Health and Safety at Work Act 1974 & Subsidiary Regulations
Control of Substances Hazardous to Health Regulations (COSHH)
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

No Chemical Safety Assessment has been carried out for this mixture by the supplier.

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

SECTION 16: Other information

Full text of H-Statements

H226	:	Flammable liquid and vapour.
H317	:	May cause an allergic skin reaction.
H318	:	Causes serious eye damage.
H332	:	Harmful if inhaled.
H335	:	May cause respiratory irritation.

Full text of other abbreviations

Acute Tox.	:	Acute toxicity
Eye Dam.	:	Serious eye damage
Flam. Liq.	:	Flammable liquids
Skin Sens.	:	Skin sensitisation
STOT SE	:	Specific target organ toxicity - single exposure
2006/15/EC	:	Europe. Indicative occupational exposure limit values
GB EH40	:	UK. EH40 WEL - Workplace Exposure Limits
2006/15/EC / TWA	:	Limit Value - eight hours
GB EH40 / TWA	:	Long-term exposure limit (8-hour TWA reference period)
GB EH40 / STEL	:	Short-term exposure limit (15-minute reference period)
ADR	:	European Agreement concerning the International Carriage of Dangerous Goods by Road
CAS	:	Chemical Abstracts Service
DNEL	:	Derived no-effect level
EC50	:	Half maximal effective concentration
GHS	:	Globally Harmonized System
IATA	:	International Air Transport Association
IMDG	:	International Maritime Code for Dangerous Goods
LD50	:	Median lethal dosis (the amount of a material, given all at once, which causes the death of 50% (one half) of a group of test animals)
LC50	:	Median lethal concentration (concentrations of the chemical in air that kills 50% of the test animals during the observation period)
MARPOL	:	International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
OEL	:	Occupational Exposure Limit
PBT	:	Persistent, bioaccumulative and toxic
PNEC	:	Predicted no effect concentration
REACH	:	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
SVHC	:	Substances of Very High Concern
vPvB	:	Very persistent and very bioaccumulative

Further information

Classification of the mixture:

Classification procedure:

SAFETY DATA SHEET

According to REACH Regulation (EC) No 1907/2006, as amended by UK REACH Regulations SI 2019/758



Sika® Plumbers Gold

Date of last issue: 25.06.2025
Revision Date: 20.11.2025

Version 5.8

Print Date 20.11.2025

Skin Sens. 1

H317

Calculation method

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.



Changes as compared to previous version !

GB / EN