

STICK 2 EPOXY PUTTY AQUA

Page: 1

Compilation date: 31/10/2014

Revision No: 3

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: STICK 2 EPOXY PUTTY AQUA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: PC1: Adhesives, sealants.

1.3. Details of the supplier of the safety data sheet

Company name: EVERBUILD BUILDING PRODUCTS LTD

SITE 41, KNOWSTHORPE WAY

CROSS GREEN INDUSTRIAL ESTATE

LEEDS

WEST YORKSHIRE

LS9OSW ENGLAND

Tel: 0044 113 240 3456 **Fax:** 0044 113 240 0024

Email: sds@everbuild.co.uk

1.4. Emergency telephone number

Emergency tel: 0044 113 240 3456 (office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: Xi: R36/38; Sens.: R43; N: R51/53

Classification under CLP: Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317

Most important adverse effects: Irritating to eyes and skin. May cause sensitisation by skin contact. Toxic to aquatic

organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements under CLP:

Hazard statements: H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

Signal words: Warning

Hazard pictograms: GHS07: Exclamation mark

GHS09: Environmental





STICK 2 EPOXY PUTTY AQUA

Precautionary statements: P264: Wash thoroughly after handling.

P273: Avoid release to the environment.

P280: Wear.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing.

P321: Specific treatment (see on this label).
P332+313: If skin irritation occurs: Get medical.

Label elements under CHIP:

Hazard symbols: Irritant.

Dangerous for the environment.





Risk phrases: R36/38: Irritating to eyes and skin.

R43: May cause sensitisation by skin contact.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic

environment.

Safety phrases: S2: Keep out of the reach of children.

S24: Avoid contact with skin.S29: Do not empty into drains.S37: Wear suitable gloves.

S61: Avoid release to the environment. Refer to special instructions / safety data sheets.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

EINECS	CAS	CHIP Classification	CLP Classification	Percent
500-033-5	25068-38-6	Xi: R36/38; Sens.: R43; N: R51/53	Eye Irrit. 2: H319; Skin Irrit. 2: H315; Skin Sens. 1: H317; Aquatic Chronic 2: H411	10-30%

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

202-013-9	90-72-2	Xn: R22; Xi: R36/38	Acute Tox. 4: H302; Eye Irrit. 2: H319;	1-10%
			Skin Irrit. 2: H315	

Section 4: First aid measures

Page: 2

STICK 2 EPOXY PUTTY AQUA

Page: 3

4.1. Description of first aid measures

Skin contact: Remove all contaminated clothes and footwear immediately unless stuck to skin. Wash

immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Do not induce vomiting. If conscious, give half a litre of water to drink immediately.

Consult a doctor.

Inhalation: Remove casualty from exposure ensuring one's own safety whilst doing so. Consult a

doctor

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact

with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. If outside do not approach from

downwind. If outside keep bystanders upwind and away from danger point. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not

create dust.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate

method.

STICK 2 EPOXY PUTTY AQUA

Page: 4

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed. The floor of the storage

room must be impermeable to prevent the escape of liquids.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area. **Respiratory protection:** Respiratory protection not required. in normal use.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Solid
Colour: Green

Odour: Barely perceptible odour

Evaporation rate: Slow

Solubility in water: Insoluble

Flash point°C: >93

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

STICK 2 EPOXY PUTTY AQUA

Page: 5

10.3. Possibility of hazardous reactions

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT}

ORL	MUS	LD50	15600	mg/kg
ORL	RAT	LD50	11400	mg/kg
SKN	RBT	LD50	>20	ml/kg

2,4,6-TRIS(DIMETHYLAMINOMETHYL)PHENOL

ORL	RAT	LD50	1200	mg/kg
SKN	RAT	LD50	1280	mg/kg

Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT DRM	Hazardous: calculated
Sensitisation	DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: There may be irritation and redness at the site of contact.

Eye contact: There may be irritation and redness. The eyes may water profusely.

Ingestion: There may be soreness and redness of the mouth and throat.

Inhalation: There may be irritation of the throat with a feeling of tightness in the chest.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Not biodegradable.

STICK 2 EPOXY PUTTY AQUA

Page: 6

12.3. Bioaccumulative potential

Bioaccumulative potential: Bioaccumulation potential.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Toxic to aquatic organisms. Toxic to soil organisms.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal

company.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3077

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, SOLID, N.O.S.

(BISPHENOL A-(EPICHLORHYDRIN) {REACTION PRODUCT})

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

14.5. Environmental hazards

Environmentally hazardous: Yes Marine pollutant: No

14.6. Special precautions for user

Tunnel code: E

Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture

by the supplier.

STICK 2 EPOXY PUTTY AQUA

Page: 7

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No

453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H302: Harmful if swallowed.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H411: Toxic to aquatic life with long lasting effects.

R22: Harmful if swallowed.

R36/38: Irritating to eyes and skin.

R43: May cause sensitisation by skin contact.

R51/53: Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic

environment.

Legend to abbreviations: PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = phycico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

STICK 2 EPOXY PUTTY AQUA

Page: 8

and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.