according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution







Print Date 01.11.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

Version 1.0

1.1 Product identifier

Trade name : Everbuild 406 Stabilising Solution

1.2 Relevant identified uses of the substance or mixture and uses advised against

1.3 Details of the supplier of the safety data sheet

Company : Everbuild - A Sika Company

Site 41

Knowsthorpe Way

Cross Green Industrial Estate

West Yorkshire LS9 0SW

United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone num-

ber

: 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture according to Regulation (EC) No. 1272/2008.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture according to Regulation (EC) No. 1272/2008.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Remarks : No hazardous ingredients

Revision Date 19.10.2017

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution







Version 1.0 Print Date 01.11.2017

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : No hazards which require special first aid measures.

If inhaled : Move to fresh air.

In case of skin contact : Take off contaminated clothing and shoes immediately.

Wash off with soap and plenty of water.

In case of eye contact : Remove contact lenses.

Keep eye wide open while rinsing.

If swallowed : Do not induce vomiting without medical advice.

Rinse mouth with water.

Do not give milk or alcoholic beverages.

Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : See Section 11 for more detailed information on health effects

and symptoms.

Risks : No known significant effects or hazards.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

: In case of fire, use water/water spray/water jet/carbon diox-Suitable extinguishing media

ide/sand/foam/alcohol resistant foam/chemical powder for

extinction.

5.2 Special hazards arising from the substance or mixture

ucts

Hazardous combustion prod- : No hazardous combustion products are known

5.3 Advice for firefighters

for firefighters

Special protective equipment : In the event of fire, wear self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution

Revision Date 19.10.2017





Version 1.0

Print Date 01.11.2017

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : For personal protection see section 8.

6.2 Environmental precautions

Environmental precautions : No special environmental precautions required.

6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Wipe up with absorbent material (e.g. cloth, fleece).

Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : For personal protection see section 8. No special handling

advice required. Follow standard hygiene measures when

handling chemical products

Advice on protection against

fire and explosion

: Normal measures for preventive fire protection.

Hygiene measures : When using do not eat or drink. When using do not smoke.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers

: Keep container tightly closed in a dry and well-ventilated

place. Store in accordance with local regulations.

Advice on common storage : No special restrictions on storage with other products.

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : Consult most current local Product Data Sheet prior to any

use.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Revision Date 19.10.2017

according to Regulation (EC) No. 1907/2006







Version 1.0 Print Date 01.11.2017

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Personal protective equipment

Eye protection : Safety glasses

Hand protection : Chemical-resistant, impervious gloves complying with an ap-

proved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manu-

facturer specifications.

Butyl rubber/nitrile rubber gloves (0,4 mm), Recommended: Butyl rubber/nitrile rubber gloves.

Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345,

> long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing

and stirring work.

Respiratory protection : No special measures required.

Environmental exposure controls

General advice : No special environmental precautions required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance : liquid

Colour white

Odour characteristic

Odour Threshold : No data available

: ca. 200 °C Flash point

: No data available Autoignition temperature

: No data available Decomposition temperature

Lower explosion limit (Vol-%) : No data available

Upper explosion limit (Vol-%) : No data available

Flammability No data available

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution







Print Date 01.11.2017

Explosive properties : No data available

Oxidizing properties : No data available

pH : No data available

Melting point/range / Freez-

ing point

: No data available

Boiling point/boiling range : No data available

Vapour pressure : 23 hPa

Density : ca.1 g/cm3

at 20 °C

Water solubility : No data available

Partition coefficient: n-

octanol/water

: No data available

Viscosity, dynamic : No data available

Viscosity, kinematic : > 7 mm2/s

at 40 °C

Relative vapour density : No data available

Evaporation rate : No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : No hazards to be specially mentioned.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

Country GB 100000008565

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution

Revision Date 19.10.2017



Version 1.0



Print Date 01.11.2017

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Skin corrosion/irritation

Not classified based on available information.

Serious eye damage/eye irritation

Not classified based on available information.

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information.

Respiratory sensitisation: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered

to be either persistent, bioaccumulative and toxic (PBT), or

Country GB 100000008565

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution

Revision Date 19.10.2017





Version 1.0

Print Date 01.11.2017

very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Other adverse effects

Product:

Additional ecological infor-

mation

: There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized

wherever possible.

Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe

way.

Dispose of surplus and non-recyclable products via a licensed

waste disposal contractor.

Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional

local authority requirements.

Avoid dispersal of spilled material and runoff and contact with

soil, waterways, drains and sewers.

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution

Revision Date 19.10.2017





Print Date 01.11.2017

No data available

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Version 1.0

Prohibition/Restriction

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances,

preparations and articles (Annex XVII)

: Not applicable

REACH - Candidate List of Substances of Very High

Concern for Authorisation (Article 59).

: None of the components are listed

(=> 0.1 %).

REACH - List of substances subject to authorisation

(Annex XIV)

: Not applicable

REACH Information: All substances contained in our Products are

- preregistered or registered by our upstream suppliers, and/or

preregistered or registered by us, and/or
excluded from the regulation, and/or
exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

Not applicable

VOC-CH (VOCV) : no VOC duties

VOC-EU (solvent) : Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations Health and Safety at Work Act 1974 & Subsidiary Regulations Control of Substances Hazardous to Health Regulations (COSHH)

May be subject to the Control of Major Accident Hazards

Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

This product contains substances for which Chemical Safety Assessments are still required.

CAS

DNEL

according to Regulation (EC) No. 1907/2006

Everbuild 406 Stabilising Solution

Revision Date 19.10.2017





Print Date 01.11.2017

SECTION 16: Other information

ADR Accord européen relatif au transport international des marchandises

Dangereuses par Route Chemical Abstracts Service Derived no-effect level

EC50 Half maximal effective concentration

GHS Globally Harmonized System

IATA International Air Transport Association

IMDG International Maritime Code for Dangerous Goods

LD50 Median lethal dosis (the amount of a material, given all at once, which

causes the death of 50% (one half) of a group of test animals)

LC50 Median lethal concentration (concentrations of the chemical in air that

kills 50% of the test animals during the observation period)

Version 1.0

MARPOL International Convention for the Prevention of Pollution from Ships,

1973 as modified by the Protocol of 1978

OEL Occupational Exposure Limit

PBT Persistent, bioaccumulative and toxic PNEC Predicted no effect concentration

REACH Regulation (EC) No 1907/2006 of the European Parliament and of the

Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a

European Chemicals Agency

SVHC Substances of Very High Concern

vPvB Very persistent and very bioaccumulative

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.

Changes as compared to previous version!