



SAFETY DATA SHEET

Screen - Clene 100 Sachets

According to Regulation (EC) No 1907/2006, Annex II, as amended. Commission Regulation (EU) No 2015/830 of 28 May 2015.

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Screen - Clene 100 Sachets

Product number ASCS100, ZA

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Cleaning agent.

Uses advised against No specific uses advised against are identified.

1.3. Details of the supplier of the safety data sheet

Supplier HK WENTWORTH LIMITED
32 RUE DE TOURNENFILS
91540 MENNECY
FRANCE
+33 (0) 1 82 88 47 94
info@af-net.com

Manufacturer AF INTERNATIONAL
MacDermid Alpha Electronics Solutions
ASHBY PARK
COALFIELD WAY
ASHBY de la ZOUCH
LEICESTERSHIRE. LE65 1JR
UNITED KINGDOM
+44 (0) 1530 419600
+44 (0) 1530 416640
info@af-net.com

1.4. Emergency telephone number

Emergency telephone IN CASE OF EMERGENCY CALL:
+44 1865 407333 (24hr, Provided by Carechem 24)
+353 (0)1 809 2166 (Beaumont Hospital, Republic of Ireland only, 8am-10pm, 7 days a week)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Not Classified

Health hazards Not Classified

Environmental hazards Not Classified

2.2. Label elements

Hazard statements NC Not Classified

Screen - Clene 100 Sachets

Precautionary statements P102 Keep out of reach of children.

Detergent labelling < 5% perfumes

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Composition comments None of the ingredients are required to be listed.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	If in doubt, get medical attention promptly. Show this Safety Data Sheet to the medical personnel.
Inhalation	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Loosen tight clothing such as collar, tie or belt. Get medical attention if any discomfort continues.
Ingestion	No specific recommendations. If throat irritation or coughing persists, proceed as follows. Rinse mouth. Get medical attention if any discomfort continues.
Skin contact	No specific recommendations. Rinse with water. Get medical attention if any discomfort continues.
Eye contact	Remove any contact lenses and open eyelids wide apart. Rinse with water. Get medical attention if any discomfort continues.
Protection of first aiders	Use protective equipment appropriate for surrounding materials.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Temporary irritation.
Ingestion	May cause discomfort if swallowed.
Skin contact	May cause discomfort.
Eye contact	May be slightly irritating to eyes.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
Specific treatments	No special treatment required.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	The product is not flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Screen - Clene 100 Sachets

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.
5.3. Advice for firefighters	
Protective actions during firefighting	Avoid breathing fire gases or vapours. Evacuate area. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapours and protect men stopping the leak.
Special protective equipment for firefighters	Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Firefighter's clothing conforming to European standard EN469 (including helmets, protective boots and gloves) will provide a basic level of protection for chemical incidents.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions	No specific recommendations. For personal protection, see Section 8.
-----------------------------	--

6.2. Environmental precautions

Environmental precautions	Avoid discharge into drains or watercourses or onto the ground.
----------------------------------	---

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	Reuse or recycle products wherever possible. Absorb spillage to prevent material damage. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. Dispose of contents/container in accordance with national regulations.
--------------------------------	--

6.4. Reference to other sections

Reference to other sections	For personal protection, see Section 8. For waste disposal, see Section 13.
------------------------------------	---

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions	Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimise spills. Keep container tightly sealed when not in use. Avoid the formation of mists.
Advice on general occupational hygiene	Wash promptly if skin becomes contaminated. Take off contaminated clothing. Wash contaminated clothing before reuse.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions	Store away from incompatible materials (see Section 10). No specific recommendations.
Storage class	Unspecified storage.

7.3. Specific end use(s)

Specific end use(s)	The identified uses for this product are detailed in Section 1.2.
----------------------------	---

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

2-Butoxyethanol

Screen - Clene 100 Sachets

Long-term exposure limit (8-hour TWA): WEL 25 ppm 123 mg/m³

Short-term exposure limit (15-minute): WEL 50 ppm 246 mg/m³

Sk

1-Methoxy-2-propanol

Long-term exposure limit (8-hour TWA): WEL 100 ppm 375 mg/m³

Short-term exposure limit (15-minute): WEL 150 ppm 560 mg/m³

Sk

2-(2-butoxyethoxy)ethanol

Long-term exposure limit (8-hour TWA): WEL 10 ppm 67.5 mg/m³

Short-term exposure limit (15-minute): WEL 15 ppm 101.2 mg/m³

Ethanol

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1920 mg/m³

Diethyl phthalate

Long-term exposure limit (8-hour TWA): WEL 5 mg/m³

Short-term exposure limit (15-minute): WEL 10 mg/m³

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through the skin.

8.2. Exposure controls

Appropriate engineering controls	No specific ventilation requirements.
Eye/face protection	No specific eye protection required during normal use. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.
Hand protection	No specific hand protection recommended.
Other skin and body protection	Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.
Hygiene measures	Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.
Respiratory protection	No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.
Environmental exposure controls	Not regarded as dangerous for the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Liquid-impregnated wipe.
Colour	Colourless.
Odour	Alcoholic.
Odour threshold	Not available.
pH	pH (concentrated solution): 5-7
Melting point	Not available.
Initial boiling point and range	Not available.
Flash point	Not available.

Screen - Clene 100 Sachets

Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapour pressure	2.35 kPa @ 20°C
Vapour density	Not available.
Relative density	0.993-1.003 @ 20°C
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidising properties	Does not meet the criteria for classification as oxidising.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	See the other subsections of this section for further details.
------------	--

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
-----------	---

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	No potentially hazardous reactions known.
------------------------------------	---

10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
---------------------	---

10.5. Incompatible materials

Materials to avoid	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
--------------------	--

10.6. Hazardous decomposition products

Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapours.
----------------------------------	--

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects	Not regarded as a health hazard under current legislation.
-----------------------	--

Screen - Clene 100 Sachets

Acute toxicity - oral

Summary Based on available data the classification criteria are not met.

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Summary Based on available data the classification criteria are not met.

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - inhalation

Summary Based on available data the classification criteria are not met.

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Summary Based on available data the classification criteria are not met.

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Summary Based on available data the classification criteria are not met.

Serious eye damage/irritation Based on available data the classification criteria are not met.

Respiratory sensitisation

Summary Based on available data the classification criteria are not met.

Respiratory sensitisation Based on available data the classification criteria are not met.

Skin sensitisation

Summary Based on available data the classification criteria are not met.

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Summary Based on available data the classification criteria are not met.

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Summary Based on available data the classification criteria are not met.

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity None of the ingredients are listed or exempt.

Reproductive toxicity

Summary Based on available data the classification criteria are not met.

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

Summary Based on available data the classification criteria are not met.

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

Summary Based on available data the classification criteria are not met.

Screen - Clene 100 Sachets

STOT - repeated exposure	Not classified as a specific target organ toxicant after repeated exposure.
<u>Aspiration hazard</u>	
Summary	Based on available data the classification criteria are not met.
Aspiration hazard	Based on available data the classification criteria are not met.
General information	No specific health hazards known. The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Temporary irritation.
Ingestion	May cause discomfort if swallowed.
Skin contact	May cause discomfort.
Eye contact	May be slightly irritating to eyes.
Route of exposure	Ingestion Inhalation Skin and/or eye contact
Target organs	No specific target organs known.

SECTION 12: Ecological information

Ecotoxicity	Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.
--------------------	---

12.1. Toxicity

Toxicity	Based on available data the classification criteria are not met.
-----------------	--

Acute aquatic toxicity

Summary	Based on available data the classification criteria are not met.
----------------	--

Chronic aquatic toxicity

Summary	Based on available data the classification criteria are not met.
----------------	--

12.2. Persistence and degradability

Persistence and degradability	The degradability of the product is not known.
--------------------------------------	--

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
----------------------------------	---------------------------------------

Partition coefficient	Not available.
------------------------------	----------------

12.4. Mobility in soil

Mobility	No data available.
-----------------	--------------------

12.5. Results of PBT and vPvB assessment

12.6. Other adverse effects

Other adverse effects	None known.
------------------------------	-------------

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	The generation of waste should be minimised or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way.
----------------------------	---

Screen - Clene 100 Sachets

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

SECTION 14: Transport information

General The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78
and the IBC Code**

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations

Health and Safety at Work etc. Act 1974 (as amended).
The Carriage of Dangerous Goods and Use of Transportable Pressure Equipment Regulations 2009 (SI 2009 No. 1348) (as amended) ["CDG 2009"].
EH40/2005 Workplace exposure limits.

EU legislation

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
Commission Regulation (EU) No 2015/830 of 28 May 2015.
Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

Product Type

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

Inventories

EU - EINECS/ELINCS

None of the ingredients are listed or exempt.

Screen - Clene 100 Sachets

SECTION 16: Other information

**Abbreviations and acronyms
used in the safety data sheet**

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road.
ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways.
RID: European Agreement concerning the International Carriage of Dangerous Goods by Rail.
IATA: International Air Transport Association.
ICAO: Technical Instructions for the Safe Transport of Dangerous Goods by Air.
IMDG: International Maritime Dangerous Goods.
CAS: Chemical Abstracts Service.
ATE: Acute Toxicity Estimate.
LC₅₀: Lethal Concentration to 50 % of a test population.
LD₅₀: Lethal Dose to 50% of a test population (Median Lethal Dose).
EC₅₀: 50% of maximal Effective Concentration.
PBT: Persistent, Bioaccumulative and Toxic substance.
vPvB: Very Persistent and Very Bioaccumulative.

Training advice

Read and follow manufacturer's recommendations.

Issued by

Damian Robertson

Revision date

28/09/2021

Revision

3.1

SDS number

211

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.