

	<b>Product Safety Data Sheet (PSDS)</b>	Version: R0001.0001
		Date of issue: 2021-02-05
	<b>INR18650 MJ1</b>	Revision date: 2021-02-05
		Change List:

Copyright 2020. LG Energy Solution, Ltd. all rights reserved.

## SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

### 1.1. Product identifier

Version	Items	Description	Date
V01	Origin	Initial Release	2021.02.05

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

#### 1.2.1. Relevant identified uses

- Not available

#### 1.2.2. Uses advised against

- Not available

### 1.3. Details of the supplier of the safety data sheet

Manufacturer/Supplier : LG Energy Solution  
 Address :  
 Telephone :  
 Email :

### 1.4. Emergency telephone number

Emergency number : 112

See section 16.6 for the list of telephone number of National Helpdesks in the European Economic Area.

	<b>Product Safety Data Sheet (PSDS)</b>	Version: R0001.0001
		Date of issue: 2021-02-05
		Revision date: 2021-02-05
		Change List:

Copyright 2020. LG Energy Solution, Ltd. all rights reserved.

## SECTION 2: HAZARD IDENTIFICATION

These products are classified as Articles under OSHA Hazard Communication Standard and are not subject to the requirements for Information in the Supply Chain (Safety Data Sheets and Labels).

While batteries may release hazardous substances if damaged, this is not an intended release as defined under OSHA.

Batteries are not classified as hazardous under the 29 CFR 1910.1200.

The following information is provided to assist in the safe use of our products.

CAUTION: Battery can explode or leak if heated, disassembled, shorted, recharged, exposed to fire or high temperature or inserted incorrectly. Keep in original package until ready to use. Do not carry batteries loose in your pocket or purse. Keep batteries away from children. If swallowed, consult a physician at once. Under certain misuse conditions and by abusively opening the battery, exposed lithium can react with water or moisture in the air causing potential thermal burns or fire.

## SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

Name	CAS No.	% [weight]
Aluminium Foil	7429-90-5	2 - 10
Nikel compound (proprietary)	1313-99-1	0 - 80
Manganese compound (proprietary)	1313-13-9	0 - 15
Cobalt compound (proprietary)	1307-96-6	0 - 15
Styrene-Butadiene-Rubber	9003-55-3	< 1
Polyvinylidene Fluoride (PVDF)	24937-79-9	< 5
Copper Foil	7440-50-8	2 - 10
Carbon (proprietary)	7440-44-0	10 - 30
Electrolyte (proprietary)	96-49-1	10 - 20
Steel, Nickel and inert materials	N/A	Remainder

## SECTION 4: FIRST AID MEASURES

### 4.1. Description of first aid measures

#### General

- The chemicals and metals in this product are contained in a sealed can. Exposure to the contents will not occur unless the battery leaks, is exposed to high temperatures or is mechanically, physically, or electrically abused.

#### Inhalation

- When exposed to large amounts of steam and mist, move to fresh air.
- Take specific treatment if needed.

#### Skin contact

- Flush skin with plenty of water for at least 15 minutes while removing contaminated clothing and shoes.
- Wash contaminated clothing thoroughly before re-using.

#### Eye contact

- Do not rub your eyes.
- Immediately flush eyes with plenty of water for at least 15 minutes and call a doctor/physician.

#### Ingestion

- Please be advised by doctor whether induction of vomit is demanded or not.
- Rinse your mouth with water immediately.

#### Note to Physician

- Published reports recommend removal from the esophagus be done endoscopically (under direct visualization). Batteries beyond the esophagus need not be retrieved unless there are signs of injury to the GI tract or a large diameter battery fails to pass the pylorus. If asymptomatic, follow-up xrays are necessary only to confirm the passage of larger batteries. Confirmation by stool inspection is preferable under most circumstances. Potential leakage of less than 50 milligrams of dimethoxyethane and propylene carbonate. Dimethoxyethane rapidly evaporates. Do not give ipecac.

## SECTION 5: FIREFIGHTING MEASURES

### 5.1. Extinguishing media

#### General Hazard

- Cell is not flammable but internal organic material will burn if the cell is incinerated or exposed to high temperatures.

#### Suitable extinguishing media

- Use extinguishing media suitable for the materials that are burning.

### 5.2. Special hazards arising from the substance or mixture

#### Hazardous combustion products

- Combustion products include, but are not limited to hydrogen fluoride, carbon monoxide and carbon dioxide.

### 5.3. Advice for firefighters

- If possible, remove cell(s) from fire fighting area. If heated above 125°C, cell(s) may explode/vent.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Accidental release measures

- Notify safety personnel of large spills. Irritating vapors and flammable may be released from leaking or ruptured batteries. Eliminate all ignition sources. Evacuate the area and allow the vapors to dissipate.
- Clean-up personnel should wear appropriate protective clothing to avoid eye and skin contact and inhalation of vapors or fumes. Increase ventilation. Carefully collect batteries and place in an appropriate container for disposal. Remove spilled liquid with absorbent and contain for disposal.

### 6.2. Personal Precautions, protective equipment and emergency procedures

#### 6.2.1. For non-emergency personnel

- Protective equipment: Wear proper protective equipment.
- Emergency procedures: Not applicable
- If required, notify relevant authorities according to all applicable regulations.

#### 6.2.2. For emergency responders

- Wear proper personal protective apparatus as indicated in Section 8 and avoid skin contact and inhalation.
- Must work against the wind, let the upwind people to evacuate.
- Move container to safe area from the leak area.

### 6.3. Environmental precautions

- Prevent runoff and contact with waterways, drains or sewers.
- If large amounts have been spilled, inform the relevant authorities.
- Avoid dispersal of spilt material and runoff and contact with waterways, drains and sewers. If large spills, advise emergency services.

### 6.4. Methods and material for containment and cleaning up

#### 6.4.1. For containment

- Clear spills immediately
- Clean up all spills immediately.
- Control personal contact by using protective equipment.
- Prevent, by any means available, spillage from entering drains or water course.

#### 6.4.2. For cleaning up

- Large spill : Stay upwind and keep out of low areas. Dike for later disposal.
- Notify the central and local government if the emission reach the standard threshold.
- Disposal of waste shall be in compliance with the Wastes Control?Act
- Appropriate container for disposal of spilled material collected.

#### 6.4.3. Other information

- Slippery when spilt.

## SECTION 7: HANDLING AND STORAGE

### 7.1. Precautions for safe handling

- Avoid mechanical or electrical abuse. DO NOT short circuit or install incorrectly. Batteries may explode, pyrolize or vent if disassembled, crushed, recharged or exposed to high temperatures. Install batteries in accordance with equipment instructions. Replace all batteries in equipment at the same time. Do not carry batteries loose in a pocket or bag.
- Avoid contact with incompatible materials.
- Get the manual before use.
- Do not handle until all safety precautions have been read and understood.

### 7.2. Conditions for safe storage, including any incompatibilities

- Store in a cool, dry place.
- Do not apply any physical shock to container.
- Avoid direct sunlight.
- Keep in the original container.
- Please pay attention to incompatibilities materials and conditions to avoid.
- Keep sealed when not in use.

### 7.3. Specific end use(s)

- See Section 1 for information on 1.2 Relevant identified uses.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1. Exposure controls/Personal protection

#### 8.1.1. Appropriate engineering controls

- Keep away from heat and open flame. Store in a cool dry place.

#### 8.1.2. Individual protection measures, such as personal protective equipment

##### Hand protection

- Wear appropriate glove made out of rubber, neoprene, vinyl coated, PVC.

##### Eye protection

- Wear primary eye protection such as splash resistant safety goggles with a secondary protection face shield.
- Provide an emergency eye wash station and quick drench shower in the immediate work area.

##### Respiratory Protection

- Respiratory protection is ranked in order from minimum to maximum.
- Consider warning properties before use.

##### Skin protection

- Wear appropriate clothing.

##### Others

- It is necessary to wear protective clothes and other protection equipment. Cover your face, head and neck.
- Prior to removing protective garments the employee should undergo decontamination and be required to shower upon removal of the garments and hood.
- Emergency deluge showers and eyewash fountains, supplied with potable water, should be located near, within sight of, and on the same level with locations where direct exposure is likely.

##### Thermal hazards

- Not available

## SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

### 9.1. Information on basic physical and chemical properties

Appearance(State)	Other
Appearance(Color)	Not available
Odor	Not available
Odor threshold	Not available
pH	Not available
Melting point/Freezing point	Not available
Initial boiling point and boiling range	Not available
Flash point	Not available
Evaporation rate	Not available

Flammability(solid, gas)	Not available
Upper/Lower Flammability or explosive limits	Not available
Vapour pressure	Not available
Vapour density	Not available
Relative density	Not available
Solubility	Insoluble
Partition coefficient of n-octanol/water	Not available
Autoignition temperature	Not available
Decomposition temperature	Not available
Viscosity	Not available
Explosive properties	Not available
Oxidising properties	Not available

## 9.2. Other information

- Not available

## SECTION 10: STABILITY AND REACTIVITY

### 10.1. Reactivity

- None

### 10.2. Chemical Stability

- This product is stable under recommended storage and handling conditions.

### 10.3. Conditions to avoid

- Avoid exposure to heat and open flame.
- Do not puncture, crush or incinerate.

### 10.4. Incompatible materials

- Not available

### 10.5. Hazardous decomposition products

- None during normal operating conditions. If cells are opened, hydrogen fluoride and carbon monoxide may be released.

## SECTION 11: TOXICOLOGICAL INFORMATION

### 11.1. Toxicological information

- This product does not elicit toxicological properties during routine handling and use.
- If the cells are opened through misuse or damage, discard immediately. Internal components of cell are irritants and sensitizers.

## SECTION 12: ECOLOGICAL INFORMATION

### 12.1. Ecological information

- Some materials within the cell are bioaccumulative. Under normal conditions, these materials are contained and pose no risk to persons or the surrounding environment.

## SECTION 13: DISPOSAL CONSIDERATIONS

### 13.1. Waste treatment methods

- Disposal should be in accordance with national and local regulations. Do not incinerate for disposal except for in a controlled incinerator.

## SECTION 14: TRANSPORT INFORMATION

### 14.1. UN No.

#### 14.1.1. UN No. (ADR/RID/ADN)

- 3480
- 3481

**14.1.2. UN No. (IMDG)**

- 3480
- 3481

**14.1.3. UN No. (ICAO)**

- 3480
- 3481

**14.2. UN proper shipping name**

- LITHIUM ION BATTERIES (including lithium ion polymer batteries)
- LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT (including lithium ion polymer batteries)

**14.3. Transport hazard class(es)****14.3.1. ADR/RID/ADN Class**

- 9
- 9

**14.3.2. ADR/RID/ADN Class**

- Class : 9, LITHIUM ION BATTERIES (including lithium ion polymer batteries)
- Class : 9, LITHIUM ION BATTERIES CONTAINED IN EQUIPMENT or LITHIUM ION BATTERIES PACKED WITH EQUIPMENT (including lithium ion polymer batteries)

**14.3.3. ADR Label No.**

- 9A
- 9A

**14.3.4. IMDG Class**

- 9
- 9

**14.3.5. ICAO Class/Division**

- 9
- 9

**14.4. Packing instruction****14.4.1. ADR/RID/ADN Packing instruction**

- P903
- P903

**14.4.2. IMDG Packing instruction**

- P903
- P903

**14.4.3. ICAO Packing instruction**

- P903
- P903

**14.5. Environmental hazards**

- Not available

**14.6. Special precautions for user**

- Local transport follows in accordance with Dangerous goods Safety Management Law.
- Package and transport follow in accordance with Department of Transportation (DOT) and other regulatory agency requirements.
- EmS FIRE SCHEDULE : F-A (General fire schedule)
- EmS SPILLAGE SCHEDULE : S-I (Flammable solids (repacking possible))
- Emergency Action Code : 4W(1)
- Tunnel Restriction Code : 2 (E)
- This product passed 1.2M drop test and comply with UN38.3.

No	Test item	Criteria	Result
Test 1	Altitude simulation	- After OCV (%) $\geq$ 90%	Pass
Test 2	Thermal test	- No leakage, no venting, no disassembly, no rupture, no fire	Pass
Test 3	Vibration	- Mass loss limit (leakage) 1) If $M < 1g$ , less than 0.5%, 2) If $1g \leq M \leq 75g$ , less than 0.2%, 3) If $M > 75g$ , less than 0.1%)	Pass
Test 4	Shock	- No disassembly, no rupture, no fire within 6 hours after the test	Pass
Test 5	External short circuit	- Max. Temp $\leq 170^{\circ}C$	Pass
Test 6	Impact or Crush	- No disassembly, no fire within 6 hours after the test - Max. Temp $\leq 170^{\circ}C$	Pass
Test 7	Overcharge	- No disassembly, no fire within 7 days after the test	Pass
Test 8	Forced discharge	- No disassembly, no fire within 7 days after the test	Pass

#### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

- Not applicable

### SECTION 15: REGULATORY INFORMATION

#### 15.1. Safety, health and environmental regulation / legislation specific for the substance or mixture

- This product is not hazardous under the criteria of the Federal Occupational Safety and Health Administration(OSHA) Hazard Communication Standard.(29 CFR 1910.1200)

### SECTION 16: OTHER INFORMATION

#### 16.1. Other information

- The data in this Product Safety Data Sheet relates only to the specific product designated herein and does not relate to use in combination with any other product or in any process. This PSDS may not meet regulatory requirements in other countries. This information is based on technical information believed to be reliable. It is subject to revision as additional knowledge and experiences are gained.