

Safety data sheet according to 1907/2006/EC, Article 31

Printing date 11.02.2021



Version number 4

Revision: 11.02.2021

SECTION 1: Identification of the substance/mixture and of the company/ undertaking

- **1.1 Product identifier**
 - **Trade name:** BIS SG SUPER PRECISION BS 3G*12 L117
 - **1.2 Relevant identified uses of the substance or mixture and uses advised against**
No further relevant information available.
 - **Application of the substance / the mixture** Adhesive
 - **1.3 Details of the supplier of the safety data sheet**
 - **Manufacturer/Supplier:**
UHU GmbH & Co.KG
Herrmannstraße 7
D-77815 Bühl (Baden)
Tel.: 0049-(0)7223-284-0
email: sds@boltonadhesives.com
Fax: 0049-(0)7223-284-245
 - **Further information obtainable from:** UHU QESH
 - **1.4 Emergency telephone number:**
Tel.: + 49 (0) 30/19240 (Notruf)
Tel.: + 49 (0) 72 23/28 40
- England and Wales (NHS Direct) 111
Schottland (NHS 24) 111

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**
 GHS07
Skin Irrit. 2 H315 Causes skin irritation.
Eye Irrit. 2 H319 Causes serious eye irritation.
STOT SE 3 H335 May cause respiratory irritation.
- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**
 GHS07
- **Signal word** Warning
- **Hazard-determining components of labelling:**
ethyl 2-cyanoacrylate
- **Hazard statements**
H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

(Contd. on page 2)

GB-EN

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 1)

· **Precautionary statements**

- P101 If medical advice is needed, have product container or label at hand.
- P261 Avoid breathing vapours.
- P302+P352 IF ON SKIN: Wash with plenty of soap and water.
- P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P501 Dispose of contents/container in accordance with national regulations.

· **Additional information:**

Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

· **2.3 Other hazards**

· **Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· **3.2 Mixtures**

· **Description:** Adhesive

· **Dangerous components:**

CAS: 7085-85-0	ethyl 2-cyanoacrylate	50-100%
EINECS: 230-391-5	⚠ Skin Irrit. 2, H315; Eye Irrit. 2, H319; STOT SE 3, H335	
Index number: 607-236-00-9		
Reg.nr.: 01-2119527766-29-XXXX		

· **Additional information:** For the wording of the listed hazard phrases refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**

· **General information:** No special measures required.

· **After inhalation:**

In case of unconsciousness place patient stably in side position for transportation.

· **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

· **After eye contact:**

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

· **After swallowing:** If symptoms persist consult doctor.

· **4.2 Most important symptoms and effects, both acute and delayed**

No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

SECTION 5: Firefighting measures

· **5.1 Extinguishing media**

· **Suitable extinguishing agents:**

CO2, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.

(Contd. on page 3)

GB-EN



Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 2)

- **5.2 Special hazards arising from the substance or mixture**
No further relevant information available.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures** Not required.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Send for recovery or disposal in suitable receptacles.
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
Ensure adequate ventilation.
- **6.4 Reference to other sections**
See Section 7 for information on safe handling.
See Section 8 for information on personal protection equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**
Ensure good ventilation/exhaustion at the workplace.
Open and handle receptacle with care.
Prevent formation of aerosols.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 10
- **7.3 Specific end use(s)** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.

- **8.1 Control parameters**

- **Ingredients with limit values that require monitoring at the workplace:**

7085-85-0 ethyl 2-cyanoacrylateWEL Short-term value: 1.5 mg/m³, 0.3 ppm

- **Additional information:** The lists valid during the making were used as basis.

- **8.2 Exposure controls**

- **Personal protective equipment:**

- **General protective and hygienic measures:**

The usual precautionary measures are to be adhered to when handling chemicals.
Keep away from foodstuffs, beverages and feed.

(Contd. on page 4)

GB-EN

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 3)

Immediately remove all soiled and contaminated clothing
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes and skin.

· **Respiratory protection:** Not required.

· **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

Nitrile gloves with a material thickness of > 0.1 mm (penetration time < 30s).

Protective nitrile rubber gloves according to EN 374 are recommended for prolonged contact.

Material thickness > 0.4 mm

Breakthrough time > 30 minutes

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:**

Safety glasses



Tightly sealed goggles

Goggles recommended during refilling

SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

· **Form:**

Fluid

· **Colour:**

According to product specification

· **Odour:**

Characteristic

· **Odour threshold:**

Not determined.

· **pH-value:**

Not determined.

· **Change in condition**

· **Melting point/freezing point:**

Undetermined.

· **Initial boiling point and boiling range:** 60 °C

· **Flash point:**

82 °C

· **Flammability (solid, gas):**

Not applicable.

(Contd. on page 5)

GB-EN



Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 4)

· Decomposition temperature:	Not determined.
· Auto-ignition temperature:	Product is not selfigniting.
· Explosive properties:	Product does not present an explosion hazard.
· Explosion limits:	
Lower:	Not determined.
Upper:	Not determined.
· Vapour pressure:	Not determined.
· Density at 20 °C:	1.044 g/cm ³
· Relative density	Not determined.
· Vapour density	Not determined.
· Evaporation rate	Not determined.
· Solubility in / Miscibility with water:	Not miscible or difficult to mix.
· Partition coefficient: n-octanol/water:	Not determined.
· Viscosity:	
Dynamic at 20 °C:	70 mPas
Kinematic:	Not determined.
· Solvent content:	
Solids content:	6.0 %
· 9.2 Other information	All relevant physical data were determined for the mixture. All non-determined data are not measurable or not relevant for the characterization of the mixture.

SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation**
Causes skin irritation.
- **Serious eye damage/irritation**
Causes serious eye irritation.

(Contd. on page 6)

GB-EN



Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 5)

- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Acute effects (acute toxicity, irritation and corrosivity)** Not applicable.
- **Sensitisation** Not applicable.
- **Repeated dose toxicity** Not applicable.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Not applicable.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**
May cause respiratory irritation.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation**
Must not be disposed together with household garbage. Do not allow product to reach sewage system.
Disposal must be made according to official regulations.
- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- **14.1 UN-Number**
- **ADR/ADN, IMDG, IATA** not regulated
- **ADN** not regulated

(Contd. on page 7)

GB-EN



Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 6)

· 14.2 UN proper shipping name · ADR/ADN, ADN, IMDG, IATA	not regulated
· 14.3 Transport hazard class(es) · ADR/ADN, ADN, IMDG, IATA · Class	not regulated
· 14.4 Packing group · ADR/ADN, IMDG, IATA	not regulated
· 14.5 Environmental hazards:	Not applicable.
· 14.6 Special precautions for user	Not applicable.
· 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code	Not applicable.
· Transport/Additional information:	Not dangerous according to the above specifications.
· UN "Model Regulation":	not regulated

SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- Directive 2012/18/EU
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3
- **DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**
- None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H335 May cause respiratory irritation.

· **Classification according to Regulation (EC) No 1272/2008**

Skin corrosion/irritation Serious eye damage/eye irritation Specific target organ toxicity (single exposure)	The classification of the mixture is generally based on the calculation method using substance data according to Regulation (EC) No 1272/2008.
--	--

- **Department issuing SDS:** UHU QESH
- **Contact:** UHU QESH

(Contd. on page 8)

GB-EN



Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 11.02.2021

Version number 4

Revision: 11.02.2021

Trade name: BIS SG SUPER PRECISION BS 3G*12 L117

(Contd. of page 7)

· **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

· *** Data compared to the previous version altered.**

GB-EN