

# UTD2025C

# Digital Storage Oscilloscope



## SPECIFICATIONS

Feature	UTD2025C
<b>Bandwidth</b>	25 MHz
<b>Rise Time</b>	≤14 ns
<b>Sample Range</b>	250MS/s
<b>Vertical Sensitivity</b>	2mV ~ 10V/div
<b>Record Length (Max)</b>	2 x 512k
<b>Sample Rate</b>	Real time 250MS/s
<b>Scan Time Base</b>	20ns ~ 50s/div
<b>Trigger Type</b>	Edge, Pulse, Video and Alternate
<b>Automatic Waveform Measurements</b>	28
<b>Ports</b>	Standard: USB Device, USB Host, PASS/FAIL. Optional: LAN
<b>Mathematics</b>	Add, Subtract, Multiply, Divide, FFT
<b>Applications</b>	College Education, R&D, Electronic product assemble line, Industrial Control etc.
<b>Display</b>	64k, Full colour LCD, 320 x 240

## GENERAL CHARACTERISTICS

<b>Power</b>	100 - 240VACRMS, 45Hz - 440Hz, CAT II
<b>LCD Size</b>	Diagonal 145mm (5.7 inches)
<b>Product Color</b>	Red and Grey
<b>Product Net Weight</b>	2.5kg (Excluding packaging)
<b>Product Size</b>	320mm x 150mm x 130mm
<b>Standard Accessories</b>	Probe x 2 (1x, 10x switchable), Power Cord and English Manual
<b>Standard Individual Packing</b>	Gift Box
<b>Standard Quantity Per Carton</b>	2 pcs
<b>Standard Carton Measurement</b>	445 x 410 x 270mm (0.055 CBM Per Export Carton)
<b>Standard Carton Gross Weight</b>	9.2kg

Specifications and other information are subject to change without further notice.