according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

 Version
 Revision Date:
 SDS Number:
 Date of last issue: 10.11.2016

 1.5
 28.04.2017
 1340635-00006
 Date of first issue: 12.02.2015

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : DOW CORNING(R) FIRESTOP 400 SEALANT

Product code : 00000000003282040

1.2 Relevant identified uses of the substance or mixture and uses advised against

Use of the Sub- : Flame retardants

stance/Mixture

1.3 Details of the supplier of the safety data sheet

Company : Dow Corning Europe S.A.

rue Jules Bordet - Parc Industriel - Zone C

B-7180 Seneffe

Telephone : English Tel: +49 611237507

Deutsch Tel: +49 611237500 Français Tel: +32 64511149 Italiano Tel: +32 64511170 Español Tel: +32 64511163

E-mail address of person

responsible for the SDS

sdseu@dowcorning.com

### 1.4 Emergency telephone number

Dow Corning (Barry U.K. 24h) Tél: +44 1446732350 Dow Corning (Wiesbaden 24h) Tél: +49 61122158 Dow Corning (Seneffe 24h) Tel: +32 64 888240

### **SECTION 2: Hazards identification**

### 2.1 Classification of the substance or mixture

### Classification (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

## 2.2 Label elements

### Labelling (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

#### Additional Labelling

EUH210 Safety data sheet available on request.

EUH208 Contains 5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-

isothiazolone. May produce an allergic reaction.

according to Regulation (EC) No. 1907/2006



# DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

## 2.3 Other hazards

None known.

## **SECTION 3: Composition/information on ingredients**

#### 3.2 Mixtures

Chemical nature : Acrylic

dispersion

### **Hazardous components**

Chemical name	CAS-No.	Classification	Concentration
	EC-No.		(% w/w)
	Index-No.		
	Registration number		
5-Chloro-2-methyl-3(2H)-	55965-84-9	Acute Tox. 3; H301	>= 0.0002 - <
isothiazolone, mixt. with 2-methyl-	247-500-7	Acute Tox. 2; H330	0.0015
3(2H)-isothiazolone	613-167-00-5	Acute Tox. 2; H310	
		Skin Corr. 1B; H314	
		Eye Dam. 1; H318	
		Skin Sens. 1A; H317	
		Aquatic Acute 1;	
		H400	
		Aquatic Chronic 1;	
		H410	

### Alternative CAS Numbers for some regions

CAS-No.	Alternative CAS Number(s)
55965-84-9	2682-20-4, 26172-55-4

For explanation of abbreviations see section 16.

## **SECTION 4: First aid measures**

## 4.1 Description of first aid measures

Protection of first-aiders : No special precautions are necessary for first aid responders.

If inhaled : If inhaled, remove to fresh air.

Get medical attention if symptoms occur.

In case of skin contact : Wash with water and soap as a precaution.

Get medical attention if symptoms occur.

In case of eye contact : Flush eyes with water as a precaution.

Get medical attention if irritation develops and persists.

If swallowed, DO NOT induce vomiting.

Get medical attention if symptoms occur. Rinse mouth thoroughly with water.

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

### 4.2 Most important symptoms and effects, both acute and delayed

None known.

### 4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically and supportively.

## **SECTION 5: Firefighting measures**

### 5.1 Extinguishing media

Suitable extinguishing media : Water spray

Alcohol-resistant foam Carbon dioxide (CO2)

Dry chemical

Unsuitable extinguishing

media

None known.

### 5.2 Special hazards arising from the substance or mixture

Specific hazards during fire-

fighting

Exposure to combustion products may be a hazard to health.

Hazardous combustion prod: :

ucts

Carbon oxides Metal oxides Formaldehyde

## 5.3 Advice for firefighters

Special protective equipment:

for firefighters

Wear self-contained breathing apparatus for firefighting if nec-

essary. Use personal protective equipment.

Specific extinguishing meth-

ods

Use extinguishing measures that are appropriate to local cir-

cumstances and the surrounding environment. Use water spray to cool unopened containers.

Remove undamaged containers from fire area if it is safe to do

SO.

Evacuate area.

## **SECTION 6: Accidental release measures**

### 6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Follow safe handling advice and personal protective equip-

ment recommendations.

### 6.2 Environmental precautions

Environmental precautions : Discharge into the environment must be avoided.

Prevent further leakage or spillage if safe to do so. Retain and dispose of contaminated wash water.

Local authorities should be advised if significant spillages

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

cannot be contained.

### 6.3 Methods and material for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material.

For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, store recovered material in appropriate container. Clean up remaining materials from spill with suitable absor-

bent.

Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to deter-

mine which regulations are applicable.

Sections 13 and 15 of this SDS provide information regarding

certain local or national requirements.

### 6.4 Reference to other sections

See sections: 7, 8, 11, 12 and 13.

## **SECTION 7: Handling and storage**

## 7.1 Precautions for safe handling

Technical measures : See Engineering measures under EXPOSURE

CONTROLS/PERSONAL PROTECTION section.

Local/Total ventilation : Use only with adequate ventilation.

Advice on safe handling : Handle in accordance with good industrial hygiene and safety

practice.

Take care to prevent spills, waste and minimize release to the

environment.

Hygiene measures : Ensure that eye flushing systems and safety showers are

located close to the working place. When using do not eat, drink or smoke. Wash contaminated clothing before re-use.

### 7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers

Keep in properly labelled containers. Store in accordance with

the particular national regulations.

Advice on common storage : Do not store with the following product types:

Strong oxidizing agents

### 7.3 Specific end use(s)

Specific use(s) : These precautions are for room temperature handling. Use at

elevated temperature or aerosol/spray applications may re-

quire added precautions.

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

 Version
 Revision Date:
 SDS Number:
 Date of last issue: 10.11.2016

 1.5
 28.04.2017
 1340635-00006
 Date of first issue: 12.02.2015

## **SECTION 8: Exposure controls/personal protection**

## 8.1 Control parameters

Contains no substances with occupational exposure limit values.

### Derived No Effect Level (DNEL) according to Regulation (EC) No. 1907/2006:

Substance name	End Use	Exposure routes	Potential health ef-	Value
			fects	
Metal Oxide	Workers	Inhalation	Long-term local ef- fects	3.59 mg/m3
	Consumers	Ingestion	Long-term systemic effects	2.37 mg/kg bw/day

### Predicted No Effect Concentration (PNEC) according to Regulation (EC) No. 1907/2006:

Substance name	Environmental Compartment	Value
Metal Oxide	Fresh water	74.9 µg/l
	Sewage treatment plant	20 mg/l

### 8.2 Exposure controls

### **Engineering measures**

Processing may form hazardous compounds (see section 10). Ensure adequate ventilation, especially in confined areas.

Minimize workplace exposure concentrations.

### Personal protective equipment

Eye protection : Wear the following personal protective equipment:

Safety glasses

Hand protection

Remarks : Wash hands before breaks and at the end of workday.

Skin and body protection : Skin should be washed after contact.

Respiratory protection : Use respiratory protection unless adequate local exhaust

ventilation is provided or exposure assessment demonstrates that exposures are within recommended exposure guidelines.

Filter type : Particulates type (P)

## **SECTION 9: Physical and chemical properties**

### 9.1 Information on basic physical and chemical properties

Appearance : paste

Colour : in accordance with the product description

Odour : slight

according to Regulation (EC) No. 1907/2006



## **DOW CORNING(R) FIRESTOP 400 SEALANT**

П

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

Odour Threshold : No data available

pH : Not applicable

Melting point/freezing point : No data available

Initial boiling point and boiling

range

Not applicable

Flash point : Not applicable

Evaporation rate : Not applicable

Flammability (solid, gas) : Not classified as a flammability hazard

Upper explosion limit / Upper

flammability limit

No data available

Lower explosion limit / Lower

flammability limit

No data available

Vapour pressure : Not applicable

Relative vapour density : No data available

Relative density : 1.5

Solubility(ies)

Water solubility : No data available

Partition coefficient: n-

octanol/water

No data available

Auto-ignition temperature : No data available

Decomposition temperature : No data available

Viscosity

Viscosity, dynamic : Not applicable

Explosive properties : Not explosive

Oxidizing properties : The substance or mixture is not classified as oxidizing.

9.2 Other information

Molecular weight : No data available

Self-ignition : The substance or mixture is not classified as pyrophoric. The

substance or mixture is not classified as self heating.

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

## **SECTION 10: Stability and reactivity**

### 10.1 Reactivity

Not classified as a reactivity hazard.

### 10.2 Chemical stability

Stable under normal conditions.

### 10.3 Possibility of hazardous reactions

Hazardous reactions : Use at elevated temperatures may form highly hazardous

compounds.

Can react with strong oxidizing agents.

Hazardous decomposition products will be formed at elevated

temperatures.

10.4 Conditions to avoid

Conditions to avoid : None known.

10.5 Incompatible materials

Materials to avoid : Oxidizing agents

10.6 Hazardous decomposition products

Thermal decomposition : Formaldehyde

## **SECTION 11: Toxicological information**

## 11.1 Information on toxicological effects

Information on likely routes of : Skin contact exposure Ingestion

Eye contact

## **Acute toxicity**

Not classified based on available information.

### Components:

## 5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Acute oral toxicity : LD50 (Rat): 64 mg/kg

Acute inhalation toxicity : LC50 (Rat): 0.171 mg/l

Exposure time: 4 h

Test atmosphere: dust/mist

Assessment: Corrosive to the respiratory tract.

Acute dermal toxicity : LD50 (Rat): 87.12 mg/kg

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

### Skin corrosion/irritation

Not classified based on available information.

#### Components:

### 5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Result: Corrosive after 3 minutes to 1 hour of exposure

Remarks: Based on harmonised classification in EU regulation 1272/2008, Annex VI

#### Serious eye damage/eye irritation

Not classified based on available information.

### **Components:**

### 5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Result: Irreversible effects on the eye

Remarks: Based on harmonised classification in EU regulation 1272/2008, Annex VI

### Respiratory or skin sensitisation

### Skin sensitisation

Not classified based on available information.

## Respiratory sensitisation

Not classified based on available information.

### Components:

## 5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Test Type: Buehler Test Exposure routes: Skin contact

Species: Guinea pig Result: positive

Assessment: Probability or evidence of high skin sensitisation rate in humans

### Germ cell mutagenicity

Not classified based on available information.

### Carcinogenicity

Not classified based on available information.

## Reproductive toxicity

Not classified based on available information.

## STOT - single exposure

Not classified based on available information.

### STOT - repeated exposure

Not classified based on available information.

### **Aspiration toxicity**

Not classified based on available information.

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

## **SECTION 12: Ecological information**

### 12.1 Toxicity

### **Components:**

5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Toxicity to fish LC50 (Oncorhynchus mykiss (rainbow trout)): 0.19 mg/l

Exposure time: 96 h

Toxicity to daphnia and other :

aquatic invertebrates

EC50 (Daphnia magna (Water flea)): 0.16 mg/l

Exposure time: 48 h

Toxicity to algae ErC50 (Skeletonema costatum (marine diatom)): 0.0052 mg/l

Exposure time: 48 h

NOEC (Skeletonema costatum (marine diatom)): 0.00049 mg/l

Exposure time: 48 h

M-Factor (Acute aquatic tox-

icity)

100

Toxicity to fish (Chronic tox-

icity)

NOEC: 0.02 mg/l Exposure time: 36 d

Species: Oncorhynchus mykiss (rainbow trout)

Toxicity to daphnia and other : aquatic invertebrates (Chron-

NOEC: 0.10 mg/l Exposure time: 21 d

ic toxicity)

Species: Daphnia magna (Water flea)

M-Factor (Chronic aquatic

toxicity)

: 100

### 12.2 Persistence and degradability

### **Components:**

5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Biodegradability Result: Not readily biodegradable.

> Biodegradation: 62 % Exposure time: 28 d

Method: OECD Test Guideline 301B

### 12.3 Bioaccumulative potential

### **Components:**

5-Chloro-2-methyl-3(2H)-isothiazolone, mixt. with 2-methyl-3(2H)-isothiazolone:

Partition coefficient: n-

octanol/water

log Pow: < 1

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

### 12.4 Mobility in soil

No data available

### 12.5 Results of PBT and vPvB assessment

Not relevant

#### 12.6 Other adverse effects

No data available

## **SECTION 13: Disposal considerations**

#### 13.1 Waste treatment methods

Product : Dispose of in accordance with local regulations.

According to the European Waste Catalogue, Waste Codes

are not product specific, but application specific.

Waste codes should be assigned by the user, preferably in

discussion with the waste disposal authorities.

Contaminated packaging : Empty containers should be taken to an approved waste han-

dling site for recycling or disposal.

If not otherwise specified: Dispose of as unused product.

### **SECTION 14: Transport information**

#### 14.1 UN number

Not regulated as a dangerous good

### 14.2 UN proper shipping name

Not regulated as a dangerous good

## 14.3 Transport hazard class(es)

Not regulated as a dangerous good

## 14.4 Packing group

Not regulated as a dangerous good

### 14.5 Environmental hazards

Not regulated as a dangerous good

### 14.6 Special precautions for user

Not applicable

### 14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Remarks : Not applicable for product as supplied.

## **SECTION 15: Regulatory information**

## 15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, Not applicable

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

 Version
 Revision Date:
 SDS Number:
 Date of last issue: 10.11.2016

 1.5
 28.04.2017
 1340635-00006
 Date of first issue: 12.02.2015

preparations and articles (Annex XVII)

REACH - Candidate List of Substances of Very High : Not applicable

Concern for Authorisation (Article 59).

Regulation (EC) No 1005/2009 on substances that de- : Not applicable

plete the ozone layer

Regulation (EC) No 850/2004 on persistent organic pol-

lutants

Regulation (EC) No 649/2012 of the European Parliament and the Council concerning the export and import

of dangerous chemicals

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

Not applicable

Not applicable

Not applicable

Other regulations:

Take note of Directive 92/85/EEC regarding maternity protection or stricter national regulations, where applicable.

The components of this product are reported in the following inventories:

REACH : All ingredients (pre-)registered or exempt.

## 15.2 Chemical safety assessment

A Chemical Safety Assessment has not been carried out.

### **SECTION 16: Other information**

## **Full text of H-Statements**

H301 : Toxic if swallowed.

H310 : Fatal in contact with skin.

H314 : Causes severe skin burns and eye damage.

H317 : May cause an allergic skin reaction.

H318 : Causes serious eye damage.

H330 : Fatal if inhaled.

H400 : Very toxic to aquatic life.

H410 : Very toxic to aquatic life with long lasting effects.

### Full text of other abbreviations

Acute Tox. : Acute toxicity

Aquatic Acute : Acute aquatic toxicity
Aquatic Chronic : Chronic aquatic toxicity
Eye Dam. : Serious eye damage
Skin Corr. : Skin corrosion
Skin Sens. : Skin sensitisation

according to Regulation (EC) No. 1907/2006



## DOW CORNING(R) FIRESTOP 400 SEALANT WHITE

Version Revision Date: SDS Number: Date of last issue: 10.11.2016 1.5 28.04.2017 1340635-00006 Date of first issue: 12.02.2015

ADN - European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways; ADR - European Agreement concerning the International Carriage of Dangerous Goods by Road; AICS - Australian Inventory of Chemical Substances; ASTM - American Society for the Testing of Materials; bw - Body weight; CLP - Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DSL - Domestic Substances List (Canada); ECHA - European Chemicals Agency; EC-Number - European Community number; ECx -Concentration associated with x% response; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx -Concentration associated with x% growth rate response; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; n.o.s. - Not Otherwise Specified; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RID - Regulations concerning the International Carriage of Dangerous Goods by Rail; SADT - Self-Accelerating Decomposition Temperature; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TRGS - Technical Rule for Hazardous Substances; TSCA - Toxic Substances Control Act (United States); UN - United Nations; vPvB - Very Persistent and Very Bioaccumulative

#### **Further information**

Sources of key data used to compile the Safety Data Sheet

Internal technical data, data from raw material SDSs, OECD eChem Portal search results and European Chemicals Agency, http://echa.europa.eu/

Items where changes have been made to the previous version are highlighted in the body of this document by two vertical lines.

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and shall not be considered a warranty or quality specification of any type. The information provided relates only to the specific material identified at the top of this SDS and may not be valid when the SDS material is used in combination with any other materials or in any process, unless specified in the text. Material users should review the information and recommendations in the specific context of their intended manner of handling, use, processing and storage, including an assessment of the appropriateness of the SDS material in the user's end product, if applicable.

GB / EN