



SAFETY DATA SHEET

Industrial Heat Shield

According to Regulation (EC) No 1907/2006

1 IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME	Industrial Heat Shield
PRODUCT NO.	A796TF
APPLICATION	Speciality Paint
SUPPLIER	Plasti-Kote Ltd. PO Box 867, Pampisford, Cambridge, CB22 3XP T : 44 (0) 1223 836400 F : 44 (0) 1223 836686 sds@plasti-kote.co.uk
EMERGENCY TELEPHONE	+44(0)1223 836400 (08:30am to 16:00pm Monday-Friday)

2 HAZARDS IDENTIFICATION

Extremely flammable. Repeated exposure may cause skin dryness or cracking. Vapours may cause drowsiness and dizziness. Irritating to eyes. Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

CLASSIFICATION Xi;R36. F+;R12. R52/53, R66, R67.

ENVIRONMENT

The product contains a substance which is toxic to aquatic organisms and which may cause long term adverse effects in the aquatic environment.

PHYSICAL AND CHEMICAL HAZARDS

Pressurised container: Must not be exposed for temperatures above 50°C. The product is extremely flammable, and explosive vapour/air mixtures may be formed even at normal room temperatures.

HUMAN HEALTH

In high concentrations, vapours and spray mists are narcotic and may cause headache, fatigue, dizziness and nausea.

3 COMPOSITION/INFORMATION ON INGREDIENTS

Industrial Heat Shield

Name	EC No.	CAS-No.	Content	Classification
ACETONE	200-662-2	67-64-1	30-60%	F;R11 Xi;R36 R66 R67
ISOBUTYL ACETATE	203-745-1	110-19-0	10-30%	F;R11 R66
BUTANE	203-448-7	106-97-8	10-30%	F+;R12
A MIXTURE OF MIXED LINEAR AND BRANCHED C6-ALKYL ACETATES	421-230-1	88230-35-7	1-5%	N;R51/53
XYLENE	215-535-7	1330-20-7	1-5%	R10 Xn;R20/21 Xi;R38
BUTANOL-norm	200-751-6	71-36-3	1-5%	R10 Xn;R22 Xi;R37/38,R41 R67
SOLVENT NAPHTHA (PETROLEUM), LIGHT ALIPHATIC	265-192-2	64742-89-8	1-5%	Xn;R65. Xi;R38. F;R11. N;R51/53. R67.
AMORPHOUS SILICA		112926-00-8	< 1%	Xi;R37.
TALC	238-877-9	14807-96-6	< 1%	-
CARBON BLACK	215-609-9	1333-86-4	< 1%	-

The Full Text for all R-Phrases are Displayed in Section 16

4 FIRST-AID MEASURES

GENERAL INFORMATION

Move the exposed person to fresh air at once.

INHALATION

Move the exposed person to fresh air at once. Perform artificial respiration if breathing has stopped. Keep the affected person warm and at rest. Get prompt medical attention.

INGESTION

Immediately rinse mouth and provide fresh air. Do not induce vomiting. Get medical attention if any discomfort continues.

SKIN CONTACT

Wash skin with soap and water. Get medical attention if any discomfort continues.

EYE CONTACT

Immediately rinse with water. Continue to rinse for at least 15 minutes. Make sure to remove any contact lenses from the eyes before rinsing. Get medical attention promptly if symptoms occur after washing.

5 FIRE-FIGHTING MEASURES

EXTINGUISHING MEDIA

Water spray, foam, dry powder or carbon dioxide.

SPECIAL FIRE FIGHTING PROCEDURES

Use water spray to reduce vapours. Aerosol cans may explode in a fire. Cool aerosol containers exposed to heat with water spray and remove container, if no risk is involved.

UNUSUAL FIRE & EXPLOSION HAZARDS

Extremely flammable. Forms explosive mixtures with air. May explode in a fire. Vapours are heavier than air and may spread near ground to sources of ignition.

SPECIFIC HAZARDS

Pressurised container: Must not be exposed for temperatures above 50°C.

6 ACCIDENTAL RELEASE MEASURES

PERSONAL PRECAUTIONS

Ensure suitable personal protection (including respiratory protection) during removal of spillages in a confined area.

ENVIRONMENTAL PRECAUTIONS

Avoid discharge into drains.

Industrial Heat Shield

SPILL CLEAN UP METHODS

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers. Provide ventilation and confine spill. Do not allow runoff to sewer.

7 HANDLING AND STORAGE

USAGE PRECAUTIONS

Keep away from heat, sparks and open flame. Read and follow manufacturer's recommendations. Avoid inhalation of vapours and spray mists. Do not spray on a naked flame or any incandescent material. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited. Use explosion proof electric equipment.

STORAGE PRECAUTIONS

Extremely flammable. Store at moderate temperatures in dry, well ventilated area. Keep away from heat, sparks and open flame. Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.

8 EXPOSURE CONTROLS/PERSONAL PROTECTION

Name	Std	TWA - 8 hrs		STEL - 15 min		Notes
ACETONE	WEL	500 ppm	1210 mg/m3	1500 ppm	3620 mg/m3	
AMORPHOUS SILICA	WEL		2,4 mg/m3			
BUTANE	WEL	600 ppm	1450 mg/m3	750 ppm	1810 mg/m3	
BUTANOL-norm	WEL			50 ppm	154 mg/m3	Sk
CARBON BLACK	WEL		3,5 mg/m3		7 mg/m3	
ISOBUTYL ACETATE	WEL	150 ppm	724 mg/m3	187 ppm	903 mg/m3	
TALC	WEL		1 mg/m3			
XYLENE	WEL	50 ppm	220 mg/m3	100 ppm	441 mg/m3	Sk

WEL = Workplace Exposure Limit.
Sk = Can be absorbed through skin.

INGREDIENT COMMENTS

WEL = Workplace Exposure Limits SUP = Supplier's recommendation.

PROCESS CONDITIONS

Provide eyewash station.

RESPIRATORY EQUIPMENT

No specific recommendation made, but respiratory protection must be used if the general level exceeds the Recommended Workplace Exposure Limit. In case of inadequate ventilation use suitable respirator. Chemical respirator with organic vapour cartridge.

HAND PROTECTION

For prolonged or repeated skin contact use suitable protective gloves. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material.

EYE PROTECTION

Wear approved chemical safety goggles where eye exposure is reasonably probable.

HYGIENE MEASURES

When using do not eat, drink or smoke. Wash promptly if skin becomes wet or contaminated.

9 PHYSICAL AND CHEMICAL PROPERTIES

APPEARANCE	Aerosol
COLOUR	Varying
ODOUR	of solvents

Industrial Heat Shield

PHYSICAL DATA	Information given concerns the major ingredient. 23 Flammable gas. Propane/Butane		
COMMENTS			
FLASH POINT (°C)	<-40°C	AUTO IGNITION TEMPERATURE (°C)	410-580
FLAMMABILITY LIMIT - LOWER(%)	1.8%	FLAMMABILITY LIMIT - UPPER(%)	9.5%

10 STABILITY AND REACTIVITY

STABILITY

Highly volatile.

CONDITIONS TO AVOID

Avoid heat, flames and other sources of ignition. Avoid exposure to high temperatures or direct sunlight.

11 TOXICOLOGICAL INFORMATION

SKIN CONTACT

Skin irritation is not anticipated when used normally. Repeated exposure may cause skin dryness or cracking.

EYE CONTACT

Irritating to eyes. Spray and vapour in the eyes may cause irritation and smarting.

HEALTH WARNINGS

In high concentrations, vapours are narcotic and may cause headache, fatigue, dizziness and nausea. Arrhythmia, (deviation from normal heart beat).

ROUTE OF ENTRY

Inhalation.

TARGET ORGANS

Central nervous system. Respiratory system, lungs.

MEDICAL SYMPTOMS

Narcotic effect. Vapours may cause drowsiness and dizziness.

12 ECOLOGICAL INFORMATION

ECOTOXICITY

The product contains substances which are toxic to aquatic organisms and which may cause long term adverse effects in the aquatic environment. Dangerous for the environment if discharged into watercourses. Do not allow to enter drains, sewers or watercourses.

13 DISPOSAL CONSIDERATIONS

GENERAL INFORMATION

Waste is classified as hazardous waste.

DISPOSAL METHODS

Make sure containers are empty before discarding (explosion risk). Do not puncture or incinerate even when empty. Dispose of waste and residues in accordance with local authority requirements.

WASTE CLASS

EWC : 08 01 11

14 TRANSPORT INFORMATION

Industrial Heat Shield



PROPER SHIPPING NAME	AEROSOLS (IATA: Aerosols, flammable)		
UN NO. ROAD	1950	ADR CLASS NO.	2, 5F
ADR CLASS	Class 2.1: Flammable gases.	ADR PACK GROUP	-
TUNNEL RESTRICTION CODE	(E)	ADR LABEL NO.	2.1
RID CLASS NO.	2, 5F	RID PACK GROUP	-
UN NO. SEA	1950	IMDG CLASS	2.1
IMDG PACK GR.	-	EMS	F-D, S-U
UN NO. AIR	1950	AIR CLASS	2.1
AIR PACK GR.	-		

15 REGULATORY INFORMATION

LABELLING



Irritant



Extremely Flammable

RISK PHRASES

R12	Extremely flammable.
R36	Irritating to eyes.
R52/53	Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

SAFETY PHRASES

A1	Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.
A2	Do not spray on a naked flame or any incandescent material.
S2	Keep out of the reach of children
S16	Keep away from sources of ignition - No smoking.
S23	Do not breathe vapour/spray.
S24/25	Avoid contact with skin and eyes.
S26	In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S51	Use only in well-ventilated areas.
S60	This material and its container must be disposed of as hazardous waste.

UK REGULATORY REFERENCES

Health and Safety at Work Act 1974. Chemicals (Hazard Information & Packaging) Regulations.

Industrial Heat Shield

EU DIRECTIVES

Dangerous Preparations Directive 1999/45/EC. Aerosol directive 75/324/EEC as amended by 94/01/EEC. Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

STATUTORY INSTRUMENTS

Control of Substances Hazardous to Health. The Aerosol Dispensers Regulations 1977 and 1997.

APPROVED CODE OF PRACTICE

Safety Data Sheets for Substances and Preparations. Classification and Labelling of Substances and Preparations Dangerous for Supply. British Aerosol Manufacturers Association Standard

16 OTHER INFORMATION

REVISION DATE 08-10-2009

RISK PHRASES IN FULL

NC	Not classified.
R10	Flammable.
R11	Highly flammable.
R12	Extremely flammable.
R20/21	Harmful by inhalation and in contact with skin.
R22	Harmful if swallowed.
R36	Irritating to eyes.
R37	Irritating to respiratory system.
R37/38	Irritating to respiratory system and skin.
R38	Irritating to skin.
R41	Risk of serious damage to eyes.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R65	Harmful: may cause lung damage if swallowed.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

DISCLAIMER

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.