## OPEN FRAME POWER SUPPLY 12VDC 200WATT

STONTRONICS: PSF-200-12

#### **Features:**

- Universal Input
- High Efficiency
- 3 Year Warranty
- Efficiency Level VI





#### **Description:**

The 200W open frame power supply range has been specially designed to offer high efficiency, long life and high reliability for use in a variety of applications. Each model is approved to CE, CB, UL and comes with a 3 year warranty.

SPECIFICATION		
Part Number		PSF-200-12
DC Voltage		12V
Rated Current		16.6A
Current Range		0~16A
Ripple & Noise	0~70°C	<120mV
	-20~0°C	<200mV
Voltage ADJ. Range		±10% of rated output voltage,
Line Regulation		±0.5%
Load Regulation		±2.0%
Set-up Time		≤2S (230VAC input, Full load) & ≤4S (115VAC input, Full load)
Hold up Time		≥16mS/150W 10mS/200W (115 / 230VAC IN AT FULL LOAD)
Temperature Coefficient		±0.03%/
Overshoot and Undershoot		<5.0%
Input voltage range		90Vac~264Vac,127Vdc~370Vdc
Input frequency range		47Hz~63Hz
Efficiency 115Vacinput		89%
AC Current (max.)		3A
Inrush current		<50A@230Vac <30A@115Vac Cold start
Leakage Current		≤3.5mA
Over Load		125%-150% of rated output voltage, Hiccup mode, auto recovery
Over Voltage		125%-150% of rated output voltage, Hiccup mode, auto recovery
Short Circuit		Long-term mode, auto recovery
Operating amb. Temp. & Hum.		-20°C~70°C; 20%~90%RH No condensing
Storage Temp. & Hum.		-40°C~85°C; 10%~95%RH No condensing
Safety Standards		UL60950-1; EN60950-1: 2006
Withstand Voltage		Primary-Secondary:3.0KVa; ≤10mA. Primary-PG:1.5KVac; ≤10mA. Secondary-PG:0.5KVDC; ≤10mA.
Isolation Resistance		≥10M ohms
MTBF		More than 100,000Hrs
Dimension (L*W*	H)	128×76.5×34.6 mm

# OPEN FRAME POWER SUPPLY 12VDC 200WATT



STONTRONICS: PSF-200-12

### **Diagrams**

