

Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Aqua Paint Marker Pen
Yellow
Bulk

1.2. Relevant identified uses of the substance or mixture and uses advised against

Paints

1.3. Details of the supplier of the safety data sheet

CRC Industries UK Ltd.
Ambersil House - Wylds Road
Castlefield Industrial Estate
TA6 4DD Bridgwater Somerset
United Kingdom
Tel.: +44 1278 727200
Fax.: +44 1278 425644
E-mail : hse.uk@crcind.com

1.4. Emergency telephone number

(+44)(0)1278 72 7200

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008

Physical:	Not classified
Health:	Not classified
Environment:	Not classified
Other hazards :	Contains: 1,2-benzisothiazol-3(2H)-one May produce an allergic reaction.

Classification according to 67/548/EEC or 1999/45/EC:

Health:	Not classified
Physical:	Not classified
Environment:	Not classified



Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

Other hazards : Not classified

2.2. Label elements

Labelling according to Regulation (EC) No 1272/2008

None

Supplemental Hazard information:

Contains:

1,2-benzisothiazol-3(2H)-one
May produce an allergic reaction.

2.3. Other hazards

None

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable.

3.2. Mixtures

Hazardous ingredient	CAS-nr.	EC-nr	w/w %	symbol	R-phrases*	Notes
ethanediol; ethylene glycol	107-21-1	203-473-3	1-5	Xn	22	A
1,2-benzisothiazol-3(2H)-one	2634-33-5	220-120-9	<0.05	Xn,N	22-38-41-43-50	

Explanation notes

A : substance with Community workplace exposure limit

Hazardous ingredient	Registration number	CAS-nr.	EC-nr	w/w %	Hazard Class and Category	Hazard statement	Notes
ethanediol; ethylene glycol	01-2119456816-28	107-21-1	203-473-3	1-5	Acute Tox. 4	H302	A
1,2-benzisothiazol-3(2H)-one		2634-33-5	220-120-9	<0.05	Acute Tox. 4, Skin Irrit. 2, Eye Dam. 1, Skin Sens. 1, Aquatic Acute 1	H302,H315,H318,H317,H400	

Explanation notes

A : substance with Community workplace exposure limit

(* Explanation phrases : see chapter 16)

SECTION 4: First aid measures

4.1. Description of first aid measures

Contact with eyes : If substance has got into eyes, immediately wash out with plenty of water for several minutes

Seek medical attention if irritation persists

Contact with skin : Wash with water and soap.

Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

Inhalation :	Seek medical attention if irritation persists Fresh air, keep warm and at rest.
Ingestion :	Seek medical attention if ill effects occur If swallowed do not induce vomiting Seek medical advice

4.2. Most important symptoms and effects, both acute and delayed

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	May produce an allergic reaction. May cause irritation. Symptoms : redness and pain
Eye contact :	May cause irritation. Symptoms : redness and pain

4.3. Indication of any immediate medical attention and special treatment needed

General Advice :	If you feel unwell, seek medical advice (show the label where possible) If symptoms persist always call a doctor
-------------------------	---

SECTION 5: Firefighting measures

5.1. Extinguishing media

foam, carbon dioxide or dry agent

5.2. Special hazards arising from the substance or mixture

Forms hazardous decomposition products
CO,CO2

5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water
In case of fire, do not breathe fumes

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources
Ensure adequate ventilation
Wear suitable protective clothing including eye/face protection.

6.2. Environmental precautions

Do not allow to enter public sewers and watercourses



Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

If polluted water reaches drainage systems or water courses, immediately inform appropriate authorities

6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material

6.4. Reference to other sections

For further information see section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well ventilated areas
Avoid contact with skin and eyes.
Wash thoroughly after use
Wear protective gloves/protective clothing/eye protection/face protection.

7.2. Conditions for safe storage, including any incompatibilities

Keep in a cool, dry, well ventilated place
Keep out of reach of children.

7.3. Specific end use(s)

Paints

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure limits :

Hazardous ingredient	CAS-nr.	method	
EU established exposure limits:			
ethanediol; ethylene glycol	107-21-1	TWA	20 ppm
		STEL	40 ppm
National established exposure limits, United Kingdom			
ethanediol; ethylene glycol	107-21-1	TWA	20 ppm
		STEL	40 ppm

8.2. Exposure controls

Control procedures :	Ensure adequate ventilation
Personal protection :	Take precautions to avoid contact with skin and eyes when handling the product.

Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

inhalation :	Ensure adequate ventilation In case of insufficient ventilation, wear suitable respiratory equipment.
recommended respiratory protection:	air purifying respirator equipped with ABEK type cartridge in combination with an oil proof solid and liquid particulate filter
hands and skin :	Wear suitable protective gloves against chemicals
Recommended gloves:	Nitrile
eyes :	Wear safety goggles.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Apperance : physical state :	Liquid.
colour :	Yellow.
odour :	Characteristic odor.
pH :	Not available.
Boiling point/range :	> 100 °C
Flash point :	> 100 °C
Evaporation rate :	Not available.
Explosion limits : upper limit :	Not available.
lower limit :	Not available.
Vapour pressure :	Not available.
Relative density :	Not available.
Solubility in water :	Soluble in water
Auto-ignition :	> 200 °C
Viscosity :	Not available.

9.2. Other information

SECTION 10: Stability and reactivity

10.1. Reactivity

No hazardous reactions known if used for its intended purpose

10.2. Chemical stability

Stable

10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

10.4. Conditions to avoid

Avoid overheating

10.5. Incompatible materials

Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

Strong oxidising agent

10.6. Hazardous decomposition products

CO,CO2

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Information on likely routes of exposure:

Inhalation :	Inhalation of solvent vapours may give rise to nausea, headaches and dizziness
Ingestion :	May cause gastrointestinal disturbances
Skin contact :	May cause irritation. May produce an allergic reaction.
Eye contact :	May cause irritation.

Toxicological data :

Hazardous ingredient	CAS-nr.	method	
ethanediol; ethylene glycol	107-21-1	LD50 oral rat	> 2000 mg/kg
		LD50 derm.rabit	> 10000 mg/kg

SECTION 12: Ecological information

12.1. Toxicity

Not classified

Ecotoxicological data:

No information available

12.2. Persistence and degradability

No experimental data available

12.3. Bioaccumulative potential

No experimental data available

12.4. Mobility in soil

Soluble in water

Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

12.5. Results of PBT and vPvB assessment

No information available

12.6. Other adverse effects

No information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product : This material and its container must be disposed of in a safe way.
Do not discharge into drains or the environment, dispose to an authorised waste collection point.
National regulations : Disposal should be in accordance with local, state or national legislation

SECTION 14: Transport information

14.1. UN number

UN-number : Not classified as hazardous for transport

14.2. UN proper shipping name

Proper shipping name: Not applicable.

14.3. Transport hazard class(es)

Class: Not applicable.
ADR/RID - Classification code: Not applicable.

14.4. Packing group

Packing group: Not applicable.

14.5. Environmental hazards

ADR/RID - Environmentally hazardous: No
IMDG - Marine pollutant: No
IATA/ICAO - Environmentally hazardous: No

14.6. Special precautions for user

IMDG - Ems: Not applicable.



Productname : Aqua Paint Marker Pen
Ref.Nr.: BDS001693_3_20150106 (EN)

Creationdate : 06.01.15 Version : 1.0
Replaces:

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

15.2. Chemical safety assessment

No information available

SECTION 16: Other information

*Explanation risk-phrases: R22: Harmful if swallowed.
R38: Irritating to skin.
R41: Risk of serious damage to eyes.
R43: May cause sensitization by skin contact.
R50

*Explanation hazard statements: H302 : Harmful if swallowed.
H315 : Causes skin irritation.
H317 : May cause an allergic skin reaction.
H318 : Causes serious eye damage.
H400 : Very toxic to aquatic life.

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks, no part of these documents may be reproduced by any process without written permission from CRC.