



Pre-filter



Main-filter

STANDARD FILTER-SET ZEROSMOG GUARD

ORDER NO: FT91000048

Compatible with the following filtration units:

- > ZeroSmog Guard Light
- > ZeroSmog Guard
- > ZeroSmog Guard 2

Clean Air is a Worker's Right!

Breathe easy in a healthy production environment all day long.

The new Weller ZeroSmog Guard under-the-bench fume extraction units

+ KEY FEATURES

TECHNICAL DATA ZEROSMOG GUARD PRE-FILTER
FILTRATION EFFICIENCY ePM1-75 (ISO 16890)
PHYSICAL DIMENSIONS: 23 x 23cm (9" x 9")
MATERIAL COMPOSITION Fibreglass mat
INSTALLATION GUIDELINES Wear suitable PPE. Access pre-filter mat via the door on the top of the ZeroSmog Guard unit Exercise care to minimise release of absorbed particles install new filter mat.
RECOMMENDED REPLACEMENT INTERVAL As application/usage requires (e.g. once per month)
PACKAGING UNIT 5
Subject to technical alterations and amendments.

TECHNICAL DATA GUARD MAIN FILTER
COMPOSITION HEPA particle & Activated Carbon Gas Media
Physical Dimensions: 265 x 265 x 155mm (10,4 x 10,4 x 6,1")
WEIGHT 2120g (74.8oz)
PARTICLE FILTER PORTION PARTICLE FILTRATION EFFICIENCY HEPA H13 (99,95% of MPPS)
HEPA SURFACE AREA 1.5m ²
GAS FILTER PORTION Composition: Activated Carbon granules
GAS MEDIA MASS 1.0 kg
INSTALLATION GUIDELINES Wear suitable PPE. Loosen hold down straps of ZeroSmog Guard unit. Filter can be removed towards the side or the rear of the unit. Insert new filter Press down top cover whilst locking down hold down straps
RECOMMENDED REPLACEMENT INTERVAL As application/usage requires (e.g. 6 – 12 months)
RELEVANT STANDARDS ISO 16890 and EN 779:2019
DISPOSAL INSTRUCTIONS Consult the authorized waste manager for recovery and disposal operations.
STORAGE CONDITIONS 5-30°C (41-86°F), avoid sources of heat, humidity, radiation. Maximum shelf life of 2 years.
PACKAGING UNIT 1
Subject to technical alterations and amendments.

#PowerfulTogether

weller-tools.com

Weller® is a registered trademark of Apex Brands, Inc. © 2024 | Specifications subject to change without notice.



[More information](#)