

## **Material Safety Data Sheet**

### **Tesa 62992 Alcohol Wipe**

#### 1) Identification of the substance/preparation and the company

Product name:  
70% Alcohol Wipe

Company:  
tesa UK Ltd  
Yeomans Drive  
Blakelands, Milton Keynes  
MK14 5LS

#### 2) Composition/information on ingredients

An aqueous/alcoholic based liquid absorbed on to synthetic towelling sheets.

Ingredient	Einecs No	CAS No	% in product	Symbol	Risk
Propan-2-ol	200-661-7	67-63-0	70%	F, Xi	R11, R36, R67

#### 3) Hazard identification

Flammable  
Irritant to the eyes  
Vapour may cause drowsiness or dizziness

#### 4) First aid measures

Inhalation - Ensure patient has good supply of fresh air. If breathing is difficult, perform artificial respiration and obtain medical attention.  
Ingestion - Rinse mouth and provide fresh air. Do not induce vomiting. Drink fresh water.  
Skin contact - Remove the affected person from the source of the contamination. Remove any saturated clothing and wash the skin with plenty of water.  
Eye contact - Rinse thoroughly with plenty of water. If irritation persists, obtain medical attention.



#### 5) Fire fighting measures

The product is flammable. The liquid portion is water soluble.

Suitable extinguishing media:

Water

Alcohol resistant foam

Carbon dioxide

Dry powder

#### 6) Accidental release measures

Avoid contact with eyes.

Clean up procedure: Ensure good ventilation. Contain and soak up with non-combustible absorbent material and place into sealed containers. Do not allow to enter waterways or drains.

#### 7) Handling & storage

Keep away from oxidising agents, heat, sparks and open flames. Avoid spillage, skin and eye contact.

#### 8) Exposure controls/personal protection

If large quantities are being handled or exposure is lengthy or repeated, wear goggles and gloves and ensure that there is good ventilation.

No special precautions are required under normal conditions of use.

#### 9) Physical & chemical properties

Appearance: Liquid absorbed on to towelling.

Odour: characteristic of isopropanol (propan-2-ol).

Specific gravity: ~ 0.86 @ 20°C

Flash point: Not measured, but expected to be low enough to be classed as highly flammable.

pH – approximately neutral.

#### 10) Stability & reactivity

Stable and non reactive. Avoid strong oxidising agents, heat, sparks, and open flames.

#### 11) Toxicological information

LD 50: Not measured

LC 50: Not measured

The isopropanol (propan-2-ol) contained in this product is irritating to the eyes and its vapour may cause drowsiness or dizziness if exposure is lengthy or repeated. However, this preparation is expected to be non toxic and non irritant under normal or reasonably foreseeable conditions of use.

---

A tesa Company

Registered in England No. 841180

Registered Office: as above



#### 12) Ecological information

Biodegradability: Not measured. The product is expected to be readily biodegradable.  
Fish toxicity: Not measured. Do not allow to enter soil, waterways or drains.

#### 13) Disposal considerations

Absorb in a non-combustible material and dispose of in accordance with local regulations.

#### 14) Transport information

When shipping bulk product, care should be taken to ensure compliance with local and national regulations, CHIP regulations and hazchem requirements. No special labelling is required for the finished product.

#### 15) Regulatory information

Risk phrases: (For Propan-2-ol))  
R11 Highly flammable  
R36 Irritating to eyes  
R67 Vapours may cause drowsiness or giddiness.

#### 16) Other information

Observe national and local legal requirements.

---

A tesa Company

Registered in England No. 841180  
Registered Office: as above