



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 10

Loctite Super Glue3 Minitrio Pasco

SDS No. : 590326
V001.1

Revision: 24.01.2018

printing date: 31.01.2020

Replaces version from: 13.01.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Loctite Super Glue3 Minitrio Pasco

Contains:

Ethyl 2-cyanoacrylate CAS-No. 7085-85-0

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Super glue

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Specific target organ toxicity - single exposure	Category 3
H335 May cause respiratory irritation.	
Target organ: respiratory tract irritation	

2.2. Label elements

Label elements (CLP):

Hazard pictogram:**Signal word:**

Warning

Hazard statement:H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.**Supplemental information**

EUH202 Cyanoacrylate. Danger. Bonds skin and eyes in seconds. Keep out of the reach of children.

Precautionary statement:P261 Avoid breathing vapours.
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P302+P352 IF ON SKIN: Wash with plenty of soap and water.
P501 Dispose of contents/container in accordance with national regulation.**2.3. Other hazards**Persons suffering from allergic reactions to acrylates should avoid contact with the product.
Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.**SECTION 3: Composition/information on ingredients****3.1. Substances****General chemical description:**

Adhesive

Base substances of preparation:

Cyanoacrylate

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Ethyl 2-cyanoacrylate 7085-85-0	230-391-5 01-2119527766-29	80- 100 %	Eye Irrit. 2 H319 STOT SE 3 H335 Skin Irrit. 2 H315

**For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.****SECTION 4: First aid measures****4.1. Description of first aid measures****General information:**

In case of adverse health effects seek medical advice.

Inhalation:

Move to fresh air, consult doctor if complaint persists.

Skin contact:

Do not pull bonded skin apart. It may be gently peeled apart using a blunt object such as a spoon, preferably after soaking in warm soapy water.

Cyanoacrylates give off heat on solidification. In rare cases a large drop will generate enough heat to cause a burn.

Burns should be treated normally after the adhesive has been removed from the skin.

If lips are accidentally stuck together apply warm water to the lips and encourage maximum wetting and pressure from saliva inside the mouth.

Peel or roll lips apart. Do not try to pull the lips apart with direct opposing action.

Eye contact:

If the eye is bonded closed, release eyelashes with warm water by covering with wet pad.

Cyanoacrylate will bond to eye protein and will cause periods of weeping which will help to debond the adhesive.

Keep eye covered until debonding is complete, usually within 1-3 days.

Do not force eye open. Medical advice should be sought in case solid particles of cyanoacrylate trapped behind the eyelid cause any abrasive damage.

Ingestion:

Ensure that breathing passages are not obstructed. The product will polymerise immediately in the mouth making it almost impossible to swallow. Saliva will slowly separate the solidified product from the mouth (several hours).

4.2. Most important symptoms and effects, both acute and delayed

Causes serious eye irritation.

SKIN: Redness, inflammation.

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

5.3. Advice for firefighters

Wear protective equipment.

Wear self-contained breathing apparatus.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective equipment.

Danger of slipping on spilled product.

Ensure adequate ventilation.

Avoid contact with skin and eyes.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Remove with liquid-absorbing material (sand, peat, sawdust).

Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Open and handle container with care.
Avoid skin and eye contact.
Ensure that workrooms are adequately ventilated.

Hygiene measures:

Do not eat, drink or smoke while working.
Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Keep container tightly sealed.
Avoid moisture.
For optimum shelf life store in original containers under refrigerated conditions at 2°C to 8°C.
Store in a cool, well-ventilated place.
Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

7.3. Specific end use(s)

Super glue

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Ethyl 2-cyanoacrylate 7085-85-0 [ETHYL CYANOACRYLATE]	0,3	1,5	Short Term Exposure Limit (STEL):		EH40 WEL

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Ethyl 2-cyanoacrylate 7085-85-0 [ETHYL CYANOACRYLATE]	0,2		Time Weighted Average (TWA):		IR_OEL

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Ethyl 2-cyanoacrylate 7085-85-0	Workers	Inhalation	Long term exposure - local effects		9,25 mg/m ³	
Ethyl 2-cyanoacrylate 7085-85-0	Workers	Inhalation	Long term exposure - systemic effects		9,25 mg/m ³	
Ethyl 2-cyanoacrylate 7085-85-0	General population	Inhalation	Long term exposure - local effects		9,25 mg/m ³	
Ethyl 2-cyanoacrylate 7085-85-0	General population	Inhalation	Long term exposure - systemic effects		9,25 mg/m ³	

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Suitable breathing mask when there is inadequate ventilation.

Combination filter: ABEKP (EN 14387)

This recommendation should be matched to local conditions.

Hand protection:

Recommended are gloves made from Nitril rubber (Material thickness >0,1 mm, Perforation time < 30s).Gloves should be replaced after each short time contact or contamination. Available at laboratory specialized trade or at pharmacies / chemist's shops.

In the case of longer contact protective gloves made from nitrile rubber are recommended according to EN 374.

material thickness > 0.4 mm

Perforation time > 30 minutes

In the case of longer and repeated contact please note that in practice the penetration times may be considerably shorter than those determined according to EN 374. The protective gloves must always be checked for their suitability for use at the specific workplace (e.g. mechanical and thermal stress, product compatibility, antistatic effects, etc.). The gloves must be replaced immediately at the first signs of wear and tear. The information provided by the manufacturers and given in the relevant trade association regulations for industrial safety must always be observed. We recommend that a hand care plan is drawn up in cooperation with a glove manufacturer and the trade association in accordance with the local operating conditions.

Eye protection:

Goggles which can be tightly sealed.

Protective eye equipment should conform to EN166.

Skin protection:

Suitable protective clothing

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid liquid colourless, slightly yellowish
Odor	pungent
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	> 150 °C (> 302 °F)
Flash point	80 °C (176 °F); Supplier method
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density (25 °C (77 °F))	0,55 - 1,55 g/cm ³
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable

Decomposition temperature	No data available / Not applicable
Viscosity (; 25 °C (77 °F))	20 - 1.200 mPa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Rapid exothermic polymerization will occur in the presence of water, amines, alkalis and alcohols.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

None known.

SECTION 11: Toxicological information

General toxicological information:

Persons suffering from allergic reactions to acrylates should avoid contact with the product.

11.1. Information on toxicological effects

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Ethyl 2-cyanoacrylate 7085-85-0	LD50	> 5.000 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Ethyl 2-cyanoacrylate 7085-85-0	LD50	> 2.000 mg/kg	rabbit	OECD Guideline 402 (Acute Dermal Toxicity)

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

Bonds skin in seconds. Considered to be of low toxicity: acute dermal LD50 (rabbit)>2000mg/kg
Due to polymerisation at the skin surface allergic reaction is unlikely to occur

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Ethyl 2-cyanoacrylate 7085-85-0	slightly irritating	24 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Liquid product will bond eyelids. In a dry atmosphere (RH<50%) vapours may cause irritation and lachrymatory effect

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Ethyl 2-cyanoacrylate 7085-85-0	irritating	72 h	rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Ethyl 2-cyanoacrylate 7085-85-0	not sensitising		guinea pig	not specified

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Ethyl 2-cyanoacrylate 7085-85-0	negative	bacterial reverse mutation assay (e.g Ames test)			OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Ethyl 2-cyanoacrylate 7085-85-0	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Ethyl 2-cyanoacrylate 7085-85-0	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure::

No data available.

Aspiration hazard:

No data available.

SECTION 12: Ecological information**General ecological information:**

Do not empty into drains, soil or bodies of water.

12.1. Toxicity**Toxicity (Fish):**

No data available.

Toxicity (Daphnia):

No data available.

Chronic toxicity to aquatic invertebrates

No data available.

Toxicity (Algae):

No data available.

Toxicity to microorganisms

No data available.

12.2. Persistence and degradability

Hazardous substances CAS-No.	Result	Test type	Degradability	Exposure time	Method
Ethyl 2-cyanoacrylate 7085-85-0		aerobic	57 %	28 d	OECD Guideline 301 D (Ready Biodegradability: Closed Bottle Test)

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

Hazardous substances CAS-No.	LogPow	Temperature	Method
Ethyl 2-cyanoacrylate 7085-85-0	0,776	22 °C	EU Method A.8 (Partition Coefficient)

12.5. Results of PBT and vPvB assessment

This mixture does not contain any substances that are assessed to be a PBT or vPvB.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of waste and residues in accordance with local authority requirements.

Disposal of uncleaned packages:

Use packages for recycling only when totally empty.

Waste code

080409

SECTION 14: Transport information**14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	3334

14.2. UN proper shipping name

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Aviation regulated liquid, n.o.s. (Cyanoacrylate ester)

14.3. Transport hazard class(es)

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	9

14.4. Packing group

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	III

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable
-----	----------------

RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	Primary packs containing less than 500ml are unregulated by this mode of transport and may be shipped unrestricted.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %
(VOCV 814.018 VOC regulation
CH)

15.2. Chemical safety assessment

A chemical safety assessment has been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H315 Causes skin irritation.
H319 Causes serious eye irritation.
H335 May cause respiratory irritation.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.

Annex - Exposure Scenarios:

Exposure Scenarios for ethyl 2-cyanoacrylate can be downloaded under the following link:
http://mymsds.henkel.com/mymsds/.470833.en.ANNEX_DE.15743123.0.DE.pdf
Alternatively they can be accessed on the internet site www.mymsds.henkel.com by entering number 470833.