

Model TGR-PP-12V-3000-B

Lithium-ion Rechargeable Battery Pack (12V & 5V outputs) Specification

Features and notes:

- Provides both a 12v 3A output and a 5V 2A output, suitable for powering a wide range of LED light bars, Flexible LED strip, Booth lighting, Bluetooth Speakers, Smartphones and Digital Cameras
- Ultra Compact Size (145 x 85 x 28mm) and high power density. Long life operation
- Over charge protection, Over discharge protection and short circuit protection
- · Includes UK charger and connection cable
- Please turn switch to 'I' when charging. The built in LED indicator will change from Red to Green once the battery is fully charged
- Indoor use only









Compatible: LED strip light products, CCTV Camera, IP Camera , LED Panel, Amplifier, Modern, Speaker, etc



Small and light, easy to carry





1. 前言 Preface

This specification describes the type and size, performance, technical characteristics, warning and caution of the 11.1V Lithium-ion Battery pack. The specification only applies to 11.1V Lithium-ion Battery pack supplied by **Tiger Power Supplies**

2. 产品应用说明图示:Application picture:





Operation guidance

OPERATION SURVAINED

1. Power ON and OFF

ON: Push switch to Position "I" to make power on

OFF: Push switch to Position "O" to make power off

2.Capacity display(Fuel Gauge): There are 5 power indicators, Push the switch to Position "I" to make battery power on.

The power and capacity indicator lights will be lighted.

TIGER

How to charge the power bank

- 1. Connect the AC-DC charger to the power socket(100-240V available) 2. Push the switch of the power bank to position" I" to make the charging
- circuit breakover.

 3. Connect the power bank to the AC-DC charger
- 4. The LED indicator of the AC-DC charger showing RED means the
- charging process is working.

 The LED indicator of the AC-DC charger showing GREEN means the charging process has completed or the charging circuit is open.

 5. The LED indicator of the AC-DC charger will change from RED to
- GREEN while the power bank is charged with 95% of the full.

 6. After the unit is fully charged, please remove the AC wall charger in time.

 7. Full charge time (estimated)=Capacity of power bank / output current of charger.

Compatible with

Compatible with LED strip light products, CCTV Camera, IP Camera, Telescopes, LED Panel, Amplifier, Modem, Car DVR, Speaker, mobile phone, breast pump portable and most 12V devices, etc.

1x DC 5.5x2.1mm 1 female to 2 male power splitter cable

1x 12.6V AC-DC charger

www. Tiger Power Supplies. com







12.6V AC-DC Charger

How to use the 1 Female to 2 Male cable





You can output while charging at the same time.





www.TigerPowerSupplies.com



4.通用电气指标 GENERAL AND ELECTRICAL REQUIREMENTS

Name	Value	Unit	Tolerance	Remarks
Charging Voltage				
DC 5521 Socket	12.6V	Vdc	Тур.	
Charging Current				
DC 5521 Socket				
@12.6V/1A DC	1	Α	Тур.	
Output Voltage				
DC 5521 Socket	9	Vdc	Min.	The output voltage is output directly
@12V OUT	11.1	Vdc	Тур	from 3S Li-lon battery by through the
	12.6	Vdc	Max.	PCM,So the output voltage is not constant.
USB-A@5V OUT	5	Vdc	Тур	The output voltage is constant
Output Current				
DC 5521 Socket				
@12V OUT	3	Α	Max.	
USB-A				
@5 OUT	2	Α	Max.	
Output Power				
DC 5521 Socket				
@12V OUT	36	W	Max.	
USB-A				
@5 OUT	10	W	Max	
Quiescent Power Consumption				
Power on@no load	0.09	W	Max.	
Power off	3	mW	Max.	

5.内置锂电池组及相关参数 Battery Pack Specifications

项目 Items	标准 Standard	备注 Comments
标称电压(V)		
Nominal voltage(V)	11.1V	
典型容量(Ah)		
Typical Capacity(Ah)	6000mAh	At 0.2C discharge rate
最小容量(Ah)		
Minimum Capacity (Ah)	5200mAh	At 0.2C discharge rate
工作温度范围℃	Charge:	0°C ~+45°C
Operation temperature range ${}^{\circ}\! \mathbb{C}$	Discharge:	-20℃~+75℃
存储温度范围℃	-10°C∼50°C	Recommended long-term
Storage temperature range °C	at half charged state	storage temperature is 15~25℃
储存环境湿度	RH: 65±20%	
Storage environment humidity		
环境湿度	≤85%RH	
Environment humidity		



6.内置保护电路电性能参数 PCM Electrical Characteristics(Ta=25℃)

NO.		标准 Standard	
1 Over o		过充电检测电压 Over charge protection voltage	12.7±0.05V
	过充电保护 Over discharge protection	过充电检测延时时间 Over charge protection delay time	0.5-2S
	·	过充电恢复电压 Over charge release voltage	12.4±0.5V
过放电保护 Ove discharge protection		过放电检测电压 Over discharge protection voltage	7.2V±0.1V
		过放电检测延时时间 Over discharge protection delay	80-200mS
	过放电保护 Over	过放电恢复电压 Over discharge release voltage	8.4±0.1V
		过电流检测电流 Over current protection current	6.5±1A
		过电流检测延时时间 Over current protection delay	40~100ms
		过流恢复 Over current release	充电激活或断开负载 Charging release or off-load
短路保护 3 short circuit protection		检测状态 Condition	外部短路 Outside short circuit
	short circuit	检测延时时间 Short circuit protection delay time	200~500us
	·	恢复状态 Release condition	充电激活或断开负载 Charging release or off-load
4	最大持续充放电电流 Max continuous charge current/discharge current		3A



7.外观及出货标准 Appearance And Delivery Condition

7.1 外观: 外壳表面无划痕、脏污; 外壳无漏打螺丝、壳离现象。。

Appearance: No scratches and smudginess on the surface of the shell. No missing screws and separation of the shell.

7.2 功能: 所有产品均要经过相关程序所要求的测试;

Functions: All products should be tested as required by concerned processes.

8.标准测试条件 Standard Test Conditions

8.1 Environmental Conditions 环境要求:

除非特殊说明,否则所有测试都在温度 25±2℃,湿度 65±20%,气压 86kPa~106kPa 的环境中测试 Unless otherwise specified, all tests stated in this specification are conducted at temperature 25±2℃and humidity 65±20%, air pressure 86kPa~106kPa.

8.2 Measuring Equipment 测量设备

a) 测量电压用的直流电压表精度不低于 0.5 级, 电压表内阻不低于 1kΩ/V;

Voltage is measured by D.C. voltmeter which precision is higher than 0.5 grade and self resistance is higher than $1k\Omega/V$;

b) 测量电流用的直流电表精度不低于 0.5 级;

Current is measured by D.C. meter which precision is higher than 0.5 grade;

- c) 测量温度用的温度计应具有适当的量程,其分度值不应大于 0.5℃ Temperature is measured by thermometer which has proper measuring range and division value is lower than 0.5℃:
- d)测量时间用的计时器应按时、分、秒分度,至少应具有±1%的准确度;

The timer used in measuring should be degreed in hour, minute and second, and should have degree of accuracy no more than ±1%.

8.3 测试条件 Test conditions

测试电池必须是本公司出厂时间不超过一个月,且电池未进行过五次以上充放电循环除非另有规定。本规格书中各项试验应在标准大气条件下进行:.温度: 25℃±2℃; 相对湿度: 65±20%。.

The cells to be tested should be new cells and within one month after shipment from our factory and the cells shall not be cycled over five times before the testing. All the tests in this specification shall be conducted in an ambient temperature of 25° C $\pm 2^{\circ}$ C under a humidity of $65\pm 20\%$, unless otherwise specified .



9.充放电特性 Characteristics

9.1 标准充电 Standard charge

用直流稳压电源以电压为12.6V,电流0.2C(A)恒流充电至电流降至0.02C(A)。

Charge the battery with DC stabilized power supply12.6V, constant-current 0.2C(A) current until current reach to 0.02C (A) .

9.2标准放电 standard discharge

以0.2C放电到电压7.2V或电池组截止为止。

Discharge the battery at 0.2C to 7.2V or the protection circuit come to protection, stop.

9.3电池电性能 Battery Electrical Performance

测试项目 Test Items	测试方法 Test Methods	测试标准 Test Standards
9.3.1 0.2C 放电性能	电池按 9.1 规定充电后,在 8.1 规定条件下	≥100% Nominal capacity
0.2C Discharging Performance	搁置 0.5~1 小时, 而后以 0.2 C(A)放电到	
	终止电压。	
	After standard charge, store the battery	
	for 0.5 \sim 1hr under 8.1 specified	
	conditions, then discharge at 0.2C(A) to	
N No. 11 AV	cut-off voltage.	
9.3.2 高温性能	电芯按 9.1 规定充电结束后,将电芯放入	≥95% Nominal capacity
High Temperature Performance	55℃±2℃的高温箱中恒温2小时,然后以	电池不爆炸不起火
	0.2 C(A)放电至终止电压,实验结束后,	The battery no explosion,no
	将电芯取出在8.1规定条件下搁置2小时,	fire
	然后目测电芯外观。	
	After standard charge, put the cells into	
	55°C±2°C high temperature box with	
	constant temperature for 2hrs, then	
	discharging at 0.2C(A) to cut-off voltage.	
	Then take the cell out, stored for 2hrs under 8.1 specified conditions, check the	
	exterior appearance.	
9.3.3 荷电保持能力	电芯按 9.1 规定充电结束后, 在 8.1 规定	荷电保持恢复率≥95%
Charge Retention	条件下搁置28天,再以0.2C放电至终止	capacity retention rate≥95%
	电压。	of minimum capacity
	After standard charge, store the cells for	, ,
	28 days under 8.1 specified conditions,	
	then discharge at 0.2C to cut-off voltage	
9.3.4 循环寿命	电芯按 9.1 规定充电后,搁置 0.5~1hr, 然	容量保持率≥80%
Cycle Life	后以 0.2C(A)放电至终止电压,放电结束	Capacity retention rate≥80%
	后,搁置 0.5~1hr,再进行下一个充放电	
	循环,连续循环 300 次。	
	1) standard charge at 0.2C(A),	
	2) rest 0.5~1 hr	
	3) discharge at 0.2C(A) to cut off voltage	
	4) rest 0.5~1hr	
	repeat the above steps until 300 cycles.	



10.注意事项 Cautions

- 10.1 充电电流不得超过本标准书中规定的最大充电电流。使用高于推荐值电流充电将可能引起电芯的充放电性能、机械性能和安全性能的问题,并可能会导致发热或泄漏。Charging current should be less than maximum charge current specified in the Product Specification. Charging with higher current than recommended value may cause damage to cell electrical, mechanical and safety performance and could lead to heat generation or leakage.
- **10.2** 放电电流不得超过本标准书规定的最大放电电流,大电流放电会导致电芯容量剧减并导致过热。The cell shall be discharged at less than the maximum discharge current specified in the Product Specification. High discharging current may reduce the discharging capacity significantly or cause over-heat.
- **10.3** 在电芯长期未使用期间,它可能会因其自放电特性而处于某种过放电状态。为防止过放电的发生,电池应定期充电,将其电压维持在 11.7V 至 12V 之间。 过放电会导致电芯性能、电池功能的丧失。It should be noted that the cell would be possible to be at a over-discharged state by its self-discharge characteristics in case the cell is not used for long time. In order to prevent over-discharging, the cell shall be charged periodically to maintain between 11.7V and 12V.Over-discharging may causes loss of cell performance, characteristics, or battery functions.
- **10.4** 电芯储存温度湿度请按照如下方法储存: The storage temperature and humidity of the battery are as below: -10 $^{\circ}$ $^{\circ}$ $^{\circ}$ within one month (一个月)0 $^{\circ}$ $^{\circ}$ $^{\circ}$ within 2 months (两个月)15 $^{\circ}$ $^{\circ}$ $^{\circ}$ for 3 months and above 3 months (≥3 个月) Humidity: 65±20%RH (湿度 65±20%RH).
- 10.5 严禁拆卸电池 Prohibition of disassembly.
- **10.6** 远离热源、火源; Do not expose the battery to extreme heat or flame.
- **10.7** 禁止反接电池组的正负极,禁止对电池组进行反充电; Do not reverse the polarity of the battery pack for any reason.
- **10.8**禁止将电池组投入水中或弄湿, Do not immerse the battery pack in water or sea water, or get it wet.
- **10.9** 用专用的充电器充电; Use a constant current, constant voltage (CC/CV) lithium-ion (Li+) battery charge controller.