

# 1572 ESD Kraftform Micro screwdriver for Microstix® screws, m x 40 mm

ESD Series



|                        |               |                               |              |
|------------------------|---------------|-------------------------------|--------------|
| <b>EAN:</b>            | 4013288181169 | <b>Size:</b>                  | 157x13x13 mm |
| <b>Part number:</b>    | 05030080001   | <b>Weight:</b>                | 13 g         |
| <b>Article number:</b> | 1572 ESD      | <b>Country of origin:</b>     | CZ           |
|                        |               | <b>Customs tariff number:</b> | 82054000     |

- Screwdriver for Microstix® screws
- ESD-safe tool thanks to surface resistance of  $\leq 10^9$  Ohm
- Ergonomic Kraftform handle for pleasant and low-fatigue working
- The Wera Black Point tip offers an exact fit and optimum corrosion protection
- Take it easy tool finder: colour coding according to profile and size
- Hexagonal anti-roll feature against rolling away

ESD-safe screwdriver for Microstix® screws. Dependable protection against electrostatic energy and associated damage. Comes with an ergonomic Kraftform Micro handle for pleasant and low-fatigue working and Black Point tip for high corrosion protection. "Take it easy" tool finder with colour coding according to profiles and size stamp - for simple and rapid accessing of the required tool.



## Web link

[https://products.wera.de/en/screwdrivers\\_esd\\_series\\_1572\\_esd.html](https://products.wera.de/en/screwdrivers_esd_series_1572_esd.html)

Wera - 1572 ESD  
05030080001 - 4013288181169

Wera Werkzeuge GmbH  
Korzerter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

### Wera ESD Tools



The requirements for ESD-safe screwdrivers are specified in the European standard DIN EN 61340-5-1. This standard also includes a handle that has to be out of a defined conductive material. The Wera products in the ESD series satisfy these standards and the even more stringent requirements demanded by some technology companies.

### High protection




The electric surface resistance of the Wera ESD material is  $\leq 10^{10}$  ohm. This securely protects components against electrostatic energy and associated damage.

### Kraftform Micro handle




Multi-component screwdriver handle for ergonomic working.

### The power zone




The power zone has integrated soft zones near the blade tip to ensure high torque transfer for loosening or tightening screws without losing contact with the screw.

### The precision zone



The precision zone directly above the blade gives the user a better feel for the right rotation angle during fine adjustment work.

### The fast-turning zone




The fast-turning zone just below the rotating cap allows rapid twisting.

### Rotating cap and fast-turning zone



The fast-turning zone just below the rotating cap allows rapid twisting. This makes time-consuming grip adjustments as with other conventional precision screwdrivers unnecessary.

### "Take it easy" Tool Finder



Screwdrivers with "Take it easy" tool finder: colour coding according to profile and size stamp.

### Web link

[https://products.wera.de/en/screwdrivers\\_esd\\_series\\_1572\\_esd.html](https://products.wera.de/en/screwdrivers_esd_series_1572_esd.html)

Wera - 1572 ESD

05030080001 - 4013288181169

Wera Werkzeuge GmbH

Korzerter Straße 21-25

D-42349 Wuppertal

Tel: +49 (0)2 02 / 40 45-0

E-Mail: [info@wera.de](mailto:info@wera.de)

Further versions in this product family:

|             |  | <br>mm | <br>mm | <br>mm | <br>inch |
|-------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|
| 05030080001 | m                                                                                 | 40                                                                                      | 97                                                                                      | 2.5                                                                                       | 1 9/16"                                                                                     |
| 05030081001 | 00                                                                                | 40                                                                                      | 97                                                                                      | 2.5                                                                                       | 1 9/16"                                                                                     |
| 05030082001 | F                                                                                 | 40                                                                                      | 97                                                                                      | 2.5                                                                                       | 1 9/16"                                                                                     |
| 05030083001 | 0                                                                                 | 40                                                                                      | 97                                                                                      | 2.5                                                                                       | 1 9/16"                                                                                     |
| 05030084001 | 1                                                                                 | 40                                                                                      | 97                                                                                      | 2.5                                                                                       | 1 9/16"                                                                                     |