

Safety Data Sheet according to (EC) No 1907/2006 as amended

Page 1 of 12

LOCTITE SI 5660 TB100ML

SDS No. : 357861 V006.0 Revision: 12.09.2023 printing date: 13.09.2023 Replaces version from: 25.01.2023

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SI 5660 TB100ML

1.2. Relevant identified uses of the substance or mixture and uses advised against Intended use: Silicone sealant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd Adhesives Wood Lane End HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000

SDSinfo.Adhesive@henkel.com

For Safety Data Sheet updates please visit our website https://mysds.henkel.com/index.html#/appSelection or www.henkel-adhesives.com.

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information Safety data sheet available on request.

2.3. Other hazards

None if used properly.

Following substances are present in a concentration \geq the concentration limit for depiction in Section 3 and fulfill the criteria for PBT/vPvB, or were identified as endocrine disruptor (ED):

This mixture does not contain any substances in a concentration \geq the concentration limit for depiction in Section 3 that are assessed to be a PBT, vPvB or ED.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No. EC Number REACH-Reg No.	Concentration	Classification	Specific Conc. Limits, M- factors and ATEs	Add. Information
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9 272-697-1 01-2119379499-16	1- < 5%	STOT RE 2, Inhalation, H373		

If no ATE values are displayed, please refer to LD/LC50 values in Section 11. For full text of the H - statements and other abbreviations see section 16 "Other information".

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation: Move to fresh air. If symptoms persist, seek medical advice.

Skin contact: Rinse with running water and soap. Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media Suitable extinguishing media:

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons: High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO2) and nitrogen oxides (NOx) can be released. Silicon dioxide

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid contact with skin and eyes. Ensure adequate ventilation. Wear protective equipment.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal. For large spills absorb onto inert absorbent material and place in sealed container for disposal. Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact. See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed. Wash hands before work breaks and after finishing work. Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Ensure good ventilation/extraction. Store in a cool, well-ventilated place. Refer to Technical Data Sheet Never allow product to get in contact with water during storage

7.3. Specific end use(s) Silicone sealant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

Ingredient [Regulated substance]	ррт	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [Dust, inhalable dust]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [Dust, respirable dust]		4	Time Weighted Average (TWA):		EH40 WEL

Occupational Exposure Limits

Valid for

Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [DUSTS NON-SPECIFIC]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [DUSTS NON-SPECIFIC]		10	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [Calcium carbonate]		10	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [Calcium carbonate]		4	Time Weighted Average (TWA):		IR_OEL

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls: Ensure good ventilation/extraction.

Respiratory protection: Ensure adequate ventilation. An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing. Protective eye equipment should conform to EN166.

Skin protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

. Information on basic physical and chemical p	noperues
Delivery form	paste
Colour	grey
Odor	ester-like
Physical state	liquid
Melting point	Not applicable, Product is a liquid
Solidification temperature	< -40 °C (< -40 °F)
Initial boiling point	> 200 °C (> 392 °F)
Flammability	The product is not flammable.
Explosive limits	Not applicable, The product is not flammable.
Flash point	> 93 °C (> 199.4 °F)
Auto-ignition temperature	Not applicable, The product is not flammable.
Decomposition temperature	Not applicable, Substance/mixture is not self-reactive, no organic peroxide and does not decompose under foreseen conditions of use
pH	Not applicable, Product is non-soluble (in water).
Viscosity (kinematic)	Currently under determination
Solubility (qualitative)	Polymerises in presence of water.
(20 °C (68 °F); Solvent: Water)	
Solubility (qualitative)	Not determined
(Solvent: Acetone)	
Partition coefficient: n-octanol/water	Not applicable
	Mixture
Vapour pressure	< 10 mm hg
(20 °C (68 °F))	
Density	1,45 g/cm3 None
(25 °C (77 °F))	
Relative vapour density:	>1
(20 °C)	
Particle characteristics	Not applicable
	Product is a liquid

9.2. Other information

Other information not applicable for this product

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with oxidants, acids and lyes

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use. Excessive heat.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

None if used for intended purpose.

SECTION 11: Toxicological information

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute oral toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Silica, surface treated with Hexamethyldisilazane -	LD50	> 5.000 mg/kg	rat	OECD Guideline 401 (Acute Oral Toxicity)
Nano 7631-86-9				

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances	Value	Value	Species	Method
CAS-No.	type			
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	LD50	> 5.000 mg/kg	rabbit	not specified

Acute inhalative toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Test atmosphere	Exposure time	Species	Method
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	LC50	> 5,01 mg/l	dust/mist	4 h	rat	OECD Guideline 436 (Acute Inhalation Toxicity: Acute Toxic Class (ATC) Method)

Skin corrosion/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances	Result	Exposure	Species	Method
CAS-No.		time		
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	not irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Silica, surface treated with	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Hexamethyldisilazane - Nano				
7631-86-9				

Respiratory or skin sensitization:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Test type	Species	Method
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	negative	bacterial reverse mutation assay (e.g Ames test)			OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	negative	in vitro mammalian chromosome aberration test			OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	negative	mammalian cell gene mutation assay			OECD Guideline 490 (In Vitro Mammalian Cell Gene Mutation Tests Using the Thymidine Kinase Gene)
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	negative	oral: gavage		rat	OECD Guideline 475 (Mammalian Bone Marrow Chromosome Aberration Test)

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure:

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Route of application	Exposure time / Frequency of treatment	Species	Method
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	NOAEL 491,5 mg/kg	oral: feed	6 months daily	rat	not specified
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	NOAEL 0,01 mg/kg	inhalation: dust	12 months 6 h/d, 5 d/wk	rat	not specified
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	NOAEL 0,01 mg/kg	inhalation: dust	12 months 6 h/d, 5 d/wk	monkey	not specified

Aspiration hazard:

No data available.

11.2 Information on other hazards

not applicable

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances	Value	Value	Exposure time	Species	Method
CAS-No.	type				
Silica, surface treated with	LC50	> 10.000 mg/l	96 h	Brachydanio rerio (new name:	OECD Guideline 203 (Fish,
Hexamethyldisilazane - Nano		-		Danio rerio)	Acute Toxicity Test)
7631-86-9					-

Toxicity (aquatic invertebrates):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Silica, surface treated with	EC50	> 1.000 mg/l	24 h	Daphnia magna	OECD Guideline 202
Hexamethyldisilazane - Nano					(Daphnia sp. Acute
7631-86-9					Immobilisation Test)

Chronic toxicity (aquatic invertebrates):

The table below presents the data of the classified substances present in the mixture.

CLC N	Value type	Value	Exposure time	Species	Method
Silica, surface treated with	NOEC	132,7 mg/l	21 d	Daphnia magna	OECD 211 (Daphnia
Hexamethyldisilazane - Nano					magna, Reproduction Test)
7631-86-9					

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances	Value	Value	Exposure time	Species	Method
CAS-No.	type				
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	EC50	> 173,1 mg/l	72 h	Desmodesmus subspicatus	OECD Guideline 201 (Alga, Growth Inhibition Test)
Silica, surface treated with Hexamethyldisilazane - Nano 7631-86-9	NOEC	173,1 mg/l	72 h	Desmodesmus subspicatus	OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity (microorganisms):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

The table below presents the data of the classified substances present in the mixture.

Hazardous substances	Value	Value	Exposure time	Species	Method
CAS-No.	type		_	-	
Silica, surface treated with	EC50	> 2.500 mg/l	3 h	activated sludge of a	OECD Guideline 209
Hexamethyldisilazane - Nano		-		predominantly domestic sewage	(Activated Sludge,
7631-86-9					Respiration Inhibition Test)

12.2. Persistence and degradability

No substance data available.

No data available.

12.3. Bioaccumulative potential

No data available.

12.4. Mobility in soil

No substance data available. No data available.

12.5. Results of PBT and vPvB assessment

The table below presents the data of the classified substances present in the mixture.

Hazardous substances CAS-No.	PBT / vPvB
Silica, surface treated with	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very
Hexamethyldisilazane - Nano	Bioaccumulative (vPvB) criteria.
7631-86-9	

12.6. Endocrine disrupting properties

not applicable

12.7. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal: Do not empty into drains / surface water / ground water. Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 10 Waste adhesives and sealants other than those mentioned in 08 04 09.

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

14.1. UN number or ID number Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR. 14.2. UN proper shipping name Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR. 14.3. Transport hazard class(es) Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR. 14.4. Packing group Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR. 14.5. **Environmental hazards** Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR. 14.6. Special precautions for user Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR. 14.7. Maritime transport in bulk according to IMO instruments not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixtureOzone Depleting Substance (ODS) (Regulation (EC) No 1005/2009):Not applicablePrior Informed Consent (PIC) (Regulation (EU) No 649/2012):Not applicablePersistent organic pollutants (Regulation (EU) 2019/1021):Not applicableVOC content< 3 %</td>

15.2. Chemical safety assessment

(2010/75/EC)

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows: H373 May cause damage to organs through prolonged or repeated exposure.

ED:	Substance identified as having endocrine disrupting properties
EU OEL:	Substance with a Union workplace exposure limit
EU EXPLD 1:	Substance listed in Annex I, Reg (EC) No. 2019/1148
EU EXPLD 2	Substance listed in Annex II, Reg (EC) No. 2019/1148
SVHC:	Substance of very high concern (REACH Candidate List)
PBT:	Substance fulfilling persistent, bioaccumulative and toxic criteria
PBT/vPvB:	Substance fulfilling persistent, bioaccumulative and toxic plus very persistent and very
	bioaccumulative criteria
vPvB:	Substance fulfilling very persistent and very bioaccumulative criteria

Further information:

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (SDSinfo.Adhesive@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.