



Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 11

LOCTITE SF 7500 known as Loctite 7500

SDS No. : 173216
V004.1

Revision: 21.05.2015

printing date: 16.07.2017

Replaces version from: 25.06.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SF 7500 known as Loctite 7500

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Rust preventor

1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44(0)8701906777

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Chronic hazards to the aquatic environment

H412 Harmful to aquatic life with long lasting effects.

Category 3

2.2. Label elements

Label elements (CLP):

Hazard statement:

H412 Harmful to aquatic life with long lasting effects.

Precautionary statement: Prevention

P273 Avoid release to the environment.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients**3.2. Mixtures****General chemical description:**

Primer

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
5-Nonylsalicylaldoxime 50849-47-3	256-798-8	> 1- < 2,5 %	Acute Tox. 4; Oral H302 Skin Irrit. 2 H315 Aquatic Acute 1 H400 Aquatic Chronic 1 H410
2-(2-Butoxyethoxy)ethanol 112-34-5	203-961-6 01-2119475104-44	1- < 2,5 %	Eye Irrit. 2 H319

For full text of the H - statements and other abbreviations see section 16 "Other information".
Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.**4.2. Most important symptoms and effects, both acute and delayed**

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures**Combustion behaviour:**

The product itself does not burn. Any fire extinguishing action should be appropriate to the surroundings. In case of fire product may cause hazard; see combustion gases / decomposition products.

5.1. Extinguishing media**Suitable extinguishing media:**

water, carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

None

5.3. Advice for firefighters

Fire fighters should wear positive pressure self-contained breathing apparatus (SCBA).

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed.

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

7.3. Specific end use(s)

Rust preventor

SECTION 8: Exposure controls/personal protection

8.1. Control parameters**Occupational Exposure Limits**Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m³	Value type	Short term exposure limit category / Remarks	Regulatory list
Diiron trioxide 1309-37-1 [ROUGE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Diiron trioxide 1309-37-1 [ROUGE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Diiron trioxide 1309-37-1 [IRON OXIDE, FUME (AS FE)]		5	Time Weighted Average (TWA):		EH40 WEL
Diiron trioxide 1309-37-1 [IRON OXIDE, FUME (AS FE)]		10	Short Term Exposure Limit (STEL):		EH40 WEL
2-(2-Butoxyethoxy)ethanol 112-34-5 [2-(2-BUTOXYETHOXY)ETHANOL]	15	101,2	Short Term Exposure Limit (STEL):		EH40 WEL
2-(2-Butoxyethoxy)ethanol 112-34-5 [2-(2-BUTOXYETHOXY)ETHANOL]	10	67,5	Time Weighted Average (TWA):		EH40 WEL
2-(2-Butoxyethoxy)ethanol 112-34-5 [2-(2-BUTOXYETHOXY)ETHANOL]	10	67,5	Time Weighted Average (TWA):	Indicative	ECTLV
2-(2-Butoxyethoxy)ethanol 112-34-5 [2-(2-BUTOXYETHOXY)ETHANOL]	15	101,2	Short Term Exposure Limit (STEL):	Indicative	ECTLV
Barium sulfate 7727-43-7 [BARIUM SULPHATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Barium sulfate 7727-43-7 [BARIUM SULPHATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, PARTICULATES]		10	Time Weighted Average (TWA):		EH40 WEL
Propane-1,2-diol 57-55-6 [PROPANE-1,2-DIOL, TOTAL VAPOUR AND PARTICULATES]	150	474	Time Weighted Average (TWA):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		7	Short Term Exposure Limit (STEL):		EH40 WEL
Carbon black 1333-86-4 [CARBON BLACK]		3,5	Time Weighted Average (TWA):		EH40 WEL

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
2-(2-Butoxyethoxy)ethanol 112-34-5	aqua (freshwater)					1 mg/L	
2-(2-Butoxyethoxy)ethanol 112-34-5	aqua (marine water)					0,1 mg/L	
2-(2-Butoxyethoxy)ethanol 112-34-5	aqua (intermittent releases)					3,9 mg/L	
2-(2-Butoxyethoxy)ethanol 112-34-5	sediment (freshwater)				4 mg/kg		
2-(2-Butoxyethoxy)ethanol 112-34-5	sediment (marine water)				0,4 mg/kg		
2-(2-Butoxyethoxy)ethanol 112-34-5	STP					200 mg/L	
2-(2-Butoxyethoxy)ethanol 112-34-5	oral				56 mg/kg		
2-(2-Butoxyethoxy)ethanol 112-34-5	soil				0,4 mg/kg		

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
2-(2-Butoxyethoxy)ethanol 112-34-5	Workers	Inhalation	Long term exposure - systemic effects		67,5 mg/m ³	
2-(2-Butoxyethoxy)ethanol 112-34-5	Workers	Dermal	Long term exposure - systemic effects		20 mg/kg bw/day	
2-(2-Butoxyethoxy)ethanol 112-34-5	general population	Inhalation	Acute/short term exposure - local effects		60,7 mg/m ³	
2-(2-Butoxyethoxy)ethanol 112-34-5	general population	Inhalation	Long term exposure - systemic effects		40,5 mg/m ³	
2-(2-Butoxyethoxy)ethanol 112-34-5	general population	Dermal	Long term exposure - systemic effects		50 mg/kg bw/day	
2-(2-Butoxyethoxy)ethanol 112-34-5	Workers	Inhalation	Acute/short term exposure - local effects		101,2 mg/m ³	
2-(2-Butoxyethoxy)ethanol 112-34-5	Workers	Inhalation	Long term exposure - local effects		67,5 mg/m ³	
2-(2-Butoxyethoxy)ethanol 112-34-5	general population	oral	Long term exposure - systemic effects		5 mg/kg bw/day	
2-(2-Butoxyethoxy)ethanol 112-34-5	general population	Inhalation	Long term exposure - local effects		40,5 mg/m ³	

Biological Exposure Indices:

None

8.2. Exposure controls:Respiratory protection:
Ensure adequate ventilation.

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; \geq 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid
Odor	grey
Odour threshold	characteristic
	No data available / Not applicable
pH	1,5 - 3,4
()	
Initial boiling point	Aqueous solution
Flash point	> 100 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	No data available / Not applicable
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Miscible
(Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

None if used properly.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

This material is considered to have low toxicity if swallowed.

Inhalative toxicity:

Due to the low volatility of the product there are no hazards associated with inhalation under normal conditions of use

Skin irritation:

Prolonged or repeated contact may cause skin irritation.

Eye irritation:

Prolonged or repeated contact may cause eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
2-(2- Butoxyethoxy)ethanol 112-34-5	LD50	> 2.000 mg/kg	oral		rat	EU Method B.1 (Acute Toxicity (Oral))

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
2-(2- Butoxyethoxy)ethanol 112-34-5	LD50	2.800 mg/kg	dermal		rabbit	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
2-(2- Butoxyethoxy)ethanol 112-34-5	not irritating		rabbit	Draize Test

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
2-(2- Butoxyethoxy)ethanol 112-34-5	moderately irritating		rabbit	

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
2-(2-Butoxyethoxy)ethanol 112-34-5	not sensitising	Guinea pig maximisation test	guinea pig	Magnusson and Kligman Method

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
2-(2-Butoxyethoxy)ethanol 112-34-5	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)

Repeated dose toxicity

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
2-(2-Butoxyethoxy)ethanol 112-34-5	LOAEL=51 - 65 mg/kg	oral: gavage	90 days 5 days/week	rat	
2-(2-Butoxyethoxy)ethanol 112-34-5	NOAEL=< 50 mg/kg	oral: gavage	90 days 5 days/week	rat	
2-(2-Butoxyethoxy)ethanol 112-34-5	NOAEL=2 - 6 ppm	inhalation	90 days	rat	
2-(2-Butoxyethoxy)ethanol 112-34-5	NOAEL=> 2.000 mg/kg		13 weeks 6 hours/day, 5 days/week	rat	

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.
Harmful to aquatic life with long lasting effects.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
2-(2-Butoxyethoxy)ethanol 112-34-5	LC50	1.300 mg/l	Fish	96 h	Lepomis macrochirus	OECD Guideline 203 (Fish, Acute Toxicity Test)
2-(2-Butoxyethoxy)ethanol 112-34-5	EC50	3.300 mg/l	Daphnia	24 h	Daphnia magna	
2-(2-Butoxyethoxy)ethanol 112-34-5	EC50	> 100 mg/l	Algae	96 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)
	NOEC	> 100 mg/l	Algae	96 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)

12.2. Persistence and degradability

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
---------------------------------	--------	-------------------------	---------------	--------

2-(2-Butoxyethoxy)ethanol 112-34-5	readily biodegradable	aerobic	> 60 %	OECD Guideline 301 C (Ready Biodegradability: Modified MITI Test (I))
---------------------------------------	-----------------------	---------	--------	-----------------------------------------------------------------------

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
2-(2-Butoxyethoxy)ethanol 112-34-5	0,56					

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
2-(2-Butoxyethoxy)ethanol 112-34-5	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

080111

SECTION 14: Transport information

- 14.1. UN number**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.2. UN proper shipping name**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.3. Transport hazard class(es)**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.4. Packaging group**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.5. Environmental hazards**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.6. Special precautions for user**
Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
- 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**
not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 5 %
(1999/13/EC)

VOC Paints and Varnishes (EU):

Product (sub)category: Primer
Phase I (from 1.1.2007): 540 g/l
max. VOC content: 72 g/l

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H302 Harmful if swallowed.

H315 Causes skin irritation.

H319 Causes serious eye irritation.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.