#### Regulation EC No 1907/2006 Art.31

ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Productname: Ref.Nr.: UDS000282 3 20210111 (EN) Replaces: UDS000282 20200615

# SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

#### **ADHESIVE MP 100**

Aerosol

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Adhesives

## 1.3. Details of the supplier of the safety data sheet

**CRC Industries UK Ltd.** Wylds Road **Castlefield Industrial Estate TA6 4DD Bridgwater Somerset United Kingdom** 

Tel.: +44 1278 727200 Fax.: +44 1278 425644 E-mail: hse.uk@crcind.com

#### 1.4. Emergency telephone number

(+44)(0)1278 72 7200 (office hours)

## **SECTION 2: Hazards identification**

# 2.1. Classification of the substance or mixture

## Classification according to Regulation (EC) No 1272/2008

Physical: Aerosols, category 1

Extremely flammable aerosol.

Pressurised container: May burst if heated.

Classification is based on test data.

Health: Carcinogenicity, category 2

Suspected of causing cancer. Skin irritation, category 2 Causes skin irritation. Eye irritation, category 2 Causes serious eye irritation.

Specific target organ toxicity - single exposure, category 3

May cause drowsiness or dizziness.

Classification based on calculation method. Not classified **Environment:** 



1/10

#### **CRC Industries UK Limited**

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

#### Regulation EC No 1907/2006 Art.31

Productname: ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Ref.Nr.: Replaces: UDS000282 20200615 UDS000282 3 20210111 (EN)

Classification based on calculation method.

#### 2.2. Label elements

## Labelling according to Regulation (EC) No 1272/2008

Product identifier: Contains:

dichloromethane; methylene chloride

Hazard pictogram(s):







Signal word: Danger

Hazard statement(s): H222: Extremely flammable aerosol.

H229: Pressurised container: May burst if heated.

H351: Suspected of causing cancer.

H315: Causes skin irritation.

H319: Causes serious eve irritation.

H336: May cause drowsiness or dizziness.

P102: Keep out of reach of children. Precautionary statement(s):

P210: Keep away from heat, hot surfaces, sparks, open flames and other

ignition sources. No smoking.

P211: Do not spray on an open flame or other ignition source.

P251: Do not pierce or burn, even after use.

P281: Use personal protective equipment as required.

P308/313: IF exposed or concerned: Get medical advice/attention.

P410/412: Protect from sunlight. Do not expose to temperatures exceeding

50°C/122°F.

P501-2: Dispose of contents/container to an authorised waste collection point.

#### 2.3. Other hazards

No information available

# SECTION 3: Composition/information on ingredients

#### 3.1. Substances

Not applicable.

#### 3.2. Mixtures

| Hazardous ingredient   | Registration number      | CAS-<br>nr.    | EC-<br>nr     |           | Hazard Class and Category  | Hazard statement              | Notes |
|--|--------------------------|----------------|---------------|-----------|--|-------------------------------|-------|
| Hydrocarbons,C3-4-rich,<br>petroleum distillate Petroleumgas<br>(1,3-butadiene < 0.1%) | 01-<br>2119485926-<br>20 | 68512-<br>91-4 | 270-<br>990-9 | 30-<br>60 | Press. Gas, Flam.<br>Gas 1                                       | H280,H220                     | K,G   |
| dichloromethane; methylene chloride  | 01-<br>2119480404-<br>41 | 75-09-2        | 200-<br>838-9 | 20-<br>50 | Carc. 2, Skin Irrit. 2,<br>Eye Irrit. 2, STOT SE<br>3, STOT RE 2 | H351,H315,H319,H335,H336,H373 |       |
| butanone; ethyl methyl ketone  | 01-<br>2119457290-       | 78-93-3        | 201-<br>159-0 | 0-<br>2.5 | Flam. Liq. 2, Eye Irrit. 2, STOT SF 3                            | H225,H319,H336                | Α     |



#### Regulation EC No 1907/2006 Art.31

ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Productname: Ref.Nr.: UDS000282 3 20210111 (EN) Replaces: UDS000282 20200615

43

#### **Explanation notes**

A: substance with Community workplace exposure limit

G: exempted from the obligation to register in accordance with art.2(7) of REACH Regulation No 1907/2006

K: not classified as carcinogen, less than 0.1% w/w 1,3-butadiene (Einecs-nr. 203-450-8)

(\* Explanation phrases : see chapter 16)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

Contact with eyes: If substance has got into eyes, immediately wash out with plenty of water

Seek medical advice

Contact with skin: Remove contaminated clothing immediately and drench affected skin with

> plenty of water. Then wash with soap and water Seek medical attention if irritation persists

Inhalation: Fresh air, keep warm and at rest.

If breathing is difficult give oxygen

Apply artificial respiration only if patient is not breathing

Seek immediate medical attention

Ingestion: Do not induce vomiting

Rinse mouth with water (do not swallow)

If swallowed seek medical advice immediately and show this container or

label.

# 4.2. Most important symptoms and effects, both acute and delayed

Inhalation: May cause irritation.

High concentrations may cause narcotic effects.

Symptoms: sore throat, cough, shortness of breath, severe breathing

difficulties, headache

After vomiting of swallowed product aspiration into lungs is likely. Solvents Ingestion:

may induce chemical pneumonia.

Symptoms: abdominal pain, dizziness, diarrhea, cough, headache

Skin contact: May cause irritation.

Prolonged skin contact will result in defatting of the skin, leading to irritation,

and in some cases, dermatitis Symptoms: redness and pain

Eye contact: May cause irritation.

Symptoms: redness and pain

#### 4.3. Indication of any immediate medical attention and special treatment needed

**General Advice:** If any symptoms should occur, seek medical advice.

If you feel unwell, seek medical advice (show the label where possible

Methylene chloride is classified as carcinogenic Cat.2

In case of repeated exposures, regular medical examination is advised

# SECTION 5: Firefighting measures



#### Regulation EC No 1907/2006 Art.31

 Productname :
 ADHESIVE MP 100
 Creationdate :
 11.01.21 Version : 4.0

 Ref.Nr.:
 UDS000282\_3\_20210111 (EN)
 Replaces:
 UDS000282\_20200615

## 5.1. Extinguishing media

foam, carbon dioxide or dry agent

## 5.2. Special hazards arising from the substance or mixture

Aerosols may explode if heated above 50°C Forms hazardous decomposition products CO,CO2,HCl chlorinated compounds

#### 5.3. Advice for firefighters

Keep container(s) exposed to fire cool, by spraying with water In case of fire, do not breathe fumes Substance evolves toxic fumes, wear self-contained breathing apparatus

## SECTION 6: Accidental release measures

#### 6.1. Personal precautions, protective equipment and emergency procedures

Shut off all ignition sources Ensure adequate ventilation Wear suitable protective clothing and gloves.

#### 6.2. Environmental precautions

Do not allow to enter public sewers and watercourses

#### 6.3. Methods and material for containment and cleaning up

Absorb spillage in suitable inert material Wash spill site with water and detergent

#### 6.4. Reference to other sections

For further information see section 8

# SECTION 7: Handling and storage

## 7.1. Precautions for safe handling

Keep away from heat and sources of ignition
Take precautionary measures against static discharges
Equipment should be earthed
Use explosion-proof electrical/ventilating/lighting/.../equipment.
Use only non-sparking tools.
Do not breathe aerosols or vapours.
Ensure adequate ventilation



Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

#### Regulation EC No 1907/2006 Art.31

ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Productname: Ref.Nr.: UDS000282 3 20210111 (EN) Replaces: UDS000282 20200615

Avoid contact with skin and eyes.

Wash thoroughly after use

Wear protective gloves/protective clothing/eye protection/face protection.

## 7.2. Conditions for safe storage, including any incompatibilities

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C.

Keep in a cool, dry, well ventilated place

Keep out of reach of children.

#### 7.3. Specific end use(s)

Adhesives

# SECTION 8: Exposure controls/personal protection

## 8.1. Control parameters

#### **Exposure limits:**

| Hazardous ingredient                                 | CAS-nr. | method       |         |
|--|---------|--------------|---------|
| EU established exposure limits:                      |         |              |         |
| dichloromethane; methylene chloride                  | 75-09-2 | TWA          | 100 ppm |
|  |         | STEL         | 200 ppm |
| butanone; ethyl methyl ketone                        | 78-93-3 | TWA          | 200 ppm |
|  |         | STEL         | 300 ppm |
| National established exposure limits, United Kingdom |         |              |         |
| dichloromethane; methylene chloride                  | 75-09-2 | TWA          | 100 ppm |
|  |         | STEL         | 300 ppm |
| butanone; ethyl methyl ketone                        | 78-93-3 | TWA          | 200 ppm |
|  |         | STEL         | 300 ppm |
| National established exposure limits, Ireland        |         | <del>.</del> |         |
| dichloromethane; methylene chloride                  | 75-09-2 | TWA          | 50 ppm  |
|  |         | STEL         | -       |
| butanone; ethyl methyl ketone                        | 78-93-3 | TWA          | 200 ppm |
|  |         | STEL         | 300 ppm |

#### 8.2. Exposure controls

Control procedures: Ensure adequate ventilation

Keep away from heat and sources of ignition

Personal protection: Take precautions to avoid contact with skin and eyes when handling the

product.

Ensure adequate ventilation

inhalation: In case of insufficient ventilation, wear suitable respiratory equipment. recommended respiratory protection: Air purifying respirator equiped with organic gas/vapor cartridge (type AX)

hands and skin: Wear suitable protective gloves

The breakthrough time of the glove should be longer than the total duration of



#### Regulation EC No 1907/2006 Art.31

ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Productname: Ref.Nr.: UDS000282 3 20210111 (EN) Replaces: UDS000282 20200615

product use. If work lasts longer than the breakthrough time, gloves should be

changed part-way through.

Recommended gloves: (butyl rubber)

Wear safety eyewear according to EN 166. eyes:

## SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

(for aerosols data for the product without propellant)

**Appearance : physical state :** Propane/butane propelled liquid.

colour: Brown. odour: Solvent. pH: Not applicable.

Boiling point/range: 39 °C Flash point: None

Evaporation rate: Not available.

Explosion limits: upper limit: 19 % lower limit: 1.8 %

Vapour pressure: Not available.

Relative density: 1.22 g/cm3 (@ 25°C). Solubility in water : Partly soluble in water

**Auto-ignition:** 605 °C Viscosity: Not available.

#### 9.2. Other information

VOC = volatile organic 666 g/l compounds

## SECTION 10: Stability and reactivity

#### 10.1. Reactivity

No hazardous reactions known if used for its intended purpose

## 10.2. Chemical stability

Stable

## 10.3. Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose

#### 10.4. Conditions to avoid

Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Avoid overheating



#### Regulation EC No 1907/2006 Art.31

Productname: ADHESIVE MP 100

Ref.Nr.: UDS000282 3 20210111 (EN) Creationdate: Replaces:

11.01.21 Version: 4.0 UDS000282 20200615

## 10.5. Incompatible materials

Strong oxidising agent

## 10.6. Hazardous decomposition products

CO,CO2,HCI traces of chlorine and phosgene

# SECTION 11: Toxicological information

## 11.1. Information on toxicological effects

| acute toxicity:                    | based on available data the classification criteria are not met |
|------------------------------------|---|
| skin corrosion/irritation:         | Causes skin irritation.   |
| serious eye damage/irritation:     | Causes serious eye irritation.                                  |
| respiratory or skin sensitisation: | based on available data the classification criteria are not met |
| germ cell mutagenicity:            | based on available data the classification criteria are not met |
| carcinogenicity:                   | Suspected of causing cancer.                                    |
| toxicity for reproduction:         | based on available data the classification criteria are not met |
| STOT-single exposure:              | May cause drowsiness or dizziness.                              |
| STOT repeated exposure:            | based on available data the classification criteria are not met |
| aspiration hazard:                 | based on available data the classification criteria are not met |

## Information on likely routes of exposure:

Inhalation: May cause irritation.

High concentrations may cause narcotic effects.

Ingestion: After vomiting of swallowed product aspiration into lungs is likely. Solvents

may induce chemical pneumonia.

Skin contact: Irritating to skin Eye contact: Irritating to eyes

#### Toxicological data:

| Hazardous ingredient                | CAS-nr. | method        |              |
|-------------------------------------|---------|---------------|--------------|
| dichloromethane; methylene chloride | 75-09-2 | LD50 oral rat | > 2000 mg/kg |
|                                     |         | LD50 derm.rat | > 2000 mg/kg |
| butanone; ethyl methyl ketone       | 78-93-3 | LD50 oral rat | > 2000 mg/kg |

May cause damage to organs through prolonged or repeated exposure .

Methylene chloride is classified as carcinogenic Cat.2

# SECTION 12: Ecological information

#### 12.1. Toxicity

Not classified



7 / 10

#### **CRC Industries UK Limited**

#### Regulation EC No 1907/2006 Art.31

Productname: ADHESIVE MP 100

Ref.Nr.: UDS000282\_3\_20210111 (EN) Creationdate: Replaces:

11.01.21 Version: 4.0 UDS000282 20200615

## **Ecotoxicological data:**

| Hazardous ingredient                | CAS-nr. | method       |            |
|-------------------------------------|---------|--------------|------------|
| dichloromethane; methylene chloride | 75-09-2 | IC50 algae   | > 662 mg/l |
|                                     |         | LC50 fish    | 193 mg/l   |
|                                     |         | EC50 daphnia | 27 mg/l    |

#### 12.2. Persistence and degradability

No information available

#### 12.3. Bioaccumulative potential

No information available

#### 12.4. Mobility in soil

Partly soluble in water

#### 12.5. Results of PBT and vPvB assessment

No information available

# 12.6. Other adverse effects

No information available GWP (global warming potential): 5

# SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

# SECTION 14: Transport information

## 14.1. UN number

UN-number: 1950

# 14.2. UN proper shipping name

Proper shipping name: **AEROSOLS** 

#### 14.3. Transport hazard class(es)

2.1 Class: Subsidiary risk: 6.1



8 / 10

## **CRC Industries UK Limited**

Ambersil House, Wylds Road, Castlefield Industrial Estate, Bridgwater, Somerset, TA6 4DD
Tel: +44 (0)1278 727200 Fax: +44 (0)1278 425644 web: www.ambersil.com

#### Regulation EC No 1907/2006 Art.31

ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Productname: Ref.Nr.: UDS000282 3 20210111 (EN) Replaces: UDS000282 20200615

ADR/RID - Classification code: 5TF

#### 14.4. Packing group

Not applicable. Packing group:

#### 14.5. Environmental hazards

ADR/RID - Environmentally No hazardous: IMDG - Marine pollutant: Nο IATA/ICAO - Environmentally No hazardous:

#### 14.6. Special precautions for user

| ADR/RID - Tunnelcode: | (D)      |
|-----------------------|----------|
| IMDG - Ems:           | F-D, S-U |
| IATA/ICAO - PAX:      | 203      |
| IATA/ICAO - CAO       | 203      |

#### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Not applicable.

# SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

The Safety Data Sheet is compiled according to the current European requirements.

Regulation (EC) No 1907/2006 (REACH)

Regulation (EC) No 1272/2008 (CLP)

Dir. 2013/10/EU, 2008/47/EC amendment of the aerosol dispenser directive 75/324/EEC.

## 15.2. Chemical safety assessment

No information available

# SECTION 16: Other information

\*Explanation hazard statements: H220 : Extremely flammable gas.

H225: Highly flammable liquid and vapour.

H280 : Contains gas under pressure; may explode if heated.

H315: Causes skin irritation.

H319: Causes serious eye irritation.

H335: May cause respiratory irritation.

H336: May cause drowsiness or dizziness.

H351: Suspected of causing cancer.

H373: May cause damage to organs through prolonged or repeated exposure



#### Regulation EC No 1907/2006 Art.31

Productname: ADHESIVE MP 100 Creationdate: 11.01.21 Version: 4.0 Ref.Nr.: UDS000282 3 20210111 (EN) Replaces: UDS000282 20200615

**REVISIONS IN CHAPTRE:** Classification according to Regulation (EC) No 1272/2008

Labelling according to Regulation (EC) No 1272/2008

TWA = time weight average acronyms and synonyms:

> STEL = short time exposure limit VOC = volatile organic compounds PBT = persistant bioaccumulative toxic vPvB = very persitant very bioaccumulative

This product should be stored, handled and used in accordance with good industrial hygiene practices and in conformity with any legal regulation.

The information contained herewith is based on the present state of our knowledge and is intended to describe our products from the point of view of safety requirements. It does not guarantee any specific properties. Apart from any fair dealing for purposes of study, research and review of health, safety and environmental risks,no part of these documents may be reproduced by any process without written permission from CRC.

