

Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 11

Loctite 241

SDS No. : 173035 V004.0 Revision: 10.02.2015 printing date: 12.03.2015 Replaces version from: 09.02.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Loctite 241

Contains:

Cumene hydroperoxide

1.2. Relevant identified uses of the substance or mixture and uses advised against Intended use:

Adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Ltd Wood Lane End HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000 Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Specific target organ toxicity - single exposure	Category 3
H335 May cause respiratory irritation.	
Target organ: respiratory tract irritation	
Chronic hazards to the aquatic environment	Category 3
H412 Harmful to aquatic life with long lasting effects.	

Classification (DPD):

Xn - Harmful
R20 Harmful by inhalation.
Xi - Irritant
R36/37 Irritating to eyes and respiratory system.
Dangerous for the environment
R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:	
Signal word:	Warning
Hazard statement:	H319 Causes serious eye irritation. H335 May cause respiratory irritation. H412 Harmful to aquatic life with long lasting effects.
Precautionary statement:	***For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements***
Precautionary statement: Prevention	P261 Avoid breathing vapours. P273 Avoid release to the environment.
Precautionary statement: Response	P337+P313 If eye irritation persists: Get medical advice/attention.

Label elements (DPD):

Xn - Harmful



Risk phrases:

R20 Harmful by inhalation.

R36/37 Irritating to eyes and respiratory system.

R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

S23 Do not breathe vapour.

S25 Avoid contact with eyes.

S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S51 Use only in well-ventilated areas.

S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

Additional labeling:

For consumer use only: S2 Keep out of the reach of children. S46 If swallowed, seek medical advice immediately and show this container or label.

Contains:

Cumene hydroperoxide, N,N-Diethyl-p-toluidine

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Methacrylate resin based threadlocker

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	2,5-< 3 %	Acute toxicity 4; Dermal H312 Specific target organ toxicity - repeated exposure 2 H373 Acute toxicity 4; Oral H302 Organic peroxides E H242 Acute toxicity 3; Inhalation H331 Skin corrosion 1B H314 Chronic hazards to the aquatic environment 2 H411
N,N-Diethyl-p-toluidine 613-48-9	210-345-0	1- < 2,5 %	Acute toxicity 3; Oral H301 Acute toxicity 3; Dermal H311 Acute toxicity 3; Inhalation H331 Specific target organ toxicity - repeated exposure 2 H373 Chronic hazards to the aquatic environment 3 H412
N,N-dimethyl-o-toluidine 609-72-3	210-199-8	0,1-< 1 %	Specific target organ toxicity - repeated exposure 2 H373 Chronic hazards to the aquatic environment 3 H412 Acute toxicity 3; Inhalation H331 Acute toxicity 3; Dermal H311 Acute toxicity 3; Oral H301

For full text of the H - statements and other abbreviations see section 16 "Other information". Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Cumene hydroperoxide 80-15-9	201-254-7	2,5 - < 3 %	T - Toxic; R23 Xn - Harmful; R21/22, R48/20/22 C - Corrosive; R34 O - Oxidizing; R7
			N - Dangerous for the environment; R51/53
N,N-Diethyl-p-toluidine 613-48-9	210-345-0	1 - < 2,5 %	T - Toxic; R23/24/25 R33 R52/53
N,N-dimethyl-o-toluidine 609-72-3	210-199-8	0,1 - < 1 %	T - Toxic; R23/24/25 R33 R52/53
Cumene 98-82-8	202-704-5	0,25 - < 2,5 %	R10 Xn - Harmful; R65 Xi - Irritant; R37 N - Dangerous for the environment; R51/53

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.

Substances without classification may have community workplace exposure limits available.

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap. Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

RESPIRATORY: Irritation, coughing, shortness of breath, chest tightness.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Foam, extinguishing powder, carbon dioxide.

Extinguishing media which must not be used for safety reasons:

None known

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO2) and nitrogen oxides (NOx) can be released.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures Ensure adequate ventilation. Avoid skin and eye contact.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal. For large spills absorb onto inert absorbent material and place in sealed container for disposal. Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

7.1. Precautions for safe handling

Use only in well-ventilated areas. Avoid skin and eye contact. See advice in section 8

Hygiene measures:

Good industrial hygiene practices should be observed. Do not eat, drink or smoke while working. Wash hands before work breaks and after finishing work.

7.2. Conditions for safe storage, including any incompatibilities

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

7.3. Specific end use(s)

Adhesive

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

Ingredient	ppm	mg/m ³	Туре	Category	Remarks
CUMENE	50	250	Short Term Exposure		EH40 WEL
98-82-8			Limit (STEL):		
CUMENE			Skin designation:	Can be absorbed through the	EH40 WEL
98-82-8				skin.	
CUMENE	25	125	Time Weighted Average		EH40 WEL
98-82-8			(TWA):		
CUMENE	50	250	Short Term Exposure	Indicative	ECTLV
98-82-8			Limit (STEL):		
CUMENE	20	100	Time Weighted Average	Indicative	ECTLV
98-82-8			(TWA):		

Biological Exposure Indices:

None

8.2. Exposure controls:

Respiratory protection:

Ensure adequate ventilation.

Do not inhale vapors and fumes.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance

Flash point

Density

() Bulk density

Viscosity

Melting point

Flammability

Explosive limits

Evaporation rate Vapor density

Vapour pressure (25,0 °C (77 °F)) Vapour pressure

Decomposition temperature

(50 °C (122 °F))

Viscosity (kinematic)

Explosive properties

Solubility (qualitative)

(Solvent: Water) Solubility (qualitative)

(Solvent: Acetone) Solidification temperature

Auto-ignition temperature

Partition coefficient: n-octanol/water

liquid

Odor	blue characteristic
Odour threshold	No data available / Not applicable
pH	3,00 - 6,00
() Initial boiling point	> 149 °C (> 300.2 °F)

> 149 °C (> 300.2 °F) $> 100 \ ^{\circ}C \ (> 212 \ ^{\circ}F)$ No data available / Not applicable 0,1330000 mbar < 300 mbar

1,0800 g/cm3

No data available / Not applicable Not miscible

Miscible

No data available / Not applicable No data available / Not applicable

9.2. Other information

Oxidising properties

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Peroxides. Reaction with strong bases Reaction with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

No decomposition if stored and applied as directed.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

STOT-single exposure:

May cause respiratory irritation.

Skin irritation:

Prolonged or repeated contact may cause skin irritation.

Eye irritation:

Causes serious eye irritation.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LD50	550 mg/kg	oral		rat	

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	corrosive		rabbit	Draize Test

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of	Metabolic activation /	Species	Method
		administration	Exposure time		
Cumene hydroperoxide	positive	bacterial reverse	without		OECD Guideline 471
80-15-9		mutation assay (e.g			(Bacterial Reverse Mutation
		Ames test)			Assay)
Cumene hydroperoxide	negative	dermal		mouse	
80-15-9					

Repeated dose toxicity

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
Cumene hydroperoxide 80-15-9		inhalation: aerosol	6 h/d5 d/w	rat	

SECTION 12: Ecological information

General ecological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity

Ecotoxicity:

Do not empty into drains / surface water / ground water. Harmful to aquatic life with long lasting effects.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	Toxicity Test) OECD Guideline 202 (Daphnia sp. Acute
Cumene hydroperoxide 80-15-9	ErC50	3,1 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	Immobilisation Test) OECD Guideline 201 (Alga, Growth Inhibition Test)

12.2. Persistence and degradability

Persistence and Biodegradability:

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Cumene hydroperoxide 80-15-9		no data	0 %	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution
				Test)

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Mobility:

Cured adhesives are immobile.

Bioaccumulative potential:

No data available.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Cumene hydroperoxide 80-15-9		9,1		calculation		OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Cumene hydroperoxide 80-15-9	2,16					

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations. Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information

14.1.	UN number
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.2.	UN proper shipping name
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.3.	Transport hazard class(es)
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.4.	Packaging group
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.5.	Environmental hazards
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.6.	Special precautions for user
	Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.
14.7.	Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code
	not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content (1999/13/EC) < 3,00 %

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text

- of all abbreviations indicated by codes in this safety data sheet are as follows:
 - R10 Flammable.
 - R21/22 Harmful in contact with skin and if swallowed.
 - R23 Toxic by inhalation.
 - R23/24/25 Toxic by inhalation, in contact with skin and if swallowed.

R33 Danger of cumulative effects.

R34 Causes burns.

R37 Irritating to respiratory system.

- R48/20/22 Harmful: danger of serious damage to health by prolonged exposure through inhalation and if swallowed.
- R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
- R52/53 Harmful to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

R65 Harmful: may cause lung damage if swallowed.

R7 May cause fire.

H242 Heating may cause a fire.

- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H311 Toxic in contact with skin.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H331 Toxic if inhaled.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.