




Parts Information:
Bench Grinder Ø150mm & Wire Wheel Combination with Work Light
250W/230V
Model No: BG150XWL



NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk



Parts Information:
**Bench Grinder Ø150mm & Wire Wheel
 Combination with Work Light 250W/230V
 Model No: BG150XWL**

Item	Part No.	Description
1	MSP518.S	Machine Screw Pan Head Phillips M5x18mm (Single)
2	BG150WL.02	Left Guard Cover
3	BG150WL.03	Hex Nut M12 (Left hand Thread)
4	BG150WL.04	Wheel Flange
5	BG150/15	Grinding Stone Ø150 X 20mm 32(13)mm Bore A60P Fine
--	BG150/16	Grinding Stone Ø150 X 20mm 32(13)mm Bore A36Q Coarse
6	MSP510.SB	Machine Screw Pan Head Phillips M5x10mm Black
7	BG150WL.07	Left Guard Inner Cover
8	BG150WL.08	Left Spark Deflector
9	FWM5.SB	Flat Washer M5 Black (Single)
10	MSP58.SB	Machine Screw Pan Head Phillips M5x8mm Black
11	BG150WL.11	Left Eyeshield Mount Rod
12	BG150WL.12	Bracket
13	FWM6.SB	Flat Washer M6 Black (Single)
14	BG200WL.15	Hex Bolt M6x14
15	BG200WL.15	Hex Bolt M6x14
16	BG150WL.16	Eyeshield Plate
17	BG150WL.17	Big Flat Washer 5mm
18	DAS151.14	Screw (M4x10)
19	MSP5122.S	Machine Screw Pan Head Phillips M5x122mm (Single)
20	BG150WL.20	Right Eyeshield Mount Rod
21	BG150WL.21	End Cap
22	SN8.S	Steel Nut M8 Zinc Din934 (Single)
23	BG150WL.23	Wavy Washer 35mm
24	B/6202-2RS	Bearing 6202-2RS
25	BG150WL.25	Stator
26	BG150WL.26	Rotor
27	SN5.SB	Steel Nut M5 Black (Single)
28	NLN5.S	Nyloc Nut M5 Zinc Din 985 (Single)
29	BG150WL.29	Left Work Rest
30	BG150WL.30	Eyeshield
31	BG150WL.31	Work Rest Lock Knob
32	SWM5.SB	Spring Washer M5 Black (Single)
33	FWM6.SB	Flat Washer M6 Black (Single)
34	SN6.S	Steel Nut M6 Zinc Din934 (Single)

Item	Part No.	Description
35	SN12.S	Steel Nut M12 Zinc Din934 (Single)
36	BG150/WW1	Wire Wheel Ø150 x 13mm 13mm Bore Narrow
37	BG150WL.49	Strain Relief (c/w Lock Nut M16)
38	BG150WL.38	Toothed Locking Washer 4mm
39	MSP410.SB	Machine Screw Pan Head Phillips M4x10mm Black
40	BG150WL.40	Right Guard Inner Cover
41	BG150WL.41	Cord Bushing
42	BG150WL.42	Capacitor 4uF 450V
43	BG150WL.43	Capacitor Stand
44	FWM4.S	Flat Washer M4 Single
45	BG150WL.45	Wheel Dressing Tool
46	BG150WL.46	Lamp Assembly
47	BG150WL.47	Motor Housing
48	MC3CX0.75	Mains Cable Blk, 3 Core, 0.75 mm ²
49	BG150WL.49	Strain Relief (c/w Lock Nut M16)
50	EU1011	Nut (M10x1)
51	BG150WL.51	Toothed Locking Washer 10mm
52	BG150WL.52	Switch Plate
53	BG150WL.53	Switch
54	SN4.S	Steel Nut M4 Zinc Din934 (Single)
55	MSP416.SB	Machine Screw Pan Head Phillips M4x16mm Black
56	BG150WL.56	Big Flat Washer 4mm
57	BG150WL.57	Rubber Foot
58	BG150WL.58	Tool Tray
59	BG150WL.59	Base Plate Ass'y
60	BG150WL.60	Right Movable Work Rest
61	FWM4.SB	Flat Washer M4 Black (Single)
62	BG150WL.62	Bulb
63	BG150WL.63	Magnified Eyeshield
64	BG150WL.64	Dressing Tool Base
65	BG150WL.65	Flat Washer 10mm
66	SWM6.SB	Spring Washer M6 Black (Single)
67	MSP58.SB	Machine Screw Pan Head Phillips M5x8mm Black
68	BG150WL.68	Right Guard Cover
69	BG150WL.69	Right Spark Deflector
70	BG150WL.70	Lamp With Protective Guard

NOTE: It is our policy to continually improve products and as such we reserve the right to alter data, specifications and component parts without prior notice.

IMPORTANT: No liability is accepted for incorrect use of product.

WARRANTY: Guarantee is 12 months from purchase date, proof of which will be required for any claim.

Sealey Group, Kempson Way, Suffolk Business Park, Bury St Edmunds, Suffolk. IP32 7AR



01284 757500



01284 703534



sales@sealey.co.uk



www.sealey.co.uk