

SAFETY DATA SHEET

Label Remover

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name 41926 400ML INK and GUM REMOVER

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses INK and DIRT REMOVER

1.3. Details of the supplier of the safety data sheet

Supplier

Draper Tools Ltd
Hursley Road
Chandlers Ford
Eastleigh
Hants
SO53 1YF

1.4. Emergency telephone number

Draper Helpline +44 (0) 2380 494344

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (EC 1272/2008)

Physical hazards Aerosol 1 - H222, H229
Health hazards Skin Irrit. 2 - H315 Skin Sens. 1 - H317 STOT SE 3 - H336
Environmental hazards Aquatic Chronic 2 - H411

Classification (67/548/EEC or 1999/45/EC) F+;R12. R66.

Human health Gas or vapour is harmful on prolonged exposure or in high concentrations. In high concentrations, vapours and aerosol mists have a narcotic effect and may cause headache, fatigue, dizziness and nausea. Deliberately concentrating and inhaling the contents of this container is dangerous and can be fatal.

Environmental The product is not expected to be hazardous to the environment.

Physicochemical Aerosol containers can explode when heated, due to excessive pressure build-up. The product is extremely flammable. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

2.2. Label elements

Pictogram



Signal word

Danger

Label Remover

Hazard statements	H222 Extremely flammable aerosol. H229 Pressurised container: may burst if heated H315 Causes skin irritation. H317 May cause an allergic skin reaction. H336 May cause drowsiness or dizziness. H411 Toxic to aquatic life with long lasting effects.
Precautionary statements	P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. P211 Do not spray on an open flame or other ignition source. P251 Do not pierce or burn, even after use. P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F. P102 Keep out of reach of children. P260 Do not breathe vapour/ spray. P271 Use only outdoors or in a well-ventilated area. P501 Dispose of contents/ container in accordance with local regulations.
Contains	ALIPHATIC HYDROCARBON (D40), Orange Terpene
Detergent labelling	≥ 30% aliphatic hydrocarbons, 15 - < 30% perfumes

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

ALIPHATIC HYDROCARBON (D40)	30-60%
CAS number: —	EC number: 919-857-5
	REACH registration number: 01-2119463258-33-XXXX
Classification	Classification (67/548/EEC or 1999/45/EC)
Flam. Liq. 3 - H226	Xn;R65. R10,R66.
STOT SE 3 - H336	
Asp. Tox. 1 - H304	
PETROLEUM GASES, LIQUEFIED; PETROLEUM GAS	30-60%
CAS number: 68476-85-7	EC number: 270-704-2
Classification	Classification (67/548/EEC or 1999/45/EC)
Flam. Gas 1 - H220	F+;R12 Carc. Cat. 1;R45 Muta. Cat. 2;R46
Press. Gas, Liquefied - H280	

Label Remover

Orange Terpene		10-30%
CAS number: 8028-48-6	EC number: 232-433-8	REACH registration number: 01-2119493353-35
M factor (Chronic) = 1		
Classification		Classification (67/548/EEC or 1999/45/EC)
Flam. Liq. 3 - H226		Xn;R65. R10.
Skin Irrit. 2 - H315		
Skin Sens. 1 - H317		
Asp. Tox. 1 - H304		
Aquatic Chronic 1 - H410		

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Move affected person to fresh air at once.
Inhalation	If spray/mist has been inhaled, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. If breathing stops, provide artificial respiration. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Ingestion	Rinse mouth thoroughly with water. Do not induce vomiting. Get medical attention immediately.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
----------------------------	---

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	Extinguish with foam, carbon dioxide, dry powder or water fog.
-------------------------------------	--

5.2. Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Extremely flammable. Forms explosive mixtures with air. Vapours are heavier than air and may spread near ground and travel a considerable distance to a source of ignition and flash back.
-------------------------	---

5.3. Advice for firefighters

Protective actions during firefighting	Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Use water to keep fire exposed containers cool and disperse vapours. Warn firefighters that aerosols are involved.
---	--

SECTION 6: Accidental release measures

Label Remover

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Provide adequate ventilation. Use suitable respiratory protection if ventilation is inadequate. Avoid inhalation of vapours.

6.2. Environmental precautions

Environmental precautions Avoid the spillage or runoff entering drains, sewers or watercourses. Contain spillage with sand, earth or other suitable non-combustible material.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Eliminate all sources of ignition. No smoking, sparks, flames or other sources of ignition near spillage. Provide adequate ventilation. Absorb spillage with non-combustible, absorbent material. Leave small quantities to evaporate, if safe to do so. Do not allow material to enter confined spaces, due to the risk of explosion.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Read and follow manufacturer's recommendations. Keep away from heat, sparks and open flame. Eliminate all sources of ignition. Do not spray on a naked flame or any incandescent material.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Extremely flammable. Keep away from heat, sparks and open flame. Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use. Store in tightly-closed, original container in a dry, cool and well-ventilated place.

7.3. Specific end use(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

ALIPHATIC HYDROCARBON (D40)

Long-term exposure limit (8-hour TWA): SUP 1040 mg/m³

PETROLEUM GASES, LIQUEFIED; PETROLEUM GAS

Long-term exposure limit (8-hour TWA): WEL 1000 ppm 1750 mg/m³

Short-term exposure limit (15-minute): WEL 1250 ppm 2180 mg/m³

Orange Terpene

Long-term exposure limit (8-hour TWA): WEL 800 mg/m³

WEL = Workplace Exposure Limit

Ingredient comments WEL = Workplace Exposure Limits

ALIPHATIC HYDROCARBON (D40)

Label Remover

DNEL	Workers - Dermal; Long term systemic effects: 300 mg/kg/day
	Workers - Inhalation; Long term systemic effects: 1500 mg/m ³
	Consumer - Dermal; Long term systemic effects: 300 mg/kg
	Consumer - Inhalation; Long term systemic effects: 900 mg/m ³
	Consumer - Oral; Long term systemic effects: 300 mg/kg/day

Orange Terpene (CAS: 8028-48-6)

DNEL	Consumer - Oral, Dermal; Long term systemic effects: 4.44 mg/kg/day
	Workers - Dermal; Long term systemic effects: 8.89 mg/kg/day
	Consumer - Inhalation; Long term systemic effects: 7.78 mg/m ³
	Workers - Inhalation; Long term systemic effects: 31.1 mg/m ³
PNEC	- Fresh water; 0.054 mg/l
	- Sediment (Freshwater); 1.3 mg/kg
	- Intermittent release; 0.00577 mg/l
	- Sediment (Marinewater); 0.13 mg/kg
	- Marine water; 0.0054 mg/l
	- STP; 2.1 mg/l
	- Soil; 0.261 mg/kg

8.2. Exposure controls

Appropriate engineering controls	Provide adequate ventilation. Avoid inhalation of vapours and spray/mists. Observe any occupational exposure limits for the product or ingredients.
Personal protection	When using do not smoke.
Eye/face protection	Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. The following protection should be worn: Chemical splash goggles.
Hand protection	Due to the packaging form, aerosol, risk of skin contact is small. Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material.
Hygiene measures	Wash promptly if skin becomes contaminated. Wash at the end of each work shift and before eating, smoking and using the toilet. Use appropriate hand lotion to prevent defatting and cracking of skin. Wash hands thoroughly after handling.
Respiratory protection	If ventilation is inadequate, suitable respiratory protection must be worn.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Appearance	Aerosol.
Colour	Colourless to pale yellow.
Odour	Organic solvents. Orange.
Flash point	< -40°C
Upper/lower flammability or explosive limits	Lower flammable/explosive limit: 1.8% Upper flammable/explosive limit: 9.5%
Auto-ignition temperature	410-580°C
Comments	Information given is applicable to the major ingredient.

9.2. Other information

Label Remover

Other information	Not available.
Volatile organic compound	This product contains a maximum VOC content of 710 g/l.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	Stable at normal ambient temperatures and when used as recommended.
------------	---

10.2. Chemical stability

Stability	Heat, sparks, flames.
-----------	-----------------------

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Does not decompose when used and stored as recommended.
------------------------------------	---

10.4. Conditions to avoid

Conditions to avoid	Avoid heat, flames and other sources of ignition. Avoid exposing aerosol containers to high temperatures or direct sunlight.
---------------------	--

10.5. Incompatible materials

Materials to avoid	Keep away from oxidising materials, heat and flames.
--------------------	--

10.6. Hazardous decomposition products

Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Toxic and corrosive gases or vapours.
----------------------------------	--

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General information	Deliberately concentrating and inhaling the contents of this container is dangerous and can be fatal.
Inhalation	In high concentrations, vapours and aerosol mists have a narcotic effect and may cause headache, fatigue, dizziness and nausea. Unconsciousness, possibly death.
Skin contact	Skin irritation should not occur when used as recommended. Repeated exposure may cause skin dryness or cracking.
Eye contact	Vapour or spray in the eyes may cause irritation and smarting.
Acute and chronic health hazards	Arrhythmia (deviation from normal heart beat). Vapours may cause headache, fatigue, dizziness and nausea.
Route of entry	Inhalation
Target organs	Central nervous system Respiratory system, lungs
Medical symptoms	Skin irritation. Arrhythmia (deviation from normal heart beat). Vapours may cause drowsiness and dizziness.

ALIPHATIC HYDROCARBON (D40)

Acute toxicity - oral

Acute toxicity oral (LD ₅₀) mg/kg)	5,000.0
---	---------

Label Remover

Species	Rat
ATE oral (mg/kg)	5,000.0
<u>Acute toxicity - dermal</u>	
Acute toxicity dermal (LD ₅₀ mg/kg)	5,000.0
Species	Rabbit
ATE dermal (mg/kg)	5,000.0
<u>Acute toxicity - inhalation</u>	
Acute toxicity inhalation (LC ₅₀ dust/mist mg/l)	5.0
Species	Rat

SECTION 12: Ecological Information

Ecotoxicity No negative effects on the aquatic environment are known. The product is not expected to be toxic to aquatic organisms.

12.1. Toxicity

Toxicity Not available.

ALIPHATIC HYDROCARBON (D40)

Acute toxicity - fish	LL ₅₀ , 96 hours: >1000 mg/l, Onchorhynchus mykiss (Rainbow trout)
Acute toxicity - aquatic invertebrates	EC ₅₀ , 48 hours: 1000 mg/l, Daphnia magna
Acute toxicity - aquatic plants	EC ₅₀ , : >1000 mg/l, Pseudokirchneriella subcapitata NOEC, : 100 mg/l, Pseudokirchneriella subcapitata

Orange Terpene

Acute toxicity - fish	LC ₅₀ , 96 hours: 0.7 mg/l, Pimephales promelas (Fat-head Minnow)
Acute toxicity - aquatic invertebrates	EC ₅₀ , 48 hours: 0.67 mg/l, Daphnia magna
Acute toxicity - aquatic plants	IC ₅₀ , 72 hours: 150 mg/l, Desmodemus subspicatus

Chronic aquatic toxicity

M factor (Chronic) 1

12.2. Persistence and degradability

Persistence and degradability Not available.

Orange Terpene

Biodegradation - Degradation 72-83.4 %: 28 days

12.3. Bioaccumulative potential

Bioaccumulative potential Not available.

Label Remover

Orange Terpene

Bioaccumulative potential BCF: 32-156,

Partition coefficient log Pow: ≥ 4 (>80% product)

12.4. Mobility in soil

Mobility Not known.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment Not available.

12.6. Other adverse effects

Other adverse effects Not available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Do not puncture or incinerate, even when empty.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. Containers should be thoroughly emptied before disposal because of the risk of an explosion. Empty containers must not be punctured or incinerated because of the risk of an explosion.

SECTION 14: Transport information

General This product is packed in accordance with the Limited Quantity Provisions of CDGCPL2, ADR and IMDG. These provisions allow transport of aerosols of less than 1 litre packed in cartons of less than 30kg gross weight to be exempt from control providing that they are labelled in accordance with the requirements of these regulations to show that they are being transported as Limited Quantities. Aerosols not so packed and labelled must show the following.

14.1. UN number

UN No. (ADR/RID)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950
UN No. (ADN)	1950

14.2. UN proper shipping name

Proper shipping name (ADR/RID)	AEROSOLS
Proper shipping name (IMDG)	AEROSOLS (CONTAINS Orange Terpene)
Proper shipping name (ICAO)	AEROSOLS
Proper shipping name (ADN)	AEROSOLS

14.3. Transport hazard class(es)

ADR/RID class	2.1
ADR/RID classification code	5F
ADR/RID label	2.1

Label Remover

IMDG class	2.1
ICAO class/division	2.1
ADN class	2.1

Transport labels



14.4. Packing group

ADR/RID packing group	None
IMDG packing group	None
ADN packing group	None
ICAO packing group	None

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant



14.6. Special precautions for user

Ems	F-D, S-U
ADR transport category	2
Tunnel restriction code	(D)

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations	The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (SI 2009 No. 716).
EU legislation	Commission Regulation (EU) No 453/2010 of 20 May 2010.
Guidance	Workplace Exposure Limits EH40. CHIP for everyone HSG228. Safety Data Sheets for Substances and Preparations. Approved Classification and Labelling Guide (Sixth edition) L131. British Aerosol Manufacturers Code of Practice 7th. Edition 1999

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	Supplemental information added.
-------------------	---------------------------------

Label Remover

Revision date	15/03/2017
Revision	2
SDS number	11139
SDS status	Approved.
Risk phrases in full	R10 Flammable. R12 Extremely flammable. R65 Harmful: may cause lung damage if swallowed. R66 Repeated exposure may cause skin dryness or cracking.
Hazard statements in full	H220 Extremely flammable gas. H222 Extremely flammable aerosol. H226 Flammable liquid and vapour. H229 Pressurised container: may burst if heated H280 Contains gas under pressure; may explode if heated. H304 May be fatal if swallowed and enters airways. H315 Causes skin irritation. H317 May cause an allergic skin reaction. H336 May cause drowsiness or dizziness. H410 Very toxic to aquatic life with long lasting effects. H411 Toxic to aquatic life with long lasting effects.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.