



SAFETY DATA SHEET BLOC LUBE RED

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product identifier

Product name BLOC LUBE RED
Product No. BLR, EBLR10SL, EBLR15ML, ZE

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Tamper evident seal
Uses advised against At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

1.3. Details of the supplier of the safety data sheet

Supplier ELECTROLUBE. A division of HK
WENTWORTH LTD
ASHBY PARK, COALFIELD WAY,
ASHBY DE LA ZOUCH, LEICESTERSHIRE
LE65 1JR
UNITED KINGDOM
+44 (0)1530 419600
+44 (0)1530 416640
info@hkw.co.uk

1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm Mon – Fri

SECTION 2: HAZARDS IDENTIFICATION

2.1. Classification of the substance or mixture

Classification (1999/45/EEC) Xi;R36. F;R11. R66, R67.

2.2. Label elements

Labelling



Irritant



Highly flammable

Risk Phrases

R11	Highly flammable
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

Safety Phrases

S16	Keep away from sources of ignition - No smoking.
S25	Avoid contact with eyes.
S37	Wear suitable gloves.
S51	Use only in well-ventilated areas.

2.3. Other hazards

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.2. Mixtures

BLOC LUBE RED

BUTYL ACETATE -norm		30-60%
CAS-No.: 123-86-4	EC No.: 204-658-1	
Classification (EC 1272/2008) Flam. Liq. 3 - H226 EUH066 STOT SE 3 - H336	Classification (67/548/EEC) R10 R66 R67	
ETHYL ACETATE		10-30%
CAS-No.: 141-78-6	EC No.: 205-500-4	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 EUH066 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R66 R67	
PROPAN-2-OL		10-30%
CAS-No.: 67-63-0	EC No.: 200-661-7	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Eye Irrit. 2 - H319 STOT SE 3 - H336	Classification (67/548/EEC) F;R11 Xi;R36 R67	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

SECTION 4: FIRST AID MEASURES**4.1. Description of first aid measures****Inhalation**

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention.

Ingestion

DO NOT INDUCE VOMITING! Rinse mouth thoroughly. Get medical attention.

Skin contact

Wash the skin immediately with soap and water. Get medical attention if irritation persists after washing.

Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes and get medical attention.

4.2. Most important symptoms and effects, both acute and delayed**4.3. Indication of any immediate medical attention and special treatment needed**

Treat symptomatically

SECTION 5: FIREFIGHTING MEASURES**5.1. Extinguishing media****Extinguishing media**

Use: Alcohol resistant foam. Powder. Dry chemicals, sand, dolomite etc.

5.2. Special hazards arising from the substance or mixture

BLOC LUBE RED

Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

Unusual Fire & Explosion Hazards

No unusual fire or explosion hazards noted.

5.3. Advice for firefighters

Special Fire Fighting Procedures

No specific fire fighting procedure given.

Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet. Provide adequate ventilation. In case of spills, beware of slippery floors and surfaces.

6.2. Environmental precautions

Avoid discharge into drains, water courses or onto the ground.

6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers. Wear necessary protective equipment.

6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. Collect and dispose of spillage as indicated in section 13.

SECTION 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Keep away from heat, sparks and open flame. Avoid spilling, skin and eye contact. Ventilate well, avoid breathing vapours. Use approved respirator if air contamination is above accepted level.

7.2. Conditions for safe storage, including any incompatibilities

Flammable/combustible - Keep away from oxidisers, heat and flames. Store in tightly closed original container in a dry, cool and well-ventilated place. Keep in original container.

7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
BUTYL ACETATE -norm	WEL	150 ppm	724 mg/m3	200 ppm	966 mg/m3	
ETHYL ACETATE	WEL	200 ppm		400 ppm		
PROPAN-2-OL	WEL	400 ppm	999 mg/m3	500 ppm	1250 mg/m3	

WEL = Workplace Exposure Limit.

Ingredient Comments

WEL = Workplace Exposure Limits

BLOC LUBE RED
PROPAN-2-OL (CAS: 67-63-0)

DNEL			
Industry	Dermal	888	mg/kg/day
Industry	Inhalation.	500	mg/m3
Consumer	Dermal	319	mg/kg/day
Consumer	Inhalation.	89	mg/m3
Consumer	Oral	26	mg/kg/day
PNEC			
Freshwater	140.9	mg/l	
Marinewater	140.9	mg/l	
Sediment	552	mg/kg	
Soil	28	mg/kg	

8.2. Exposure controls**Process conditions**

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

Respiratory equipment

No specific recommendation made, but respiratory protection must be used if the general level exceeds the recommended occupational exposure limit. It is recommended to use respiratory equipment with combination filter, type A2/P2.

Hand protection

Protective gloves should be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Use protective gloves made of: Butyl rubber. Nitrile.

Eye protection

Wear approved chemical safety goggles where eye exposure is reasonably probable. EN166

Other Protection

Wear suitable protective clothing as protection against splashing or contamination.

Hygiene measures

DO NOT SMOKE IN WORK AREA! Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly with soap & water if skin becomes contaminated. When using do not eat, drink or smoke.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Appearance	Liquid
Colour	Red.
Odour	Characteristic.
Viscosity	600-800 cps @ 20 °c (68 F)
Flash point	3.3 (37.94 F) CC (Closed cup).

9.2. Other information

SECTION 10: STABILITY AND REACTIVITY

10.1. Reactivity

There are no known reactivity hazards associated with this product.

10.2. Chemical stability

Stable under normal temperature conditions.

10.3. Possibility of hazardous reactions

Not determined.

Hazardous Polymerisation

Will not polymerise.

10.4. Conditions to avoid

Avoid heat, flames and other sources of ignition.

10.5. Incompatible materials**Materials To Avoid**

Strong oxidising substances.

BLOC LUBE RED

10.6. Hazardous decomposition products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1. Information on toxicological effects

Inhalation

May cause irritation to the respiratory system.

Ingestion

May cause stomach pain or vomiting.

Skin contact

Product has a defatting effect on skin. Prolonged or repeated exposure may cause severe irritation.

Eye contact

Irritating to eyes.

Toxicological information on ingredients.

PROPAN-2-OL (CAS: 67-63-0)

Acute toxicity:

Acute Toxicity (Oral LD50)

5280 mg/kg Rat

Acute Toxicity (Dermal LD50)

12800 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

72.6 mg/l (vapours) Rat 4 hours

ETHYL ACETATE (CAS: 141-78-6)

Acute toxicity:

Acute Toxicity (Oral LD50)

5620 mg/kg Rat

Acute Toxicity (Dermal LD50)

18000 mg/kg Rabbit

Acute Toxicity (Inhalation LC50)

1620 ppmV (gas) Rat 4 hours

BUTYL ACETATE -norm (CAS: 123-86-4)

Toxic Dose 1 - LD 50

14, 100 mg/kg (oral rat)

SECTION 12: ECOLOGICAL INFORMATION

Ecotoxicity

Not regarded as dangerous for the environment.

12.1. Toxicity

BLOC LUBE RED

Ecological information on ingredients.

PROPAN-2-OL (CAS: 67-63-0)

Acute Toxicity - Fish

LC50 96 hours 9640 mg/l Pimephales promelas (Fat-head Minnow)

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 13299 mg/l Daphnia magna

Acute Toxicity - Aquatic Plants

EC50 72 hours > 1.000 mg/l Scenedesmus subspicatus

Acute Toxicity - Microorganisms

EC50 > 1.000 mg/l Activated sludge

ETHYL ACETATE (CAS: 141-78-6)

Acute Toxicity - Fish

LC50 270 mg/l

Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 2306 mg/l Daphnia magna

BUTYL ACETATE -norm (CAS: 123-86-4)

LC 50, 96 Hrs, Fish mg/l

>96

EC 50, 48 Hrs, Daphnia, mg/l

72.8

IC 50, 72 Hrs, Algae, mg/l

674

12.2. Persistence and degradability

Degradability

There are no data on the degradability of this product.

12.3. Bioaccumulative potential

Bioaccumulative potential

No data available on bioaccumulation.

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

12.6. Other adverse effects

SECTION 13: DISPOSAL CONSIDERATIONS

General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements.

SECTION 14: TRANSPORT INFORMATION

14.1. UN number

UN No. (ADR/RID/ADN) 1263

UN No. (IMDG) 1263

UN No. (ICAO) 1263

14.2. UN proper shipping name

Proper Shipping Name PAINT

14.3. Transport hazard class(es)

BLOC LUBE RED

ADR/RID/ADN Class	3
ADR/RID/ADN Class	Class 3: Flammable liquids.
ADR Label No.	3
IMDG Class	3
ICAO Class/Division	3
Transport Labels	

**14.4. Packing group**

ADR/RID/ADN Packing group	II
IMDG Packing group	II
ICAO Packing group	II

14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant
No.

14.6. Special precautions for user

EMS	F-E, S-E
Emergency Action Code	•3YE
Hazard No. (ADR)	33
Tunnel Restriction Code	(D/E)

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

No information required.

SECTION 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**Uk Regulatory References**

The Control of Substances Hazardous to Health Regulations 2002 (S.I 2002 No. 2677) with amendments.
Chemicals (Hazard Information & Packaging) Regulations.

Environmental Listing

Rivers (Prevention of Pollution) Act 1961. Control of Pollution (Special Waste Regulations) Act 1980. Control of Pollution Act 1974.

Approved Code Of Practice

Classification and Labelling of Substances and Preparations Dangerous for Supply. Safety Data Sheets for Substances and Preparations.

Guidance Notes

Workplace Exposure Limits EH40.

EU Legislation

System of specific information relating to Dangerous Preparations. 2001/58/EC.

Dangerous Substance Directive 67/548/EEC.

Dangerous Preparations Directive 1999/45/EC.

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

BLOC LUBE RED

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

15.2. Chemical Safety Assessment**SECTION 16: OTHER INFORMATION****Revision Comments**

Revised in accordance with CHIP3 and EU Directives 1999/45/EC and 2001/58/EC

Issued By	Helen O'Reilly
Revision Date	NOVEMBER 2012
Revision	7
SDS No.	10801

Risk Phrases In Full

R10	Flammable.
R11	Highly flammable
R36	Irritating to eyes.
R66	Repeated exposure may cause skin dryness or cracking.
R67	Vapours may cause drowsiness and dizziness.

Hazard Statements In Full

EUH066	Repeated exposure may cause skin dryness or cracking.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.

Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.