

## SAFETY DATA SHEET FLUXCLENÉ Aerosol

### SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

#### 1.1. Product identifier

**Product name** FLUXCLENÉ Aerosol  
**Product No.** FLU-a, EFLU200D, EFLU400D, ZE

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Identified uses** Manufacture of electrical equipment  
**Uses advised against** At this moment in time we do not have information on use restrictions. They will be included in this safety data sheet when available

#### 1.3. Details of the supplier of the safety data sheet

**Supplier** ELECTROLUBE. A division of HK  
 WENTWORTH LTD  
 ASHBY PARK, COALFIELD WAY,  
 ASHBY DE LA ZOUCH, LEICESTERSHIRE  
 LE65 1JR  
 UNITED KINGDOM  
 +44 (0)1530 419600  
 +44 (0)1530 416640  
 info@hkw.co.uk

#### 1.4. Emergency telephone number

+44 (0)1530 419600 between 8.30am - 5.00pm GMT Mon – Fri

### SECTION 2: HAZARDS IDENTIFICATION

#### 2.1. Classification of the substance or mixture

##### **Classification (EC 1272/2008)**

Physical and Chemical Hazards	Flam. Aerosol 1 - H222
Human health	Skin Irrit. 2 - H315; Eye Irrit. 2 - H319; Skin Sens. 1 - H317; STOT SE 3 - H336
Environment	Aquatic Acute 1 - H400; Aquatic Chronic 1 - H410

**Classification (1999/45/EEC)** Xi; R36/38. R43. F+; R12. N; R50/53. R67.

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

##### **Environment**

Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment. Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. Use appropriate containment to avoid environmental contamination. Avoid release to the environment. Refer to special instructions/safety data sheets. Dispose of waste and residues in accordance with local authority requirements.

##### **Physical and Chemical Hazards**

Aerosol containers can explode when heated, due to excessive pressure build-up. When sprayed on a naked flame or any incandescent material the aerosol vapours can be ignited.

#### 2.2. Label elements

**Contains** Orange Terpenes

**Label In Accordance With (EC) No. 1272/2008**

# FLUXCLENE Aerosol



Signal Word

Danger

Hazard Statements

H222 Extremely flammable aerosol.  
 H315 Causes skin irritation.  
 H317 May cause an allergic skin reaction.  
 H319 Causes serious eye irritation.  
 H336 May cause drowsiness or dizziness.  
 H410 Very toxic to aquatic life with long lasting effects.

Precautionary Statements

P210 Keep away from heat/sparks/open flames/hot surfaces. - No smoking.  
 P211 Do not spray on an open flame or other ignition source.  
 P251 Pressurized container: Do not pierce or burn, even after use.  
 P280 Wear protective gloves, eye and face protection.  
 P305+351+338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
 P313 Get medical advice/attention.

Supplementary Precautionary Statements

P261 Avoid breathing vapour/spray.  
 P410+412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122°F.  
 P501 Dispose of contents/container to ...

## 2.3. Other hazards

Not Classified as PBT/vPvB by current EU criteria.

## SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS

### 3.2. Mixtures

<b>CYCLOHEXANE</b>		<b>30-60%</b>
CAS-No.: 110-82-7		EC No.: 203-806-2
Classification (EC 1272/2008)	Classification (67/548/EEC)	
Flam. Liq. 2 - H225	F;R11	
Skin Irrit. 2 - H315	Xn;R65	
STOT SE 3 - H336	Xi;R38	
Asp. Tox. 1 - H304	R67	
Aquatic Acute 1 - H400	N;R50/53	
Aquatic Chronic 1 - H410		
<b>PROPAN-2-OL</b>		<b>10-30%</b>
CAS-No.: 67-63-0		EC No.: 200-661-7
Classification (EC 1272/2008)	Classification (67/548/EEC)	
Flam. Liq. 2 - H225	F;R11	
Eye Irrit. 2 - H319	Xi;R36	
STOT SE 3 - H336	R67	

**FLUXCLENE Aerosol**

<b>1-METHOXY-2-PROPANOL</b>		<b>10-30%</b>
<b>CAS-No.: 107-98-2</b>	<b>EC No.: 203-539-1</b>	
Classification (EC 1272/2008) Flam. Liq. 3 - H226 STOT SE 3 - H336	Classification (67/548/EEC) R10 R67	
<b>HEXANE MIXTURE OF ISOMERS (MAX 5% n-HEXANE (203-777-6))</b>		<b>5-10%</b>
<b>CAS-No.: -</b>	<b>EC No.: -</b>	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Skin Irrit. 2 - H315 STOT SE 3 - H336 Asp. Tox. 1 - H304 Aquatic Chronic 2 - H411	Classification (67/548/EEC) F;R11 Xn;R65 Xi;R38 R67 N;R51/53	
<b>Orange Terpenes</b>		<b>1-5%</b>
<b>CAS-No.: 8028-48-6</b>	<b>EC No.: 232-433-8</b>	
Classification (EC 1272/2008) Flam. Liq. 3 - H226 Skin Irrit. 2 - H315 Skin Sens. 1 - H317 Asp. Tox. 1 - H304 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410	Classification (67/548/EEC) Xn;R65. Xi;R38. N;R50/53. R10,R43.	
<b>HEPTANE</b>		<b>1-5%</b>
<b>CAS-No.: 142-82-5</b>	<b>EC No.: 205-563-8</b>	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Skin Irrit. 2 - H315 STOT SE 3 - H336 Asp. Tox. 1 - H304 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410	Classification (67/548/EEC) F;R11 Xn;R65 Xi;R38 R67 N;R50/53	
<b>HEXANE-norm</b>		<b>&lt; 1%</b>
<b>CAS-No.: 110-54-3</b>	<b>EC No.: 203-777-6</b>	
Classification (EC 1272/2008) Flam. Liq. 2 - H225 Skin Irrit. 2 - H315 Repr. 2 - H361f STOT SE 3 - H336 STOT RE 2 - H373 Asp. Tox. 1 - H304 Aquatic Chronic 2 - H411	Classification (67/548/EEC) F;R11 Repr. Cat. 3;R62 Xn;R48/20,R65 Xi;R38 R67 N;R51/53	

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

# FLUXCLENE Aerosol

## Composition Comments

Ingredients not listed are classified as non-hazardous or at a concentration below reportable levels.

## SECTION 4: FIRST AID MEASURES

### 4.1. Description of first aid measures

#### Inhalation

Move the exposed person to fresh air at once. Keep the affected person warm and at rest. Get prompt medical attention. Get medical attention.

#### Ingestion

Not relevant

#### Skin contact

Wash the skin immediately with soap and water. Get medical attention if any discomfort continues.

#### Eye contact

Make sure to remove any contact lenses from the eyes before rinsing. Promptly wash eyes with plenty of water while lifting the eye lids. Continue to rinse for at least 15 minutes. Get medical attention if any discomfort continues.

### 4.2. Most important symptoms and effects, both acute and delayed

### 4.3. Indication of any immediate medical attention and special treatment needed

Treat Symptomatically.

## SECTION 5: FIREFIGHTING MEASURES

### 5.1. Extinguishing media

#### Extinguishing media

Use: Powder. Dry chemicals, sand, dolomite etc. Water spray, fog or mist.

### 5.2. Special hazards arising from the substance or mixture

#### Hazardous combustion products

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

#### Unusual Fire & Explosion Hazards

Extremely flammable. Aerosol cans may explode in a fire.

#### Specific hazards

Aerosol containers can explode when heated, due to excessive pressure build-up. Vapours may be ignited by a spark, a hot surface or an ember. The product is flammable, and heating may generate vapours which may form explosive vapour/air mixtures.

### 5.3. Advice for firefighters

#### Special Fire Fighting Procedures

Move container from fire area if it can be done without risk. Water spray should be used to cool containers.

#### Protective equipment for fire-fighters

Self contained breathing apparatus and full protective clothing must be worn in case of fire.

## SECTION 6: ACCIDENTAL RELEASE MEASURES

### 6.1. Personal precautions, protective equipment and emergency procedures

Wear protective clothing as described in Section 8 of this safety data sheet.

### 6.2. Environmental precautions

Do not discharge into drains, water courses or onto the ground.

### 6.3. Methods and material for containment and cleaning up

Extinguish all ignition sources. Avoid sparks, flames, heat and smoking. Ventilate. Absorb in vermiculite, dry sand or earth and place into containers.

### 6.4. Reference to other sections

Wear protective clothing as described in Section 8 of this safety data sheet. See section 11 for additional information on health hazards. The product contains a substance which is hazardous to aquatic organisms and which may cause long term adverse effects in the aquatic environment. See section 12 as well. For waste disposal, see section 13.

## SECTION 7: HANDLING AND STORAGE

# FLUXCLENE Aerosol

## 7.1. Precautions for safe handling

Avoid spilling, skin and eye contact. Provide good ventilation.

## 7.2. Conditions for safe storage, including any incompatibilities

Store at moderate temperatures in dry, well ventilated area.

## 7.3. Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

## SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

### 8.1. Control parameters

Name	STD	TWA - 8 Hrs		STEL - 15 Min		Notes
1-METHOXY-2-PROPANOL	WEL	100 ppm	375 mg/m <sup>3</sup>	150 ppm	560 mg/m <sup>3</sup>	Sk
CYCLOHEXANE	WEL	100 ppm	350 mg/m <sup>3</sup>	300 ppm	1050 mg/m <sup>3</sup>	
HEPTANE	WEL	500 ppm				
PROPAN-2-OL	WEL	400 ppm	999 mg/m <sup>3</sup>	500 ppm	1250 mg/m <sup>3</sup>	

WEL = Workplace Exposure Limit.

Sk = Can be absorbed through skin.

#### PROPAN-2-OL (CAS: 67-63-0)

##### DNEL

Industry	Dermal	888	mg/kg/day
Industry	Inhalation.	500	mg/m <sup>3</sup>
Consumer	Dermal	319	mg/kg/day
Consumer	Inhalation.	89	mg/m <sup>3</sup>
Consumer	Oral	26	mg/kg/day

##### PNEC

Freshwater	140.9	mg/l
Marinewater	140.9	mg/l
Sediment	552	mg/kg
Soil	28	mg/kg

### 8.2. Exposure controls

#### Protective equipment



#### Process conditions

Use engineering controls to reduce air contamination to permissible exposure level. Provide eyewash station.

#### Engineering measures

Provide adequate ventilation, including appropriate local extraction, to ensure that the defined occupational exposure limit is not exceeded.

#### Respiratory equipment

In case of inadequate ventilation and work of brief duration, use suitable respiratory equipment. Use respiratory equipment with combination filter, type A2/P3. EN14387

#### Hand protection

Protective gloves must be used if there is a risk of direct contact or splash. The most suitable glove must be chosen in consultation with the gloves supplier, who can inform about the breakthrough time of the glove material. Nitrile gloves are recommended. Gloves should conform to EN374

#### Eye protection

Wear approved, tight fitting safety glasses where splashing is probable. EN166

#### Other Protection

Wear appropriate clothing to prevent any possibility of liquid contact and repeated or prolonged vapour contact.

#### Hygiene measures

Wash hands at the end of each work shift and before eating, smoking and using the toilet. Promptly remove any clothing that becomes contaminated. Use appropriate skin cream to prevent drying of skin. When using do not eat, drink or smoke. DO NOT SMOKE IN WORK AREA!

**SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES**

**9.1. Information on basic physical and chemical properties**

Appearance	Aerosol. Liquid
Colour	Colourless.
Odour	Lemon.
Solubility	Insoluble in water
Initial boiling point and boiling range (°C)	>80 (176 F)
Melting point (°C)	<-29 (-20.2 F)
Relative density	0.780 @ 20 °C (68 F)
Vapour pressure	11.52 kPa @ 20 °C (68 F)
Flash point (°C)	0 (32 F) CC (Closed cup).
Auto Ignition Temperature (°C)	> 200 (392 F)
Flammability Limit - Lower(%)	0.6
Flammability Limit - Upper(%)	8.3

**9.2. Other information**

None.

Volatility Description                      Volatile

**SECTION 10: STABILITY AND REACTIVITY**

**10.1. Reactivity**

There are no known reactivity hazards associated with this product.

**10.2. Chemical stability**

Stable under normal temperature conditions.

**10.3. Possibility of hazardous reactions**

Not determined.

**Hazardous Polymerisation**

Will not polymerise.

**10.4. Conditions to avoid**

Avoid heat, flames and other sources of ignition. Avoid contact with acids and alkalis.

**10.5. Incompatible materials**

**Materials To Avoid**

Strong oxidising substances.

**10.6. Hazardous decomposition products**

Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

**SECTION 11: TOXICOLOGICAL INFORMATION**

**11.1. Information on toxicological effects**

**Other Health Effects**

This substance has no evidence of carcinogenic properties.

**Inhalation**

Vapours may cause headache, fatigue, dizziness and nausea. High concentrations of vapours may irritate respiratory system and lead to headache, fatigue, nausea and vomiting.

**Skin contact**

May cause sensitisation by skin contact. Prolonged or repeated exposure may cause severe irritation. Product has a defatting effect on skin. Prolonged contact may cause dryness of the skin.

# FLUXCLENE Aerosol

## Eye contact

Irritating to eyes.

## Route of entry

Skin and/or eye contact. Inhalation.

### Toxicological information on ingredients.

#### HEPTANE (CAS: 142-82-5)

##### Toxic Dose 1 - LD 50

222 mg/kg (ivn-mouse)

##### Toxic Conc. - LC 50

103 ppm/4h (inh-rat)

#### CYCLOHEXANE (CAS: 110-82-7)

##### Toxic Dose 1 - LD 50

12705 mg/kg (oral rat)

##### Toxic Dose 2 - LD 50

813 mg/kg (oral-mouse)

#### HEXANE-norm (CAS: 110-54-3)

##### Toxic Dose 1 - LD 50

28700 mg/kg (oral rat)

##### Toxic Conc. - LC 50

48000 ppm/4h (inh-rat)

#### PROPAN-2-OL (CAS: 67-63-0)

### Acute toxicity:

#### Acute Toxicity (Oral LD50)

5280 mg/kg Rat

#### Acute Toxicity (Dermal LD50)

12800 mg/kg Rabbit

#### Acute Toxicity (Inhalation LC50)

72.6 mg/l (vapours) Rat 4 hours

#### 1-METHOXY-2-PROPANOL (CAS: 107-98-2)

##### Toxic Dose 1 - LD 50

5200 mg/kg (oral rat)

##### Toxic Dose 2 - LD 50

11700 mg/kg (oral-mouse)

#### Orange Terpenes (CAS: 8028-48-6)

### Acute toxicity:

#### Acute Toxicity (Oral LD50)

5300 mg/kg Rat

#### Acute Toxicity (Dermal LD50)

> 5000 mg/kg Rabbit

## SECTION 12: ECOLOGICAL INFORMATION

### Ecotoxicity

Dangerous for the environment if discharged into watercourses.

### 12.1. Toxicity

# FLUXCLENE Aerosol

## Ecological information on ingredients.

### HEPTANE (CAS: 142-82-5)

LC 50, 96 Hrs, Fish mg/l  
4.924

### CYCLOHEXANE (CAS: 110-82-7)

LC 50, 96 Hrs, Fish mg/l  
42.3

### PROPAN-2-OL (CAS: 67-63-0)

#### Acute Toxicity - Fish

LC50 96 hours 9640 mg/l Pimephales promelas (Fat-head Minnow)

#### Acute Toxicity - Aquatic Invertebrates

EC50 48 hours 13299 mg/l Daphnia magna

#### Acute Toxicity - Aquatic Plants

EC50 72 hours > 1.000 mg/l Scenedesmus subspicatus

#### Acute Toxicity - Microorganisms

EC50 > 1.000 mg/l Activated sludge

### 1-METHOXY-2-PROPANOL (CAS: 107-98-2)

LC 50, 96 Hrs, Fish mg/l  
20800  
EC 50, 48 Hrs, Daphnia, mg/l  
23300

### Orange Terpenes (CAS: 8028-48-6)

#### Acute Toxicity - Fish

LC50 96 hours 0.71 mg/l Pimephales promelas (Fat-head Minnow)

#### Acute Toxicity - Aquatic Invertebrates

EC50 0.4 mg/l Daphnia magna

#### Acute Toxicity - Aquatic Plants

IC50 4 mg/l Selenastrum capricornutum

## 12.2. Persistence and degradability

### Degradability

There are no data on the degradability of this product.

## 12.3. Bioaccumulative potential

### Bioaccumulative potential

No data available on bioaccumulation.

## 12.4. Mobility in soil

## 12.5. Results of PBT and vPvB assessment

This product does not contain any PBT or vPvB substances.

## 12.6. Other adverse effects

## SECTION 13: DISPOSAL CONSIDERATIONS

### General information

Waste is classified as hazardous waste. Disposal to licensed waste disposal site in accordance with the local Waste Disposal Authority.

### 13.1. Waste treatment methods

Dispose of waste and residues in accordance with local authority requirements. Empty containers must not be burned because of explosion hazard.

## SECTION 14: TRANSPORT INFORMATION

### General

This product is packed in accordance with the Limited Quantity Provisions of CDGCPL2, ADR and IMDG. These provisions allow transport of aerosols of less than 1litre packed in cartons of less than 30kg gross to be exempt from control providing that they are labelled in accordance with the requirements of these regulations to show that they are being transported as Limited Quantities. Aerosols not so packed must show the following



# FLUXCLENE Aerosol

## 14.1. UN number

UN No. (ADR/RID/ADN)	1950
UN No. (IMDG)	1950
UN No. (ICAO)	1950

## 14.2. UN proper shipping name

Proper Shipping Name AEROSOLS (CYCLOHEXANE)

## 14.3. Transport hazard class(es)

ADR/RID/ADN Class	2.1
ADR/RID/ADN Class	Class 2: Gases
ADR Label No.	2.1
IMDG Class	2.1
ICAO Class/Division	2.1
Transport Labels	



## 14.4. Packing group

Not applicable.

## 14.5. Environmental hazards

Environmentally Hazardous Substance/Marine Pollutant



## 14.6. Special precautions for user

EMS	F-D, S-U
Tunnel Restriction Code	(D)

## 14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Not applicable.

## SECTION 15: REGULATORY INFORMATION

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### Statutory Instruments

The Chemicals (Hazard Information and Packaging for Supply) Regulations 2009 (S.I. 2009 No. 716). Control of Substances Hazardous to Health.

#### Guidance Notes

Workplace Exposure Limits EH40.

#### EU Legislation

Commission Directive 2000/39/EC of 8 June 2000 establishing a first list of indicative occupational exposure limit values in implementation of Council Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work.

# FLUXCLENÉ Aerosol

Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency, amending Directive 1999/45/EC and repealing Council Regulation (EEC) No 793/93 and Commission Regulation (EC) No 1488/94 as well as Council Directive 76/769/EEC and Commission Directives 91/155/EEC, 93/67/EEC, 93/105/EC and 2000/21/EC, including amendments.

Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006 with amendments.

## Authorisations (Title VII Regulation 1907/2006)

No specific authorisations are noted for this product.

## Restrictions (Title VIII Regulation 1907/2006)

No specific restrictions of use are noted for this product.

## 15.2. Chemical Safety Assessment

No chemical safety assessment has been carried out.

## SECTION 16: OTHER INFORMATION

<b>Issued By</b>	Helen O'Reilly
<b>Revision Date</b>	APRIL 2013
<b>Revision</b>	6
<b>SDS No.</b>	10371
<b>Risk Phrases In Full</b>	
R12	Extremely flammable.
R10	Flammable.
R48/20	Harmful: danger of serious damage to health by prolonged exposure through inhalation.
R65	Harmful: may cause lung damage if swallowed.
R11	Highly flammable
R36/38	Irritating to eyes and skin.
R36	Irritating to eyes.
R38	Irritating to skin.
R43	May cause sensitisation by skin contact.
R62	Possible risk of impaired fertility.
R51/53	Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
R67	Vapours may cause drowsiness and dizziness.
R50/53	Very toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.
<b>Hazard Statements In Full</b>	
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H226	Flammable liquid and vapour.
H304	May be fatal if swallowed and enters airways.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H361f	Suspected of damaging fertility.
H373	May cause damage to organs <<Organs>> through prolonged or repeated exposure.
H400	Very toxic to aquatic life.
H410	Very toxic to aquatic life with long lasting effects.
H411	Toxic to aquatic life with long lasting effects.

### Disclaimer

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.