


## BATTERY & ALTERNATOR ANALYSER

(GB)

41026

## 1.1 IDENTIFICATION

- ① 1 5.0V POOR 2 12.0V FAIR
- Battery Check
  - Battery Check
  - 3 12.5V GOOD
- Battery Check
- 4 13.0V LOW
- Alternator Check
- 5 13.5V NORMAL Alternator Check 6 14.0V STRONG - Alternator Check
- 2 Magnet
- 3 BLACK Negative (–) spring clip
- 4 RED Positive (+) terminal probe



## 1.2 TO CHECK THE CONDITION OF A BATTERY

- · Make sure terminals are clean.
- · Secure the tester to a suitable location, use magnetic back.
- Connect the black lead to the (-) negative terminal using the spring clip.
- Place the red lead on the (+) positive terminal holding the probe by the rubber insulated grip:



If the battery is in good condition 3 LED's will illuminate



If in a poor state, only 1 or 2 LED's will activate



It is possible that large capacity batteries will light up 4 LED's when in good condition, this is normal

To get a better indication of the battery condition , it is advisable to disconnect the tester, then turn the headlights on for about 2 minutes, then re-test for drain of power.

## 1.3 TO CHECK THE ALTERNATOR

- Connect the black lead to (–) terminal of the alternator.
- Start the engine idling around 2000 RPM or higher.
- Place the red probe on the (+) terminal of the alternator.



If the alternator is working correctly all 6 LED's will illuminate.

Helpline: +44 (0) 23 8049 4344 Sales Desk: +44 (0) 23 8049 4333 General Enquiries: +44 (0) 23 8026 6355 internet: drapertools.com email: sales@drapertools.com