

Order code	Manufacturer code	Description
87-1812	n/a	KAPTON TAPE 12MM X 33M (RE)
87-1814	n/a	KAPTON TAPE 19MM X 33M (RE)
87-1816	n/a	KAPTON TAPE 25MM X 33M (RE)

	Page 1 of 2
The enclosed information is believed to be correct, Information may change without notice due to product improvement. Users should ensure that the product is suitable for their use. E. & O. E.	Revision A 20/02/2007

DATA SHEET

POLYIMIDE SILICONE TAPE

DESCRIPTION
CCSNT590LC is a polyimide film coated with a silicone adhesive

MAIN CHARACTERISTICS

Adhesive Type		Silicone
Insulation Classification		H
Temperature resistance (°C)		260
Backing Thickness (μ)		25 (Kapton®)
Total Thickness (μ)		63.5
Adhesion to steel (Kg per cm)		0.3
Breaking Strength (Kg per cm)		5.4
Elongation at break (%)		60
Dielectric Strength (Volts)		7500
UL Approval		E113238
Electrical resistance		1.5 10

All values shown are approximate and are intended solely as a guide. No responsibility is accepted for their accuracy. It is the users responsibility to determine the suitability of the product for the intended application.