SAFETY DATA SHEET

Product Name: Alkaline Battery 6LR61 9V Issue Date: 01/04/2022

SECTION 1: Identification of the substance/mixture and of the company/undertaking

PRODUCT NAME: Alkaline Battery 6LR61 9V

APPLICATIONS: For Stock No.

03981 PP3 (9V) BATTERIES - PACK OF 4 03983 PP3 (9V) BATTERIES - PACK OF 2

SUPPLIER: Draper Tools Ltd

Hursley Road Chandlers Ford Eastleigh Hampshire SO53 1YF

Draper Helpline +44 (0) 2380 494344 Opening hours 8:30-17:00 Monday – Friday.

www.drapertools.com

SECTION 2: Hazards identification

Emergency overview: This product is a battery. Intended use of the product should not result in exposure to The chemical substance. In case of rupture the below hazards exist.

Classification according to GHS

Acute toxicity, oral (4)

Acute toxicity, inhalation: Dusts and mists (4)

Skin corrosion/irritation (1A, 1B, 1C)

Specific target organ toxicity, single exposure (2)

Hazardous to the aquatic environment, long-term hazard (2)

Label elements





Hazard pictogram(s)

Signal word: Danger

Hazard statement(s)

H302 Harmful if swallowed

H332 Harmful if inhaled

H314 Causes severe skin burns and eye damage

H373 May cause damage to organs through prolonged or repeated exposure

H411 Toxic to aquatic life with long lasting effects

Precautionary statement(s):

Prevention:

P201 Obtain special instructions before use.

P202 Do not handle until all safety precautions have been read and understood.

P260 Do not breathe dusts or mists.

P264 Wash skin and clothing thoroughly after handling.

P270 Do not eat, drink or smoke when using this product.

P271 Use only outdoors or in a well-ventilated area.

P273 Avoid release to the environment.

P280 Wear protective gloves, protective clothing, eye protection, face protection.

Response:

P330 Rinse mouth.

P304 + P340 IF INHALED: Remove person to fresh air and keep comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER.

P301 + P330 + P331 IF SWALLOWED: Rinse mouth. Do NOT vomiting.

P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water

P363 Wash contaminated clothing before reuse.

P321 Specific treatment (See additional emergency instructions).

P391 Collect spillage.

Storage

P405 Store locked up.

Disposal:

P501 Send contents to approved waste treatment plants.

SECTION 3: Composition/information on ingredients

Chemical characterization: Mixture

Chemical Composition	CAS No.	EC#	Weight (%)
Manganese dioxide	1313-13-9	215-202-6	35
Potassium hydroxide	1310-58-3	215-181-3	18
Zinc	7440-66-6	231-175-3	16
Iron	7439-89-6	231-096-4	15
Copper	7440-50-8	231-159-6	6
Graphite	7782-42-5	231-955-3	5
Water	7732-18-5	231-791-2	5

SECTION 4: First aid measures

Description of first aid measures

General information No special measures required.

After eye contact

Flush eyes with plenty of water for several minutes while holding eyelids open. Get medical attention if irritation persists.

After skin contact

Remove contaminated clothing and shoes. Immediately wash with water and soap and rinse thoroughly. Wash clothing and shoes before reuse. If irritation occurs, get medical attention.

After inhalation

Remove victim to fresh area. Administer artificial respiration if breathing is difficult. Seek medical attention.

After swallowing

Do not induce vomiting. Get me medical attention.

Personal protective equipment for first-aid responders: No data available.

Most important symptoms/effects, acute and delayed: No data available.

Indication of immediate medical attention and special treatment needed: Treat symptomatically.

SECTION 5: Firefighting measures

Suitable extinguishing media:

Use extinguishing agent suitable for local conditions and the surrounding environment. Such as dry powder, CO₂.

Unsuitable extinguishing media:

No date available.

Specific hazards arising from the chemical:

Specific hazards arising from the substance or mixture

Battery may trust and release hazardous decomposition products when exposed to a fire situation.

Some may burn but none ignite readily. Containers may explode when heated. Some may be transported hot.

Specific protective actions for fire-fighters:

Protective equipment: Wear self-contained respirator. Wear fully protective impervious suit.

SECTION 6: Accidental release measure

Person precautions:

Wear protective equipment. Keep unprotected persons away. Ensure adequate ventilation.

Protective equipment:

No date available.

Emergency procedures:

Remove ignition sources, evacuate area. Sweep up using a method that does not generate dust.

Collect as much of the spilled material as possible, place the spilled material into a suitable disposal container. Keep spilled material out of sewers, ditches and bodies of water.

Environmental precautions:

Do not allow material to be released to the environment without proper governmental permits.

Methods and materials for containment and cleaning up:

For all waste handling must refer to United Nations, National and Local Regulations for disposal.

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

SECTION 7: Handling and storage

Precuations for safe handling:

Avoid short circuiting the battery. Avoid mechanical damage of the battery. Do not open or disassemble. Batteries may explode or cause burns. If disassembled, crushed or exposed to fire or high temperatures. Do not short or install with incorrect plarity. Avoid all personal contact, including inhalation. Wear protective clothing when risk of exposure occurs. Use in a well-ventilated area.

Prevent concentration in hollows and sumps.

Conditions for safe storage, including any incompatibilities:

Store in a cool, dry, well-ventilated place. Keep away from heart, avoiding the long time of sunlight.

SECTION 8: Exposure controls/personal protection

Control parameters

CAS No.	ACGIH	NIOSH	OSHA
1313-13-9	N/A	N/A	N/A
1310-58-3	TLV-Peak 2mg/m3	REL-Peak 2mg/m3	N/A
7440-66-6	N/A	N/A	N/A
7439-89-6	N/A	N/A	N/A
7440-50-8	TLV-TWA 0.2mg/m3 TLV-TWA 1mg/m3	REL-TWA 1mg/m3 REL-TWA 0.1mg/m3	REL-TWA 0.1mg/m3 REL-TWA 1mg/m3
7782-42-5	TLV-TWA 2mg/m3	REL-TWA 2.5mg/m3	REL-TWA 15mg/m3 REL-TWA 20mg/m3
7732-18-5	N/A	N/A	N/A

Appropriate engineering controls:

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Remove all soiled and contaminated clothing immediately.

Wash hands before breaks and at the end of work.

Personal protective equipment:

Respiratory protection: Wear suitable protective mask. For a large number of battery leakages, wear chemical protective clothing, including self-contained breathing apparatus.

Hand Protection: Wear appropriate protective gloves to reduce skin contact.

Eye Protection: Wear safety goggles or eye protection combined with respiratory protection.

Skin and Body Protection: Working environment required, wear suitable protective clothing to minimize contact with skin. The type of protective equipment must be according to the concentration and the content of certain harzardous substances in the workplace.

SECTION 9: Physical and chemical properties

Information on basic physical and chemical properties

Colour: Blue and silver
Physica State: Cylinddrical
Odour: Not available.

PH: Not available.

Melting point/freezing point: Not available.

Boiling point or initial boilindg point and boiling Not available.

range:

Flash point:Not available.Flammability:Not available.Solubility:Not available.

Lower and upper explosion limit/flammability limit: Not available. Not available. Auto-ignition temperature: **Decomposition temperature:** Not available. Kinematic viscosity: Not available. Partition coefficient: n-octanol/water (log value): Not available. Not available. Vapour pressure: Density and /or relative density: Not available. Relative vapour density: Not available. Particle characteristics: Not available.

Other information:

Voltage 1.5V

SECTION 10: Stability and reactivity

Reactivity: No data available Chemical stability: stable

Possibility of hazardous reactions: No data available

Conditions to Avoid: Flames, sparks, and other sources of ignition, incompatible materials.

Incompatible materials: oxidizing agents, acid base.

Hazardous decompositon products: Carbon monxide, carbon dioxide.

SECTION 11: Toxicological information

Acute Toxicity:

rioute remote.		
CAS No.	LC50/LD50	
1313-13-9	No data available.	
1310-58-3	LD50 Rat (oral): 284mg/kg	
7440-66-6	LD50 Rat (oral): >2000mg/kg	
7439-89-6	No data available.	
7440-50-8	No data available.	
7782-42-5	No data available.	
7732-18-5	No data available.	

Skin corrosion/irritation: No data available.
Serious eye damage/irritation: No data available
Respiratory or skin sensitization: No data available

Germ Cell mutagenicity: No data available

Carcinogenicity: No data available Reproductive toxicity: No data available

Specific target organ toxicity-Single exposure: No data available Specific target organ toxicity-Repeated exposure: No data available

Aspiration hazard: No data available

Information on the likely routes of exposure: No data available

Eye: No data available
Skin: No data available
Ingestion: No data available
Inhalation: No data available

SECTION 12: Ecological information

Ecological Toxicity: CAS#7440-66-6

ErC50: 0.15mg/L-algae (Pseudokirchneriella subcapitata) – 72h

Persistence and degradability: No data available. Bioaccumulative Potential: No data available

Mobility in Soil: No data available

Other adverse effects: No data available

SECTION 13: Disposal considerations

Disposal methods: Recommendtion:

Consult state, local or national regulations to ensure proper disosal.

Uncleaned packaging

Recommendation: Disposal must be made according to offical regulations.

SECTION 14: Transport information

UN or ID Number	
IATA, IMDG, Model Regulation	N/A
Proper Shipping Name/Description	
IATA, IMDG, Model Regulation	N/A
Class or Div. (Sub Hazard)	
IATA, IMDG, Model Regulation	Not Subjected for transport of dangerous goods
Packing Group	
IATA, IMDG, Model Regulation	N/A
Hazard Label	
IATA, IMDG, Model Regulation	N/A
Environmental hazards	
Marine pollutant	No
Special precautions for user	No information available

Transport information: Alkaline Battery 6LR61 9V is exempt from dangerous goods. It is considered non-dangerous goods by the International Civil Aviation Organization (ICAO), the International Air Transport Association (IATA) DGR 63rd, IATA Special Provisions A123, International Martine Dangerous Goods Regulations (IMDG) (40-20) or the <Recommendations on the Transport of Dangerous Goods Model Regulation> (22nd).

S.P.A123 This entry applies to Batteries, electric storage, not otherwise listed in Subsection 4.2-List of Dangerous Goods. Examples of such batteries are: alkali-manganese, zinc-carbon and nickel-cadmium batteries. Any electrical battery or battery powered device, equipment or vehicle having the potential of a dangerous evolution of heat must be prepared for transport so as to prevent;

(a) a short-circuit (e.g. in the case of batteries, by the effective insulation of exposed terminals: or in the case of equipment, by disconnection of the battery and protection of exposed terminals); and (b) accidental activation.

The words "Not Restricted", and the Special Provision number must be included in the description of the substance on the Air Waybill as required by 8.2.6, when an Air Waybill is issued.

Separate batteries when shipping to prevent short-circuiting. They should be packed in strong packaging for support during transport.

Transport Fashion: By air, by sea, by railway, by road.

SECTION 15: Regulatory information

Safety, health and environmental regulations/legislation specific for the substance or mixture

CAS No.	TSCA	IECSC	DSL/NDSL	EINECS/ELINCS/NLP
1313-13-9	Listed	Listed	Listed DSL	Listed
1310-58-3	Listed	Listed	Listed DSL	Listed
7440-66-6	Listed	Listed	Listed DSL	Listed
7439-89-6	Listed	Listed	Listed DSL	Listed
7440-50-8	Listed	Listed	Listed DSL	Listed
7782-42-5	Listed	Listed	Listed DSL	Listed
7732-18-5	Listed	Listed	Listed DSL	Listed

SECTION 16: Other information

Issue Date: 2022-01-04

Issure Department: Technical department

Modification record:

Notice to reader

To the best of our knowledge, the information contained herein is accurate. However, neither the above named supplier nor any of its subsidiaries assumes and liability whatsoever for the accuracy or completeness of the informatio conained herein.

Final determination of suitability of any material is the sole resposibility of the user. All materials may present unknown hazards and should be used with caution. Although certain hazards are described herein, we cannot guarantee that these are the only hazards that exist.

Other Information:

CAS: (Chemical Abstracts Service);

EC: (European Commission);

ACGIH: (American Conference of Governmental Industial Hygiensits);

NIOSH: (US National Institute for Occupational Safety and health);

OSHA: (US Occupational Safety and Health);

TLV: (Threshold Limit Value);

TWA: (Time Weighted Average);

STEL: (Short Term Exposure Limit);

PEL: (Permissible Exposure Level);

REL: (Recommended Exposure Limit);

PC-STEL: (Permissible concentration-short time exposure limit);

PC-TWA: (Permissible concentratin-time weighted average);

IARC: (Internatinal Agency for Research on Cancer);

LC50: (Lethal concentration, 50 percent kill);

LD50: (Lethal dose, 50 percent kill);

EC50: (Median effective concentration);

BCF: (Bioconcentration Factor).

BOD: (Biochemical oxygen demand);

IECSC: (Inventory of Existing Chemical Substances in China);

NOEC: (No observed effect concentratin);

NTP: (US National Toxicology Program);

RTECS: (Registry of Toxic Effects of Chemical Substances);

TOC: (Total Organic Carbon);

TSCA: (Toxic Substances Control Act of USA);

DSL: (the Domestic Substances List of Canada);

NDSL: (the Non-domestic Substances List of Canada);

IATA: (Internatinal Air Transport Association);

IMDG: (Internatinal Maritime Dangerous Goods);

TDG: (Recommendations on the TRANSPORT OF DANGEROUS GOODS Model Regulations)

--- End of report ---