

BOSTIK LEATHER ADHESIVE
Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

Section 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

1.1. Product Identifier

Product Name BOSTIK LEATHER ADHESIVE
Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Adhesives.
Uses advised against None known

1.3. Details of the supplier of the safety data sheet

Company Name

Bostik Limited
Common Rd
ST16 3EH
Stafford UK
Tel: +44 (1785) 27 26 25
Fax: +44 (1785) 25 72 36

E-mail address SDS.box-EU@bostik.com

1.4. Emergency telephone number

United Kingdom	+44 (1785) 272650
Ireland	+353 (1) 8624900 (Monday- Friday 9am-5pm)

Section 2: HAZARD IDENTIFICATION

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Serious eye damage/eye irritation	Category 2 - (H319)
Skin sensitisation	Category 1 - (H317)
Specific target organ toxicity (single exposure)	Category 3 - (H336)
Chronic aquatic toxicity	Category 3 - (H412)
Flammable Liquids	Category 2 - (H225)

2.2. Label Elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Contains Bisphenol-A-Epichlorhydrin Epoxy resin <= 700 MW, Methyl ethyl ketone, Acetone



Signal Word

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supercedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

DANGER

Hazard statements

H319 - Causes serious eye irritation
H336 - May cause drowsiness or dizziness
H317 - May cause an allergic skin reaction
H412 - Harmful to aquatic life with long lasting effects
H225 - Highly flammable liquid and vapour

Special provisions concerning the labelling of certain mixtures

EUH066 - Repeated exposure may cause skin dryness or cracking
EUH205 - Contains epoxy constituents. May produce an allergic reaction

Precautionary Statements - EU (§28, 1272/2008)

P101 - If medical advice is needed, have product container or label at hand
P102 - Keep out of reach of children
P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking
P271 - Use only outdoors or in a well-ventilated area
P273 - Avoid release to the environment
P280 - Wear protective gloves and eye/face protection
P302 + P350 - IF ON SKIN: Gently wash with plenty of soap and water
P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing
P403 + P233 - Store in a well-ventilated place. Keep container tightly closed
P501 - Dispose of contents/ container to an approved waste disposal plant

Additional information

This product requires tactile warnings if supplied to the general public

2.3. Other Hazards

General Hazards

In use may form flammable/explosive vapour-air mixture.

PBT and vPvB assessment

The components in this formulation do not meet the criteria for classification as PBT or vPvB

Section 3: COMPOSITION/INFORMATION ON INGREDIENTS

3.1 Substances

Mixture

3.2 Mixtures

Chemical Name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH Registration Number
Methyl ethyl ketone	201-159-0	78-93-3	>25 - <40	Eye Irrit. 2 (H319) STOT SE 3 (H336) Flam. Liq. 2 (H225) (EUH066)		01-2119457290-43 -XXXX
Acetone	200-662-2	67-64-1	>25 - <40	Eye Irrit. 2 (H319) STOT SE 3 (H336) Flam. Liq. 2 (H225) (EUH066)		01-2119471330-49 -XXXX
Bisphenol-A-Epichlorhydrin Epoxy resin <= 700 MW	500-033-5	25068-38-6	1 - <5	Skin Irrit. 2 (H315) Eye Irrit. 2 (H319) Skin Sens. 1 (H317) Aquatic Chronic 2	Eye Irrit. 2 :: C>=5% Skin Irrit. 2 :: C>=5%	01-2119456619-26 -xxxx

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

				(H411)		
--	--	--	--	--------	--	--

Full text of H- and EUH-phrases: see section 16

Note: ^ indicates not classified, however, the substance is listed in section 3 as it has an OEL.

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

Section 4: FIRST AID MEASURES

4.1. Description of first aid measures

General Advice	If medical advice is needed, have product container or label at hand.
Inhalation	Remove to fresh air.
Skin Contact	Wash with plenty of soap and water. If skin irritation occurs: Get medical advice/ attention.
Eye contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Call a doctor immediately.
Ingestion	If swallowed, do not induce vomiting: seek medical advice immediately and show this container or label.
Self-protection of the first aider	Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms None known.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors Treat symptomatically.

Section 5: FIRE-FIGHTING MEASURES

5.1. Extinguishing media

Suitable Extinguishing Media

Use CO₂, dry chemical, or foam. Move containers from fire area if you can do it without risk.

Unsuitable Extinguishing Media

Use water spray or fog; do not use straight streams

5.2. Special hazards arising from the substance or mixture

Carbon monoxide, carbon dioxide and unburned hydrocarbons (smoke).

5.3. Advice for firefighters

Wear self contained breathing apparatus for fire fighting if necessary.

Section 6: ACCIDENTAL RELEASE MEASURES

6.1. Personal precautions, protective equipment and emergency procedures

Personal Precautions

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

Remove all sources of ignition. Evacuate personnel to safe areas. Ensure adequate ventilation, especially in confined areas.

Water spray may reduce vapour; but may not prevent ignition in closed spaces.

For emergency responders

Use personal protection recommended in Section 8. Isolate the hazard area and deny entry to unnecessary and unprotected personnel.

6.2. Environmental precautions

Do not empty into drains, dispose of this material and its container at hazardous or special waste collection point. See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for Containment Dyke far ahead of spill; use dry sand to contain the flow of material. Contain and collect spillage with non-combustible absorbent material, (e.g. sand, earth, diatomaceous earth, vermiculite) and place in container for disposal according to local / national regulations (see Section 13).

Methods for cleaning up Use clean non-sparking tools to collect absorbed material. Dyke far ahead of liquid spill for later disposal.

6.4. Reference to other sections

Reference to other sections See Section 12: ECOLOGICAL INFORMATION
Section 7: HANDLING AND STORAGE
Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

Section 7: HANDLING AND STORAGE

7.1. Precautions for safe handling

Advice on safe handling

Keep away from heat/sparks/open flames/hot surfaces. — No smoking. Take precautionary measures against static charges. Use explosion-proof electrical/ventilating/lighting /equipment.

General Hygiene Considerations

Do not eat, drink or smoke when using this product. Regular cleaning of equipment, work area and clothing is recommended.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions

Keep only in the original container/package in a cool well-ventilated place.

7.3. Specific end use(s)

Other Information

Recommendation(s). Observe technical data sheet.

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1. Control parameters

Chemical Name	European Union	Ireland	United Kingdom
Methyl ethyl ketone 78-93-3	TWA: 200 ppm TWA: 600 mg/m ³ STEL: 300 ppm STEL: 900 mg/m ³	TWA: 200 ppm TWA: 600 mg/m ³ STEL: 300 ppm STEL: 900 mg/m ³ Skin	STEL: 300 ppm STEL: 899 mg/m ³ TWA: 200 ppm TWA: 600 mg/m ³ Skin
Acetone 67-64-1	TWA: 500 ppm TWA: 1210 mg/m ³	TWA: 500 ppm TWA: 1210 mg/m ³ STEL: 1500 ppm	STEL: 1500 ppm STEL: 3620 mg/m ³ TWA: 500 ppm

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

		STEL: 3630 mg/m ³	TWA: 1210 mg/m ³
Talc 14807-96-6	-	TWA: 10 mg/m ³ TWA: 0.8 mg/m ³ STEL: 30 mg/m ³ STEL: 2.4 mg/m ³	STEL: 3 mg/m ³ TWA: 1 mg/m ³

Derived No Effect Level (DNEL) No information available

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering Controls Ensure adequate ventilation, especially in confined areas.

Personal Protective Equipment

Eye/Face Protection Tight sealing safety goggles. Face protection shield.
Hand Protection Wear protective gloves. The breakthrough time of the gloves depends on the material and the thickness as well as the temperature.
Skin and Body Protection Antistatic footwear. Wear fire/flame resistant/retardant clothing. Suitable protective clothing.
Respiratory Protection In case of mist, spray or aerosol exposure wear suitable personal respiratory protection and protective suit. In case of inadequate ventilation wear respiratory protection.
Recommended Filter type: Organic gases and vapours filter conforming to EN 14387.

Environmental Exposure Controls Do not allow into any sewer, on the ground or into any body of water.

Section 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1. Information on basic physical and chemical properties

Physical State Liquid
Appearance Liquid
Colour Colourless
Odour Characteristic
Odour Threshold No information available

<u>Property</u>	<u>Values</u>	<u>Remarks • Method</u>
pH	No information available	
Melting point/freezing point	No information available	
Boiling Point	56 °C / 133 °F	
Flash Point	-20 °C / -4 °F	
Evaporation Rate	No information available	
Flammability (solid, gas)	No information available	Not applicable for liquids
Flammability Limit in Air		
Upper Flammability Limit	No information available	
Lower Flammability Limit	No information available	
Vapour Pressure	No information available	
Vapour Density	No information available	
Relative Density	No information available	
Water Solubility	No information available	
Solubility in Other Solvents	No information available	
Partition Coefficient	No information available	
Autoignition Temperature	No information available	
Decomposition Temperature	No information available	
Explosive Properties	No information available	
Explosive Limits	No information available	
Upper	No information available	
Lower	No information available	
Oxidising Properties	No information available	
Kinematic Viscosity	No information available	

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supercedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

Dynamic Viscosity No information available

9.2. Other information

Softening Point No information available
Molecular Weight No information available
Solvent content (%) No information available
Solid content (%) No information available
Density No Data Available
Bulk Density No Data Available
VOC content (%)

Section 10: STABILITY AND REACTIVITY

10.1. Reactivity

Stable under recommended storage conditions.

10.2. Chemical stability

Stable under recommended storage conditions.

Explosion Data

Sensitivity to Mechanical Impact None.

Sensitivity to Static Discharge May be ignited by friction, heat, sparks or flames.

10.3. Possibility of hazardous reactions

Possibility of Hazardous Reactions

None under normal processing.

10.4. Conditions to avoid

Keep away from heat, sparks and flames.

10.5. Incompatible materials

Strong acids and bases.

10.6. Hazardous decomposition products

None under normal use conditions.

Section 11: TOXICOLOGY INFORMATION

11.1. Information on toxicological effects

Information on likely routes of exposure

Product Information

No information or data specific to the product on this toxicological (health) effect is available.

Inhalation No Data Available.
Eye contact No Data Available.
Skin Contact No Data Available.
Ingestion No Data Available.
Sensitisation No Data Available.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin Corrosion/Irritation Not applicable.

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
 Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
 Version 1

Serious eye damage/eye irritation	Not applicable.
Sensitisation	Not applicable.
Germ Cell Mutagenicity	Not applicable.
Carcinogenicity	Not applicable.
Reproductive Toxicity	No information available.
STOT - Single Exposure	No information available.
STOT - Repeated Exposure	No information available.
Target Organ Effects	Central nervous system, Eyes, Respiratory system, Skin.
Aspiration Hazard	No information available.

Numerical measures of toxicity

Acute Toxicity

The following values are calculated based on chapter 3.1 of the GHS document mg/kg mg/l

Component Information

Toxicity Data Data obtained on the component(s) include

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Methyl ethyl ketone 78-93-3	= 2483 mg/kg (Rat)	= 5000 mg/kg (Rabbit)	= 11700 ppm (Rat) 4 h
Acetone 67-64-1	= 5800 mg/kg (Rat)	>15800 mg/Kg (rat)	= 79 mg/l(Rat) 4 h
Bisphenol-A-Epichlorhydrin Epoxy resin <= 700 MW 25068-38-6	LD50 (rat) > 2000 mg/kg	>2000 mg/Kg (rat)	-

Section 12: ECOLOGICAL INFORMATION

12.1. Toxicity

Ecotoxicity Harmful to aquatic life with long lasting effects

Component Information

Data obtained on the component(s) include

Chemical Name	Algae/aquatic plants	Fish	Crustacea	M-Factor
Methyl ethyl ketone 78-93-3	EC50=1972 mg/l (Pseudokirchneriella subcapitata)	LC50 96 h 3130 - 3320 mg/L (Pimephales promelas flow-through)	EC50 48 h > 308 mg/L (Daphnia magna)	
Acetone 67-64-1	-	LC50 96 h 4.74 - 6.33 mL/L (Oncorhynchus mykiss)	EC50 48 h 10294 - 17704 mg/L (Daphnia magna Static)	
Bisphenol-A-Epichlorhydrin Epoxy resin <= 700 MW 25068-38-6	-	1.2 mg/l 96Hr (Oncorhynchus mykiss)	2.7 mg/l 48hr Daphia Magna	

12.2. Persistence and degradability

No information available.

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

12.3. Bioaccumulative potential

No information available.

Partition coefficient No information available

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

The components in this formulation do not meet the criteria for classification as PBT or vPvB.

12.6. Other Adverse Effects

No information available

Endocrine Disruptor Information

.

Chemical Name	EU - Endocrine Disruptors Candidate List	EU - Endocrine Disruptors - Evaluated Substances
Bisphenol-A-Epichlorhydrin Epoxy resin <= 700 MW 25068-38-6	Group III Chemical	

Section 13: DISPOSAL CONSIDERATIONS

13.1. Waste treatment methods

Waste from Residues/Unused Products Disposal should be in accordance with applicable regional, national and local laws and regulations.

Contaminated Packaging Improper disposal or reuse of this container may be dangerous and illegal.

European Waste Catalogue 08 04 09* waste adhesives and sealants containing organic solvents or other dangerous substances

Other Information Waste codes should be assigned by the user based on the application for which the product was used.

Section 14: TRANSPORTATION INFORMATION

ADR

14.1 UN/ID no UN1133
14.2 Proper Shipping Name Adhesives
14.3 Hazard Class 3
Hazard Labels 3
14.4 Packing Group III
Description UN1133, Adhesives, 3, III, (D/E)
14.5 Environmental Hazard Not applicable
14.6 Special Provisions None
Classification Code F1
Tunnel restriction code (D/E)
Limited Quantity (LQ) 5 L
ADR Hazard Id (Kemmler Number) 30

IMDG

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supersedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

14.1 UN/ID no	UN1133
14.2 Proper Shipping Name	Adhesives
14.3 Hazard Class	3
14.4 Packing Group	III
Description	UN1133, Adhesives, 3, III, (-20°C c.c.)
14.5 Marine Pollutant	Np
14.6 Special Provisions	223, 955
Limited Quantity (LQ)	5 L
EmS-No	F-E, S-D
14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code	No information available

RID

14.1 UN/ID no	UN1133
14.2 Proper Shipping Name	Adhesives
14.3 Hazard Class	3
Hazard Labels	3
14.4 Packing Group	III
Description	UN1133, Adhesives, 3, III
14.5 Environmental Hazard Classification Code	Not applicable F1
14.6 Special Provisions	None
Limited Quantity (LQ)	5 L

ICAO (air)

14.1 UN/ID no	UN1133
14.2 Proper Shipping Name	Adhesives
14.3 Hazard Class	3
14.4 Packing Group	III
Description	UN1133, Adhesives, 3, III
14.5 Environmental Hazard	Not applicable
14.6 Special Provisions	A3

IATA

14.1 UN/ID no	UN1133
14.2 Proper Shipping Name	Adhesives
14.3 Hazard Class	3
14.4 Packing Group	III
Description	UN1133, Adhesives, 3, III
14.5 Environmental Hazard	Not applicable
14.6 Special Provisions	A3
Limited Quantity (LQ)	10 L
ERG Code	3L

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

EU-REACH (1907/2006) - Candidate List of Substances of Very High Concern (SVHC) for Authorization in accordance with Article 59

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supercedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

EU-REACH (1907/2006) - Annex XIV - List of substances subject to Authorization

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

Dangerous substance category per Seveso Directive (2012/18/EU)

P5a - FLAMMABLE LIQUIDS
or
P5b - FLAMMABLE LIQUIDS
or
P5c - FLAMMABLE LIQUIDS

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Persistent Organic Pollutants

Not applicable

15.2. Chemical safety assessment

None

Section 16: OTHER INFORMATION

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

H315 - Causes skin irritation
H319 - Causes serious eye irritation
H317 - May cause an allergic skin reaction
H411 - Toxic to aquatic life with long lasting effects
H336 - May cause drowsiness or dizziness
H225 - Highly flammable liquid and vapour
EUH066 - Repeated exposure may cause skin dryness or cracking

Legend

SVHC: Substances of Very High Concern for Authorisation:

Section 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

TWA	TWA (time-weighted average)	STEL	STEL (Short Term Exposure Limit)
Ceiling	Maximum limit value	*	Skin designation

PBT Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
STOT (RE): Specific target organ toxicity - Repeated exposure
STOT (SE): Specific target organ toxicity - Single exposure
EWC: European Waste Catalogue

Key literature references and sources for data

Classification and labeling data calculated from data received from raw material suppliers

Prepared By Product Safety & Regulatory Affairs

Safety Data Sheet

BOSTIK LEATHER ADHESIVE
Supercedes Date: 19-Jun-2017

Revision Date 19-Jun-2017
Version 1

Revision Date 19-Jun-2017

Indication of changes

Revision Note Not applicable.

Training Advice Provide adequate information, instruction, and training for operator

Additional information No information available

This safety data sheet complies with the requirements of: Regulation (EC) No. 1907/2006

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet