

Product Specification PDF

Date	Correct as of 14th Aug 2019
Brand	C.K
Product	T4856
Description	Xonic 4 In 1 Trimmer
Barcode	5013969642506
Commodity code	8205400000
Country of origin	DE



Features & Benefits

~ Zirconia ceramic tips ~ safe trimming of highly sensitive electrical components ~ No electromagnetic induction ~ No eddy current loss in HF (high frequency) ~ 100 % electric insulation ~ 100 % non-magnetic ~ 100 % non-static ~ Unequalled resistance to wear □ 10 x better than metal / 100 x better than plastic ~ Total heat resistance of blades up to 1000°C ~ Extremely low thermal conductivity ~ 100 % rustproof ~ Highly resistant to all strong acids (other than Hydrofluoric) ~ Anti-stick surface to prevent solder, soft or silverm to adhere to surfaces ~ Contamination free blades make them suitable for clean-rooms ~ Screwdriver handle with 2 reversible double blade inserts ~ Blade inserts: Slotted 0,9 mm and 1,8 mm, as well as PH 0 and PH 0 special Visible blade length: all 15 mm Overall length: 145 mm

Applicable Standards

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	10	0
Width mm	12	70	130	0
Depth mm	12	20	245	0
Height mm	155	210	70	0
Weight	12	26	345	0.00
Packaging Information	Card use	Card	Box	loose
	Card gms	6	85	0
	Plastic use	Blister	0	-
	Plastic gms	8	0	0
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0