widespread solutions



Air Extraction Hood and Spray Booth

Captures, filters and expels for a cleaner, healthier working environment within art, graphics, design technology areas, crafts and modelling and more...

Applications include filtration and extraction of:

Aerosol adhesives (glue booth for Spray Mount), aerosol lacquers and fixatives and airbrush sprays applied to artwork up to A1 size. A2 or A1 drawing boards can be placed into the hoods at an angle for efficient overspray capture.

The workstation hood also accommodates prototypes, models, ceramic parts, PCB's etc, placed onto the hood base to be sprayed, soldered, cleaned, glued, moulded, sanded etc.

A200H-D and A100H-D

Extraction cabinets (All odours and gases are extracted to atmosphere)



employe and va

Demonstrating adequate control of the risks to the health of employees, students and the general public, from dusts, powders, mists, fumes and vapours is the fundamental requirement of the Control of Substances Hazardous to Health (COSHH) regulations 2002 and 2004.



www.widespreadsolutions.co.uk

GraphicAir Extraction Cabinets Model No's A200H-D and A100H-D

NOTE: These units exhaust air via flexi-duct to atmosphere.

Description


Steel construction finished in dove grey – fan/filter unit mounted onto hood enclosure - particulate filter – centrifugal blower (A100H-D has 2 blowers) external rotor motor type, brushless, UL, VDE and CSA approved - sealed electrical wiring and switch, downstream of filter. Flexi-duct(s) 2 metres x 100mm dia. (A100H-D has 2 ducts).

Operation

All WS filtration and extraction systems carry a lifetime warranty, are quiet in operation and can be assembled in seconds. Place onto a desk, bench or trolley and then simply plug in and switch on.

For artwork applications, standard A2 (A200H-D) or A1 (A100H-D) drawing boards can be placed within the hood enclosure. The boards fit at an angle for efficient overspray capture.

3D items, models, printed circuit boards etc. may be placed onto the hood base for spraying, cleaning, sanding, gluing etc. The Flexi-duct(s) can be fixed to a standard domestic vent(s) or simply placed through a partially open window to facilitate portability or convenience.



Filtration

The particulate (intake) filter is a three stage graduated fibre filter with a high 'dust' holding capacity for long life. Filtration to 5 micron particles. NB: Spray particulate sizes vary from 10 to 20 microns.

The dual process of filtration and then extraction to atmosphere via flexi-duct, vastly reduces and/or eliminates operator exposures to potentially hazardous substances.

Specification

Model Number	Fan Motor* Spec	Air Volume At Free Air	Ave. Air Velocity At Filter Face	Ave. Air Velocity At Hood Face	Noise Level LAeq dB(A)
A200H-D	230V 50Hz 105W	355 m3/hr	0.6 m/sec	0.25 m/sec	58
A100H-D	230V 50Hz 210W	710 m3/hr	0.6 m/sec	0.27 m/sec	60

* 110 Volts 50 or 60Hz available if required.

These cabinets are designed for studio / classroom / workshop cleanliness and for immediate operator protection whereby 'large' particulates (> 5 microns) are filtered out and 'fine' particulates (<5 microns) together with odours, gases, vapours and fumes within the hood enclosure are exhausted to atmosphere via the flexi-duct(s). Also see TechFlo filtration and extraction cabinets for higher specification equipment.

Please contact WS for advice on the choice of machine for any given situation.

WS Ltd, Unit 1 Levens Hall Park, Lund Lane, Harrogate, HG3 2BG, UK T: +44 (0) 1423 522836 F: +44 (0) 1423 525656 E: enquiries@widespreadsolutions.co.uk Web: www.widespreadsolutions.co.uk

We go to great lengths to ensure accuracy in our literature, however we cannot be held responsible for errors or omissions. Information is given for guidance only and we reserve the right to alter specification.