



Safety Data Sheet

Page 1 of 9

Loctite 5615 400ml _Kit comp. B

SDS No. : 312315

V001.6

Revision: 04.08.2016

printing date: 13.07.2017

Section 1. Identification of the substance/preparation and of the company/undertaking

Product name:

Loctite 5615 400ml _Kit comp. B

Other means of identification:

Loctite 5615 400ml _Kit comp. B

Product code:

IDH1269215

Recommended use of the chemical and restrictions on use

Intended use:

Silicone sealant

Identification of manufacturer, importer or distributor

Manufacturer: Henkel S.p.A., Milano, Via C. Amoretti No. 78, 20157 Milano, Italy. Phone: +39-2-357-921 Fax: +39-2-355-2550

Importer: Henkel Thailand Ltd The Offices at Centralworld, 35th Floor, 999/9 Rama 1 Rd, Kwang Patumwan, Khet Patumwan, Bangkok 10330, Thailand. Phone : +6622098000 Fax : +6622098008

E-mail address of person responsible for Safety Data Sheet:

ap-ua-psra.sea@henkel.com

Emergency information:

FOR EMERGENCIES ONLY (Spill, major leak, Fire, Exposure, or Accident). Call CHEMTREC: +1 703-741-5970

Section 2. Hazards identification

GHS Classification:

Hazard Class

Serious eye damage/eye irritation

Hazard Category

Category 2

GHS label elements:

Hazard pictogram:



Signal word:

Warning

Hazard statement:

H319 Causes serious eye irritation.

Precaution:

Prevention:

P264 Wash hands thoroughly after handling.

P280 Wear eye protection/face protection.

Response:

P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+P313 If eye irritation persists: Get medical advice/attention.

Section 3. Composition / information on ingredients

Substance or Mixture:

Mixture

Declaration of hazardous chemical:

Hazard component CAS-No.	Content	GHS Classification
Limestone 1317-65-3	60- 100 %	
Octadecanoic acid 57-11-4	1- 10 %	Acute hazards to the aquatic environment 3 H402
3-(Trimethoxysilyl)propylamine 13822-56-5	1- 10 %	Flammable liquids 4 H227 Acute toxicity 5; Oral H303 Skin corrosion/irritation 2 H315 Serious eye damage/eye irritation 1 H318

Section 4. First aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

Indication of immediate medical attention and special treatment needed:

See section: Description of first aid measures

Section 5. Fire fighting measures

Suitable extinguishing media:

Carbon dioxide, foam, powder

Specific hazards arising from the chemical:

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO₂) and nitrogen oxides (NO_x) can be released.

Special protection equipment and precautions for firefighters:

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Section 6. Accidental release measures

Personal precautions:

Avoid skin and eye contact.

Environmental precautions:

Do not let product enter drains.

Clean-up methods:

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Section 7. Handling and storage

Handling:

Use only in well-ventilated areas.

Avoid skin and eye contact.

Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.

Storage:

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

Section 8. Exposure controls / personal protection

Components with specific control parameters for workplace:

Limestone 1317-65-3	Value type	Time Weighted Average (TWA):
	mg/m³	10
STEARATES (EXCEPT STEARATES OF TOXIC METALS) 57-11-4	Value type	Time Weighted Average (TWA):
	mg/m³	10
	Remarks	ACGIH

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A (EN 14387)

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Wear protective glasses.

Protective eye equipment should conform to EN166.

Body protection:

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Engineering controls:

Ensure good ventilation/extraction.

Hygienic measures:

Good industrial hygiene practices should be observed.

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Section 9. Physical and chemical properties

Appearance:	white viscous, liquid
Odor:	alcohol-like
Odor threshold (CA):	No data available.
pH:	Not applicable
Melting point / freezing point:	No data available.
Specific gravity:	No data available.
Boiling point:	No data available.
Flash point:	> 100.00 °C (> 212 °F)

(no method)

Evaporation rate:	No data available.
Flammability (solid, gas):	No data available.
Lower explosive limit:	No data available.
Upper explosive limit:	No data available.
Vapor pressure:	No data available.
Vapor density:	No data available.
Density:	1.6500 g/cm ³
Solubility:	No data available.
Partition coefficient: n-octanol/water:	No data available.
Auto ignition:	No data available.
Decomposition temperature:	No data available.
Viscosity:	10,000 - 60,000 mPa.s
(; 25 °C (77 °F); Shear gradient: 20 s ⁻¹ ; Method: ; LCT STM 738; Rheological Data from flow curves)	
VOC content: (2010/75/EC)	< 5 %

Section 10. Stability and reactivity

Reactivity/Incompatible materials:

None if used for intended purpose.

Chemical stability:

Stable under recommended storage conditions.

Conditions to avoid:

No decomposition if used according to specifications.

Hazardous decomposition products:

carbon oxides.

Section 11. Toxicological information

Dermal toxicity: Acute toxicity estimate (ATE) : > 2,000 mg/kg
Method: Calculation method

Symptoms of Overexposure: EYE: Irritation, conjunctivitis.
Prolonged or repeated contact may cause skin irritation.

Acute oral toxicity:

Limestone 1317-65-3	Value type	LD50
	Value	> 5,000 mg/kg
	Species	rat
	Method	
Octadecanoic acid 57-11-4	Value type	LD50
	Value	> 5,000 mg/kg
	Species	rat
	Method	OECD Guideline 401 (Acute Oral Toxicity)
3-(Trimethoxysilyl)propylamine 13822-56-5	Value type	LD50
	Value	2,970 mg/kg
	Species	Sprague-Dawley rat
	Method	OECD Guideline 401 (Acute Oral Toxicity)

Acute dermal toxicity:

Limestone 1317-65-3	Value type	LD50
	Value	> 5,000 mg/kg
	Species	rat
	Method	
3-(Trimethoxysilyl)propylamine 13822-56-5	Value type	LD50
	Value	11,300 mg/kg
	Species	New Zealand white rabbit
	Method	OECD Guideline 402 (Acute Dermal Toxicity)

Skin corrosion/irritation:

Limestone 1317-65-3	Result	not irritating
	Exposure time	4 h
	Species	rabbit
	Method	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Octadecanoic acid 57-11-4	Result	not irritating
	Exposure time	
	Species	rabbit
	Method	
3-(Trimethoxysilyl)propylamine 13822-56-5	Result	irritating
	Exposure time	4 h
	Species	rabbit
	Method	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Limestone 1317-65-3	Result	not irritating
	Exposure time	
	Species	rabbit
	Method	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Octadecanoic acid 57-11-4	Result	not irritating
	Exposure time	
	Species	rabbit
	Method	Draize Test
3-(Trimethoxysilyl)propylamine 13822-56-5	Result	highly irritating
	Exposure time	
	Species	rabbit
	Method	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Limestone 1317-65-3	Result	not sensitising
	Test type	Mouse local lymphnode assay (LLNA)
	Species	mouse
	Method	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)
Octadecanoic acid 57-11-4	Result	not sensitising
	Test type	
	Species	
	Method	
3-(Trimethoxysilyl)propylamine 13822-56-5	Result	not sensitising
	Test type	Guinea pig maximisation test
	Species	guinea pig
	Method	OECD Guideline 406 (Skin Sensitisation)

Germ cell mutagenicity:

Limestone 1317-65-3	Result	negative
	Type of study / Route of administration	bacterial reverse mutation assay (e.g Ames test)
	Metabolic activation / Exposure time	with and without
	Method	OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Limestone 1317-65-3	Result	negative
	Type of study / Route of administration	in vitro mammalian chromosome aberration test
	Metabolic activation / Exposure time	with and without
	Method	OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
Limestone 1317-65-3	Result	negative
	Type of study / Route of administration	mammalian cell gene mutation assay
	Metabolic activation / Exposure time	with and without
	Method	OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
Octadecanoic acid 57-11-4	Result	negative
	Type of study / Route of administration	bacterial reverse mutation assay (e.g Ames test)
	Metabolic activation / Exposure time	with and without
	Method	

Repeated dose toxicity:

Limestone 1317-65-3	Result	NOAEL=1,000 mg/kg
	Route of application	oral: gavage
	Exposure time / Frequency of treatment	48 ddaily
	Species	rat
	Method	OECD Guideline 422 (Combined Repeated Dose Toxicity Study with the Reproduction / Developmental Toxicity Screening Test)
Octadecanoic acid 57-11-4	Result	NOAEL=15,000 mg/kg
	Route of application	oral: unspecified
	Exposure time / Frequency of treatment	21 d
	Species	mouse
	Method	

Section 12. Ecological information**Ecotoxicity:**

Do not empty into drains / surface water / ground water.

Toxicity:

Limestone 1317-65-3	Value type	LC50
	Value	> 10,000 mg/l
	Acute Toxicity Study	Fish
	Exposure time	96 h
	Species	Not specified
	Method	OECD Guideline 203 (Fish, Acute Toxicity Test)
Limestone 1317-65-3	Value type	EC50
	Value	> 1,000 mg/l
	Acute Toxicity Study	Daphnia
	Exposure time	48 h
	Species	Daphnia magna
	Method	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Limestone 1317-65-3	Value type	EC50
	Value	> 200 mg/l
	Acute Toxicity Study	Algae
	Exposure time	72 h
	Species	Not specified
	Method	OECD Guideline 201 (Alga, Growth Inhibition Test)
Limestone 1317-65-3	Value type	EC50
	Value	> 1,000 mg/l
	Acute Toxicity Study	Bacteria
	Exposure time	3 h
	Species	activated sludge of a predominantly domestic sewage
	Method	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)
Octadecanoic acid 57-11-4	Value type	LC50
	Value	> 10,000 mg/l
	Acute Toxicity Study	Fish

	Exposure time	48 h
	Species	Leuciscus idus
	Method	DIN 38412-15
Octadecanoic acid 57-11-4	Value type	EC50
	Value	40 mg/l
	Acute Toxicity Study	Daphnia
	Exposure time	24 h
	Species	Daphnia magna
	Method	
Octadecanoic acid 57-11-4	Value type	EC50
	Value	22 mg/l
	Acute Toxicity Study	Algae
	Exposure time	72 h
	Species	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)
	Method	DIN 38412-09
	Value type	EC0
	Value	8.8 mg/l
	Acute Toxicity Study	Algae
	Exposure time	72 h
	Species	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)
	Method	DIN 38412-09
Octadecanoic acid 57-11-4	Value type	EC0
	Value	10,000 mg/l
	Acute Toxicity Study	Bacteria
	Exposure time	16 h
	Species	
	Method	
3-(Trimethoxysilyl)propylamine 13822-56-5	Value type	LC50
	Value	1,264 mg/l
	Acute Toxicity Study	Fish
	Exposure time	
	Species	Pimephales promelas
	Method	OECD Guideline 203 (Fish, Acute Toxicity Test)
3-(Trimethoxysilyl)propylamine 13822-56-5	Value type	EC50
	Value	302 mg/l
	Acute Toxicity Study	Daphnia
	Exposure time	
	Species	Daphnia magna
	Method	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
3-(Trimethoxysilyl)propylamine 13822-56-5	Value type	EC 50
	Value	3,400 mg/l
	Acute Toxicity Study	Bacteria
	Exposure time	
	Species	
	Method	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

Persistence and degradability:

Octadecanoic acid 57-11-4	Result	readily biodegradable
	Route of application	aerobic
	Degradability	95 %
	Method	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
3-(Trimethoxysilyl)propylamine 13822-56-5	Result	
	Route of application	aerobic
	Degradability	67 %
	Method	OECD Guideline 301 A (new version) (Ready Biodegradability: DOC Die Away Test)

Bioaccumulative potential / Mobility in soil:

Octadecanoic acid 57-11-4	LogKow	8.23
	Temperature	
	Method	

Section 13. Disposal considerations

Product

Method of disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Packaging

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Section 14. Transport information

General information:

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

Section 15. Regulatory information

Regulatory Information:

Ministry of Industry Notice. The system to classify and communicate the hazard of hazardous material, BE. 2555

Global inventory status:

Regulatory list	Notification
TSCA	yes
AICS	yes
NDSL	yes
PICCS (PH)	yes
IECSC	yes

Section 16. Other information

Disclaimer:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.