

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017



BUILDING TRUST



Version 1.0

Print Date 29.06.2017

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Everbuild Blackjack 908 D.P.M

1.2 Relevant identified uses of the substance or mixture and uses advised against

Product use : Bituminous coating

1.3 Details of the supplier of the safety data sheet

Company : Everbuild – A Sika Company
Site 41
Knowsthorpe Way
Cross Green Industrial Estate
Leeds
West Yorkshire LS9 0SW
United Kingdom

Telephone : 0113 240 3456

E-mail address : everbuild.sds@uk.sika.com

1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Skin irritation, Category 2 H315: Causes skin irritation.

Eye irritation, Category 2 H319: Causes serious eye irritation.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Warning

Hazard statements : H315 Causes skin irritation.
H319 Causes serious eye irritation.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017



BUILDING TRUST



Version 1.0

Print Date 29.06.2017

Precautionary statements : **Prevention:**
P264 Wash skin thoroughly after handling.
P280 Wear protective gloves/ eye protection/ face protection.

Response:
P302 + P352 IF ON SKIN: Wash with plenty of water.
P332 + P313 If skin irritation occurs: Get medical advice/ attention.
P337 + P313 If eye irritation persists: Get medical advice/ attention.
P362 + P364 Take off contaminated clothing and wash it before reuse.

2.3 Other hazards

This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

Chemical name CAS-No. EC-No. Registration number	Classification (REGULATION (EC) No 1272/2008)	Concentration [%]
caustic potash 1310-58-3 215-181-3 01-2119487136-33-XXXX	Met. Corr.1; H290 Acute Tox.4; H302 Skin Corr.1A; H314 Eye Dam.1; H318	>= 0,5 - < 1

For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : Move out of dangerous area.
Consult a physician.
Show this safety data sheet to the doctor in attendance.

If inhaled : Move to fresh air.
Consult a physician after significant exposure.

In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.

In case of eye contact : Immediately flush eye(s) with plenty of water.
Remove contact lenses.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



Keep eye wide open while rinsing.
If eye irritation persists, consult a specialist.

If swallowed : Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : Excessive lachrymation
Erythema
Dermatitis
See Section 11 for more detailed information on health effects and symptoms.

Risks : irritant effects

Causes skin irritation.
Causes serious eye irritation.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Personal precautions : Use personal protective equipment.
Deny access to unprotected persons.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



6.2 Environmental precautions

Environmental precautions : If the product contaminates rivers and lakes or drains inform respective authorities.

6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Soak up with inert absorbent material (e.g. sand, silica gel, acid binder, universal binder, sawdust).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see section 8). Do not get in eyes, on skin, or on clothing. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place. Containers which are opened must be carefully re-sealed and kept upright to prevent leakage. Store in accordance with local regulations.

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Components	CAS-No.	Value	Control parameters *	Basis *
------------	---------	-------	----------------------	---------

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



caustic potash	1310-58-3	STEL	2 mg/m3	GB EH40
----------------	-----------	------	---------	---------

8.2 Exposure controls

Personal protective equipment

- Eye protection : Safety glasses with side-shields conforming to EN166
Eye wash bottle with pure water
- Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.
- Suitable for short time use or protection against splashes:
Butyl rubber/nitrile rubber gloves (0,4 mm),
Contaminated gloves should be removed.
Suitable for permanent exposure:
Viton gloves (0.4 mm),
breakthrough time >30 min.
- Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.
- Respiratory protection : Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
organic vapor filter (Type A)
A1: < 1000 ppm; A2: < 5000 ppm; A3: < 10000 ppm
Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficient to keep the concentrations under the occupational exposure limits then respiration protection measures must be used.

Environmental exposure controls

- General advice : If the product contaminates rivers and lakes or drains inform respective authorities.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance	: liquid
Colour	: black
Odour	: characteristic
Odour Threshold	: No data available
Flash point	: Not applicable
Autoignition temperature	: No data available
Decomposition temperature	: No data available
Lower explosion limit (Vol-%)	: No data available
Upper explosion limit (Vol-%)	: No data available
Flammability	: No data available
Explosive properties	: No data available
Oxidizing properties	: No data available
pH	: No data available
Melting point/range / Freezing point	: No data available
Boiling point/boiling range	: No data available
Vapour pressure	: 0,01 hPa
Density	: ca.1 g/cm ³ at 20 °C
Water solubility	: No data available
Partition coefficient: n-octanol/water	: No data available
Viscosity, dynamic	: No data available
Viscosity, kinematic	: > 7 mm ² /s at 40 °C
Relative vapour density	: No data available
Evaporation rate	: No data available

9.2 Other information

No data available

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017



BUILDING TRUST



Version 1.0

Print Date 29.06.2017

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

Not classified based on available information.

Components:

caustic potash:

Acute oral toxicity : Acute toxicity estimate: 500 mg/kg
Method: Converted acute toxicity point estimate

Skin corrosion/irritation

Causes skin irritation.

Serious eye damage/eye irritation

Causes serious eye irritation.

Respiratory or skin sensitisation

Skin sensitisation: Not classified based on available information.

Respiratory sensitisation: Not classified based on available information.

Germ cell mutagenicity

Not classified based on available information.

Carcinogenicity

Not classified based on available information.

Reproductive toxicity

Not classified based on available information.

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



STOT - single exposure

Not classified based on available information.

STOT - repeated exposure

Not classified based on available information.

Aspiration toxicity

Not classified based on available information.

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Other adverse effects

Product:

Additional ecological information : There is no data available for this product.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017



BUILDING TRUST



Version 1.0

Print Date 29.06.2017

local authority requirements.
Avoid dispersal of spilled material and runoff and contact with
soil, waterways, drains and sewers.

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated
by dangerous substances

SECTION 14: Transport information

14.1 UN number

Not regulated as a dangerous good

14.2 UN proper shipping name

Not regulated as a dangerous good

14.3 Transport hazard class(es)

Not regulated as a dangerous good

14.4 Packing group

Not regulated as a dangerous good

14.5 Environmental hazards

Not regulated as a dangerous good

14.6 Special precautions for user

No data available

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Prohibition/Restriction

REACH - Restrictions on the manufacture, placing on
the market and use of certain dangerous substances,
preparations and articles (Annex XVII) : Not applicable

REACH - Candidate List of Substances of Very High
Concern for Authorisation (Article 59). : None of the components are listed
(=> 0.1 %).

REACH - List of substances subject to authorisation
(Annex XIV) : Not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



REACH Information: All substances contained in our Products are
- preregistered or registered by our upstream suppliers, and/or
- preregistered or registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

Seveso III: Directive 2012/18/EU of the European Parliament and of the Council on the control of major-accident hazards involving dangerous substances.

Not applicable

VOC-CH (VOCV) : no VOC duties

VOC-EU (solvent) : Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : Environmental Protection Act 1990 & Subsidiary Regulations
Health and Safety at Work Act 1974 & Subsidiary Regulations
Control of Substances Hazardous to Health Regulations (COSHH)
May be subject to the Control of Major Accident Hazards Regulations (COMAH), and amendments.

15.2 Chemical safety assessment

This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

Full text of H-Statements

H290	May be corrosive to metals.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H318	Causes serious eye damage.

Full text of other abbreviations

Acute Tox.	Acute toxicity
Eye Dam.	Serious eye damage
Met. Corr.	Corrosive to metals
Skin Corr.	Skin corrosion
ADR	Accord européen relatif au transport international des marchandises Dangereuses par Route
CAS	Chemical Abstracts Service
DNEL	Derived no-effect level
EC50	Half maximal effective concentration
GHS	Globally Harmonized System
IATA	International Air Transport Association
IMDG	International Maritime Code for Dangerous Goods
LD50	Median lethal dosis (the amount of a material, given all at once, which

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Everbuild Blackjack 908 D.P.M

Revision Date 29.06.2017

Version 1.0

Print Date 29.06.2017



BUILDING TRUST



LC50	causes the death of 50% (one half) of a group of test animals) Median lethal concentration (concentrations of the chemical in air that kills 50% of the test animals during the observation period)
MARPOL	International Convention for the Prevention of Pollution from Ships, 1973 as modified by the Protocol of 1978
OEL	Occupational Exposure Limit
PBT	Persistent, bioaccumulative and toxic
PNEC	Predicted no effect concentration
REACH	Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH), establishing a European Chemicals Agency
SVHC	Substances of Very High Concern
vPvB	Very persistent and very bioaccumulative

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.



Changes as compared to previous version !