



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

LOCTITE SF 7070 known as Loctite 7070 Cleaner

SDS No. : 153660  
V004.0

Revision: 18.07.2017  
printing date: 18.04.2019

Replaces version from: 31.03.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE SF 7070 known as Loctite 7070 Cleaner

#### Contains:

Limonene, D-

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Solvent based cleaner

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd  
Adhesives  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000  
Fax-no.: +44 (1442) 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Flammable liquids	Category 3
H226 Flammable liquid and vapor.	
Skin irritation	Category 2
H315 Causes skin irritation.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Chronic hazards to the aquatic environment	Category 2
H411 Toxic to aquatic life with long lasting effects.	

#### 2.2. Label elements

##### Label elements (CLP):

**Hazard pictogram:****Signal word:**

Warning

**Hazard statement:**

H226 Flammable liquid and vapor.  
H315 Causes skin irritation.  
H317 May cause an allergic skin reaction.  
H411 Toxic to aquatic life with long lasting effects.

**Precautionary statement:  
Prevention**

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.  
No smoking.  
P273 Avoid release to the environment.  
P280 Wear protective gloves.

**Precautionary statement:  
Response**

P302+P352 IF ON SKIN: Wash with plenty of soap and water.  
P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

**2.3. Other hazards**

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**SECTION 3: Composition/information on ingredients****3.2. Mixtures****General chemical description:**

Cleaner

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Isoparaffinic Hydrocarbon 90622-57-4	292-459-0 01-2119472146-39	50- 100 %	Flam. Liq. 3 H226 Asp. Tox. 1; Oral H304
Limonene, D- 5989-27-5	227-813-5	10- 20 %	Flam. Liq. 3 H226 Aquatic Acute 1 H400 Skin Irrit. 2 H315 Skin Sens. 1 H317 Aquatic Chronic 1 H410 Asp. Tox. 1 H304

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

**Declaration of ingredients according to Detergent Regulation 648/2004/EC**

&gt; 30 %                      aliphatic hydrocarbons

Allergenic fragrance                      Limonene  
ingredients >=100 ppm:

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

**Inhalation:**

Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**

Rinse with running water and soap.

Obtain medical attention if irritation persists.

**Eye contact:**

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

**Ingestion:**

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

### 4.2. Most important symptoms and effects, both acute and delayed

SKIN: Rash, Urticaria.

SKIN: Redness, inflammation.

Prolonged or repeated contact may cause eye irritation.

### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

Small amounts of liquid aspirated into the respiratory system during ingestion or from vomiting may cause bronchopneumonia or pulmonary oedema.

Do not induce vomiting.

Seek medical attention from a specialist.

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

**Suitable extinguishing media:**

carbon dioxide, foam, powder, water spray jet, fine water spray

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

### 5.2. Special hazards arising from the substance or mixture

Do not expose to direct heat.

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

### 5.3. Advice for firefighters

Wear self-contained breathing apparatus.

**Additional information:**

In case of fire, keep containers cool with water spray.

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.

Remove sources of ignition.

Ensure adequate ventilation.

### 6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

### 6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.  
For large spills absorb onto inert absorbent material and place in sealed container for disposal.  
Store in a partly filled, closed container until disposal.

### 6.4. Reference to other sections

See advice in section 8

## SECTION 7: Handling and storage

### 7.1. Precautions for safe handling

Avoid skin and eye contact.  
Keep away from sources of ignition - no smoking.  
Vapours should be extracted to avoid inhalation.  
See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.  
Do not eat, drink or smoke while working.  
Good industrial hygiene practices should be observed.

### 7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, dry place.  
Do not store near sources of heat or ignition, or reactive materials.  
Refer to Technical Data Sheet

### 7.3. Specific end use(s)

Solvent based cleaner

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

None

#### Occupational Exposure Limits

Valid for  
Ireland

None

#### Biological Exposure Indices:

None

### 8.2. Exposure controls:

Engineering controls:  
Ensure good ventilation/extraction.

Respiratory protection:  
Ensure adequate ventilation.  
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area  
Filter type: A (EN 14387)

**Hand protection:**

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq 0.4$  mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

**Eye protection:**

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	liquid Colorless
Odor	citrus-fruit-like
Odour threshold	No data available / Not applicable
pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	155 - 210 °C (311 - 410 °F)
Flash point	43 °C (109.4 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	
lower	0,6 % (V)
upper	7 % (V)
Vapour pressure (20 °C (68 °F))	2,3 hPa
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	0,76 - 0,78 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Insoluble
Solubility (qualitative) (Solvent: Acetone)	Miscible
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

Ignition temperature 200 °C (392 °F)

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Strong oxidizing agents.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**Stable under normal conditions of storage and use.  
Heat, flames, sparks and other sources of ignition.**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

None if used for intended purpose.

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**Oral toxicity:**

May cause irritation to the digestive tract.

**Skin irritation:**

Causes skin irritation.

**Eye irritation:**

Prolonged or repeated contact may cause eye irritation.

**Sensitizing:**

May cause an allergic skin reaction.

**Acute oral toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	LD50	> 5.000 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)
Limonene, D- 5989-27-5	LD50	> 5.000 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

**Acute inhalative toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

**Acute dermal toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	LD50	> 3.000 mg/kg	dermal		rabbit	not specified
Limonene, D- 5989-27-5	LD50	> 5.000 mg/kg	dermal		rabbit	OECD Guideline 402 (Acute Dermal Toxicity)

**Skin corrosion/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	not irritating		rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)
Limonene, D- 5989-27-5	moderately irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

**Serious eye damage/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)
Limonene, D- 5989-27-5	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

**Respiratory or skin sensitization:**

Hazardous components CAS-No.	Result	Test type	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	not sensitising	Guinea pig maximisation test	guinea pig	OECD Guideline 406 (Skin Sensitisation)
Limonene, D- 5989-27-5	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

**Germ cell mutagenicity:**

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
	negative	sister chromatid exchange assay in mammalian cells	with and without		OECD Guideline 479 (Genetic Toxicology: In Vitro Sister Chromatid Exchange Assay in Mammalian Cells)
Isoparaffinic Hydrocarbon 90622-57-4	negative			rat	OECD Guideline 474 (Mammalian Erythrocyte Micronucleus Test)
	negative			mouse	OECD Guideline 478 (Genetic Toxicology: Rodent Dominant Lethal Test)
Limonene, D- 5989-27-5	negative	bacterial reverse mutation assay (e.g Ames test)	with and without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
	negative	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)
	negative	mammalian cell gene mutation assay	with and without		OECD Guideline 476 (In vitro Mammalian Cell Gene Mutation Test)
	negative	sister chromatid exchange assay in mammalian cells	with and without		OECD Guideline 479 (Genetic Toxicology: In Vitro Sister Chromatid Exchange Assay in Mammalian Cells)
Limonene, D- 5989-27-5	negative	oral: gavage		rat	not specified

**Reproductive toxicity:**

Hazardous substances CAS-No.	Result / Classification	Species	Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	NOAEL P = >= 1.720 mg/kg NOAEL F1 = >= 1.720 mg/kg	screening inhalation		rat	OECD Guideline 421 (Reproduction / Developmental Toxicity Screening Test)

**Repeated dose toxicity**

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
Limonene, D- 5989-27-5	NOAEL=825 mg/kg	oral: gavage	16 dOnce per day; 5 days/week	rat	OECD Guideline 407 (Repeated Dose 28-Day Oral Toxicity in Rodents)
Limonene, D- 5989-27-5	NOAEL=600 mg/kg	oral: gavage	13 wOnce per day; 5 days/week	rat	OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents)

**SECTION 12: Ecological information****General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.



**12.1. Toxicity****Ecotoxicity:**

Toxic to aquatic life with long lasting effects.

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Isoparaffinic Hydrocarbon 90622-57-4	LC50	> 100 mg/l	Fish	96 h	Daphnia magna	OECD Guideline 203 (Fish, Acute Toxicity Test)
Isoparaffinic Hydrocarbon 90622-57-4	EC50	> 100 mg/l	Daphnia	96 h		OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Isoparaffinic Hydrocarbon 90622-57-4	NOEC	> 1 mg/l	chronic Daphnia	21 d	Daphnia magna	OECD 211 (Daphnia magna, Reproduction Test)
Limonene, D- 5989-27-5	LC50	0,702 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Limonene, D- 5989-27-5	EC50	577 µg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

**12.2. Persistence and degradability****Persistence and Biodegradability:**

The product is not biodegradable.

**Persistence and degradability:****Degradation of surfactants**

The product does not contain surface-active substances as defined in the EU Detergent Regulation (EC/648/2004).

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Isoparaffinic Hydrocarbon 90622-57-4	readily biodegradable	aerobic	77,6 %	OECD Guideline 301 F (Ready Biodegradability: Manometric Respirometry Test)
Limonene, D- 5989-27-5	readily biodegradable		41 - 98 %	OECD Guideline 301 C (Ready Biodegradability: Modified MITI Test (I))

**12.3. Bioaccumulative potential / 12.4. Mobility in soil****Mobility:**

The product evaporates readily.

**Bioaccumulative potential:**

No data available for the product.

Hazardous components CAS-No.	LogPow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Isoparaffinic Hydrocarbon 90622-57-4	> 5,1					not specified
Limonene, D- 5989-27-5	4,57					not specified

**12.5. Results of PBT and vPvB assessment**

Hazardous components CAS-No.	PBT/vPvB

Isoparaffinic Hydrocarbon 90622-57-4	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
---	---

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

14 06 03 - other solvents and solvent mixtures

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

**SECTION 14: Transport information****14.1. UN number**

ADR	1268
RID	1268
ADN	1268
IMDG	1268
IATA	1268

**14.2. UN proper shipping name**

ADR	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent)
RID	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent)
ADN	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent)
IMDG	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent,limonene)
IATA	Petroleum distillates, n.o.s. (Stoddard Solvent)

**14.3. Transport hazard class(es)**

ADR	3
RID	3
ADN	3
IMDG	3
IATA	3

**14.4. Packing group**

ADR	III
RID	III
ADN	III
IMDG	III
IATA	III

**14.5. Environmental hazards**

ADR	Environmentally Hazardous
RID	Environmentally Hazardous

ADN	Environmentally Hazardous
IMDG	Marine pollutant
IATA	not applicable

**14.6. Special precautions for user**

ADR	not applicable Tunnelcode: (D/E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

**SECTION 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content (2010/75/EC)	100 %
-----------------------------	-------

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H226 Flammable liquid and vapor.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**