

Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 10

SDS No.: 153660 V003.8

Revision: 21.05.2015

printing date: 14.07.2017

Replaces version from: 12.02.2015

LOCTITE SF 7070 known as Loctite 7070

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE SF 7070 known as Loctite 7070

Contains:

Isoparaffins C9-12 Limonene, D-

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Solvent based cleaner

1.3. Details of the supplier of the safety data sheet

Henkel Ltd Adhesives Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 (1442) 278000 Fax-no.: +44 (1442) 278071

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

$\textbf{Classification} \ (\textbf{CLP}) \textbf{:}$

Flammable liquids Category 3

H226 Flammable liquid and vapor.

Skin irritation Category 2

H315 Causes skin irritation.

Skin sensitizer Category 1

H317 May cause an allergic skin reaction.

Aspiration hazard Category 1

H304 May be fatal if swallowed and enters airways.

Chronic hazards to the aquatic environment Category 2

H411 Toxic to aquatic life with long lasting effects.

2.2. Label elements

Label elements (CLP):

V003.8

Hazard pictogram:



Signal word: Danger

Hazard statement: H226 Flammable liquid and vapor.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H411 Toxic to aquatic life with long lasting effects.

Precautionary statement:

Prevention

P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources.

No smoking.

P280 Wear protective gloves.

P273 Avoid release to the environment.

Precautionary statement:

Response

P301+P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor.

P331 Do NOT induce vomiting.

P302+P352 IF ON SKIN: Wash with plenty of water.

P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Cleaner

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components	EC Number	content	Classification
CAS-No.	REACH-Reg No.		
Isoparaffins C9-12 90622-57-4	292-459-0 01-2119472146-39	50- 100 %	Flam. Liq. 3 H226 Asp. Tox. 1; Oral H304 Aquatic Chronic 4 H413
Limonene, D- 5989-27-5	227-813-5	10- 20 %	Flam. Liq. 3 H226 Aquatic Acute 1 H400 Skin Irrit. 2 H315 Skin Sens. 1 H317 Aquatic Chronic 1 H410 Asp. Tox. 1 H304

For full text of the H - statements and other abbreviations see section 16 "Other information". Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to Detergent Regulation 648/2004/EC

> 30 % aliphatic hydrocarbons

Allergenic fragrance ingredients >= 100 ppm:

Limonene

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eve contact

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

ASPIRATION: Coughing, shortness of breath, nausea. Delayed effect: bronchopneumonia or pulmonary oedema

SKIN: Rash, Urticaria.

Prolonged or repeated contact may cause eye irritation.

SKIN: Redness, inflammation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

Small amounts of liquid aspirated into the respiratory system during ingestion or from vomiting may cause bronchopneumonia or pulmonary oedema.

Do not induce vomiting.

Seek medical attention from a specialist.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

carbon dioxide, foam, powder, water spray jet, fine water spray

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

Do not expose to direct heat.

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.

Remove sources of ignition.

Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

Wipe up using absorbent material.

Store in a partly filled, closed container until disposal.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid skin and eye contact.

Keep away from sources of ignition - no smoking.

Vapours should be extracted to avoid inhalation.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, dry place.

Do not store near sources of heat or ignition, or reactive materials.

7.3. Specific end use(s)

Solvent based cleaner

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for

Great Britain

None

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; >= 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eve protection:

Safety glasses with sideshields or chemical safety goggles should be worn if there is a risk of splashing.

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance liquid

Colorless

Odor citrus-fruit-like

Odour threshold No data available / Not applicable

pH Not applicable

Initial boiling point 155 - 210 °C (311 - 410 °F)

Flash point 43 °C (109.4 °F)

Decomposition temperature No data available / Not applicable

Vapour pressure 2,3 hPa

(20 °C (68 °F))

Density 0,76 - 0,78 g/cm3

(20 °C (68 °F))

Bulk density
No data available / Not applicable
Viscosity
No data available / Not applicable
Viscosity (kinematic)
No data available / Not applicable
Explosive properties
No data available / Not applicable

Solubility (qualitative) Insoluble

(Solvent: Water)

Solubility (qualitative) Miscible

(Solvent: Acetone)

Solidification temperature

Mo data available / Not applicable
Melting point

No data available / Not applicable
Flammability

No data available / Not applicable
Auto-ignition temperature

No data available / Not applicable

Explosive limits

lower 0,6 %(V) upper 7 %(V)

Partition coefficient: n-octanol/water

Evaporation rate

Vapor density

Oxidising properties

No data available / Not applicable

9.2. Other information

Ignition temperature 200 °C (392 °F)

SECTION 10: Stability and reactivity

10.1. Reactivity

Strong oxidizing agents.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

Stable under normal conditions of storage and use. Heat, flames, sparks and other sources of ignition.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

None if used for intended purpose.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Aspiration hazard:

May be fatal if swallowed and enters airways.

Oral toxicity:

May cause irritation to the digestive tract.

Skin irritation:

Causes skin irritation.

Eye irritation:

Prolonged or repeated contact may cause eye irritation.

Sensitizing:

May cause an allergic skin reaction.

Acute oral toxicity:

Hazardous components	Value	Value	Route of	Exposure	Species	Method
CAS-No.	type		application	time		

Acute inhalative toxicity:

Hazardous components	Value	Value	Route of	Exposure	Species	Method
CAS-No.	type		application	time		

Acute dermal toxicity:

Hazardous components	Value	Value	Route of	Exposure	Species	Method
CAS-No.	type		application	time		

Skin corrosion/irritation:

Hazardous components	Result	Exposure	Species	Method
CAS-No.		time		
Limonene, D-	moderately irritating	4 h	rabbit	OECD Guideline 404 (Acute
5989-27-5				Dermal Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Limonene, D- 5989-27-5	sensitising	Mouse local lymphnod	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)
		e assay (LLNA)		

SECTION 12: Ecological information

General ecological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity

Ecotoxicity:

Toxic to aquatic life with long lasting effects.

Do not empty into drains / surface water / ground water.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Limonene, D- 5989-27-5	LC50	0,702 mg/l	Fish	96 h	Pimephales promelas	OECD Guideline 203 (Fish, Acute Toxicity Test)
Limonene, D- 5989-27-5	EC50	577 μg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

12.2. Persistence and degradability

Persistence and Biodegradability:

The product is not biodegradable.

Persistence and degradability:

Degradation of surfactants

The product does not contain surface-active substances as defined in the EU Detergent Regulation (EC/648/2004).

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Limonene, D- 5989-27-5	readily biodegradable		41 - 98 %	OECD Guideline 301 C (Ready Biodegradability: Modified MITI
3707 27 3				Test (I))

12.3. Bioaccumulative potential / 12.4. Mobility in soil

Mobility:

The product evaporates readily.

Bioaccumulative potential:

No data available for the product.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Limonene, D-	4,57					
5989-27-5						

12.5. Results of PBT and vPvB assessment

No data available.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

14 06 03 - other solvents and solvent mixtures

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

V003.8

MSDS-No.: 153660

SECTION 14: Transport information

14.1. **UN** number

ADR	1268
RID	1268
ADN	1268
IMDG	1268
IATA	1268

14.2. UN proper shipping name

ADR	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent)
RID	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent)
ADN	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent)
IMDG	PETROLEUM DISTILLATES, N.O.S. (Stoddard Solvent, limonene)

IATA Petroleum distillates, n.o.s. (Stoddard Solvent)

14.3. Transport hazard class(es)

ADR	3
RID	3
ADN	3
IMDG	3
IATA	3

14.4. Packaging group

ADR	III
RID	III
ADN	III
IMDG	III
IATA	III

14.5. **Environmental hazards**

ADR	Environmentally Hazardous
RID	Environmentally Hazardous
ADN	Environmentally Hazardous
IMDG	Environmentally Hazardous
IATA	not applicable

not applicable

14.6. Special precautions for user

ADR	not applicable
	Tunnelcode: (D/E)
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content (1999/13/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text

of all abbreviations indicated by codes in this safety data sheet are as follows:

H226 Flammable liquid and vapor.

H304 May be fatal if swallowed and enters airways.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H400 Very toxic to aquatic life.

H410 Very toxic to aquatic life with long lasting effects.

H413 May cause long lasting harmful effects to aquatic life.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.