

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: KIL-BLOCK ORIGINAL

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Professional use of washing and cleaning products. Consumer use of washing and cleaning products.

1.3. Details of the supplier of the safety data sheet

Company name: Kilrock Products Ltd

Units 1b/2b

Alma Road ind Est

Chesham

Buckinghamshire

HP5 3HB

United Kingdom

Tel: +44 (0)1494 793900

Email: velda@kilrock.co.uk

1.4. Emergency telephone number

Emergency tel: +44 (0)1494 793900

(office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Skin Corr. 1B: H314; Met. Corr. 1: H290; -: EUH031

Classification under CHIP: C: R35

Most important adverse effects: Causes severe skin burns and eye damage. May be corrosive to metals. Contact with acids liberates toxic gas.

2.2. Label elements

Label elements under CLP:

Hazard statements: H314: Causes severe skin burns and eye damage.

H290: May be corrosive to metals.

EUH031: Contact with acids liberates toxic gas.

Signal words: Danger

Hazard pictograms: GHS05: Corrosion



SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 2

Precautionary statements: P405: Store locked up.
P102: Keep out of reach of children.
P280: Wear protective gloves/protective clothing/eye protection/face protection.
P301+330+331: IF SWALLOWED: rinse mouth. Do NOT induce vomiting.
P304+340: IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P234: Keep only in original container.
P501: Dispose of contents/container to hazardous or special waste collection point.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

SODIUM HYDROXIDE

EINECS	CAS	CHIP Classification	CLP Classification	Percent
215-185-5	1310-73-2	-	Skin Corr. 1A: H314	30-60%

Section 4: First aid measures

4.1. Description of first aid measures

- Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin. Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Transfer to hospital if there are burns or symptoms of poisoning.
- Eye contact:** Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.
- Ingestion:** Wash out mouth with water. Do not induce vomiting. Give 1 cup of water to drink every 10 minutes. If unconscious, check for breathing and apply artificial respiration if necessary. If unconscious and breathing is OK, place in the recovery position. Transfer to hospital as soon as possible.
- Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so. If unconscious and breathing is OK, place in the recovery position. If conscious, ensure the casualty sits or lies down. If breathing becomes bubbly, have the casualty sit and provide oxygen if available. Transfer to hospital as soon as possible.

4.2. Most important symptoms and effects, both acute and delayed

- Skin contact:** Blistering may occur. Progressive ulceration will occur if treatment is not immediate.
- Eye contact:** Corneal burns may occur. May cause permanent damage.

[cont...]

SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 3

Ingestion: Corrosive burns may appear around the lips. Blood may be vomited. There may be bleeding from the mouth or nose.

Inhalation: There may be shortness of breath with a burning sensation in the throat. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Eye bathing equipment should be available on the premises.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: Corrosive. In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Mark out the contaminated area with signs and prevent access to unauthorised personnel. Do not attempt to take action without suitable protective clothing - see section 8 of SDS. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Clean-up should be dealt with only by qualified personnel familiar with the specific substance. Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS. Refer to section 13 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

[cont...]

SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 4

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): PC35: Washing and cleaning products (including solvent based products).

Section 8: Exposure controls/personal protection

8.1. Control parameters

Hazardous ingredients:

SODIUM HYDROXIDE

Workplace exposure limits / OELV:

Respirable dust

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK / IRE	-	2 mg/m ³	-	-

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Respiratory protective device with particle filter.

Hand protection: PVC gloves. Rubber gloves.

Eye protection: Tightly fitting safety goggles. Ensure eye bath is to hand.

Skin protection: Impermeable protective clothing.

Environmental: Refer to specific Member State legislation for requirements under Community environmental legislation.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Odourless

Oxidising: Non-oxidising (by EC criteria)

Solubility in water: Soluble

Boiling point/range°C: 105 - 140

Melting point/range°C: -12 - 10

Flammability limits %: lower: Not applicable.

upper: Not applicable.

Flash point°C: Not applicable.

Part.coeff. n-octanol/water: Not applicable.

Autoflammability°C: Not applicable.

Vapour pressure: < 24 hPa at 20°C

Relative density: 1.32

pH: 14

VOC g/l: Not applicable.

[cont...]

SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 5

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.
Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Hazardous ingredients:

SODIUM HYDROXIDE

IPR	MUS	LD50	40	mg/kg
ORL	RBT	LDLO	500	mg/kg

Relevant effects for mixture:

Effect	Route	Basis
Corrosivity	OPT INH DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: Blistering may occur. Progressive ulceration will occur if treatment is not immediate.

Eye contact: Corneal burns may occur. May cause permanent damage.

Ingestion: Corrosive burns may appear around the lips. Blood may be vomited. There may be bleeding from the mouth or nose.

Inhalation: There may be shortness of breath with a burning sensation in the throat. Exposure may cause coughing or wheezing.

Delayed / immediate effects: Immediate effects can be expected after short-term exposure.

[cont...]

SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 6

Other information: Not applicable.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal company.

Disposal of packaging: Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1824

14.2. UN proper shipping name

Shipping name: SODIUM HYDROXIDE SOLUTION

14.3. Transport hazard class(es)

Transport class: 8

14.4. Packing group

Packing group: II

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

[cont...]

SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 7

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: E

Transport category: 2

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: Not applicable.

15.2. Chemical Safety Assessment

Chemical safety assessment: A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

This safety data sheet is prepared in accordance with Commission Regulation (EC) No 1272/2008.

Phrases used in s.2 and s.3: EUH031: Contact with acids liberates toxic gas.
H290: May be corrosive to metals.
H314: Causes severe skin burns and eye damage.
R35: Causes severe burns.

Legend to abbreviations: PNEC = predicted no effect level
DNEL = derived no effect level
LD50 = median lethal dose
LC50 = median lethal concentration
EC50 = median effective concentration
IC50 = median inhibitory concentration
dw = dry weight
bw = body weight
cc = closed cup
oc = open cup
MUS = mouse
GPG = guinea pig
RBT = rabbit
HAM = hamster
HMN = human
MAM = mammal
PGN = pigeon

[cont...]

SAFETY DATA SHEET

KIL-BLOCK ORIGINAL

Page: 8

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular

PCP = phycico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.