

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** MOTIP® PAINT REMOVER 500 ML
- **Article number:** 090410
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Sector of Use**  
SU21 Consumer uses: Private households / general public / consumers  
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Product category** PC9a Coatings and paints, thinners, paint removers
- **Process category**  
PROC7 Industrial spraying  
PROC11 Non industrial spraying
- **Application of the substance / the mixture** Paint remover
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
MOTIP DUPLI B.V.  
Wolframweg 2  
NL- 8471 XC Wolvega  
The Netherlands  
Tel: +31 (0)561 694400  
Fax: +31 (0)561 694411  
e-mail: msds@nl.motipdupli.com
- **Further information obtainable from:** Department Product Safety
- **1.4 Emergency telephone number:**  
+31 (0)561-694400 (09:00h - 17:00h)

UK: NPIS National Poisons Information Centre Tel: +44 0344 892 0111

### SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Aerosol 1 H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**  
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02

- **Signal word** Danger

(Contd. on page 2)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 1)

**· Hazard statements***H222-H229 Extremely flammable aerosol. Pressurised container: May burst if heated.***· Precautionary statements***P101 If medical advice is needed, have product container or label at hand.**P102 Keep out of reach of children.**P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.**P211 Do not spray on an open flame or other ignition source.**P251 Do not pierce or burn, even after use.**P260 Do not breathe spray.**P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.**P501 Dispose of contents / container in accordance with regional regulations.***· 2.3 Other hazards****· Results of PBT and vPvB assessment****· PBT:** Not applicable.**· vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

**· 3.2 Chemical characterisation: Mixtures****· Description:** Mixture of substances listed below with nonhazardous additions.**· Dangerous components:**

CAS: 115-10-6 EINECS: 204-065-8 Index number: 603-019-00-8 Reg.nr.: 01-2119472128-37	dimethyl ether Flam. Gas 1, H220 Press. Gas (Comp.), H280	50-<75%
CAS: 109-87-5 EINECS: 203-714-2 Reg.nr.: 01-2119664781-31	dimethoxymethane Flam. Liq. 2, H225	25-<50%
CAS: 646-06-0 EINECS: 211-463-5 Index number: 605-017-00-2	1,3-dioxolane Flam. Liq. 2, H225	10-<12.5%
CAS: 67-56-1 EINECS: 200-659-6 Index number: 603-001-00-X Reg.nr.: 01-2119433307-44	methanol Flam. Liq. 2, H225 Acute Tox. 3, H301; Acute Tox. 3, H311; Acute Tox. 3, H331 STOT SE 1, H370	<1%
CAS: 108-01-0 EINECS: 203-542-8 Index number: 603-047-00-0 Reg.nr.: 01-2119492298-24	2-dimethylaminoethanol Flam. Liq. 3, H226 Acute Tox. 3, H331 Skin Corr. 1B, H314; Eye Dam. 1, H318 Acute Tox. 4, H302; Acute Tox. 4, H312; STOT SE 3, H335	≤0.5%

**· Additional information:** For the wording of the listed hazard phrases refer to section 16.

### SECTION 4: First aid measures

**· 4.1 Description of first aid measures****· After inhalation:** Supply fresh air; consult doctor in case of complaints.**· After skin contact:** Generally the product does not irritate the skin.**· After eye contact:** Rinse opened eye for several minutes under running water.**· After swallowing:** Drink plenty of water and provide fresh air. Call for a doctor immediately.**· 4.2 Most important symptoms and effects, both acute and delayed** No further relevant information available.**· 4.3 Indication of any immediate medical attention and special treatment needed**

No further relevant information available.

GB

(Contd. on page 3)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

Trade name: **MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 2)

### SECTION 5: Firefighting measures

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture**  
During heating or in case of fire poisonous gases are produced.
- **5.3 Advice for firefighters -**
- **Protective equipment:** Mouth respiratory protective device.

### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Mount respiratory protective device.  
Wear protective equipment. Keep unprotected persons away.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Dispose contaminated material as waste according to item 13.  
Ensure adequate ventilation.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
No special measures required.
- **Information about fire - and explosion protection:**  
Do not spray onto a naked flame or any incandescent material.  
Keep ignition sources away - Do not smoke.  
Keep respiratory protective device available.  
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:**  
Observe official regulations on storing packagings with pressurised containers.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:** Keep container tightly sealed.
- **Storage class:** 2 B
- **7.3 Specific end use(s)** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**

· <b>Ingredients with limit values that require monitoring at the workplace:</b>	
<b>115-10-6 dimethyl ether</b>	
WEL	Short-term value: 958 mg/m <sup>3</sup> , 500 ppm
	Long-term value: 766 mg/m <sup>3</sup> , 400 ppm

(Contd. on page 4)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 3)

**109-87-5 dimethoxymethane**

WEL Short-term value: 3950 mg/m<sup>3</sup>, 1250 ppm  
Long-term value: 3160 mg/m<sup>3</sup>, 1000 ppm

**67-56-1 methanol**

WEL Short-term value: 333 mg/m<sup>3</sup>, 250 ppm  
Long-term value: 266 mg/m<sup>3</sup>, 200 ppm  
Sk

**108-01-0 2-dimethylaminoethanol**

WEL Short-term value: 22 mg/m<sup>3</sup>, 6 ppm  
Long-term value: 7.4 mg/m<sup>3</sup>, 2 ppm

· **Additional information:** The lists valid during the making were used as basis.

· **8.2 Exposure controls**

· **Personal protective equipment:**

· **General protective and hygienic measures:**

Use suitable respiratory protective device in case of insufficient ventilation.

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

· **Respiratory protection:**



Filter ABEK

In case of brief exposure or low pollution use respiratory filter device. In case of intensive or longer exposure use self-contained respiratory protective device.

· **Protection of hands:**

In case of contact with spray dust protective gloves made of butyl should be used (min. 0.4 mm thick), e.g. KCL Camatril, article no. 898 or similar products

Due to missing tests no recommendation to the glove material can be given for the product/ the preparation/ the chemical mixture.

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

· **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

· **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

· **Eye protection:** Not required.

## SECTION 9: Physical and chemical properties

· **9.1 Information on basic physical and chemical properties**

· **General Information**

· **Appearance:**

Form: Aerosol

Colour: Whitish

· **Odour:** Solvent-like

· **Odour threshold:** Not determined.

· **pH-value:** Not determined.

(Contd. on page 5)

GB

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 4)

· <b>Change in condition</b>	
<b>Melting point/freezing point:</b>	Undetermined.
<b>Initial boiling point and boiling range:</b>	Not applicable, as aerosol.
· <b>Flash point:</b>	<0 °C (<32 °F) Not applicable, as aerosol.
· <b>Flammability (solid, gas):</b>	Not applicable.
· <b>Ignition temperature:</b>	235 °C (455 °F)
· <b>Decomposition temperature:</b>	Not determined.
· <b>Explosive properties:</b>	Product is not explosive. However, formation of explosive air/vapour mixtures are possible.
· <b>Explosion limits:</b>	
<b>Lower:</b>	2.2 Vol %
<b>Upper:</b>	26.2 Vol %
· <b>Vapour pressure at 20 °C (68 °F):</b>	4000 hPa (3000.2 mm Hg)
· <b>Density at 20 °C (68 °F):</b>	0.8 g/cm <sup>3</sup> (6.7 lbs/gal)
· <b>Relative density</b>	Not determined.
· <b>Vapour density</b>	Not determined.
· <b>Evaporation rate</b>	Not applicable.
· <b>Solubility in / Miscibility with water:</b>	Not miscible or difficult to mix.
· <b>Partition coefficient: n-octanol/water:</b>	Not determined.
· <b>Viscosity:</b>	
<b>Dynamic:</b>	Not determined.
<b>Kinematic:</b>	Not determined.
· <b>Solvent content:</b>	
<b>Organic solvents:</b>	88.2 %
<b>VOC (EC)</b>	---
	678.6 g/l
· <b>VOC-EU%</b>	88.25 %
· <b>Solids content:</b>	1.1 %
· <b>9.2 Other information</b>	No further relevant information available.

\*

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

\*

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity** Based on available data, the classification criteria are not met.
- **Primary irritant effect:**
- **Skin corrosion/irritation** Based on available data, the classification criteria are not met.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.

(Contd. on page 6)

GB

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 5)

- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

### SECTION 12: Ecological information

#### 12.1 Toxicity

##### Aquatic toxicity:

##### 115-10-6 dimethyl ether

EC50 / 96 h	155 mg/l (algae)
LC50 / 48 h	>4000 mg/l (daphnia magna)
LC50 / 96 h	>4000 mg/l (fish)

- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Additional ecological information:**
- **General notes:**  
Water hazard class 2 (German Regulation) (Self-assessment): hazardous for water  
Do not allow product to reach ground water, water course or sewage system.  
Danger to drinking water if even small quantities leak into the ground.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **12.6 Other adverse effects** No further relevant information available.

### SECTION 13: Disposal considerations

#### 13.1 Waste treatment methods

##### Recommendation

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

##### European waste catalogue

08 01 11*	waste paint and varnish containing organic solvents or other hazardous substances
15 01 04	metallic packaging

##### Uncleaned packaging:

##### Recommendation:

Disposal must be made according to official regulations.  
Pressurized container: protect from sunlight and do not expose to temperatures exceeding 50°C. Do not pierce or burn, even after use.  
Do not spray on a naked flame or any incandescent material.

### SECTION 14: Transport information

#### 14.1 UN-Number

##### ADR, IMDG, IATA

UN1950

#### 14.2 UN proper shipping name

##### ADR

1950 AEROSOLS

##### IMDG

AEROSOLS

(Contd. on page 7)



**Safety data sheet**  
according to 1907/2006/EC, Article 31



Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 6)

· <b>IATA</b>	<b>AEROSOLS, flammable</b>
· <b>14.3 Transport hazard class(es)</b>	
· <b>ADR</b>	
	
· <b>Class</b>	2 5F Gases.
· <b>Label</b>	2.1
· <b>IMDG, IATA</b>	
	
· <b>Class</b>	2.1
· <b>Label</b>	2.1
· <b>14.4 Packing group</b>	
· <b>ADR, IMDG, IATA</b>	not regulated
· <b>14.5 Environmental hazards:</b>	Not applicable.
· <b>14.6 Special precautions for user</b>	Warning: Gases.
· <b>Danger code (Kemler):</b>	-
· <b>EMS Number:</b>	F-D,S-U
· <b>Stowage Code</b>	SW1 Protected from sources of heat. SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.
· <b>Segregation Code</b>	SG69 For AEROSOLS with a maximum capacity of 1 litre: Segregation as for class 9. Stow "separated from" class 1 except for division 1.4. For AEROSOLS with a capacity above 1 litre: Segregation as for the appropriate subdivision of class 2. For WASTE AEROSOLS: Segregation as for the appropriate subdivision of class 2.
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
· <b>ADR</b>	
· <b>Limited quantities (LQ)</b>	1L
· <b>Excepted quantities (EQ)</b>	Code: E0 Not permitted as Excepted Quantity Code: E0 Not permitted as Excepted Quantity
· <b>Transport category</b>	2
· <b>Tunnel restriction code</b>	D
· <b>IMDG</b>	
· <b>Limited quantities (LQ)</b>	1L
· <b>Excepted quantities (EQ)</b>	Code: E0 Not permitted as Excepted Quantity Code: E0 Not permitted as Excepted Quantity

(Contd. on page 8)

# Safety data sheet

## according to 1907/2006/EC, Article 31

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 7)

· **UN "Model Regulation":**

UN 1950 AEROSOLS, 2.1

### SECTION 15: Regulatory information

· **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**· **Directive 2012/18/EU**· **Named dangerous substances - ANNEX I** None of the ingredients is listed.· **Seveso category P3a** FLAMMABLE AEROSOLS· **Qualifying quantity (tonnes) for the application of lower-tier requirements** 150 t· **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t· **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3· **National regulations:**· **Other regulations, limitations and prohibitive regulations**· **Substances of very high concern (SVHC) according to REACH, Article 57**

None of the ingredients is listed.

· **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Relevant phrases**

H220 Extremely flammable gas.

H225 Highly flammable liquid and vapour.

H226 Flammable liquid and vapour.

H280 Contains gas under pressure; may explode if heated.

H301 Toxic if swallowed.

H302 Harmful if swallowed.

H311 Toxic in contact with skin.

H312 Harmful in contact with skin.

H314 Causes severe skin burns and eye damage.

H318 Causes serious eye damage.

H331 Toxic if inhaled.

H335 May cause respiratory irritation.

H370 Causes damage to organs.

· **Department issuing SDS:** R&D legislation and regulatory advisor· **Contact:** msds@nl.motipdupli.com· **Abbreviations and acronyms:**

RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)

ICAO: International Civil Aviation Organisation

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Flam. Gas 1: Flammable gases – Category 1

Aerosol 1: Aerosols – Category 1

Press. Gas (Comp.): Gases under pressure – Compressed gas

Flam. Liq. 2: Flammable liquids – Category 2

(Contd. on page 9)



**Safety data sheet**  
**according to 1907/2006/EC, Article 31**

Printing date 07.01.2020

Version number 2

Revision: 17.12.2019

**Trade name: MOTIP® PAINT REMOVER 500 ML**

(Contd. of page 8)

*Flam. Liq. 3: Flammable liquids – Category 3*  
*Acute Tox. 3: Acute toxicity - oral – Category 3*  
*Acute Tox. 4: Acute toxicity - oral – Category 4*  
*Skin Corr. 1B: Skin corrosion/irritation – Category 1B*  
*Eye Dam. 1: Serious eye damage/eye irritation – Category 1*  
*STOT SE 1: Specific target organ toxicity (single exposure) – Category 1*  
*STOT SE 3: Specific target organ toxicity (single exposure) – Category 3*  
**. \* Data compared to the previous version altered.**

GB