

## Section 1. Product and Company Identification.

**1.1 Model Number;** CV9612 v1

**1.2 Description;** Universal Stretch CVJ Boot Ø56-116mm (Pack of 12 x CV96)

Grease sachet: 60 grams each.

1.3 Manufacturer;

Sealey Group. Kempson Way, Bury St. Edmunds, Suffolk.

**IP32 7AR** 

1.4 Emergency telephone number; 44 (0) 1284 757 500 (Office Hours)

Date of source compilation; 12 October 2011

## Section 2. Hazards Identification.

2.1 Classification of the substance or mixture.

Carc. 1B Carc. Cat. 2

#### Risk phrases;

R45 May cause cancer.

#### 2.2 Label elements.

#### Hazard statements;

H350 May cause cancer.

#### Precautionary statements;

P304 + P341 IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337 + P313 If eye irritation persists: Get medical advice/attention.

P301 + P331 IF SWALLOWED: Do NOT induce vomiting.

P301 + P310 IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

P403 + P235 Store in a well-ventilated place. Keep cool.

P285 In case of inadequate ventilation wear respiratory protection.

P262 Do not get in eyes, on skin, or on clothing.

P260 Do not breathe fumes/vapours.

P280 Wear protective gloves/protective clothing/eye protection/.

P361 Remove/Take off immediately all contaminated clothing.

P360 Rinse immediately contaminated clothing and skin with plenty of water before removing clothes.

P332 + P313 If skin irritation occurs: Get medical advice/attention.

P403 + P233 Store in a well-ventilated place. Keep container tightly closed.

#### 2.3 Other hazards.

None identified.



### Section 3. Substances.

			Classification	
3.1 Chemical Name (substance)	3.1 CAS No.	3.2 Concentration Weight	Hazard Class & Category Code	Hazard Statements
Blend of mineral oils. Distillates (petroleum),	64742-52-5	000/ 020/	Carc. 1B Carc. Cat. 2; R45	H350
Hydrotreated heavy naphtha. Distillates (petroleum), hydrotreated heavy paraff.	64742-54-7	88% - 92%	Carc. 1B Carc. Cat. 2; R45	H350
Zinc Dialkyldithiophosphate >1.5%	68649-42-3	1% - 1.5%	-	-

For full text of Phrases and Statements, see Section 16.

### Section 4. First Aid Measures.

#### **4.1** Description of first aid measures

#### Inhalation

Under normal conditions of intended use, this material is not expected to be an inhalation hazard. IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.

#### **Skin Contact**

Rinse immediately contaminated clothing and skin with plenty of water before removing clothes.

If grease has been injected under the skin, get Medical advice/attention immediately.

If skin irritation occurs: Get medical advice/attention.

### **Eye Contact**

IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

If eye irritation persists: Get medical advice/attention.

#### Ingestion

IF SWALLOWED: Do NOT induce vomiting.

IF SWALLOWED: Immediately call a POISON CENTER or doctor/physician.

- **4.2.** Most important symptoms and effects, both acute and delayed No information available.
- **4.3.** Indication of any immediate medical attention and special treatment needed No information available.



## **Section 5. Fire Fighting Measures.**

#### 5.1. Extinguishing media

Rinse immediately contaminated clothing and skin with plenty of water before removing clothes.

### **5.2.** Special hazards arising from the substance or mixture

This product may give rise to hazardous fumes in a fire

#### 5.3. Advice for fire-fighters

Wear self-contained breathing apparatus.

### Section 6. Accidental Release Measures.

**6.1.** Personal precautions, protective equipment and emergency procedures Ventilate area.

#### **6.2.** Environmental precautions

Do not allow to enter water courses, sewers, drains, water supplies.

### 6.3. Methods and material for containment and cleaning up

Absorb in inert material such as sand or absorbent granules.

Dispose of in accordance with Section 13.

#### 6.4. Reference to other sections

See Section 7 for information on Safe Handling

See Section 8 for information of Personal Protective Equipment.

See Section 13 for information on disposal.

## Section 7. Handling and Storage.

#### 7.1. Precautions for safe handling

Avoid skin and eye contact.

Avoid inhalation of vapour – ensure adequate ventilation and/or use local extraction.

Wear polythene, Nitrile or Viton gloves.

Wear safety glasses.

Wear suitable protective clothing.

Ambient Relative Humidity should be >35% to minimise discomfort.

#### **7.2.** Conditions for safe storage, including any incompatibilities

Store in a well-ventilated place. Keep container tightly closed.

Store in a dry place.

Store in a well-ventilated place. Keep cool.

Keep away from oxidising agents and from strong acids/alkalis.

#### **7.3.** Specific end use(s)

Intended for use as the grease for use with the Model Number identified in 1.1 with Description stated in 1.2.



## Section 8. Exposure Controls/Personal Protection.

#### **8.1.** Control parameters

P262 Do not get in eyes, on skin, or on clothing.

P304 + P341 IF INHALED: If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.

P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P260 Do not breathe fumes/vapours.

P280 Wear protective gloves/protective clothing/eye protection/.

P361 Remove/Take off immediately all contaminated clothing.

P360 Rinse immediately contaminated clothing and skin with plenty of water before removing clothes.

P332 + P313 If skin irritation occurs: Get medical advice/attention.

#### **8.2.** Exposure controls

#### **Appropriate Engineering Controls**

Ensure adequate ventilation.

Ambient Relative Humidity should be >35% to minimise discomfort.

#### **Eye/Face Protection**

EN 166 approved eye protection.

#### **Skin Protection**

Nitrile or Viton gloves.

EN 13034 approved protective clothing.

#### **Respiratory Protection**

No protection is ordinarily required under normal conditions of use and with adequate ventilation. In case of inadequate ventilation wear respiratory protection.

**Specific Hygiene Measures:** Always observe good personal hygiene measures, such as washing after handling the material and before eating, drinking, and/or smoking. Routinely wash work clothing and protective equipment to remove contaminants. Discard contaminated clothing and footwear that cannot be cleaned. Practice good housekeeping.



Grey/Black. Smooth Semi-Fluid to Stiff Grease.

# Section 9. Physical and Chemical Properties.

9.1. Information on basic physical and chemical properties

(a) Appearance:

The following information is not a technical specification or sales specification.

(b) Odour: Odourless.

(c) Odour threshold; No information available.

(d) pH: Neutral

(e) Melting point; Melts above 200°C

(f) Initial boiling point and boiling range; No information available.

(g) Flash point; Exceed 200°C

(h) Evaporation rate;
No information available.
(i) Flammability (solid, gas);
No information available.
No information available.

(k) Vapour pressure;
No information available.
(l) Vapour density;
No information available.

(m) Relative density; 0.82-0.85 (Measured as kg/litre) @15°C

(n) Solubility(ies); Soluble in oil. Insoluble in water.

(o) Partition coefficient: n-octanol/water; No information available.

(p) Auto-ignition temperature; Exceeds 200°C

(q) Decomposition temperature;
 (r) Viscosity;
 (s) Explosive properties;
 (t) Oxidising properties.
 No information available.
 No information available.

**9.2** Other information No information available.



## Section 10. Stability and Reactivity.

10.1. Reactivity10.2. Chemical stabilityNo dangerous reactions known.Stable under normal conditions.

**10.3.** Possibility of hazardous reactions None known.

**10.4.** Conditions to avoid Heat.

**10.5.** Incompatible materials Strong oxidising agents.

**10.6.** Hazardous decomposition products Combustion will generate smoke, carbon dioxide and

carbon monoxide.

## **Section 11. Toxicological Information.**

**11.1.** Information on toxicological effects

No information available.

## **Section 12. Ecological Information.**

**12.1.** Toxicity

No information available. **12.2.** Persistence and degradability

Only slightly biodegradable.

**12.3.** Bioaccumulative potential Product is not expected to bioaccumulate.

**12.4.** Mobility in soil Non-volatile. Poorly absorbed into soils or sediments.

**12.5.** Results of PBT and vPvB assessment No information available. **12.6.** Other adverse effects No information available.

## **Section 13. Disposal Considerations.**

13.1. Waste treatment methods

Disposal must be in accordance with local authority regulations.

Do not dispose of at landfill sites.

Do not incinerate.

# **Section 14. Transport Information.**

ADR. International Carriage of Dangerous Goods by Road.

Not regulated.

IATA. International Air Transport Association.

Not regulated.

IMDG. International Maritime Dangerous Goods.

Not regulated.



## **Section 15. Regulatory Information.**

**15.1.** Safety, health and environmental regulations/legislation specific for the substance or mixture No information available.

**15.2.** Chemical safety assessment No information available.

## Section 16. Additional Information.

Full text of Phrases and Statements used in Section 3;

H350 May cause cancer.

R45 May cause cancer.

The above information is believed to be accurate and represents the best information currently available.

No warranty is expressed or implied by the above information.

We assume no liability resulting from use of the above information.

The end user should conduct their own investigations to determine the suitability of the above information for their particular purpose.

Issue level	Date	Revisions
1	04/03/16	First issue.
2	29/06/16	Sections 2, 3, 7, 8
3	27/02/17	Format only.

End of Safety Data Sheet.