

SAFETY DATA SHEET

Version 1

Issue Date 06-Nov-2014
Revision date 06-Nov-2014

1. IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING

PRODUCT NAME: 16049 10.8V HAMMER DRILL STORMFORCE

APPLICATIONS: 10.8V HAMMER DRILL STORMFORCE

SUPPLIER: Draper Tools Ltd
Hursley Road
Chandlers Ford
Eastleigh
Hampshire
SO53 1YF

Draper Helpline +44 (0) 2380 494344

2. HAZARDS IDENTIFICATION

GHS Classification

Not a dangerous substance or mixture according to the Globally Harmonized System (GHS)

Label elements

Symbols/Pictograms None
Signal word None
Hazard Statements Not applicable
Precautionary Statements Not applicable

Hazards not otherwise classified (HNOC)

No information available

Unknown acute toxicity

No information available

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical nature

Article

Chemical Name	CAS No	Weight-%
Nickel-cobalt-manganese ternary materials	-	30 - 32
Iron	7439-89-6	25 - 27
Graphite	7782-42-5	14 - 15
Copper	7440-50-8	13 - 15
Aluminum foil	7429-90-5	6 - 7
Polypropylene(PP)	9003-07-0	2 - 3
Lithium	7439-93-2	1 - 2

4. FIRST AID MEASURES

Description of first aid measures

General advice	Remove contaminated clothing and shoes. If symptoms persist, call a physician.
Inhalation	Not an expected route of exposure. IF INHALED: Remove victim to fresh air and keep at rest in a position comfortable for breathing.
Skin Contact	Wash hands thoroughly after handling. .
Eye contact	Not an expected route of exposure. .
Ingestion	Not an expected route of exposure. If swallowed, call a poison control center or physician immediately. Rinse mouth.

Most important symptoms and effects, both acute and delayed

No information available.

Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Extinguishing media

Suitable extinguishing media	Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.
Unsuitable extinguishing media	No information available.

Specific hazards arising from the chemical

Thermal decomposition can lead to release of irritating and toxic gases and vapors

Protective equipment and precautions for firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Evacuate personnel to safe areas
Ensure adequate ventilation, especially in confined areas
Remove all sources of ignition
Use personal protection recommended in Section 8

Methods and material for containment and cleaning up

Pick up and transfer to properly labeled containers
Avoid release to the environment

7. HANDLING AND STORAGE

Precautions for safe handling

Handle in accordance with good industrial hygiene and safety practice
Ensure adequate ventilation, especially in confined areas
Avoid creating dust
Avoid contact with eyes
Wash thoroughly after handling
Use personal protection recommended in Section 8

Conditions for safe storage, including any incompatibilities

Keep containers tightly closed in a dry, cool and well-ventilated place
Keep away from heat

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH	Denmark	European Union
Graphite (CAS #: 7782-42-5)	TWA: 2 mg/m ³ respirable fraction all forms except graphite fibers	-	-	TWA: 2.5 mg/m ³	-
Copper (CAS #: 7440-50-8)	TWA: 0.2 mg/m ³ fume TWA: 1 mg/m ³ Cu dust and mist	-	-	TWA: 1.0 mg/m ³ TWA: 0.1 mg/m ³	-
Aluminum foil (CAS #: 7429-90-5)	TWA: 1 mg/m ³ respirable fraction	TWA: 15 mg/m ³ total dust TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 15 mg/m ³ total dust (vacated) TWA: 5 mg/m ³ respirable fraction (vacated) TWA: 5 mg/m ³ Al Aluminum	TWA: 10 mg/m ³ total dust TWA: 5 mg/m ³ respirable dust TWA: 5 mg/m ³ Al	TWA: 5 mg/m ³ TWA: 2 mg/m ³	-

Chemical Name	Latvia	France	Finland	Germany	Italy
Aluminum foil (CAS #: 7429-90-5)	TWA: 2 mg/m ³	TWA: 10 mg/m ³ TWA: 5 mg/m ³	TWA: 1.5 mg/m ³	TWA: 4 mg/m ³ TWA: 1.5 mg/m ³	-

Chemical Name	Poland	Portugal	Spain	Switzerland	Netherlands
Aluminum foil (CAS #: 7429-90-5)	TWA: 2.5 mg/m ³ TWA: 1.2 mg/m ³	TWA: 10 mg/m ³ TWA: 5 mg/m ³	TWA: 10 mg/m ³ TWA: 5 mg/m ³	TWA: 3 mg/m ³	TWA: 0.05 mg/m ³

Chemical Name	Norway	United Kingdom	Australia	Austria	Belgium
Graphite (CAS #: 7782-42-5)	-	-	3 mg/m ³	STEL 10 mg/m ³ TWA: 5 mg/m ³	-
Copper (CAS #: 7440-50-8)	-	-	1 mg/m ³ 0.2 mg/m ³	STEL 4 mg/m ³ STEL 0.4 mg/m ³ TWA: 1 mg/m ³ TWA: 0.1 mg/m ³	-
Aluminum foil (CAS #: 7429-90-5)	TWA: 5 mg/m ³ STEL: 10 mg/m ³	STEL: 30 mg/m ³ STEL: 12 mg/m ³ TWA: 10 mg/m ³ TWA: 4 mg/m ³	10 mg/m ³ 5 mg/m ³	STEL 20 mg/m ³ TWA: 10 mg/m ³	-

Appropriate engineering controls

Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Respiratory protection	If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.
Hand Protection	Wear protective gloves.
Eye/face protection	No special technical protective measures are necessary.
Skin and body protection	Wear suitable protective clothing.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Appearance	Solid
Color	No information available

Odor	Odorless
Odor Threshold	Not determined
pH	Not determined
Melting point/freezing point	Not determined
Boiling point / boiling range	Not determined
Flash point	Not applicable
Evaporation rate	Not determined
Flammability (solid, gas)	Not determined
Flammability Limit in Air	Not determined
Vapor Pressure	Not applicable
Vapor density	Not determined
Density	Not determined
Relative density	Not determined
Bulk density	Not determined
Specific gravity	Not determined
Water solubility	Not determined
Partition coefficient (LogPow)	Not determined
Autoignition temperature	Not determined
Decomposition temperature	Not determined
Kinematic viscosity	Not determined
Dynamic viscosity	Not determined
Explosive properties	Not an explosive
Oxidizing properties	Not determined

Other information

No information available

10. STABILITY AND REACTIVITY**Reactivity**

Stable under recommended storage and handling conditions (see SECTION 7, handling and storage).

Chemical stability

Stable under normal conditions

Possibility of Hazardous Reactions

None under normal processing

Conditions to avoid

Strong heating. Incompatible materials

Incompatible materials

Strong acids Strong bases Strong oxidizing agents

Hazardous Decomposition Products

None known based on information supplied

11. TOXICOLOGICAL INFORMATION**Information on likely routes of exposure**

Inhalation	Inhalation of vapors in high concentration may cause irritation of respiratory system
Eye contact	Contact with eyes may cause irritation
Skin Contact	Substance may cause slight skin irritation
Ingestion	Ingestion may cause irritation to mucous membranes

Information on toxicological effects

Acute toxicity

Chemical Name	Oral LD50	Dermal LD50	Inhalation LC50
Iron (CAS #: 7439-89-6)	98.6 g/kg bw (rat)	-	-
Copper (CAS #: 7440-50-8)	> 2500 mg/kg bw(rat)	> 2000 mg/kg bw(rat)	=1.03 mg/L/4 h(rat)
Polypropylene (CAS #: 9003-07-0)	>5 g/kg	-	-

Skin corrosion/irritation

Non-irritating to the skin

Serious eye damage/eye irritation

No eye irritation

Sensitization

No information available

Germ cell mutagenicity

No information available

Carcinogenicity

No information available

Reproductive toxicity

No information available

STOT - single exposure

No information available

STOT - repeated exposure

No information available

Aspiration hazard

No information available

12. ECOLOGICAL INFORMATION**Ecotoxicity**

Chemical Name	Algae/aquatic plants EC50	Fish LC50	Crustacea EC50
Iron (CAS #: 7439-89-6)	-	-	> 100 mg/L/48h (Daphnia magna)
Copper (CAS #: 7440-50-8)	0.031 - 0.054 mg/L/96h Pseudokirchneriella subcapitata static 0.0426 - 0.0535 mg/L/72h Pseudokirchneriella subcapitata static	-	-

Persistence and degradability

No information available

Bioaccumulative potential

No information available

Mobility in soil

No information available

Other adverse effects

No information available

13. DISPOSAL CONSIDERATIONS**Waste treatment methods**

Disposal of wastes Disposal should be in accordance with applicable regional, national and local laws and regulations

Contaminated packaging Dispose of in accordance with federal, state and local regulations

Chemical Name	California Hazardous Waste Status
Copper 7440-50-8	Toxic
Aluminum foil 7429-90-5	Ignitable powder

14. TRANSPORT INFORMATION**DOT**

UN/ID No. Not regulated

Proper shipping name Not regulated

Hazard Class Not regulated

Packing Group Not regulated

Special precautions No information available

Marine pollutant Not applicable

15. REGULATORY INFORMATION**International Inventories**

Component	AICS	DSL/NDL	EINECS/ELI NCS	ENCS	IECSC	KECL	PICCS	TSCA
Iron 7439-89-6	X	X	X	-	X	X	X	X
Graphite 7782-42-5	X	X	X	-	X	X	X	X
Copper 7440-50-8	X	X	X	-	X	X	X	X
Aluminum foil 7429-90-5	X	X	X	-	X	X	X	X
Lithium 7439-93-2	X	X	X	X	X	X	X	X

"- Not Listed

"X" Listed

US Federal Regulations**SARA 313**

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product contains a chemical or chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

Chemical Name	SARA 313 - Threshold Values %
Aluminum foil - 7429-90-5	1.0

SARA 311/312 Hazard Categories

No information available

CWA (Clean Water Act)

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Copper 7440-50-8	-	X	X	-

CERCLA

No information available

US State Regulations

California Proposition 65

No information available

U.S. State Right-to-Know Regulations

No information available

16. OTHER INFORMATION

Revision Note

Issue Date	06-Nov-2014
Revision date	06-Nov-2014
Revision Note	Not applicable

Key or legend to abbreviations and acronyms used in the safety data sheet

TWA - TWA (time-weighted average)
STEL - STEL (Short Term Exposure Limit)
Ceiling - Maximum limit value
TSCA - United States Toxic Substances Control Act Section 8(b) Inventory
DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List
EINECS/ELINCS - European Inventory of Existing Chemical Substances/European List of Notified Chemical Substances
ENCS - Japan Existing and New Chemical Substances
IECSC - China Inventory of Existing Chemical Substances
KECL - Korean Existing and Evaluated Chemical Substances
PICCS - Philippines Inventory of Chemicals and Chemical Substances
AICS - Australian Inventory of Chemical Substances

Disclaimer

The information provided in this Material Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

----- End of Safety Data Sheet -----