



INSPECTION LAMP

11764, 11765, 11766 & 11767



IMPORTANT: Please read these instructions carefully to ensure the safe and effective use of this product and save these instructions for future reference. This manual has been compiled by Draper Tools and is an integrated part of the product with which it is enclosed and should be kept with it for future references.

This manual describes the purpose for which the product has been designed and contains all the necessary information to ensure its correct and safe use. We recommend that this manual is read before any operation or, before performing any kind of adjustment to the product and prior to any maintenance tasks. By following all the general safety instructions contained in this manual, it will ensure both product and operator safety, together with longer life of the product itself.

All photographs and drawings in this manual are supplied by Draper Tools to help **ill**ustrate the operation of the product. Whilst every effort has been made to ensure accuracy of information contained in this manual, the Draper Tools policy of continuous improvement determines the right to make modifications without prior warning.

1.1 INTRODUCTION:

USER MANUAL FOR: INSPECTION LAMP Stock nos. 11764, 11765, 11766 & 11767. Part nos. RIL/COB1000/B, RIL/COB1000/G, RIL/COB1000/V.

1.2 REVISIONS:

Date first published August 2019

As our user manuals are continually updated, users should make sure that they use the very latest version.

Downloads are available from: http://www.drapertools.com/manuals

DRAPER TOOLS LIMITED HURSLEY ROAD CHANDLER'S FORD EASTLEIGH HAMPSHIRE SO53 1YF UK WEBSITE: PRODUCT HELPLINE: GENERAL FAX: drapertools.com +44 (0) 23 8049 4344 +44 (0) 23 8026 0784

1.3 UNDERSTANDING THIS MANUALS SAFETY CONTENT:

WARNING! Information that draws attention to the risk of injury or death.

CAUTION! Information that draws attention to the risk of damage to the product or surroundings.

1.4 COPYRIGHT © NOTICE:

Copyright C Draper Tools Limited.

Permission is granted to reproduce this publication for personal & educational use only. Commercial copying, redistribution, hiring or lending is prohibited.

No part of this publication may be stored in a retrieval system or transmitted in any other form or means without written permission from Draper Tools Limited.

In all cases this copyright notice must remain intact.

2.1 CONTENTS

Page	conte	nt Page	
1	TITLE P.	AGE	
	1.1	INTRODUCTION	
	1.2	REVISION HISTORY	
	1.3	UNDERSTANDING THIS MANUAL	
	1.4	COPYRIGHT NOTICE	
2	CONTENTS		
	2.1	CONTENTS	
3	GUARAI		
	3.1	GUARANTEE	
4	INTROD		
	4.1	SCOPE4	
	4.2	SPECIFICATION	
	4.3	HANDLING & STORAGE	
5	HEALTH	I & SAFETY INFORMATION	
	5.1	GENERAL SAFETY INSTRUCTIONS	
	5.2	CONNECTION TO THE POWER SUPPLY (CHARGER)	
6		ICATION	
	6.1	WHAT'S IN THE BOX?	
7	UNPACH	KING & CHECKING	
	7.1	PACKAGING	
8		RING THE INSPECTION LAMP	
	8.1	CHARGING	
9	OPERA	FING THE INSPECTION LAMP	
	9.1	OPERATION	
10	MAINTE	NANCE	
11	EXPLAN	IATION OF SYMBOLS	
	11.1	EXPLANATION OF SYMBOLS	
12	DISPOS	AL	
		DISPOSAL	
DECLA	RATION	OF CONFORMITY ENCLOSED	

3.1 GUABANTEE

Draper tools have been carefully tested and inspected before shipment and are guaranteed to be free

Draper tools have been carefully tested and inspected before shipment and are guaranteed to be free from defective materials and workmanship. Should the tool develop a fault, please return the complete tool to your nearest distributor or contact Draper Tools Limited, Chandler's Ford, Eastleigh, Hampshire, SO53 1YF. England. Telephone Sales Desk: (023) 8049 4333 or Product Helpline (023) 8049 4344. A proof of purchase must be provided with the tool. If upon inspection it is found that the fault occurring is due to defective materials or workmanship, repairs will be carried out free of charge. This guarantee period covering parts/labour is 12 months from the date of purchase except where tools are hired out when the guarantee period is 90 days from the date of purchase. This guarantee does not apply to normal wear and tear, nor does it cover any damage caused by misuse, careless or unsafe handling, alterations, accidents, or repairs attempted or made by any personnel other than the authorised Draper warranty repair agent. Note: If the tool is found not to be within the terms of warranty, repairs and carriage charges will be quoted and made accordingly. This guarantee applies in lieu of any other guarantee expressed or implied and variations of its terms are not authorised.

are not authorised

Vour Draper guarantee is not effective unless you can produce upon request a dated receipt or invoice to verify your proof of purchase within the guarantee period. Please note that this guarantee is an additional benefit and does not affect your statutory rights. Draper Tools Limited.

4. INTRODUCTION

4.1 SCOPE

10W COB LED rechargeable inspection lamp, to be used as an inspection lamp or as a torch. Magnets on the base and on the rear, two 360° swivel hooks. Base pivots 180°, supplied with mains charger and USB C charging lead.

4.2 SPECIFICATION

Stock nos.. Part nos COBIED 10W Lumens

High)
Mědium)
Low)
Lamp operating time:	
High	r
Mēdium	
Low	
SMD LED	V
Lumens)
Lamp operating time	s
Battery:	
Type Li-ior	n
Rated Voltage	/
Rating	٦
Charging time	s
Charger:	
Rated Voltage 230V-	~
Rated Frequency	z
Rated Power Input	V
Rated D.C. Output Voltage 5V DC	2
Rated D.C. Output Current	A
Construction	

4.3 HANDLING & STORAGE

Do not drop the inspection lamp as this can damage and shorten the life span of the unit. Store in a dry location as damp conditions can damage the inspection lamp. Charging on a regular basis is advised to prolong the life of the battery cells.

5. HEALTH & SAFETY INFORMATION

5.1 GENERAL SAFETY INSTRUCTIONS

ver Tools Safety Warnings General Po

WARNING: Read all instructions. Failure to follow all instructions listed below may result in electric shock, fi serious injury. Save all warnings and instructions for future reference e to follow all lectric shock, fire and/or

The term "power tool" in the warnings refers to your mains operated (corded) power tool or battery operated (cordless) power tool.

Work area safety

- Ke a)
 - ep work area clean and well lit. Cluttered or dark eas invite accidents.
 - areas invite accidents. b) Do not operate power tools in explosive atmospheres, such as in the presence of flammable liquids, gases or dust. Power tools create sparks which may ignite the dust or fumes. c) Keep children and bystanders away while operating a power tool. Distractions can cause you to lose contro Elocated F deta.
- ating 2)
 - a power tool. Distractions can cause you to lose control. ectrical Safety Power tool plugs must match the outlet. Never modify the plug in any way. Do not use any adapter plugs with earhed (grounded) power tools. Unmodified plugs and matching outlets will reduce risk of electrical shock. Avoid body contact with earthed or grounded surfaces such as pipes, radiators, ranges and refrigerators. There is an increased risk of electric shock if your body is earthed or grounded. Do not expose power tools to rain or wet conditions. Water entering a power tool will increase the risk of electric shock. Do not abuse the cord. Never use the cord for a
 - b)
 - C)
 - electric shock. Do not abuse the cord. Never use the cord for carrying, pulling or unplugging the power tool. Keep cord away from heat, oil, sharp edges or moving parts. Damaged or entangled cords increase the risk of electric shock. d)
 - When operating a power tool outdoors, use an extension cord suitable for outdoor use. Use of a cord suitable for outdoor use reduces the risk of elect e
 - If operating a power tool in a damp location is unavoidable, use a residual current device (RCD) protected supply. Use of an RCD reduces the risk of electric shock.
- 3)
- electric shock. rsonal Safety Stay alert, watch what you are doing and use common sense when operating a power tool. Do not use a power tool while you are tired or under the influence of drugs, alcohol or medication. A moment of inattention while operating power tools may result in serious personal injury. Use personal protective equipment. Always wear eye protection. Protective equipment such as dust mask, non-skid safety shoes, hard hat, or hearing protection used for appropriate conditions will reduce personal injuries. Prevent unintentional starting Ensure the a)
 - b)
 - Prevent unintentional starting. Ensure the switch is in the off position before connecting to power source and/or battery pack, picking up or carrying the tool. Carrying power tools with your finger on the switch or energising power tools that have the switch or C) itch on nvites accide
 - Remove any adjusting key or wrench before turning the power tool on. A wrench or a key left attached to a rotating part of the power tool may result in personal d) rotatir injury.


- Do not overreach. Keep proper footing and balance at all times. This enables better control of the power tool in unexpect d situations
- f) /ay
- in unexpected situations. Dress properly, Do not wear loose clothing or jewellery. Keep your hair, clothing and gloves awa from moving parts. Loose clothes, jewellery or long hair can be caught in moving parts. If devices are provided for the connection of dust extraction and collection facilities, ensure these an connected and property used. Use of dust collection can reduce dust related hazards. g) are
- 4) Po
- bein reduce dust related hazards. were Tool Use And Care Do not force the power tool. Use the correct power tool for your application. The correct power tool will do the job better and safer at the rate for which it was designed.
 - b)
 - c)
 - It by Do Detice and Seler at the rate to much which designed. Do not use the power tool if the switch does not turn it on and off. Any power tool that cannot be controlled with the switch is dangerous and must be repaired. Disconnect the plug from the power source and/or the battery pack from the power source and/or the battery pack from the power source and/or power tools. Such preventive safety measures reduce the risk of starting the power tool accidentally. Store fidle power tools out of the reach of children and do not allow persons unfamiliar with the power tool or these instructions to operate the power tools accidental vests. d)
 - users. Maintain power tools. Check for misalignment or binding of moving parts, breakage of parts and any other condition that may affect the power tools operation. If damaged, have the power tools repaired before use. Many accidents are caused by poorly maintained power tools. Keep cutting tools with sharp cutting edges are less likely to bind and are easier to control. Use the power tool accessories and tool bits etc. e)
 - f)
 - Lises merry to unit and and easier to control. Use the power tool, accessories and tool bits etc., in accordance with these instructions, taking into account the working conditions and the work to b performed. Use of the power tool for operations different from intended could result in a hazardous situation a) situation
- 5) Ba
- Interview of the second second
 - b.
 - another battery pack. Use power tools only with specifically designated battery packs. Use of any other battery packs may create a risk of injury and fire. When battery pack is not in use, keep it away from other metal objects, like paper clips, coins, keys, nails, screws or other small metal objects, that can make a connection from one terminal to another. Shorting the battery terminals together may cause burns or a fire. c.
 - or a tre. Under abusive conditions, liquid may be ejected from the battery; avoid contact. If contact accidentally occurs, flush with water. If liquid contacts eyes, additionally seek medical help. Liquid ejected from the battery may cause irritation or burns. d.
- 6) S
- Have your power tool serviced by a qualified rep person using only identical replacement parts. This will ensure that the safety of the power tool is estimated a.

5.2 CONNECTION TO THE POWER SUPPLY (CHARGER)

Make su e power supply information on the product's compatible with the power supply you intend rating plate is c to connect it to This lamp comes supplied with a UK standard 3 pin transformer. It is designed for connection to a domestic power supply rated at 230V AC.

6. IDENTIFICATION

It is Class 2 (double insulated); is designed for connect to a power supply matching that detailed on the rating label and compatible with the plug fitted. ction label and compatible with the plug fitted. If an extension lead is required, use an approved and compatible lead rated for this appliance, Follow all the instruction supplied with the extension lead. This product requires no earth connection as supplementary insulation is applied to the basic insulation to protect against electric shock in the event of failure of the basic insulation.



7. UNPACKING & CHECKING

7.1 PACKAGING

Carefully remove the product from the packaging and examine it for any sign of damage caused during shipping. Lay the contents out and check them. If any part is damaged or missing, do not attempt to use the tool and contact the Draper Helpline immediately (see back page for details). Retain the packaging material at least during the guarantee period: in case the product needs to be returned for repair.

Warning! Some of the packaging materials used may be harmful to children, keep them out of reach from children

Disposed of any packaging correctly and according to local regulations.

8. PREPARING THE INSPECTION LAMP

8.1 **CHARGING - FIG.1**

Connect the charging USB C socket (7), which is located on the rear of the inspection lamp. Connect the 230V charger to a power supply and turn it on

The charging indicator LED ③ will illuminate to show the charging has started.

NOTE: The charging indicator remains lit and does not extinguish when the lamp is fully charged.

Disconnect the charger from the inspection lamp when it has been charged for a sufficient time.

9. OPERATING THE INSPECTION LAMP

OPERATION - FIG.2 9,1

CAUTION: Never shine the LED light directly into your or anyone else's eyes

run through the sequence of modes (3W SMD LED, 10W COB LEDs and off), press the on/off ④ button.

The lamp can be suspended on 360° swivel hooks (6) or attached by the magnets (8) and (9) located on the rear or of the lamp. During operation, the battery indicator LEDs will illuminate to show battery charge level. , ear or base

10. MAINTENANCE

Keep the inspection lamp clean from dirt and grease, using a damp cloth. Do not submerge in water.

11. EXPLANATION OF SYMBOLS

10.1 EXPLANATION OF SYMBOLS

Carefully remove the product from the packaging and examine it for any sign of damage Class II construction (Double insulated).



WEEE Do not dispose of Waste Electrical & Electronic Equipment in with domestic rubbish



For indoor use only. Do not expose to rain.

12. DISPOSAL

12.1 DISPOSAL

- At the end of the product's working life, or when it can no longer be repaired, ensure that it is disposed of according to national regulations.
 - Contact your local authority for details of collection schemes in your area. In all circumstances:
 - Do not dispose of power tools with domestic waste.
 - Do not incinerate.
 - Do not abandon in the environment.
 - Do not dispose of WEEE* as unsorted municipal waste.
 - * Waste Electrical & Electronic Equipment.



FIG.1



FIG.2

CONTACT US

Draper Tools Limited, Hursley Road, Chandler's Ford, Eastleigh, Hampshire. SO53 1YF. U.K.

Helpline: +44 (0) 23 8049 4344

Sales Desk: +44 (0) 23 8049 4333

Internet: www.drapertools.com

E-mail: sales@drapertools.com

General Enquiries: (023) 8026 6355

Service/Warranty Repair Agent:

For aftersales servicing or warranty repairs, please contact the Draper Tools Helpline for details of an agent in your local area.

YOUR DRAPER STOCKIST

©Published by Draper Tools Limited.

No part of this publication may be reproduced, stored in a retrieval system or transmitted in any form or by any means, electronic, mechanical photocopying, recording or otherwise without prior permission in writing from Draper Tools Ltd.