



# FLEXIBLE NOZZLE UNDERBODY **COATING GUN**

**15875**



These instructions accompanying the product are the original instructions. This document is part of the product, keep it for the life of the product passing it on to any subsequent holder of the product. Read all these instructions before assembling, operating or maintaining this product.

This manual has been compiled by Draper Tools describing the purpose for which the product has been designed, and contains all the necessary information to ensure its correct and safe use. By following all the general safety instructions contained in this manual, it will ensure both product and operator safety, together with longer life of the product itself.

All photographs and drawings in this manual are supplied by Draper Tools to help illustrate the operation of the product.

Whilst every effort has been made to ensure the accuracy of information contained in this manual, the Draper Tools policy of continuous improvement determines the right to make modifications without prior warning.

# 1. TITLE PAGE

---

## 1.1 INTRODUCTION:

**USER MANUAL FOR: Flexible nozzle underbody coating gun**

**Stock No: 15875**

**Part No: DAT-UCG**

## 1.2 REVISIONS

---

**Date first published April 2021.**

---

---

---

---

As our user manuals are continually updated, users should make sure that they use the very latest version.

**Downloads are available from:** <http://drapertools.com/manuals>

Draper Tools Limited  
Hursley Road  
Chandler's Ford  
Eastleigh  
Hampshire  
SO53 1YF  
UK

**Website:** [drapertools.com](http://drapertools.com)

**Product Helpline:** +44 (0) 23 8049 4344

**General Fax:** +44 (0) 23 8026 0784

## 1.3 UNDERSTANDING THIS MANUAL'S SAFETY CONTENT

**WARNING!** – Information that draws attention to the risk of injury or death.

**CAUTION!** – Information that draws attention to the risk of damage to the product or surroundings.

## 1.4 COPYRIGHT © NOTICE

Copyright © Draper Tools Limited.

Permission is granted to reproduce this publication for personal and educational use only. Commercial copying, redistribution, hiring or lending is prohibited.

No part of this publication may be stored in a retrieval system or transmitted in any other form or means without written permission from Draper Tools Limited.

In all cases this copyright notice must remain intact.

## 2. CONTENTS

---

<b>1. TITLE PAGE</b>	
1.1 INTRODUCTION.....	2
1.2 REVISIONS.....	2
1.3 UNDERSTANDING THIS MANUAL'S SAFETY CONTENT.....	2
1.4 COPYRIGHT © NOTICE .....	2
<b>2. CONTENTS</b>	
2.1 CONTENTS .....	3
<b>3. WARRANTY</b>	
3.1 WARRANTY.....	4
<b>4. INTRODUCTION</b>	
4.1 SCOPE.....	4
4.2 SPECIFICATION .....	4
<b>5. HEALTH AND SAFETY INFORMATION</b>	
5.1 GENERAL SAFETY INSTRUCTIONS FOR COMPRESSED AIR .....	4
5.2 COMPRESSED AIR SAFETY FOR PNEUMATIC EQUIPMENT .....	4
5.3 PRODUCT SELECTION .....	4
5.4 RECOMMENDED AIR SUPPLY SET UP.....	5
<b>6. TECHNICAL DESCRIPTION</b>	
6.1 IDENTIFICATION .....	5
<b>7. MAINTENANCE</b>	
7.1 EVERY-DAY MAINTENANCE CHECKS .....	5
7.2 AFTER USE MAINTENANCE CHECKS .....	5
<b>8. EXPLANATION OF SYMBOLS</b> .....	5
<b>9. DISPOSAL</b> .....	5

# 3. WARRANTY

## 3.1 WARRANTY

Draper tools have been carefully tested and inspected before shipment and are guaranteed to be free from defective materials and workmanship.

Should the tool develop a fault, please return the complete tool to your nearest distributor or contact

**Draper Tools Limited, Chandler's Ford, Eastleigh, Hampshire, SO53 1YF. England.**

**Telephone Sales Desk: (023) 8049 4333 or Product Help Line (023) 8049 4344.**

A proof of purchase **must** be provided with the tool.

If upon inspection it is found that the fault occurring is due to defective materials or workmanship, repairs will be carried out free of charge. This warranty period covering parts/labour is 6 months from the date of purchase except where tools are hired out when the warranty period is 90 days from the date of purchase. This warranty does not apply to any consumable parts, any type of battery or normal wear and tear, nor does it cover any damage caused by misuse, careless or unsafe handling, alterations, accidents, or repairs attempted or made by any personnel other than the authorised Draper warranty repair agent.

**Note:** If the tool is found not to be within the terms of warranty, repairs and carriage charges will be quoted and made accordingly.

This warranty applies in lieu of any other warranty expressed or implied and variations of its terms are not authorised.

Your Draper warranty is not effective unless you can produce upon request a dated receipt or invoice to verify your proof of purchase within the warranty period.

Please note that this warranty is an additional benefit and does not affect your statutory rights.

**Draper Tools Limited.**

# 4. INTRODUCTION

## 4.1 SCOPE

Part of our core range, this product is suitable for enthusiasts and tradespersons alike. This vehicle underbody coating gun can be used on the vehicle chassis for rustproofing and is suitable for various kinds of primer and sub coat paints. It accepts most types of 1L coating tins and it is supplied with a 1/4" BSP adaptor and a 300mm flexible nozzle, for accurate spraying and fitting into confined spaces such as wheel arches.

## 4.2 SPECIFICATION

Stock no .....	15875
Part no .....	DAT-UCG
Air inlet .....	1/4" BSP
Rated air pressure .....	30~120 psi
Maximum air pressure .....	150 psi
Air consumption.....	270 L/min
Recommended air pressure .....	2 – 4 bar
Nett weight .....	0.34kg

# 5. HEALTH & SAFETY INFORMATION

## 5.1 GENERAL SAFETY INSTRUCTIONS FOR COMPRESSED AIR

Following Safety instructions should be strictly followed. Failure to do so may result in accidents, equipment malfunctioning, serious personal Injury and / or loss of life.

Compressed air is a source of considerable energy. When handling products dealing with compressed air, the following precautions must be taken to prevent accidents.

1. Ensure that compressed air is not blocked or in contact with any part of your body.
2. Before connecting any pneumatic equipment to the compressed air supply, all mounted fittings, piping assemblies and electrical connections should be checked for security. All plastic plugs in the equipment used for protection during shipping should be removed.
3. No piping alterations, removal of fittings, repairing of equipment etc. Should be attempted with air supplies connected. Air and electrical supplies must be disconnected before beginning any adjustment, maintenance or dismantling of equipment.
4. The maximum allowable operating pressures, temperature, flows etc. must be strictly observed. Failure to do so might result in catastrophic failure of equipment, and result in serious personal injury and / or death. Refer to individual catalogues for this information, and any other operating or application limitations.

## 5.2 COMPRESSED AIR SAFETY FOR PNEUMATIC EQUIPMENT

### Warning!

1. Compatibility of pneumatic equipment  
Ensuring the compatibility of the procured FRL equipment is the responsibility of the person who designs the Pneumatic system and/ or System specifications. This should be based on specifications or after analysis and / or tests to meet specific requirements.
2. Repair & Maintenance  
Assembly, handling, or repair of pneumatic systems should be performed by only trained and experienced operators.
3. Safety First  
Do not service machinery / equipment or attempt to remove any component until safety is confirmed.
  - i. Inspection and maintenance of machinery / equipment should only be performed after confirmation that both compressed air and electrical supply have been positively disconnected and all residual compressed air in the system has been completely exhausted to the atmosphere.
4. Contact the manufacturer if equipment is to be used in any of the following conditions:
  - i. Equipment is to be used in conditions beyond the given specifications, or if equipment is to be used outdoors.
  - ii. Equipment is to be used in conjunction with atomic energy, railroad, air navigation, automobiles or related vehicles, medical equipment or safety equipment.
  - iii. In applications that adversely effect humans, animals, or property requiring special safety analysis.

## 5.3 PRODUCT SELECTION

### Warning!

Standard Filters, Regulators, Lubricators and Filter- Regulator Combination units should be used in accordance with the specifications mentioned in the specification sheets. While installing and using this equipment, please also follow the respective specification & instruction manual available for each product.

Wherever this symbol ⚠ is shown, it indicates CAUTION! and/or WARNING!


It indicates that operator error can lead to damage and malfunctioning of the pneumatic equipment and can lead to serious personal injury or loss of life.

1. Air Filter and Lubricator  
Standard Filters and Lubricators incorporate polycarbonate bowls and / or observation windows. Do not use filters & lubricators in an environment that will expose the above components to synthetic fluids, organic solvents, corrosive chemicals, cutting lubricants, thread sealant or similar materials.  
Make sure that the condensate in periodically drained when using manual drain valves on Filters.
2. Regulator
  - a. Safety devices shall be placed to prevent secondary (output) pressure from rising past the set pressure.  
This will ensure that damage to the components on the secondary side will be minimized in the event of a malfunction.




- b. In a standard regulator, when the supply pressure is removed or disconnected, either of the following may happen:
    1. The residual pressure will remain on the secondary side of the regulator.
    2. The pressure on the secondary side of the regulator will exhaust.  
The designer should add components to the circuit to compensate for any of the above conditions.
  - c. Regulator operation may be affected when used in Balanced or Secondary sealed circuits. Please consult the manufacturer regarding these applications.
3. Lubricators
- Ensure proper function of the Lubricator. Minimum airflow rate should be ensured for effective lubrication.

### 5.4 RECOMMENDED AIR SUPPLY SET UP



## 6. TECHNICAL DESCRIPTION

### 6.1 IDENTIFICATION



- |                      |                         |
|----------------------|-------------------------|
| ① Air nozzle         | ⑤ Tube                  |
| ② Handle             | ⑥ 300mm flexible nozzle |
| ③ 1/4" BSP air inlet | ⑦ Air nozzle            |
| ④ Trigger            | ⑧ 1/4" BSP adaptor      |

## 7. MAINTENANCE



#### Warning!

- Disconnect from the air supply before carrying out any adjustments, servicing or maintenance.
- Never use any sockets or accessories that are not hardened for impact use.

### 7.1 EVERY-DAY MAINTENANCE CHECKS

Before connection to the air supply:

- Drain the compressor reservoir of condensate.
- Drain the air lines of condensate.
- Drain the combined separator filter, regulator, water trap.
- Fill up the combined separator filter, regulator, lubricant reservoir.
- Check the line pressure is correct for the tool.

### 7.2 AFTER USE MAINTENANCE CHECKS

- Repeat the above procedures.
- Lubricate the tool with approximately 1.5ml of oil directly down the air inlet.

## 8. EXPLANATION OF SYMBOLS



Read the instruction manual.



Wear safety glasses.



Warning!



Do not abandon into the environment.

## 9. DISPOSAL



- At the end of the machine's working life, or when it can no longer be repaired, ensure that it is disposed of according to national regulations.
  - Contact your local authority for details of collection schemes in your area.
- In all circumstances:
- Do not dispose of power tools with domestic waste.
  - Do not incinerate.
  - During decommissioning of the equipment, certain hazards should be understood and avoided:
    - Only with the line pressure released shall the equipment be disassembled.
    - Goggles should be worn.

## CONTACTS

Draper Tools Limited, Hursley Road,  
Chandler's Ford, Eastleigh, Hampshire. SO53 1YF. U.K.

Helpline: (023) 8049 4344

Sales Desk: (023) 8049 4333

Internet: [drapertools.com](http://drapertools.com)

E-mail: [sales@drapertools.com](mailto:sales@drapertools.com)

General Enquiries: (023) 8026 6355

Service/Warranty Repair Agent:

For aftersales servicing or warranty repairs, please contact the  
Draper Tools Helpline for details of an agent in your local area.

YOUR DRAPER STOCKIST

DBTL0421

©Published by Draper Tools Limited.

No part of this publication may be reproduced, stored in a retrieval system or transmitted in any form or by any means, electronic, mechanical photocopying, recording or otherwise without prior permission in writing from Draper Tools Ltd.