



**SAFETY DATA SHEET**  
FINISH REVIVER

Page: 1

Compilation date: 16/04/2013

Revision date: 01/03/2018

Revision No: 5

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** FINISH REVIVER

**Product code:** FINR

**Synonyms:** FINISH REVIVER

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**1.3. Details of the supplier of the safety data sheet**

**Company name:** Rustins Ltd

Waterloo Road

Cricklewood

London

NW2 7TX

United Kingdom

**Tel:** +44 (0)208 450 4666

**Fax:** +44 (0)208 452 2008

**Email:** [rustins@rustins.co.uk](mailto:rustins@rustins.co.uk)

**1.4. Emergency telephone number**

**Emergency tel:** .+44(0)2084504666 (Office hours only)

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Skin Sens. 1: H317; Aquatic Chronic 3: H412; -: EUH208

**Most important adverse effects:** Contains gum turpentine. May produce an allergic reaction. May cause an allergic skin reaction. Harmful to aquatic life with long lasting effects.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** EUH208: Contains gum turpentine. May produce an allergic reaction.

H317: May cause an allergic skin reaction.

H412: Harmful to aquatic life with long lasting effects.

**Hazard pictograms:** GHS07: Exclamation mark



**Signal words:** Warning

[cont...]

# SAFETY DATA SHEET

FINISH REVIVER

Page: 2

**Precautionary statements:** P102: Keep out of reach of children.

P301+312: IF SWALLOWED: Call a doctor if you feel unwell.

P262: Do not get in eyes, on skin, or on clothing.

P280: Wear protective gloves and eye protection.

P302+352: IF ON SKIN: Wash with plenty of water/soap.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

##### 1,2,4-TRIMETHYLBENZENE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
202-436-9	95-63-6	-	Flam. Liq. 3: H226; Acute Tox. 4: H332; Eye Irrit. 2: H319; STOT SE 3: H335; Skin Irrit. 2: H315; Aquatic Chronic 2: H411	1.350%

##### GUM TURPENTINE

-	-	-	Acute Tox. 4: H302+312+332; Aquatic Chronic 2: H411; Eye Irrit. 2: H319; Flam. Liq. 3: H226; Skin Irrit. 2: H315; Skin Sens. 1: H317	0.990%
---	---	---	--	--------

##### LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

265-199-0	64742-95-6	-	Asp. Tox. 1: H304; Flam. Liq. 3: H226; STOT SE 3: H335; Aquatic Chronic 2: H411	0.900%
-----------	------------	---	---	--------

##### MESITYLENE

203-604-4	108-67-8	-	Flam. Liq. 3: H226; STOT SE 3: H335; Aquatic Chronic 2: H411	0.225%
-----------	----------	---	--	--------

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Wash immediately with plenty of soap and water. Remove all contaminated clothes and footwear immediately unless stuck to skin. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Consult a doctor.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Consult a doctor.

**Inhalation:** Move to fresh air in case of accidental inhalation of vapours. Consult a doctor.

[cont...]

# SAFETY DATA SHEET

FINISH REVIVER

Page: 3

## 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** No symptoms.

## 4.3. Indication of any immediate medical attention and special treatment needed

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Carbon dioxide. Water spray, fog or mist. Alcohol resistant foam. Dry chemical powder. Water spray. Water fog.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** Harmful.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Mechanically ventilate the spillage area whilst avoiding the formation of explosive concentrations - see section 9 of SDS. Mark out the contaminated area with signs and prevent access to unauthorised personnel. Refer to section 8 of SDS for personal protection details.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method. Wash the ground with an appropriate self-emulsifying solvent.

### 6.4. Reference to other sections

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Smoking is forbidden. Ensure there is sufficient ventilation of the area.

[cont...]

# SAFETY DATA SHEET

FINISH REVIVER

Page: 4

## 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Keep container tightly closed. Store in a cool, well ventilated area.

**Suitable packaging:** Glass. Coated steel.

## 7.3. Specific end use(s)

## Section 8: Exposure controls/personal protection

### 8.1. Control parameters

**Hazardous ingredients:**

**1,2,4-TRIMETHYLBENZENE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	125 mg/m <sup>3</sup>	-	-	-

**MESITYLENE**

UK	25 ppm	-	-	-
----	--------	---	---	---

### DNEL/PNEC Values

**DNEL / PNEC** No data available.

### 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Respiratory protection not required. Self-contained breathing apparatus must be available in case of emergency.

**Hand protection:** Impermeable gloves. Rubber gloves.

**Eye protection:** Safety glasses with side-shields. Ensure eye bath is to hand.

**Skin protection:** Protective clothing.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Thick liquid.

**Colour:** Brown.

**Odour:** Slight and characteristic.

**Evaporation rate:** No data available.

**Oxidising:** No data available.

**Solubility in water:** Miscible

**Viscosity:** Viscous

**Boiling point/range°C:** No data available.

**Melting point/range°C:** No data available.

**Flammability limits %: lower:** No data available.

**upper:** No data available.

**Flash point°C:** >61

**Part.coeff. n-octanol/water:** No data available.

**Autoflammability°C:** No data available.

**Vapour pressure:** No data available.

**Relative density:** 1.146 @ 20 C

[cont...]

# SAFETY DATA SHEET

FINISH REVIVER

Page: 5

pH: No data available.

VOC g/l: No data available.

## 9.2. Other information

Other information: No data available.

## Section 10: Stability and reactivity

### 10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

### 10.2. Chemical stability

Chemical stability: Stable under normal conditions.

### 10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

### 10.4. Conditions to avoid

Conditions to avoid: Heat.

### 10.5. Incompatible materials

Materials to avoid: Not applicable.

### 10.6. Hazardous decomposition products

Haz. decomp. products: No data available.

## Section 11: Toxicological information

### 11.1. Information on toxicological effects

Hazardous ingredients:

#### 1,2,4-TRIMETHYLBENZENE

IPR	RAT	LDLO	1752	mg/kg
ORL	RAT	LD50	5	gm/kg

#### LOW BOILING POINT NAPHTHA - UNSPECIFIED - SOLVENT NAPHTHA (PETROLEUM), LIGHT AROM.

ORL	RAT	LD50	8400	mg/kg
-----	-----	------	------	-------

#### MESITYLENE

IPR	GPG	LDLO	1303	mg/kg
-----	-----	------	------	-------

Relevant hazards for product:

Hazard	Route	Basis
--------	-------	-------

[cont...]

# SAFETY DATA SHEET

FINISH REVIVER

Page: 6

Respiratory/skin sensitisation	DRM	Hazardous: calculated
--------------------------------	-----	-----------------------

## Symptoms / routes of exposure

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness.

**Ingestion:** There may be soreness and redness of the mouth and throat.

**Inhalation:** No symptoms.

## Section 12: Ecological information

### 12.1. Toxicity

**Ecotoxicity values:** No data available.

### 12.2. Persistence and degradability

**Persistence and degradability:** Biodegradable.

### 12.3. Bioaccumulative potential

**Bioaccumulative potential:** No bioaccumulation potential.

### 12.4. Mobility in soil

**Mobility:** Soluble in water. Absorbed only slowly into soil. Volatile.

### 12.5. Results of PBT and vPvB assessment

**PBT identification:** This product is not identified as a PBT/vPvB substance.

### 12.6. Other adverse effects

**Other adverse effects:** No data available.

## Section 13: Disposal considerations

### 13.1. Waste treatment methods

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

## Section 14: Transport information

### 14.1. UN number

**UN number:** UN1263

### 14.2. UN proper shipping name

**Shipping name:** PAINT

### 14.3. Transport hazard class(es)

**Transport class:** 3

[cont...]

# SAFETY DATA SHEET

FINISH REVIVER

Page: 7

## 14.4. Packing group

## 14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

## 14.6. Special precautions for user

## Section 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

### 15.2. Chemical Safety Assessment

**Chemical safety assessment:** Safety Data Sheet complies with UK regulatory references in accordance with CHIP 3.1.

## Section 16: Other information

### Other information

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

\* indicates text in the SDS which has changed since the last revision.

**Phrases used in s.2 and s.3:** EUH208: Contains <name of sensitising substance>. May produce an allergic reaction.

H226: Flammable liquid and vapour.

H302+312+332: Harmful if swallowed, in contact with skin or if inhaled.

H304: May be fatal if swallowed and enters airways.

H315: Causes skin irritation.

H317: May cause an allergic skin reaction.

H319: Causes serious eye irritation.

H332: Harmful if inhaled.

H335: May cause respiratory irritation.

H411: Toxic to aquatic life with long lasting effects.

H412: Harmful to aquatic life with long lasting effects.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product. As the specific conditions of use of the product are outside the supplier's control, the user is responsible for ensuring that the requirements of relevant legislation are complied with.