

Product Specification PDF

Date	Correct as of 11th May 2020
Brand	C.K
Product	T3787DF 115
Description	SensoPlus Tungsten Carbide Side Cutter 125mm
Barcode	5013969985870
Commodity code	8203200000
Country of origin	DE



Features & Benefits

~ Special alloy steel, drop forged, hardened & tempered for exceptional strength & durability ~ Precision box joint construction for permanent, adjustment free jaw alignment ~ Induction hardened jaws for outstanding long term performance ~ Mirror polished surface eliminates the risk of damage from flaking chrome ~ Spot welded double leaf springs for consistent, repetitive action ~ Ergonomically designed dual component handles for increased comfort & control ~ Fully ESD compliant for safe use on sensitive electronic components ~ According to IEC 61340 5.1 & 5.2 ~ Tungsten carbide blades for extreme demands e.g. piano, nickel and diode wires that are used in electronics and aerospace industries ~ Tapered and relieved head for confined spaces ~ Bevel: Full Flush Cut ~ Length of cutting edges: 10 mm ~ Overall length: 125 mm ~ Cutting capacities wire: Piano: 0,4 mm / Hard: 0,8 mm / Soft: 1,8 mm

Applicable Standards

IEC 61340 5.1 & 5.2

Health & Safety

None applicable

Warranty

C.K products are guaranteed for 1year against imperfect materials or workmanship. Damage caused through normal wear and tear or resulting from inappropriate use, is not covered.

Product Weights and Measures

	Product only	Product & primary packaging	Secondary packaging	Transit packaging
Item Quantity	1	1	0	120
Width mm	75	60	0	380
Depth mm	8	25	0	300
Height mm	125	160	0	360
Weight	54	73	0	9.4
Packaging Information	Card use	Box	0	Case
	Card gms	18	0	675
	Plastic use	Bag	0	-
	Plastic gms	1	0	-
	Metal use	0	0	-
	Metal gms	0	0	0
	Timber use	0	0	-
	Timber gms	0	0	0