

PROPANE**Safety Data Sheet****1. IDENTIFICATION****1.1 Product identifier**

Product name VORTEX PROPANE GAS
Chemical name: PROPANE, PROPYLENE MIXTURES, STABILIZED

1.2 Uses

SOLDERING & BRAZING

1.3 Details of the supplier of the product

Supplier name Arctic Hayes Ltd
Address 9 Millshaw Park Ave, Leeds, LS11 0LR, United Kingdom
Telephone +44(0) 113 271 5245

1.4 Emergency telephone number(s)

+44(0)113 271 5245 - Mon-Thur: 08:30-17:00 | Fri: 08:30-16:00
Or call Emergency Services

2. HAZARDS IDENTIFICATION**2.1 Classification of the substance or mixture**

CLASSIFIED AS HAZARDOUS

GHS classification(s) Flammable Gases: Category 1
Gases Under Pressure: Liquefied gas

2.2 Label elements Label according to Regulation (EC) No. 1272/2008 as amended

Signal word DANGER

Pictogram(s)



Hazard statement(s)

H220 Extremely flammable gas.
H280 Contains gas under pressure; may explode if heated.

Prevention statement(s)

P210 Keep away from heat/hot surfaces/sparks/open flames and other ignition sources. No smoking.

Response statement(s)

P377 Leaking gas fire: Do not extinguish, unless leak can be stopped safely.
P381 In case of leakage, eliminate all ignition sources.

Storage statement(s)

P410 + P403 Protect from sunlight. Store in a well-ventilated place.

Disposal statement(s)

Dispose of waste and residues in accordance with local authority requirements.

2.3 Other hazards

Asphyxiant. Effects are proportional to oxygen displacement.

3. COMPOSITION/ INFORMATION ON INGREDIENTS

3.1 Substances / Mixtures

Ingredient	CAS Number	Content (v/v)	
Propane	74-98-6	90-95%	
Propylene	115-07-1	5-10%	

4. FIRST AID MEASURES

4.1 Description of first aid measures

Eye	Cold burns: Immediately flush with tepid water or with sterile saline solution. Hold eyelids apart and irrigate for 15 minutes. Seek medical attention.
Inhalation	If inhaled, remove from contaminated area. To protect rescuer, use an Air-line respirator or Self Contained breathing Apparatus (SCBA). Be aware of possible explosive atmospheres. Apply artificial respiration if not breathing. Give oxygen if available. For advice, contact a Poison Information Centre or a doctor.
Skin	Cold burns: Remove contaminated clothing and gently flush affected areas with warm water (30°C) for 15 minutes. Apply sterile dressing and treat as for a thermal burn. For large burns, immerse in warm water for 15 minutes. Do not apply any form of direct heat. Seek immediate medical attention.
Ingestion	Due to product form and application, ingestion is considered unlikely.
First aid facilities	Eye wash facilities and safety shower should be available.

4.2 Most important symptoms and effects, both acute and delayed

In high concentrations may cause asphyxiation. Direct contact with the liquefied material or escaping compressed gas may cause frostbite injury.

4.3 Immediate medical attention and special treatment needed

Note to physicians treat symptomatically.

5. FIRE FIGHTING MEASURES

5.1 Extinguishing media

Stop flow of gas if safe to do so, such as by slowly closing the cylinder valve.

5.2 Special hazards arising from the substance or mixture

Extremely flammable. Eliminate all ignition sources including cigarettes, open flames, spark producing switches/tools, heaters, naked lights, pilot lights, mobile phones etc. when handling.

5.3 Advice for firefighters

Temperatures in a fire may cause cylinders to rupture and internal pressure relief devices to be activated. Cool cylinders or containers exposed to fire by applying water from a protected location. Do not approach cylinders or containers suspected of being hot. This material is capable of forming explosive mixtures in air.

5.4 Hazchem code

2WE	
2	Fine Water Spray.
W	Risk of violent reaction or explosion. Wear liquid-tight chemical protective clothing and breathing apparatus. Contain spill and run-off.
E	Evacuation of people in and around the immediate vicinity of the incident should be considered.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

If the cylinder is leaking, evacuate area of personnel. Inform manufacturer/supplier of leak. Use Personal Protective Equipment (PPE) as detailed in Section 8 of the SDS. Ventilate area where possible and eliminate ignition sources.

6.2 Environmental precautions

Prevent from entering sewers, basements and workpits, or any place where its accumulation can be dangerous.

6.3 Methods of cleaning up

Stop the flow of material, if this is without risk. If the leak is irreparable, move the cylinder to a safe and well ventilated area, and allow to discharge. Keep area evacuated and free from ignition sources until any leaked or spilled liquid has evaporated.

6.4 Reference to other sections

See Sections 8 and 13 for exposure controls and disposal.

7. HANDLING AND STORAGE**7.1 Precautions for safe handling**

Before use carefully read the product label. Use of safe work practices are recommended to avoid eye or skin contact and inhalation. Observe good personal hygiene, including washing hands before eating. Prohibit eating, drinking and smoking in contaminated areas.

7.2 Conditions for safe storage, including any incompatibilities

Do not store near incompatible substances and sources of ignition. Cylinders should be stored: upright, prevented from falling, in a secure area; below 45°C, in a dry, well ventilated area constructed of non-combustible material with firm level floor (preferably concrete), away from areas of heavy traffic and emergency exits.

7.3 Specific end use(s)

No information provided.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION**8.1 Control parameters****Exposure standards**

Ingredient	TWA		STEL	
	ppm	mg/m ³	ppm	mg/m ³
Propane	1000	1800	--	--
Propylene	500	--	500	--

Biological limits

No biological limit values have been entered for this product.

8.2 Exposure controls**Engineering controls**

Avoid inhalation. Use in well ventilated areas. Where an inhalation risk exists, mechanical explosion proof extraction ventilation is recommended. Maintain vapour levels below the recommended exposure standard.

PPE

Eye / Face	Wear safety glasses.
Hands	Wear leather or insulated gloves.
Body	Wear coveralls.
Respiratory	Where an inhalation risk exists, wear Self Contained Breathing Apparatus (SCBA) or an Air-line respirator.

**9. PHYSICAL AND CHEMICAL PROPERTIES****9.1 Information on basic physical and chemical properties**

Physical state	Liquefied gas
Appearance	Colorless.
Odor	Odorless.
Odor threshold	No information available
pH	No data available
Melting point	No data available
Evaporation rate	Not applicable
Fire Hazard	Yes

Lower flammability limit:	2.2%
Upper flammability limit:	9.5%
Flash point	-104 °C / -156 °F
Autoignition temperature	450 °C / 842 °F
Decomposition temperature	No data available
Water solubility	Negligible
Partition coefficient	2.3
Kinematic viscosity	Not applicable

Ingredient	Molecular weight	Boiling point	Vapor Pressure	Vapor density (air=1)	Gas Density Kg/m ³ @ 20°C	Temperature Critical
Propane	44.09	-42.04 °C	8.39 bar @ 20°C	1.55	1.858	96.67 °C
Propylene	42.07	-47.72 °C	9.15 bar @ 21.1°C	1.45	1.7692	91.78°C

10. STABILITY AND REACTIVITY

10.1 Reactivity

Carefully review all information provided in sections 10.2 to 10.6.

10.2 Chemical stability

Stable under recommended conditions of storage.

10.3 Possibility of hazardous reactions

Polymerization will not occur.

10.4 Conditions to avoid

Avoid heat, sparks, open flames and other ignition sources.

10.5 Incompatible materials

Incompatible with oxidising agents (e.g. hypochlorites), acids (e.g. nitric acid), heat and ignition sources. Do not use natural rubber flexible hoses. Also incompatible (potentially violently) with oxygen, halogens and metal halides.

10.6 Hazardous decomposition products

This material will not decompose to form hazardous products other than that already present.

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity	No known toxicological effects from this product. Based on available data, the classification criteria are not met.
Skin	Not classified as a skin irritant. Contact with the liquefied material or escaping compressed gas may cause frostbite injury.
Eye	Not classified as irritating to the eyes. Contact with the liquefied material or escaping compressed gas may cause frostbite injury.
Sensitization	Not classified as causing skin or respiratory sensitisation.
Mutagenicity	Not classified as a mutagen.
Carcinogenicity	Not classified as a carcinogen.
Reproductive	Not classified as a reproductive toxin.
STOT – single exposure	Asphyxiant. Effects are proportional to oxygen displacement. Over exposure may result in dizziness, drowsiness, weakness, fatigue, breathing difficulties and unconsciousness.
STOT – repeated exposure	Not classified as causing organ effects from repeated exposure.
Aspiration	Not classified as causing aspiration.

12. ECOLOGICAL INFORMATION

12.1 Toxicity

No information provided.

12.2 Persistence and degradability

No information provided.

12.3 Bioaccumulative potential

No information provided.

12.4 Mobility in soil

No information provided.

12.5 Other adverse effects

No known ecological damage is caused by this product.

13. DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Waste disposal Cylinders should be returned to the manufacturer or supplier for disposal of contents.

Legislation Dispose of in accordance with relevant local legislation.

14. TRANSPORT INFORMATION

CLASSIFIED AS A DANGEROUS GOOD BY THE CRITERIA OF THE ADG CODE



	LAND TRANSPORT (ADG)	SEA TRANSPORT (IMDG / IMO)	AIR TRANSPORT (IATA / ICAO)
14.1 UN Number	2037	2037	2037
14.2 Proper Shipping Name	Receptacles, small containing gas (gas cartridges) without release device, non-refillable.	Receptacles, small containing gas (gas cartridges) without release device, non-refillable.	Receptacles, small containing gas (gas cartridges) without release device, non-refillable.
14.3 Transport hazard class	2.1	2.1	2.1
14.4 Packing Group	None Allocated	None Allocated	None Allocated

14.5 Environmental hazards

14.6 Special precautions for user

Hazchem code 2WE

GTEPG 2A2

EMS F-D, S-U

Other information Ensure cylinder is separated from driver and that outlet of relief device is not obstructed.

15. REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Poison schedule A poison schedule number has not been allocated to this product using the criteria in the Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP).

Classifications Safe work China criteria is based on the Globally Harmonised System (GHS) of Classification and labelling Of Chemicals.

The classifications and phrases listed below are based on the Approved Criteria for Classifying Hazardous Substances [NOHSC: 1008(2004)].

Hazard codes	F+	Extremely flammable
Risk phrases	R12	Extremely Flammable.
Safety phrases	S9 S16	Keep container in a well ventilated place. Keep away from sources of ignition - No smoking.
Inventory listing(s)	PRC : PICS (PRC Inventory of Chemical Substances) All components are listed on PICS, or are exempt.	

16. OTHER INFORMATION

Additional information	<p>The storage of significant quantities of gas cylinders must comply with GB17914-2013 the storage and handling of gases in cylinders.</p> <p>ASPHYXIANTS (1): When present in the atmospheres in high concentrations, asphyxiants reduce the oxygen concentration by displacement. Atmospheres deficient in oxygen do not provide adequate sensory warning of danger and most simple asphyxiants are odourless. Therefore it is not appropriate to recommend an exposure standard for each asphyxiant, but to maintain oxygen concentrations. However some asphyxiants may be given an exposure standard due to the potential for narcotic effects at high concentrations or an explosion hazard.</p> <p>ASPHYXIANTS (2): There is a significant hazard associated with workers entering poorly ventilated areas (e.g. tanks) where oxygen may be deficient. An air supplied breathing apparatus may be required if adequate ventilation is not ensured.</p> <p>PERSONAL PROTECTIVE EQUIPMENT GUIDELINES: The recommendation for protective equipment contained within this report is provided as a guide only. Factors such as method of application, working environment, quantity used, product concentration and the availability of engineering controls should be considered before final selection of personal protective equipment is made.</p> <p>HEALTH EFFECTS FROM EXPOSURE: It should be noted that the effects from exposure to this product will depend on several factors including: frequency and duration of use; quantity used; effectiveness of control measures; protective equipment used and method of application. Given that it is impractical to prepare a ChemAlert report which would encompass all possible scenarios, it is anticipated that users will assess the risks and apply control methods where appropriate.</p>																																								
Abbreviations	<table border="0"> <tr><td>ACGIH</td><td>American Conference of Governmental Industrial Hygienists</td></tr> <tr><td>CAS #</td><td>Chemical Abstract Service number - used to uniquely identify chemical compounds</td></tr> <tr><td>CNS</td><td>Central Nervous System</td></tr> <tr><td>EC No.</td><td>EC No - European Community Number</td></tr> <tr><td>EMS</td><td>Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)</td></tr> <tr><td>GHS</td><td>Globally Harmonized System</td></tr> <tr><td>GTEPG</td><td>Group Text Emergency Procedure Guide</td></tr> <tr><td>IARC</td><td>International Agency for Research on Cancer</td></tr> <tr><td>LC50</td><td>Lethal Concentration, 50% / Median Lethal Concentration</td></tr> <tr><td>LD50</td><td>Lethal Dose, 50% / Median Lethal Dose</td></tr> <tr><td>mg/m³</td><td>Milligrams per Cubic Metre</td></tr> <tr><td>OEL</td><td>Occupational Exposure Limit</td></tr> <tr><td>pH</td><td>relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).</td></tr> <tr><td>ppm</td><td>Parts Per Million</td></tr> <tr><td>STEL</td><td>Short-Term Exposure Limit</td></tr> <tr><td>STOT-RE</td><td>Specific target organ toxicity (repeated exposure)</td></tr> <tr><td>STOT-SE</td><td>Specific target organ toxicity (single exposure)</td></tr> <tr><td>SUSMP</td><td>Standard for the Uniform Scheduling of Medicines and Poisons</td></tr> <tr><td>TLV</td><td>Threshold Limit Value</td></tr> <tr><td>TWA</td><td>Time Weighted Average</td></tr> </table>	ACGIH	American Conference of Governmental Industrial Hygienists	CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds	CNS	Central Nervous System	EC No.	EC No - European Community Number	EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)	GHS	Globally Harmonized System	GTEPG	Group Text Emergency Procedure Guide	IARC	International Agency for Research on Cancer	LC50	Lethal Concentration, 50% / Median Lethal Concentration	LD50	Lethal Dose, 50% / Median Lethal Dose	mg/m ³	Milligrams per Cubic Metre	OEL	Occupational Exposure Limit	pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).	ppm	Parts Per Million	STEL	Short-Term Exposure Limit	STOT-RE	Specific target organ toxicity (repeated exposure)	STOT-SE	Specific target organ toxicity (single exposure)	SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons	TLV	Threshold Limit Value	TWA	Time Weighted Average
ACGIH	American Conference of Governmental Industrial Hygienists																																								
CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds																																								
CNS	Central Nervous System																																								
EC No.	EC No - European Community Number																																								
EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)																																								
GHS	Globally Harmonized System																																								
GTEPG	Group Text Emergency Procedure Guide																																								
IARC	International Agency for Research on Cancer																																								
LC50	Lethal Concentration, 50% / Median Lethal Concentration																																								
LD50	Lethal Dose, 50% / Median Lethal Dose																																								
mg/m ³	Milligrams per Cubic Metre																																								
OEL	Occupational Exposure Limit																																								
pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).																																								
ppm	Parts Per Million																																								
STEL	Short-Term Exposure Limit																																								
STOT-RE	Specific target organ toxicity (repeated exposure)																																								
STOT-SE	Specific target organ toxicity (single exposure)																																								
SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons																																								
TLV	Threshold Limit Value																																								
TWA	Time Weighted Average																																								

Revision	Description
2.0	Standard SDS Review
1.0	Initial SDS Creation

Report status

This document has been compiled by Arctic Hayes on behalf of the manufacturer, importer or supplier of the product and serves as their Safety Data Sheet ('SDS').

It's based on information concerning the product which has been provided to Arctic Hayes by the manufacturer, importer or supplier or obtained from third party sources and is believed to represent the current state of knowledge as to the appropriate safety and handling precautions for the product at the time of issue. Further clarification regarding any aspect of the product should be obtained directly from the manufacturer, importer or supplier.

All information in this Material Safety Data Sheet is believed to be accurate and reliable. However, no guarantee or warranty of any kind is made with regard to the accuracy of information or the suitability of the recommendations contained herein. It is the user's responsibility to assess the safety and toxicity of this product under their own conditions of use and to comply with all applicable laws and regulations.

End of Safety Data Sheet