

DOFF FISH BLOOD & BONE

Page: 1

Compilation date: 22/03/2017

Revision No: 1

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: DOFF FISH BLOOD & BONE

Product code: F-MC

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: SU 21 - Consumer Uses. PC12: Fertilizers.

1.3. Details of the supplier of the safety data sheet

Company name: Doff Portland Limited

Aerial Way Hucknall Nottingham NG15 6DW

UK

Tel: +(44) 115 9834 300 **Email:** help@doff.co.uk

1.4. Emergency telephone number

Emergency tel: +(44) 115 9834 300

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: This product has no classification under CLP.

2.2. Label elements

Label elements:

Precautionary statements: P102: Keep out of reach of children.

P103: Read label before use.

P264: Wash hands thoroughly after handling.

P501: Dispose of contents/container to Local authority regulations.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Contains: Inert fillers such as sand of limestone and coating materials such as oil, amine clay or

talc secondary nutrients and /or micronutrients.

[cont...]

DOFF FISH BLOOD & BONE

Page: 2

May contain some or all of the following ingredients: Ammonium sulphate, urea, mono and diammonium phosphate, superphosphate, triple superphosphate, phosphate rock, potassium chloride, potassium sulphate, calcium nitrate, urea formaldehyde.

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water. **Eye contact:** Bathe the eye with running water for 15 minutes.

Ingestion: Wash out mouth with water. If conscious, give half a litre of water to drink immediately.

Inhalation: Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.Ingestion: There may be irritation of the throat.

Inhalation: May cause irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact

with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Transfer to a closable, labelled salvage container for disposal by an appropriate

method. Wash the spillage site with large amounts of water.

DOFF FISH BLOOD & BONE

Page: 3

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid the formation or spread of dust in the air.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in a cool, well ventilated area. Keep container tightly closed. KEEP OUT OF THE

REACH OF CHILDREN.

Suitable packaging: Must only be kept in original packaging. Do not store in metal or alloy containers.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: No special requirements under normal conditions of use.

Hand protection: Protective gloves.Eye protection: Safety glasses.

Skin protection: No special requirements under normal conditions of use.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Granules
Colour: Off-white
Odour: Odourless

Solubility in water: Soluble

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

[cont...]

DOFF FISH BLOOD & BONE

Page: 4

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat. Moist air.

10.5. Incompatible materials

Materials to avoid: Bases. Strong bases.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

Excluded hazards for substance:

Hazard	Route	Basis
Acute toxicity (ac. tox. 4)	-	No hazard: calculated
Acute toxicity (ac. tox. 3)	-	No hazard: calculated
Acute toxicity (ac. tox. 2)	-	No hazard: calculated
Acute toxicity (ac. tox. 1)	-	No hazard: calculated
Skin corrosion/irritation	-	No hazard: calculated
Serious eye damage/irritation	-	No hazard: calculated
Respiratory/skin sensitisation	-	No hazard: calculated
Germ cell mutagenicity	-	No hazard: calculated
Carcinogenicity	-	No hazard: calculated
Reproductive toxicity	-	No hazard: calculated
STOT-single exposure	-	No hazard: calculated
STOT-repeated exposure	-	No hazard: calculated
Aspiration hazard	-	No hazard: calculated

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness. **Ingestion:** There may be irritation of the throat.

Inhalation: May cause irritation.

Section 12: Ecological information

DOFF FISH BLOOD & BONE

Page: 5

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Soluble in water.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Disposal should be in accordance with Local Authority Regulations. **Disposal of packaging:** Disposal should be in accordance with Local Authority Regulations.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

Transport class: This product does not require a classification for transport.

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: COUNCIL DIRECTIVE of 18 December 1975 on the approximation of the laws of the

Member States relating to fertilizers 76/116/EEC.

Fertiliser (Mammalian, Meat and Bone Meal) Regulations 1996.

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No

2015/830.

* indicates text in the SDS which has changed since the last revision.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product.

[final page]