



Doff Portland Ltd.

24/7 SuperFast Weedkiller (spray) MAPP 16282

SAFETY DATA SHEET

Product Code: FU

1. Identification of the Preparation and Company

1.1 Name of Preparation / Registration Number/ Identification: 34/7 SuperFast Weedkiller (spray)
(31.02g/l. Perlagonic acid
MAPP 16232

Packaging: HDPE trigger spray bottle
Size: Up to 3 Litres

1.2 Intended Use: As a home garden herbicide

1.3 Supplier Details: Phone +49-(0) 5155/624-0,
W.Neudorff GmbH KG Fax +49- (0) 5155/6010.
An der Muhle 3 , D -31860 Emmerthal

Marketing Company

Doff Portland Ltd
Aerial Way
Hucknall
Nottingham
NG15 6DW

CUSTOMER HELPLINE: 0115 9834300
FAX: 0115 9834330
E-mail help@doff.co.uk
www.doff.co.uk

2. Hazards Identification

2.1 Classification of Preparation: Xi: R36, R52 R-phrases 36 irritating to eyes
52 Harmful to aquatic organisms

3. Information on Ingredients

3.1 Composition: THIS PREPARATION IS NOT CLASSIFIED AS DANGEROUS UNDER
DIRECTIVE 1999/45/EC

Chemical Characterisation Herbicide with pelargonic acid – contained as ammonium salt.

<u>CAS No</u>	<u>Ec No</u>	<u>Name</u>	<u>(g/l)</u>	<u>Classification</u>
112-05-0	203-931-2	nonanoic-acid	186.7	C R34

4. First Aid Measures

4.1 Any Special Measures: N/A

4.2 Inhalation: Remove from area to fresh air. Seek medical attention if respiratory irritation develops.

4.3 Skin & Eye Exposure: **Skin:** Wash with soap and water, if irritation persists then seek medical advice.
Eye: Rinse thoroughly with clear water, if any problems seek medical advice.

4.4 Ingestion: Rinse mouth with clean water. Seek medical advice if symptoms appear.

Note to Doctor – no product specific symptoms known. Symptoms: Treat symptoms

5. Fire Fighting Measures

5.1 Suitable Extinguishing Media: Water, foam, dry powder, carbon dioxide.

5.2 Unsuitable Extinguishing Media: As appropriate for surrounding fire.

Additional Information

Fire residues and contaminated fire fighting water must be disposed of in accordance with the local regulations.



Doff Portland Ltd.

24/7 SuperFast Weedkiller (spray) MAPP 16282

6. Accidental Release Measures

6.1 Personal Precautions:

6.2 Environmental Precautions:

6.3 Clean & Disposal Methods:

Forms slippery surfaces with water.

Avoid contamination of watercourses or drains and rivers. If a large spillage of this product enters a watercourse or sewer (including via contaminated soil & vegetation) or river contact local agency/company and/or police immediately.

Use absorbent material (e.g sand, sawdust, general-purpose binder). Flush away residues with water.

7. Handling & Storage

7.1 Practical Precautions & Engineering Controls for Safe Handling:

7.2 Conditions and Quantity Limits for Safe Storage: Group 10

Wear protective equipment. Ensure good ventilation of the work area.

Storage rooms –keep only in original container.

Storage Group 10

Store in original container in a secure well ventilated and cool dry place away from extreme temperatures & direct sunlight. Keep away from food, drink, animal feeding stuffs and store out of the reach of children. Protect from frost.

8. Exposure Control & Personal Protection

8.1 Exposure Limit Values:

8.2 Occupational Exposure Controls:

8.3 Personal Protective Equipment:

Not determined for product.

Refer to COSHH assessment. Engineering controls should be used in preference to personal protective equipment.

As an amateur use product it is recommended to wear gloves and goggles.

General protective measures: Avoid long and intensive skin contact and wash hands after use. Do not inhale gases/vapours.

9. Physical & Chemical Properties

9.1 Appearance:

9.2 Odour:

9.3 pH:

9.4 Boiling Point/Range:

9.5 Flash Point/Flammability:

9.6 Explosive Properties:

9.7 Oxidising Properties:

9.8 Vapour Pressure:

9.9 Relative Density:

9.10 Solubility:

9.11 Partition Coefficient:

9.12 Viscosity:

9.13 Vapour Density:

Light yellow liquid

Characteristic

6.1

Not specified

95°C

Not classified as explosive

Not classified as oxidising

Not specified

Not specified

Unlimitedly soluble in water.

Not specified

11 16 mPa*s 20°C

Not specified

10. Stability & Reactivity

10.1 Hazardous decomposition products:

Additional information:

Unknown.

No decomposition during correct storage.

11. Toxicological Information*

Acute oral LD50 (Rat):

Acute dermal LD50 (Rat):

Irritant (Skin & Eye) (Rabbit):

Sensitisation: Guinea Pig)

>5,000 mg/kg (formulation)

>5,000 mg/kg (formulation)

Non- irritating (Skin), Irritating (Eyes)

Non-sensitising



Doff Portland Ltd.

24/7 SuperFast Weedkiller (spray) MAPP 16282

12. Ecological Information*

12.1 Eco Toxicity:	Fish NOEC 100mg/l (96 hour), Daphnia NOEC 10 mg/l (48 Hour), Algae NOEC 20 mg/l (72 hour)
12.2 Mobility:	Not specified
12.3 Persistence & Degradability:	Not specified

General regulation: biodegradable. Prevent uncontrolled leakage of product into the environment.

13. Disposal Consideration

Waste code No. 06-13/01* & 07-04-03*

Name of waste

Inorganic plant protection products, wood-preserving agents and other biocides. Organic halogenated solvents, washing liquids and mother liquors.

Waste marked with asterisk are considered to be hazardous waste pursuant to Directive 91/689/EEC on hazardous waste.

3.1 Disposal of Used Preparation:

Dispose of excess product on waste ground as per label instructions or at a local waste regulation authority.

13.2 Disposal of Packaging:

Empty packaging place into household bin.

14. Transport Information

14.1 Specific Transport Requirements: Non hazardous goods for Transport.

Road/rail : Not restricted

Air : Not restricted

15. Regulatory Information

This preparation is classified and labelled in accordance with the Control Of Pesticides Regulations (1986) and Directive 1999/45/EC.

Classification: Xi - irritant

R-phrases 36: irritating to eyes

52: Harmful to aquatic organisms.

S Phrases: S1/2: Keep locked up and out of the reach of children.

S13: Keep away from food, drink and animal feedingstuffs.

S24/25: Avoid contact with skin and eyes.

S39: Wear eye/face protection.

S46: If swallowed, seek medical advice immediately and show this container or label.

To avoid risks to man and the environment, comply with the instructions for use.

USE PESTICIDES SAFELY. READ THE LABEL.

16. Other Information

Wording of the R-phrases specified in chapter 3 (not in classification of the formulation) R34: causes burns.

This Safety Data Sheet is prepared in compliance with Directive 1999/45/EC and also Annex II of the REACH Regulation 1097/2006

Compiled using data submitted for raw materials, specific data and practical experience.

This product is intended for amateur use only.

The information given in this safety data sheet is correct to the best of our knowledge at the date of issue. It is intended as a guide for the safe use, handling, disposal, storage and transportation and is not intended as warranty or as a specification. Recipients of our products must take responsibility for observing the law and regulations. The information relates only to the product supplied and may not be suitable for use with other product materials other than those described within.

Doff Portland Limited disclaims any liability for loss or damage resulting from the use of this data, information suggestions.