

DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Page: 1

Compilation date: 13/11/2013

Revision No: 1

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Product code: F-NA-B50-DOF

1.2. Relevant identified uses of the substance or mixture and uses advised against

Use of substance / mixture: Formulated Path And Patio Cleaner

1.3. Details of the supplier of the safety data sheet

Company name: Doff Portland Limited

Aerial Way Hucknall Nottingham NG15 6DW

UK

Tel: +(44) 115 9834 300 **Email:** help@doff.co.uk

1.4. Emergency telephone number

Emergency tel: +(44) 115 9834 300

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CHIP: Xi: R36/38; N: R50

Classification under CLP: Aquatic Acute 1: H400; Skin Corr. 1B: H314

Most important adverse effects: Irritating to eyes and skin. Very toxic to aquatic organisms.

2.2. Label elements

Label elements under CLP:

Hazard statements: H314: Causes severe skin burns and eye damage.

H400: Very toxic to aquatic life.

Signal words: Danger

Hazard pictograms: GHS05: Corrosion

GHS09: Environmental





Precautionary statements: P264: Wash thoroughly after handling.

P273: Avoid release to the environment.

DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Page: 2

P280: Wear.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove

contact lenses, if present and easy to do. Continue rinsing.

P321: Specific treatment (see on this label).

P391: Collect spillage.

Label elements under CHIP:

Hazard symbols: Irritant.

Dangerous for the environment.





Risk phrases: R36/38: Irritating to eyes and skin.

R50: Very toxic to aquatic organisms.

Safety phrases: S2: Keep out of the reach of children.

S29: Do not empty into drains.

S61: Avoid release to the environment. Refer to special instructions / safety data sheets.

2.3. Other hazards

PBT: This product is not identified as a PBT substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

BENZALKONIUM CHLORIDE

EINECS	CAS	CHIP Classification	CLP Classification	Percent
-	8001-54-5	Xn: R22; C: R34; N: R50	=	1-10%

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash effected areas with soap and water for at least 15minutes while removing

contaminated clothing and shoes.

Eye contact: Immediately flood the eye with plenty of water for at least 15 minutes, holding the eye

open. Rinse affected eye with clean running water, or eyewash solution. Seek medical

attention if irritation persists.

Ingestion: If swallowed rinse mouth with water(only if the person is concious)

Inhalation: If irritation is experienced, move to fresh air. If irritation or other symptoms develop and

persists, seek medical attention.

DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Page: 3

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: Irritation

Eye contact: MAY CAUSE IRRITATION

Ingestion: Irritation

Inhalation: May cause irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Section 5: Fire-fighting measures

5.1. Extinguishing media

Extinguishing media: Dry chemical powder. Fight larger fires with water spray or alcohol resistant foam.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes of carbon dioxide / carbon monoxide.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear protective clothing to prevent contact with skin and eyes.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Larger spills should be absorbed in vermiculite, dry sand or earth and placed into a

suitable container for disposal by an appropriate method.

6.4. Reference to other sections

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid skin and eye contact.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Keep container tightly closed. Keep away from sources of ignition.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Page: 4

8.1. DNEL/PNEC Values

DNEL / PNEC No data available.

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Do not inhale vapours.

Hand protection: Protective gloves.Eye protection: Safety goggles.Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquid

Colour: Colourless

Odour: Slight Aromatic

Solubility in water: Soluble

Also soluble in: Acetone. Methanol.

Flash point°C: > 93c

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under recommended handling and storage conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

10.4. Conditions to avoid

Conditions to avoid: Heat. Sources of ignition.

10.5. Incompatible materials

Materials to avoid: Oxidising agents. Slightly reactive with acids and alkalis

10.6. Hazardous decomposition products

Section 11: Toxicological information

11.1. Information on toxicological effects

DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Page: 5

Relevant effects for mixture:

Effect	Route	Basis
Irritation	OPT DRM	Hazardous: calculated

Symptoms / routes of exposure

Skin contact: Irritation

Eye contact: MAY CAUSE IRRITATION

Ingestion: Irritation

Inhalation: May cause irritation.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

12.3. Bioaccumulative potential

12.4. Mobility in soil

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT substance.

12.6. Other adverse effects

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Transfer to a suitable container and arrange for collection by specialised disposal

company.

NB: The user's attention is drawn to the possible existence of regional or national

regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN3082

14.2. UN proper shipping name

Shipping name: ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S.

14.3. Transport hazard class(es)

Transport class: 9

14.4. Packing group

Packing group: III

DOFF SUPER CONCENTRATE PATH, PATO AND DECKING CLEANER

Page: 6

14.5. Environmental hazards

Environmentally hazardous: Yes Marine pollutant: No

14.6. Special precautions for user

Tunnel code: E
Transport category: 3

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

Specific regulations: HSE No:9736

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No

453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and 3: H314: Causes severe skin burns and eye damage.

H400: Very toxic to aquatic life. R22: Harmful if swallowed.

R34: Causes burns.

R36/38: Irritating to eyes and skin.
R50: Very toxic to aquatic organisms.

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive

and shall be used only as a guide. This company shall not be held liable for any

damage resulting from handling or from contact with the above product.