



SAFETY DATA SHEET

This safety data sheet complies with the requirements of: REACH Regulation (EC) No 1907/2006, as retained in UK law by (SI 2019/758 as amended)

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product Name BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Pure substance/mixture Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

Recommended use Moisture Absorbing Product
Uses advised against None known

1.3. Details of the supplier of the safety data sheet

Company Name

Bostik Limited
Common Rd
ST16 3EH
Stafford UK
Tel: +44 (1785) 27 26 25
Fax: +44 (1785) 25 72 36

E-mail address SDS.box-EU@bostik.com

1.4. Emergency telephone number

United Kingdom Bostik: +44 (1785) 272650 (9am to 5pm Mon-Fri)
NHS: 111

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

GB CLP (SI 2020/1567 as amended)

Serious eye damage/eye irritation	Category 2 - (H319)
--	---------------------

2.2. Label elements



Signal word
Warning

Hazard statements
H319 - Causes serious eye irritation.

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

Precautionary Statements - EU (§28, 1272/2008)

P101 - If medical advice is needed, have product container or label at hand

P102 - Keep out of reach of children

P264 - Wash skin thoroughly after handling

P305 + P351 + P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing

P337 + P313 - If eye irritation persists: Get medical advice/attention

2.3. Other hazards

No information available.

PBT & vPvB

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

SECTION 3: Composition/information on ingredients

3.1 Substances

Not applicable

3.2 Mixtures

Chemical name	EC No (EU Index No)	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH registration number
Calcium chloride	(017-013-00-2) 233-140-8	10043-52-4	40 - <80	Eye Irrit. 2 (H319)	-	01-2119494219-28-XXXX

Full text of H- and EUH-phrases: see section 16

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	Show this safety data sheet to the doctor in attendance.
Inhalation	Remove to fresh air.
Eye contact	Rinse immediately with plenty of water, also under the eyelids, for at least 15 minutes. Remove contact lenses, if present and easy to do. Continue rinsing. Keep eye wide open while rinsing. Do not rub affected area. Get medical attention if irritation develops and persists.
Skin contact	Wash skin with soap and water. In the case of skin irritation or allergic reactions see a doctor.
Ingestion	Rinse mouth. Never give anything by mouth to an unconscious person. Do NOT induce vomiting. Call a doctor.

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

Self-protection of the first aider Avoid contact with skin, eyes or clothing. Wear personal protective clothing (see section 8).

4.2. Most important symptoms and effects, both acute and delayed

Symptoms May cause redness and tearing of the eyes. Burning sensation.

4.3. Indication of any immediate medical attention and special treatment needed

Note to doctors No information available.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable Extinguishing Media Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable extinguishing media No information available.

5.2. Special hazards arising from the substance or mixture

Specific hazards arising from the chemical No information available.

Hazardous combustion products Hydrogen chloride.

5.3. Advice for firefighters

Special protective equipment and precautions for fire-fighters Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Avoid contact with skin, eyes or clothing. Use personal protective equipment as required.

Other information Refer to protective measures listed in Sections 7 and 8.

For emergency responders Use personal protection recommended in Section 8.

6.2. Environmental precautions

Environmental precautions See Section 12 for additional Ecological Information.

6.3. Methods and material for containment and cleaning up

Methods for containment Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Take up mechanically, placing in appropriate containers for disposal.

Prevention of secondary hazards Clean contaminated objects and areas thoroughly observing environmental regulations.

6.4. Reference to other sections

Reference to other sections See section 8 for more information. See section 13 for more information.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

Advice on safe handling Handle in accordance with good industrial hygiene and safety practice. Avoid contact with skin, eyes or clothing. Do not eat, drink or smoke when using this product.

General hygiene considerations Avoid contact with skin, eyes or clothing. Wear suitable gloves and eye/face protection. Do not eat, drink or smoke when using this product.

7.2. Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

7.3. Specific end use(s)

Risk Management Methods (RMM) The information required is contained in this Safety Data Sheet.

Other information Observe technical data sheet.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Exposure Limits

Derived No Effect Level (DNEL) No information available

Predicted No Effect Concentration (PNEC) No information available.

8.2. Exposure controls

Engineering controls Ensure adequate ventilation, especially in confined areas.

Personal protective equipment

Eye/face protection Tight sealing safety goggles.

Skin and body protection Suitable protective clothing.

Environmental exposure controls No information available.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state Solid

Colour White

Odour No information available.

Odour threshold No information available

Property	Values	Remarks • Method
Melting point / freezing point	No data available	None known
Initial boiling point and boiling range	No data available	None known
Flammability	No data available	None known
Flammability Limit in Air		None known
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Flash point	No data available	None known

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

Autoignition temperature	No data available	None known
Decomposition temperature		None known
pH	No data available	None known.
pH (as aqueous solution)	8 - 9	solution (1 %)
Kinematic viscosity	No data available	None known
Dynamic viscosity	No data available	
Water solubility	No data available.	None known
Solubility(ies)	No data available	None known
Partition coefficient	No data available	None known
Vapour pressure	No data available	None known
Relative density	No data available	None known
Bulk Density	2.148	
Liquid Density	No data available	
Relative vapour density	No data available	None known
Particle characteristics		
Particle Size	No information available	
Particle Size Distribution	No information available	

9.2. Other information

Solid content (%)	No information available
VOC content	No data available

9.2.1. Information with regards to physical hazard classes
Not applicable

9.2.2. Other safety characteristics
No information available

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	No information available.
------------	---------------------------

10.2. Chemical stability

Stability	Stable under normal conditions.
-----------	---------------------------------

Explosion data

Sensitivity to mechanical impact	None.
Sensitivity to static discharge	None.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	None under normal processing.
------------------------------------	-------------------------------

10.4. Conditions to avoid

Conditions to avoid	None known based on information supplied.
---------------------	---

10.5. Incompatible materials

Incompatible materials	None known based on information supplied.
------------------------	---

10.6. Hazardous decomposition products

Hazardous decomposition products	None under normal use conditions. Stable under recommended storage conditions.
----------------------------------	--

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Information on likely routes of exposure

Product Information

Inhalation	Specific test data for the substance or mixture is not available. May cause irritation of respiratory tract.
Eye contact	Specific test data for the substance or mixture is not available. Causes serious eye irritation. (based on components). May cause redness, itching, and pain.
Skin contact	Specific test data for the substance or mixture is not available. May cause irritation. Prolonged contact may cause redness and irritation.
Ingestion	Specific test data for the substance or mixture is not available. Ingestion may cause gastrointestinal irritation, nausea, vomiting and diarrhoea.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms May cause redness and tearing of the eyes.

Acute toxicity

Numerical measures of toxicity

Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Calcium chloride	=2800 - 3800 mg/kg (Rattus)	> 5000 mg/kg (Oryctolagus cuniculus)	-

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Skin corrosion/irritation	May cause skin irritation.
Serious eye damage/eye irritation	Classification based on data available for ingredients. Causes serious eye irritation.
Respiratory or skin sensitisation	Based on available data, the classification criteria are not met.
Germ cell mutagenicity	Based on available data, the classification criteria are not met.
Carcinogenicity	Based on available data, the classification criteria are not met.
Reproductive toxicity	Based on available data, the classification criteria are not met.
STOT - single exposure	Based on available data, the classification criteria are not met.

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

STOT - repeated exposure Based on available data, the classification criteria are not met.

Aspiration hazard Based on available data, the classification criteria are not met.

11.2. Information on other hazards

11.2.1. Endocrine disrupting properties

Endocrine disrupting properties No information available.

11.2.2. Other information

Other adverse effects No information available.

SECTION 12: Ecological information

12.1. Toxicity

Ecotoxicity

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea	M-Factor	M-Factor (long-term)
Calcium chloride 10043-52-4	-	LC50: =10650mg/L (96h, Lepomis macrochirus)	-	LC50: 2280000 - 3948000?g/L (48h, Daphnia magna)		

12.2. Persistence and degradability

Persistence and degradability No information available.

12.3. Bioaccumulative potential

Bioaccumulation There is no data for this product.

12.4. Mobility in soil

Mobility in soil No information available.

12.5. Results of PBT and vPvB assessment

PBT and vPvB assessment

Chemical name	PBT and vPvB assessment
Calcium chloride	The substance is not PBT / vPvB PBT assessment does not apply

12.6. Endocrine disrupting properties

Endocrine disrupting properties No information available.

12.7. Other adverse effects

No information available.

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste from residues/unused products	Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.
Contaminated packaging	Do not reuse empty containers.
Other information	Waste codes should be assigned by the user based on the application for which the product was used.

SECTION 14: Transport information

Land transport (ADR/RID)

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

IMDG

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Marine pollutant	NP
14.6 Special precautions for user	
Special Provisions	None
14.7 Maritime transport in bulk according to IMO instruments	
Transport in bulk according to Annex II of MARPOL and the IBC Code	Not applicable

Air transport (ICAO-TI / IATA-DGR)

14.1 UN number or ID number	Not regulated
14.2 UN proper shipping name	Not regulated
14.3 Transport hazard class(es)	Not regulated
14.4 Packing group	Not regulated
14.5 Environmental hazards	Not applicable
14.6 Special precautions for user	
Special Provisions	None

Section 15: REGULATORY INFORMATION

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

European Union

Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

SVHC: Substances of Very High Concern for Authorisation:

This product does not contain candidate substances of very high concern at a concentration $\geq 0.1\%$ (Regulation (EC) No. 1907/2006 (REACH), Article 59)

EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

Substance subject to authorisation per REACH Annex XIV

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

Persistent Organic Pollutants

Not applicable

National regulations

15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No Chemical Safety Assessment has been carried out for this mixture

SECTION 16: Other information

Key or legend to abbreviations and acronyms used in the safety data sheet

Full text of H-Statements referred to under section 3

H319 - Causes serious eye irritation

Legend

TWA	TWA (time-weighted average)
STEL	STEL (Short Term Exposure Limit)
Ceiling	Ceiling Limit Value
*	Skin designation
SVHC	Substance(s) of Very High Concern
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
vPvB	Very Persistent and very Bioaccumulative (vPvB) Chemicals
STOT RE	Specific target organ toxicity - Repeated exposure
STOT SE	Specific target organ toxicity - Single exposure
EWC	European Waste Catalogue
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
IMDG	International Maritime Dangerous Goods (IMDG)
IATA	International Air Transport Association (IATA)
RID	Regulations concerning the International Transport of Dangerous Goods by Rail

Key literature references and sources for data

No information available

Prepared By Product Safety & Regulatory Affairs
Revision date 20-Apr-2023

Indication of changes

Revision note SDS sections updated: 3, 9.
Training Advice No information available
Further information No information available

This material safety data sheet complies with requirements of UK REACH Regulations (SI 2019/758 as amended)

SAFETY DATA SHEET

BOSTIK BREATHE HUMIDITY ABSORBER REFILL
Supersedes Date: 20-Apr-2023

Revision date 20-Apr-2023
Revision Number 1.04

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

End of Safety Data Sheet