



SAFETY DATA SHEET T-CUT ORIGINAL RESTORER

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name T-CUT ORIGINAL RESTORER
Product number TCO050, TCO080, TCO350, TCO850

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Car maintenance product.

1.3. Details of the supplier of the safety data sheet

Supplier TETROSYL EUROPE
79 rue du chemin vert
59.273 Fretin
TEL: 03 20 28 06 30
qualite@tetrosyl-france.com

Manufacturer TETROSYL LIMITED
Bury
Lancashire
England
BL9 7NY
0161 764 5981
0161 797 5899
info@tetrosyl.com

1.4. Emergency telephone number

Emergency telephone +44 (0)161 764 5981 (24 hrs)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (SI 2019 No. 720)

Physical hazards Not Classified
Health hazards Skin Sens. 1 - H317
Environmental hazards Aquatic Chronic 3 - H412

2.2. Label elements

Hazard pictograms



Signal word Warning

Hazard statements H317 May cause an allergic skin reaction.
H412 Harmful to aquatic life with long lasting effects.

T-CUT ORIGINAL RESTORER

Precautionary statements	P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P261 Avoid breathing vapour/ spray. P273 Avoid release to the environment. P280 Wear protective gloves/ protective clothing/ eye protection/ face protection. P302+P352 IF ON SKIN: Wash with plenty of water. P333+P313 If skin irritation or rash occurs: Get medical advice/ attention. P362+P364 Take off contaminated clothing and wash it before reuse. P501 Dispose of contents/ container in accordance with national regulations.
Contains	2-METHYLISOTHIAZOL-3(2H)-ONE
Supplementary precautionary statements	P272 Contaminated work clothing should not be allowed out of the workplace. P321 Specific treatment (see medical advice on this label).

2.3. Other hazards

This substance is not classified as PBT or vPvB according to current UK criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

DISTILLATES (PETROLEUM), HYDROTREATED LIGHT; KEROSENE - UNSPECIFIED CAS number: — EC number: 926-141-6 Repeated exposure may cause skin dryness or cracking.	10-<30%
Classification Asp. Tox. 1 - H304	
Technical White Mineral Oil CAS number: 8042-47-5 EC number: 232-455-8	5-<10%
Classification Asp. Tox. 1 - H304	
HYDROCARBONS, C10, AROMATICS, <1% NAPHTHALENE CAS number: — EC number: 918-811-1	5-<10%
Classification STOT SE 3 - H336 Asp. Tox. 1 - H304 Aquatic Chronic 2 - H411	
GLYCEROL CAS number: 56-81-5 EC number: 200-289-5	1-<2%
Classification Not Classified	

T-CUT ORIGINAL RESTORER

DIETHANOLAMINE		<0.1
CAS number: 111-42-2	EC number: 203-868-0	
Classification Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT RE 2 - H373		

2-METHYLISOTHIAZOL-3(2H)-ONE		0.001 - <0.005%
CAS number: 2682-20-4	EC number: 220-239-6	
M factor (Acute) = 10	M factor (Chronic) = 1	
Corrosive to the respiratory tract. May cause an allergic skin reaction.This substance has specific concentration limits.≥0.0015		
Classification Acute Tox. 3 - H301 Acute Tox. 3 - H311 Acute Tox. 2 - H330 Skin Corr. 1B - H314 Eye Dam. 1 - H318 Skin Sens. 1A - H317 Aquatic Acute 1 - H400 Aquatic Chronic 1 - H410		

The full text for all hazard statements is displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

General information	Get medical attention if any discomfort continues. Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Inhalation	If spray/mist has been inhaled, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
Ingestion	Rinse mouth thoroughly with water. Give plenty of water to drink. Get medical attention if a large quantity has been ingested. Show this Safety Data Sheet to the medical personnel.
Skin contact	Remove contaminated clothing immediately and wash skin with soap and water.
Eye contact	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Do not rub eye.

4.2. Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.
Inhalation	Vapours may cause headache, fatigue, dizziness and nausea.
Ingestion	May cause discomfort if swallowed. May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.
Skin contact	Prolonged or repeated contact with skin may cause irritation, redness and dermatitis.

T-CUT ORIGINAL RESTORER

Eye contact May cause temporary eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations. If in doubt, get medical attention promptly.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media Extinguish with the following media: Foam, carbon dioxide or dry powder. Water. Use fire-extinguishing media suitable for the surrounding fire.

Unsuitable extinguishing media Do not use water jet as an extinguisher, as this will spread the fire.

5.2. Special hazards arising from the substance or mixture

Specific hazards No unusual fire or explosion hazards noted.

Hazardous combustion products Oxides of carbon. Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours.

5.3. Advice for firefighters

Protective actions during firefighting No specific firefighting precautions known.

Special protective equipment for firefighters Leave danger zone immediately.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions In case of spills, beware of slippery floors and surfaces. Avoid inhalation of spray mist and contact with skin and eyes.

6.2. Environmental precautions

Environmental precautions Avoid or minimise the creation of any environmental contamination. Do not discharge into drains or watercourses or onto the ground. Collect and dispose of spillage as indicated in Section 13.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Stop leak if possible without risk. Provide adequate ventilation. Contain spillage with sand, earth or other suitable non-combustible material. Avoid the spillage or runoff entering drains, sewers or watercourses. Absorb spillage with non-combustible, absorbent material. Collect and place in suitable waste disposal containers and seal securely. No smoking, sparks, flames or other sources of ignition near spillage.

6.4. Reference to other sections

Reference to other sections The product contains a substance which is hazardous to aquatic organisms and which may cause long term adverse effects in the aquatic environment. See Section 12 for additional information on ecological hazards. For personal protection, see Section 8. For waste disposal, see section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

T-CUT ORIGINAL RESTORER

Usage precautions

Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Avoid the formation of mists. Provide adequate ventilation. Read and follow manufacturer's recommendations. Do not handle broken packages without protective equipment.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions

Keep containers upright. Store in tightly-closed, original container.

7.3. Specific end use(s)

Specific end use(s)

The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure controls/Personal protection

8.1. Control parameters

Occupational exposure limits

No exposure limits known for ingredient(s).

GLYCEROL

Long-term exposure limit (8-hour TWA): WEL 10 mg/m³ mist

DIETHANOLAMINE

Long-term exposure limit (8-hour TWA): OES 3 ppm 15 mg/m³

Short-term exposure limit (15-minute): OES

WEL = Workplace Exposure Limit.

GLYCEROL (CAS: 56-81-5)

DNEL

Workers - Inhalation; Long term local effects: 56 mg/m³
General population - Inhalation; Long term local effects: 33 mg/m³
General population - Oral; Long term systemic effects: 229 mg/kg

PNEC

Fresh water; 0.885 mg/l
marine water; 0.0885 mg/l
Intermittent release; 8.85 mg/l
Sediment (Freshwater); 3.3 mg/kg
Sediment (Marinewater); 0.33 mg/kg
Soil; 0.141 mg/kg
STP; 1000 mg/l

TRIETHANOLAMINE 99% (CAS: 102-71-6)

DNEL

Workers - Inhalation; Long term systemic effects: 5 mg/m³
Workers - Inhalation; Long term local effects: 5 mg/m³
Workers - Dermal; Long term systemic effects: 6.3 mg/kg/day
General population - Inhalation; Long term systemic effects: 1.25 mg/m³
General population - Inhalation; Long term local effects: 1.25 mg/m³
General population - Dermal; Long term systemic effects: 3.1 mg/kg/day
General population - Oral; Long term systemic effects: 13 mg/kg/day

T-CUT ORIGINAL RESTORER

PNEC

Fresh water; 0.32 mg/l
marine water; 0.032 mg/l
Sediment (Freshwater); 1.7 mg/kg
Sediment (Marinewater); 0.17 mg/kg
Soil; 0.151 mg/kg
STP; 10 mg/l
Intermittent release; 5.12 mg/l

DIETHANOLAMINE (CAS: 111-42-2)

DNEL

Workers - Dermal; Long term : 0.13 mg/kg/day
Workers - Inhalation; Long term : 4 mg/m³
Workers - Inhalation; Short term : 33 mg/m³
General population - Dermal; Long term : 0.07 mg/kg/day
General population - Inhalation; Long term : 0.25 mg/m³
General population - Oral; Long term : 0.06 mg/kg/day

PNEC

Fresh water; 0.0022 mg/l
marine water; 0.00022 mg/l
Sediment (Freshwater); 0.019 mg/kg
Sediment (Marinewater); 0.0019 mg/kg

8.2. Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation.

Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. It is recommended that gloves are made of the following material: Nitrile rubber. It should be noted that liquid may penetrate the gloves. Frequent changes are recommended.

Other skin and body protection

Wear appropriate clothing to prevent repeated or prolonged skin contact. Provide eyewash station.

Hygiene measures

Wash contaminated clothing before reuse. Wash hands after contact. Wash at the end of each work shift and before eating, smoking and using the toilet. When using do not eat, drink or smoke.

Respiratory protection

No specific recommendations. Respiratory protection may be required if excessive airborne contamination occurs.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Appearance	Viscous liquid.
Colour	Beige.
Odour	Characteristic.

T-CUT ORIGINAL RESTORER

Odour threshold	Not determined.
pH	pH (concentrated solution): 8.60
Melting point	Not determined.
Initial boiling point and range	100°C @ 1013 hPa
Flash point	67°C
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Not determined.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	1.06g/cm ³ @ 20°C
Solubility(ies)	Soluble in water.
Partition coefficient	Not determined.
Auto-ignition temperature	Not determined.
Decomposition Temperature	Not determined.
Viscosity	37,000 cP @ 20°C
Oxidising properties	Not available.

9.2. Other information

Other information	None.
-------------------	-------

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity	There are no known reactivity hazards associated with this product.
------------	---

10.2. Chemical stability

Stability	Stable at normal ambient temperatures and when used as recommended.
-----------	---

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions	Not applicable.
------------------------------------	-----------------

10.4. Conditions to avoid

Conditions to avoid	There are no known conditions that are likely to result in a hazardous situation.
---------------------	---

10.5. Incompatible materials

Materials to avoid	Alkali metals.
--------------------	----------------

10.6. Hazardous decomposition products

Hazardous decomposition products	Does not decompose when used and stored as recommended.
----------------------------------	---

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Toxicological effects	No information available.
-----------------------	---------------------------

T-CUT ORIGINAL RESTORER

Inhalation	No specific health hazards known.
Ingestion	May cause discomfort if swallowed.
Skin contact	Prolonged and frequent contact may cause redness and irritation. May cause an allergic skin reaction.
Eye contact	May cause temporary eye irritation.

SECTION 12: Ecological information

Ecotoxicity	Dangerous for the environment if discharged into watercourses. The product contains a substance which is harmful to aquatic organisms and which may cause long-term adverse effects in the aquatic environment.
--------------------	---

12.1. Toxicity

Acute aquatic toxicity

Acute toxicity - fish	Not available.
------------------------------	----------------

Acute toxicity - aquatic invertebrates	Not available.
---	----------------

12.2. Persistence and degradability

Persistence and degradability	There are no data on the degradability of this product.
--------------------------------------	---

12.3. Bioaccumulative potential

Bioaccumulative potential	No data available on bioaccumulation.
----------------------------------	---------------------------------------

Partition coefficient	Not determined.
------------------------------	-----------------

12.4. Mobility in soil

Mobility	The product is soluble in water.
-----------------	----------------------------------

Adsorption/desorption coefficient	Not available.
--	----------------

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment	This substance is not classified as PBT or vPvB according to current UK criteria.
---	---

12.6. Other adverse effects

Other adverse effects	Not available.
------------------------------	----------------

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information	Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.
----------------------------	---

Disposal methods	Confirm disposal procedures with environmental engineer and local regulations.
-------------------------	--

SECTION 14: Transport information

General	The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).
----------------	--

14.1. UN number

Not applicable.

T-CUT ORIGINAL RESTORER

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

No transport warning sign required.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

Annex II of MARPOL 73/78
and the IBC Code

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations EH40/2005 Workplace exposure limits

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

Revision comments	NOTE: Lines within the margin indicate significant changes from the previous revision.
Issued by	Regulatory Department
Revision date	11/11/2022
Revision	1
SDS number	34738
SDS status	Approved.

T-CUT ORIGINAL RESTORER

Hazard statements in full

H301 Toxic if swallowed.
H302 Harmful if swallowed.
H304 May be fatal if swallowed and enters airways.
H311 Toxic in contact with skin.
H314 Causes severe skin burns and eye damage.
H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H318 Causes serious eye damage.
H330 Fatal if inhaled.
H336 May cause drowsiness or dizziness.
H373 May cause damage to organs through prolonged or repeated exposure.
H400 Very toxic to aquatic life.
H410 Very toxic to aquatic life with long lasting effects.
H411 Toxic to aquatic life with long lasting effects.
H412 Harmful to aquatic life with long lasting effects.