

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006
Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Resiblock Trade

1.2 Relevant identified uses of the substance or mixture and uses advised against

At present there is no complete information available on identified uses. When the data becomes available, it will be integrated into the safety data sheet.

1.3 Details of the supplier of the safety data sheet

Company : Sika Limited
Watchmead
Welwyn Garden City
Hertfordshire AL7 1BQ
United Kingdom

Telephone : +44 (0)1707 394444

1.4 Emergency telephone number

Emergency telephone number : +44 (0)1707 363899 (available during office hours)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Not a hazardous substance or mixture.

Classification (67/548/EEC, 1999/45/EC)

Not a hazardous substance or mixture.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Precautionary statements	: P102	Keep out of reach of children.
	Prevention:	
	P280	Wear protective gloves/ protective clothing/ eye protection/ face protection.
	Response:	
	P302 + P352	IF ON SKIN: Wash with plenty of water.
	Disposal:	
	P501	Dispose of contents/container in accordance with local regulation.

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006
Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

Not a hazardous substance or mixture.

2.3 Other hazards

This mixture contains no substance considered to be persistent, bioaccumulating nor toxic (PBT).
This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Remarks : No hazardous ingredients

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : No hazards which require special first aid measures.

If inhaled : Move to fresh air.

In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.

In case of eye contact : Flush eyes with water as a precaution.
Remove contact lenses.
Keep eye wide open while rinsing.

If swallowed : Do not induce vomiting without medical advice.
Rinse mouth with water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

Symptoms : See Section 11 for more detailed information on health effects and symptoms.

Risks : No known significant effects or hazards.

4.3 Indication of any immediate medical attention and special treatment needed

Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006
Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

5.2 Special hazards arising from the substance or mixture

Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.

Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

6.2 Environmental precautions

Environmental precautions : No special environmental precautions required.

6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Wipe up with absorbent material (e.g. cloth, fleece).
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : For personal protection see section 8. No special handling advice required. Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Normal measures for preventive fire protection.

Hygiene measures : When using do not eat or drink. When using do not smoke.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place. Store in accordance with local regulations.

Advice on common storage : No special restrictions on storage with other products.

Other data : No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : No data available



SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Personal protective equipment

- Eye protection : Safety glasses
- Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.
- Butyl rubber/nitrile rubber gloves (0,4 mm),
Recommended: Butyl rubber/nitrile rubber gloves.
- Skin and body protection : Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.
- Respiratory protection : No special measures required.

Environmental exposure controls

- General advice : No special environmental precautions required.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

- Appearance : liquid
- Colour : No data available
- Odour : No data available
- Odour Threshold : No data available
- Flash point : > 101 °C

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

Ignition temperature	: not applicable
Lower explosion limit (Vol%)	: No data available
Upper explosion limit (Vol%)	: No data available
Flammability (solid, gas)	: No data available
Oxidizing properties	: No data available
Auto-ignition temperature	: No data available
pH	: 8,5
Melting point/range / Freezing point	: No data available
Boiling point/boiling range	: 100 °C
Vapour pressure	: No data available
Density	: 1,01 g/cm ³ at 20 °C
Water solubility	: Note: soluble
Partition coefficient: n-octanol/water	: No data available
Viscosity, dynamic	: No data available
Viscosity, kinematic	: > 7 mm ² /s at 40 °C
Relative vapour density	: No data available
Evaporation rate	: No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : No hazards to be specially mentioned.

10.4 Conditions to avoid

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006
Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Acute toxicity

No data available

Skin corrosion/irritation

Product

No data available

Serious eye damage/eye irritation

Product

No data available

Respiratory or skin sensitisation

Product

No data available

Germ cell mutagenicity

Product

Mutagenicity : No data available

Carcinogenicity

Product

Carcinogenicity : No data available

Reproductive Toxicity/Fertility

Reproductive toxicity : No data available

No data available

Reproductive Toxicity/Development/Teratogenicity

Teratogenicity : No data available

No data available

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006
Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

STOT - single exposure

No data available

STOT - repeated exposure

No data available

Aspiration toxicity

No data available

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.

SAFETY DATA SHEET
according to Regulation (EC) No. 1907/2006
Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

SECTION 14: Transport information

ADR

Not dangerous goods

IATA

Not dangerous goods

IMDG

Not dangerous goods

14.6 Special precautions for user

No data available

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Labelling according to EC Directives (1999/45/EC)

Further information : The product does not need to be labelled in accordance with EC directives or respective national laws.

Prohibition/Restriction

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed (=> 0.1 %).

REACH - List of substances subject to authorisation (Annex XIV) : not applicable

REACH Information: All substances contained in our Products are
- preregistered or registered by our upstream suppliers, and/or
- preregistered or registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

VOC-CH (VOCV) : no VOC duties

VOC-EU (solvent) : not applicable

SAFETY DATA SHEET

according to Regulation (EC) No. 1907/2006

Resiblock Trade



Revision Date 16.10.2014

Version 1.0

Print Date 16.10.2014

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture:

: The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002
Control of Substances Hazardous to Health Regulations 2002
The Management of Health and Safety at Work Regulations 1999
Health and Safety at Work Act 1974
Environmental Protection Act 1990 & Subsidiary Regulations

15.2 Chemical Safety Assessment

This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.



Changes as compared to previous version !